

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845081

Luminaire Tested: **SQ4P-PP3-050U-125D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845081
REPORT IS A COMBINATION OF REPORTS P700202 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-050U-125D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6298.3 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845081

CATALOG NUMBER: SQ4P-PP3-050U-125D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845081

CATALOG NUMBER: SQ4P-PP3-050U-125D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73																			
1	103	99	95	91	98	94	91	87	85	82	80	76	74	73	69	67	66	62																			
2	94	87	80	75	89	83	77	72	75	70	66	67	64	61	61	58	56	52																			
3	86	76	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	45																			
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	45	41	38																			
5	73	61	52	46	69	58	50	45	53	47	42	48	43	39	44	39	36	33																			
6	67	55	46	40	63	52	45	39	48	41	37	44	38	34	40	35	32	29																			
7	62	49	41	35	59	47	40	34	43	37	32	40	34	30	36	32	28	26																			
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	23																			
9	54	41	33	28	51	40	32	27	36	30	26	34	28	24	31	26	23	21																			
10	50	38	30	26	48	36	30	25	34	28	24	31	26	22	29	24	21	19																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16537	16537	16537
5°	16659	16555	16498
10°	16630	16514	16441
15°	16521	16430	16339
20°	16410	16317	16195
25°	16215	16105	15945
30°	15916	15832	15631
35°	15500	15393	15197
40°	15002	14908	14738
45°	14595	14494	14347
50°	14069	13980	13844
55°	13340	13166	13066
60°	12145	11800	11741
65°	10704	10252	10217
70°	9234	8856	8856
75°	7956	7839	7725
80°	7008	7098	6918
85°	5483	5992	5992



TEST NUMBER: P845081

CATALOG NUMBER: SQ4P-PP3-050U-125D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.5	2.7
10°-20°	483.9	7.7
20°-30°	724.9	11.5
30°-40°	850.2	13.5
40°-50°	852.9	13.5
50°-60°	727.6	11.6
60°-70°	474.5	7.5
70°-80°	238.1	3.8
80°-90°	66.5	1.1
90°-100°	104.9	1.7
100°-110°	364.9	5.8
110°-120°	353.5	5.6
120°-130°	277.3	4.4
130°-140°	219.5	3.5
140°-150°	169.4	2.7
150°-160°	121.4	1.9
160°-170°	74.3	1.2
170°-180°	25.1	0.4
0°-30°	1378.3	21.9
0°-40°	2228.6	35.4
0°-60°	3809.1	60.5
0°-90°	4588.2	72.8
90°-120°	823.3	13.1
90°-150°	1489.4	23.6
90°-180°	1710.0	27.2
0°-180°	6298.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1792	1792	1792	1792	1792	
5°	1799	1782	1788	1781	1781	171
15°	1730	1713	1720	1714	1711	488
25°	1593	1574	1582	1568	1566	732
35°	1376	1362	1367	1351	1349	860
45°	1119	1111	1111	1100	1100	861
55°	829	826	818	814	812	737
65°	490	481	470	467	468	489
75°	223	223	220	218	217	242
85°	52	56	57	57	57	61
90°	4	6	6	4	2	4
95°	18	61	177	45	28	19
105°	61	86	384	647	602	64
115°	106	128	285	602	710	105
125°	144	177	266	448	535	129
135°	173	195	264	374	423	134
145°	203	216	262	322	350	127
155°	230	238	258	287	297	106
165°	252	254	260	271	273	71
175°	264	264	262	266	264	25
180°	264	264	264	264	264	



TEST NUMBER: P845081

CATALOG NUMBER: SQ4P-PP3-050U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1792.4	1792.4	1792.4	1792.4	1792.4
2.5°	1803.6	1788.9	1792.4	1789.8	1782.5
5°	1798.7	1781.9	1787.5	1781.4	1781.4
7.5°	1786.5	1768.1	1773.7	1767.6	1767.3
10°	1775.1	1756.7	1762.7	1756.1	1754.9
12.5°	1758.9	1740.5	1747.5	1739.9	1739.7
15°	1729.6	1712.6	1720.1	1713.7	1710.6
17.5°	1696.5	1678.1	1687.1	1678.4	1677.1
20°	1671.4	1653.0	1661.9	1649.5	1649.5
22.5°	1641.3	1623.0	1633.2	1616.7	1616.7
25°	1592.8	1574.4	1582.0	1567.7	1566.3
27.5°	1535.5	1517.3	1525.1	1508.9	1508.7
30°	1494.0	1476.9	1486.1	1468.8	1467.2
32.5°	1448.8	1433.0	1439.6	1422.2	1420.6
35°	1376.2	1362.4	1366.7	1351.0	1349.3
37.5°	1299.8	1285.7	1290.6	1277.0	1276.5
40°	1245.6	1236.4	1237.8	1226.6	1223.7
42.5°	1195.5	1184.9	1186.3	1175.2	1174.7
45°	1118.6	1110.8	1110.8	1099.6	1099.6
47.5°	1036.8	1030.8	1029.3	1020.1	1019.8
50°	980.2	975.6	974.0	966.1	964.5
52.5°	921.1	919.0	913.6	907.0	906.8
55°	829.3	826.4	818.5	813.6	812.3
57.5°	729.9	723.7	714.7	708.0	709.1
60°	658.2	651.9	639.5	636.3	636.3
62.5°	589.1	581.8	569.0	564.7	567.2
65°	490.3	481.1	469.6	466.7	468.0
67.5°	400.3	391.9	379.7	379.7	378.6
70°	342.3	337.7	328.3	328.3	328.3
72.5°	290.9	288.7	281.9	281.7	280.6
75°	223.2	223.2	219.9	218.3	216.7
77.5°	167.1	167.6	166.3	164.7	161.7
80°	131.9	135.1	133.6	131.9	130.2
82.5°	99.4	102.4	102.1	99.4	98.8
85°	51.8	56.4	56.6	56.6	56.6
87.5°	13.8	18.7	20.1	20.1	21.4
90°	3.9	5.9	5.9	3.9	2.0
92.5°	9.8	29.5	27.5	11.8	9.8
95°	17.7	61.0	177.0	45.2	27.5
97.5°	27.5	68.8	353.9	161.3	86.5
100°	37.4	72.8	413.0	387.4	249.7
102.5°	49.1	78.7	411.0	544.7	448.4
105°	61.0	86.5	383.5	646.9	601.7



TEST NUMBER: P845081

CATALOG NUMBER: SQ4P-PP3-050U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	94.4	116.1	299.0	650.9	741.4
115°	106.2	127.8	285.2	601.7	709.9
117.5°	118.0	141.6	277.2	556.5	664.6
120°	127.8	153.3	271.4	513.3	619.4
122.5°	135.7	165.2	267.4	477.8	574.2
125°	143.6	177.0	265.5	448.4	534.9
127.5°	151.4	184.9	265.5	426.8	499.5
130°	159.3	188.8	263.5	405.1	470.0
132.5°	167.1	190.7	263.5	389.4	444.5
135°	173.0	194.6	263.5	373.6	422.8
137.5°	180.9	198.6	263.5	359.8	405.1
140°	186.8	204.5	263.5	346.1	385.5
142.5°	194.6	210.4	263.5	332.3	367.7
145°	202.6	216.4	261.6	322.5	350.0
147.5°	210.4	222.2	259.6	312.7	334.3
150°	216.4	228.1	259.6	302.9	320.6
152.5°	224.2	234.0	257.7	293.0	308.7
155°	230.1	238.0	257.7	287.1	296.9
157.5°	235.9	243.9	257.7	281.2	289.1
160°	241.9	247.8	259.6	277.2	283.2
162.5°	247.8	251.7	259.6	273.3	277.2
165°	251.7	253.6	259.6	271.4	273.3
167.5°	255.6	257.7	259.6	269.4	269.4
170°	257.7	259.6	261.6	267.4	267.4
172.5°	261.6	261.6	261.6	265.5	265.5
175°	263.5	263.5	261.6	265.5	263.5
177.5°	263.5	263.5	261.6	265.5	263.5
180°	263.5	263.5	263.5	263.5	263.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	72.8	96.4	348.1	692.2	700.1
110°	82.6	106.2	320.6	686.3	743.3



(END OF REPORT)