

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845009

Luminaire Tested: **SQ4P-PC3-075U-125D-B35-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845009  
REPORT IS A COMBINATION OF REPORTS P700226 AND P700245  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PC3-075U-125D-B35-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7091.9 lumens  
Efficiency: N/A  
Efficacy: 109.4 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 64.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845009

CATALOG NUMBER: SQ4P-PC3-075U-125D-B35-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845009

CATALOG NUMBER: SQ4P-PC3-075U-125D-B35-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	65																			
1	101	97	93	89	95	91	88	85	81	78	76	71	69	67	62	61	59	55																			
2	92	85	78	73	86	80	74	70	71	66	63	62	59	56	55	52	50	46																			
3	84	74	67	61	79	70	64	58	62	57	53	55	51	48	48	45	43	39																			
4	77	66	58	52	72	62	55	49	55	50	45	49	45	41	43	40	37	34																			
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32	29																			
6	65	53	44	38	61	50	42	37	45	39	34	40	35	31	35	31	28	25																			
7	60	48	39	34	57	45	38	32	41	34	30	36	31	27	32	28	25	22																			
8	56	43	35	30	53	41	34	29	37	31	27	33	28	24	30	25	22	20																			
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20	18																			
10	49	36	29	24	46	35	28	23	31	26	22	28	23	20	25	21	18	16																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	15652	15652	15652
5°	15773	15669	15612
10°	15734	15661	15615
15°	15651	15651	15635
20°	15548	15593	15593
25°	15402	15512	15465
30°	15212	15396	15330
35°	14989	15216	15109
40°	14738	14948	14797
45°	14473	14574	14349
50°	14094	14094	13868
55°	13647	13470	13267
60°	12987	12727	12522
65°	12003	11765	11658
70°	10512	10593	10556
75°	8456	9357	9411
80°	6014	7927	8012
85°	3663	6648	6648



TEST NUMBER: P845009

CATALOG NUMBER: SQ4P-PC3-075U-125D-B35-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	160.6	2.3
10°-20°	460.8	6.5
20°-30°	697.8	9.8
30°-40°	836.6	11.8
40°-50°	853.0	12.0
50°-60°	744.6	10.5
60°-70°	533.1	7.5
70°-80°	274.6	3.9
80°-90°	70.4	1.0
90°-100°	150.9	2.1
100°-110°	525.0	7.4
110°-120°	508.6	7.2
120°-130°	398.9	5.6
130°-140°	315.7	4.5
140°-150°	243.7	3.4
150°-160°	174.7	2.5
160°-170°	106.8	1.5
170°-180°	36.1	0.5
0°-30°	1319.2	18.6
0°-40°	2155.8	30.4
0°-60°	3753.4	52.9
0°-90°	4631.5	65.3
90°-120°	1184.4	16.7
90°-150°	2142.8	30.2
90°-180°	2460.0	34.7
0°-180°	7091.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1696	1696	1696	1696	1696	
5°	1703	1686	1692	1687	1686	162
15°	1639	1625	1639	1639	1637	462
25°	1513	1502	1524	1519	1519	696
35°	1331	1327	1351	1342	1342	832
45°	1109	1106	1117	1103	1100	854
55°	848	838	837	825	825	756
65°	550	538	539	534	534	544
75°	237	248	262	264	264	256
85°	35	53	63	64	63	47
90°	6	8	8	6	3	5
95°	25	88	255	65	40	27
105°	88	124	552	931	866	92
115°	153	184	410	866	1021	151
125°	207	255	382	645	770	185
135°	249	280	379	538	608	193
145°	291	311	376	464	504	182
155°	331	342	371	413	427	153
165°	362	365	373	390	393	102
175°	379	379	376	382	379	36
180°	379	379	379	379	379	



TEST NUMBER: P845009

CATALOG NUMBER: SQ4P-PC3-075U-125D-B35-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1696.5	1696.5	1696.5	1696.5	1696.5
2.5°	1706.8	1691.9	1696.5	1692.7	1686.6
5°	1703.1	1686.0	1691.9	1687.0	1685.7
7.5°	1690.6	1673.8	1681.7	1678.4	1676.8
10°	1679.5	1662.4	1671.7	1668.4	1666.8
12.5°	1664.3	1648.6	1659.0	1655.9	1655.4
15°	1638.6	1624.8	1638.6	1638.6	1636.9
17.5°	1606.1	1593.7	1608.3	1609.3	1608.3
20°	1583.6	1569.8	1588.2	1586.6	1588.2
22.5°	1556.0	1544.7	1564.4	1560.3	1562.0
25°	1513.0	1502.1	1523.8	1519.2	1519.2
27.5°	1462.1	1454.1	1478.0	1472.8	1472.8
30°	1427.9	1420.4	1445.2	1439.0	1439.0
32.5°	1390.2	1385.2	1408.9	1401.4	1401.4
35°	1330.8	1327.4	1351.0	1341.5	1341.5
37.5°	1269.0	1266.3	1287.7	1276.2	1272.5
40°	1223.7	1222.4	1241.1	1228.6	1228.6
42.5°	1178.5	1176.9	1193.5	1178.3	1178.3
45°	1109.2	1106.0	1117.0	1102.6	1099.7
47.5°	1033.4	1030.4	1037.2	1021.7	1020.1
50°	981.9	978.7	981.9	967.6	966.2
52.5°	929.1	923.5	924.0	909.9	909.6
55°	848.4	837.6	837.4	824.8	824.8
57.5°	762.8	748.8	750.1	739.3	737.6
60°	703.8	688.3	689.7	680.2	678.6
62.5°	645.9	628.2	631.8	621.2	620.9
65°	549.8	537.5	538.9	534.0	534.0
67.5°	457.4	446.0	454.4	450.6	450.3
70°	389.7	381.8	392.7	392.7	391.3
72.5°	326.8	326.5	339.9	339.9	340.9
75°	237.2	248.1	262.5	264.0	264.0
77.5°	158.4	177.4	193.4	193.9	193.7
80°	113.2	134.6	149.2	152.5	150.8
82.5°	76.6	99.4	111.6	114.6	113.2
85°	34.6	53.0	62.8	64.5	62.8
87.5°	10.0	21.1	25.1	25.1	22.7
90°	5.7	8.5	8.5	5.7	2.8
92.5°	14.2	42.5	39.6	16.9	14.2
95°	25.4	87.7	254.6	65.1	39.6
97.5°	39.6	99.0	509.2	232.0	124.5
100°	53.7	104.7	594.1	557.4	359.3
102.5°	70.8	113.1	591.3	783.7	645.1
105°	87.7	124.5	551.7	930.8	865.7



TEST NUMBER: P845009

CATALOG NUMBER: SQ4P-PC3-075U-125D-B35-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	135.8	166.9	430.1	936.5	1066.6
115°	152.8	183.9	410.2	865.7	1021.3
117.5°	169.8	203.7	399.0	800.7	956.3
120°	183.9	220.7	390.4	738.4	891.2
122.5°	195.2	237.7	384.8	687.5	826.1
125°	206.6	254.6	381.9	645.1	769.5
127.5°	217.8	266.0	381.9	614.0	718.7
130°	229.2	271.6	379.1	582.8	676.2
132.5°	240.4	274.4	379.1	560.2	639.4
135°	248.9	280.1	379.1	537.5	608.3
137.5°	260.3	285.7	379.1	517.8	582.8
140°	268.8	294.3	379.1	497.9	554.6
142.5°	280.1	302.8	379.1	478.1	529.0
145°	291.4	311.2	376.3	464.0	503.6
147.5°	302.8	319.7	373.4	449.8	481.0
150°	311.2	328.2	373.4	435.7	461.2
152.5°	322.5	336.6	370.6	421.6	444.2
155°	331.0	342.3	370.6	413.1	427.2
157.5°	339.5	350.8	370.6	404.5	415.9
160°	348.0	356.5	373.4	399.0	407.4
162.5°	356.5	362.2	373.4	393.3	399.0
165°	362.2	365.0	373.4	390.4	393.3
167.5°	367.8	370.6	373.4	387.6	387.6
170°	370.6	373.4	376.3	384.8	384.8
172.5°	376.3	376.3	376.3	381.9	381.9
175°	379.1	379.1	376.3	381.9	379.1
177.5°	379.1	379.1	376.3	381.9	379.1
180°	379.1	379.1	379.1	379.1	379.1



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	104.7	138.7	500.7	995.9	1007.2
110°	118.8	152.8	461.2	987.4	1069.5



(END OF REPORT)