

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845015

Luminaire Tested: **SQ4P-PC3-0U-075D-B35-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845015  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P562810)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PC3-0U-075D-B35-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 750 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2817.3 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 25.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845015

CATALOG NUMBER: SQ4P-PC3-0U-075D-B35-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845015

CATALOG NUMBER: SQ4P-PC3-OU-075D-B35-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85																			
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																			
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60																			
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51																			
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44																			
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39																			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34																			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31																			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28																			
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9523	9523	9523
5°	9597	9534	9499
10°	9573	9528	9501
15°	9523	9523	9513
20°	9460	9487	9487
25°	9371	9438	9409
30°	9256	9368	9327
35°	9119	9258	9193
40°	8967	9094	9003
45°	8805	8867	8729
50°	8575	8575	8437
55°	8303	8194	8072
60°	7901	7743	7619
65°	7302	7156	7093
70°	6396	6444	6423
75°	5144	5689	5729
80°	3661	4824	4877
85°	2234	4054	4054



TEST NUMBER: P845015

CATALOG NUMBER: SQ4P-PC3-OU-075D-B35-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	97.7	3.5
10°-20°	280.4	10.0
20°-30°	424.6	15.1
30°-40°	509.0	18.1
40°-50°	519.0	18.4
50°-60°	453.0	16.1
60°-70°	324.3	11.5
70°-80°	167.1	5.9
80°-90°	42.3	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	802.6	28.5
0°-40°	1311.6	46.6
0°-60°	2283.6	81.1
0°-90°	2817.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2817.3	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1032	1032	1032	1032	1032	
5°	1036	1026	1029	1026	1026	98
15°	997	988	997	997	996	281
25°	920	914	927	924	924	424
35°	810	808	822	816	816	506
45°	675	673	680	671	669	519
55°	516	510	509	502	502	460
65°	334	327	328	325	325	331
75°	144	151	160	161	161	156
85°	21	32	38	39	38	29
90°	0	0	0	0	0	



TEST NUMBER: P845015

CATALOG NUMBER: SQ4P-PC3-OU-075D-B35-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1032.2	1032.2	1032.2	1032.2	1032.2
2.5°	1038.5	1029.4	1032.2	1029.9	1026.1
5°	1036.2	1025.7	1029.4	1026.4	1025.6
7.5°	1028.6	1018.4	1023.2	1021.1	1020.2
10°	1021.8	1011.4	1017.0	1015.1	1014.1
12.5°	1012.6	1003.0	1009.3	1007.5	1007.1
15°	997.0	988.5	997.0	997.0	996.0
17.5°	977.2	969.6	978.5	979.2	978.5
20°	963.5	955.1	966.3	965.4	966.3
22.5°	946.7	939.8	951.8	949.3	950.3
25°	920.5	913.9	927.1	924.3	924.3
27.5°	889.5	884.7	899.2	896.1	896.1
30°	868.8	864.2	879.3	875.5	875.5
32.5°	845.9	842.7	857.2	852.6	852.6
35°	809.6	807.6	822.0	816.2	816.2
37.5°	772.1	770.4	783.4	776.5	774.2
40°	744.5	743.7	755.1	747.5	747.5
42.5°	717.0	716.0	726.1	716.9	716.9
45°	674.8	672.9	679.6	670.9	669.0
47.5°	628.7	626.9	631.0	621.6	620.6
50°	597.4	595.5	597.4	588.7	587.8
52.5°	565.3	561.8	562.2	553.6	553.4
55°	516.2	509.6	509.4	501.8	501.8
57.5°	464.1	455.5	456.4	449.7	448.8
60°	428.2	418.8	419.6	413.8	412.9
62.5°	393.0	382.2	384.4	377.9	377.8
65°	334.5	327.0	327.8	324.9	324.9
67.5°	278.3	271.4	276.4	274.2	274.0
70°	237.1	232.3	238.9	238.9	238.1
72.5°	198.8	198.6	206.8	206.8	207.5
75°	144.3	150.9	159.6	160.7	160.7
77.5°	96.4	107.9	117.6	117.9	117.8
80°	68.9	81.9	90.8	92.8	91.8
82.5°	46.6	60.5	67.9	69.7	68.9
85°	21.1	32.3	38.3	39.2	38.3
87.5°	6.1	12.8	15.4	15.4	13.8
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)