

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845123

Luminaire Tested: **SQ4P-PP3-125U-075D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845123
REPORT IS A COMBINATION OF REPORTS P700116 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-125U-075D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT
UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6922.8 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 59.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845123

CATALOG NUMBER: SQ4P-PP3-125U-075D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845123

CATALOG NUMBER: SQ4P-PP3-125U-075D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	105	105	105	105	95	95	95	95	78	78	78	62	62	62	47	47	47	40																			
1	96	92	88	84	87	84	80	77	69	66	64	55	53	52	42	41	40	34																			
2	87	80	74	69	79	73	68	64	60	57	53	48	46	44	37	36	34	29																			
3	80	70	63	58	72	64	58	53	53	49	45	43	40	37	33	31	29	25																			
4	73	62	55	49	66	57	50	45	47	42	38	38	35	32	30	27	25	21																			
5	67	56	48	42	61	51	44	39	42	37	33	34	30	27	27	24	22	18																			
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	24	21	19	16																			
7	57	45	37	32	52	41	34	29	34	29	25	28	24	21	22	19	17	14																			
8	53	41	33	28	48	37	31	26	31	26	22	26	22	19	20	17	15	13																			
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																			
10	46	34	27	22	42	31	25	21	26	21	18	22	18	15	17	15	13	11																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10061	10061	10061
5°	10134	10072	10037
10°	10117	10046	10001
15°	10051	9996	9940
20°	9983	9927	9852
25°	9865	9797	9701
30°	9683	9632	9509
35°	9429	9365	9246
40°	9127	9069	8967
45°	8879	8816	8728
50°	8559	8504	8421
55°	8115	8011	7949
60°	7388	7180	7141
65°	6512	6237	6217
70°	5616	5387	5387
75°	4837	4770	4698
80°	4261	4314	4213
85°	3335	3642	3642



TEST NUMBER: P845123

CATALOG NUMBER: SQ4P-PP3-125U-075D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	1.5
10°-20°	294.4	4.3
20°-30°	441.0	6.4
30°-40°	517.3	7.5
40°-50°	518.9	7.5
50°-60°	442.7	6.4
60°-70°	288.7	4.2
70°-80°	144.8	2.1
80°-90°	41.6	0.6
90°-100°	253.3	3.7
100°-110°	881.3	12.7
110°-120°	853.7	12.3
120°-130°	669.7	9.7
130°-140°	530.1	7.7
140°-150°	409.1	5.9
150°-160°	293.2	4.2
160°-170°	179.4	2.6
170°-180°	60.7	0.9
0°-30°	838.5	12.1
0°-40°	1355.8	19.6
0°-60°	2317.3	33.5
0°-90°	2792.4	40.3
90°-120°	1988.3	28.7
90°-150°	3597.1	52.0
90°-180°	4130.0	59.7
0°-180°	6922.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1094	1084	1088	1084	1084	104
15°	1052	1042	1046	1043	1041	297
25°	969	958	962	954	953	446
35°	837	829	832	822	821	523
45°	680	676	676	669	669	524
55°	504	503	498	495	494	448
65°	298	293	286	284	285	298
75°	136	136	134	133	132	147
85°	32	34	34	34	34	37
90°	10	14	14	10	5	7
95°	43	147	427	109	66	45
105°	147	209	926	1563	1453	155
115°	256	309	689	1453	1714	253
125°	347	427	641	1083	1292	310
135°	418	470	636	902	1021	324
145°	489	522	632	779	845	306
155°	556	575	622	693	717	256
165°	608	613	627	655	660	171
175°	636	636	632	641	636	60
180°	636	636	636	636	636	



TEST NUMBER: P845123

CATALOG NUMBER: SQ4P-PP3-125U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1090.5	1090.5	1090.5	1090.5	1090.5
2.5°	1097.3	1088.4	1090.5	1088.9	1084.3
5°	1094.2	1084.1	1087.5	1083.7	1083.7
7.5°	1086.8	1075.6	1079.1	1075.3	1075.2
10°	1079.9	1068.7	1072.3	1068.4	1067.5
12.5°	1070.1	1058.8	1063.1	1058.5	1058.3
15°	1052.3	1041.9	1046.5	1042.6	1040.7
17.5°	1032.1	1020.9	1026.4	1021.1	1020.3
20°	1016.8	1005.6	1011.1	1003.4	1003.4
22.5°	998.5	987.3	993.5	983.6	983.6
25°	969.1	957.8	962.4	953.7	952.9
27.5°	934.1	923.1	927.9	918.0	917.8
30°	908.9	898.5	904.1	893.5	892.6
32.5°	881.4	871.8	875.8	865.2	864.3
35°	837.2	828.8	831.5	821.9	820.9
37.5°	790.8	782.2	785.1	776.9	776.6
40°	757.8	752.2	753.0	746.3	744.5
42.5°	727.3	720.9	721.7	714.9	714.6
45°	680.5	675.7	675.7	668.9	668.9
47.5°	630.8	627.2	626.2	620.5	620.4
50°	596.3	593.5	592.5	587.7	586.7
52.5°	560.4	559.1	555.8	551.8	551.6
55°	504.5	502.7	498.0	495.0	494.2
57.5°	444.1	440.3	434.9	430.8	431.4
60°	400.4	396.6	389.1	387.0	387.0
62.5°	358.4	353.9	346.2	343.6	345.0
65°	298.3	292.6	285.7	283.9	284.8
67.5°	243.6	238.4	231.0	231.0	230.4
70°	208.2	205.5	199.7	199.7	199.7
72.5°	176.9	175.7	171.5	171.3	170.7
75°	135.7	135.7	133.8	132.8	131.8
77.5°	101.7	102.0	101.2	100.2	98.3
80°	80.2	82.2	81.2	80.2	79.3
82.5°	60.5	62.2	62.1	60.5	60.2
85°	31.5	34.2	34.4	34.4	34.4
87.5°	8.4	11.4	12.2	12.2	13.0
90°	9.5	14.3	14.3	9.5	4.8
92.5°	23.8	71.2	66.4	28.5	23.8
95°	42.8	147.3	427.4	109.2	66.4
97.5°	66.4	166.3	854.9	389.5	209.0
100°	90.2	175.8	997.4	935.6	603.2
102.5°	118.7	189.9	992.7	1315.6	1082.9
105°	147.3	209.0	926.1	1562.6	1453.4



TEST NUMBER: P845123

CATALOG NUMBER: SQ4P-PP3-125U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	228.0	280.3	721.9	1572.1	1790.6
115°	256.5	308.7	688.7	1453.4	1714.5
117.5°	285.0	342.0	669.6	1344.2	1605.3
120°	308.7	370.5	655.4	1239.6	1496.1
122.5°	327.7	399.0	646.0	1154.1	1386.8
125°	346.7	427.4	641.2	1082.9	1291.9
127.5°	365.7	446.4	641.2	1030.6	1206.4
130°	384.7	455.9	636.5	978.4	1135.1
132.5°	403.8	460.7	636.5	940.4	1073.4
135°	417.9	470.2	636.5	902.4	1021.1
137.5°	436.9	479.7	636.5	869.2	978.4
140°	451.2	494.0	636.5	835.9	930.9
142.5°	470.2	508.2	636.5	802.6	888.1
145°	489.2	522.5	631.7	778.9	845.4
147.5°	508.2	536.6	627.0	755.2	807.4
150°	522.5	550.9	627.0	731.4	774.1
152.5°	541.4	565.2	622.2	707.7	745.7
155°	555.7	574.7	622.2	693.4	717.2
157.5°	569.9	588.9	622.2	679.2	698.2
160°	584.2	598.4	627.0	669.6	683.9
162.5°	598.4	608.0	627.0	660.1	669.6
165°	608.0	612.7	627.0	655.4	660.1
167.5°	617.5	622.2	627.0	650.6	650.6
170°	622.2	627.0	631.7	646.0	646.0
172.5°	631.7	631.7	631.7	641.2	641.2
175°	636.5	636.5	631.7	641.2	636.5
177.5°	636.5	636.5	631.7	641.2	636.5
180°	636.5	636.5	636.5	636.5	636.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	175.8	232.7	840.7	1671.8	1690.9
110°	199.4	256.5	774.1	1657.6	1795.3



(END OF REPORT)