

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845132

Luminaire Tested: **SQ4P-PP3-150U-050D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845132
REPORT IS A COMBINATION OF REPORTS P700143 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-150U-050D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6844.6 lumens
Efficiency: N/A
Efficacy: 114.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 59.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845132

CATALOG NUMBER: SQ4P-PP3-150U-050D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845132

CATALOG NUMBER: SQ4P-PP3-150U-050D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35	27																			
1	93	89	85	82	83	79	76	74	62	60	58	46	45	44	31	31	30	23																			
2	85	78	72	67	75	70	65	60	54	51	48	41	38	37	28	27	25	20																			
3	77	68	61	56	69	61	55	51	48	44	41	36	33	31	25	23	22	17																			
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	20	19	14																			
5	65	54	46	40	58	48	42	37	38	33	30	29	25	23	20	18	16	13																			
6	59	48	40	35	53	43	36	32	34	29	26	26	22	20	18	16	14	11																			
7	55	43	35	30	49	39	32	28	31	26	23	23	20	18	16	14	13	10																			
8	51	39	32	26	45	35	29	24	28	23	20	21	18	16	15	13	11	9																			
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10	8																			
10	44	32	25	21	39	29	23	19	23	19	16	18	15	13	13	11	9	7																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6762	6762	6762
5°	6812	6770	6746
10°	6801	6753	6723
15°	6756	6719	6681
20°	6710	6673	6622
25°	6630	6585	6520
30°	6508	6474	6392
35°	6339	6295	6215
40°	6134	6095	6026
45°	5968	5926	5868
50°	5753	5717	5661
55°	5456	5384	5342
60°	4966	4825	4801
65°	4377	4194	4178
70°	3777	3623	3623
75°	3255	3205	3158
80°	2864	2901	2827
85°	2234	2456	2456



TEST NUMBER: P845132

CATALOG NUMBER: SQ4P-PP3-150U-050D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	1.0
10°-20°	197.9	2.9
20°-30°	296.4	4.3
30°-40°	347.7	5.1
40°-50°	348.8	5.1
50°-60°	297.5	4.3
60°-70°	194.1	2.8
70°-80°	97.4	1.4
80°-90°	28.8	0.4
90°-100°	304.6	4.4
100°-110°	1059.8	15.5
110°-120°	1026.6	15.0
120°-130°	805.3	11.8
130°-140°	637.4	9.3
140°-150°	491.9	7.2
150°-160°	352.6	5.2
160°-170°	215.7	3.2
170°-180°	73.0	1.1
0°-30°	563.6	8.2
0°-40°	911.3	13.3
0°-60°	1557.6	22.8
0°-90°	1877.8	27.4
90°-120°	2391.0	34.9
90°-150°	4325.6	63.2
90°-180°	4967.0	72.6
0°-180°	6844.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	733	733	733	733	733	
5°	736	729	731	728	728	70
15°	707	700	703	701	700	200
25°	651	644	647	641	640	300
35°	563	557	559	552	552	352
45°	457	454	454	450	450	352
55°	339	338	335	333	332	301
65°	200	197	192	191	191	200
75°	91	91	90	89	89	99
85°	21	23	23	23	23	25
90°	11	17	17	11	6	8
95°	51	177	514	131	80	54
105°	177	251	1114	1879	1748	186
115°	308	371	828	1748	2062	305
125°	417	514	771	1302	1554	373
135°	503	565	765	1085	1228	390
145°	588	628	760	937	1017	368
155°	668	691	748	834	862	308
165°	731	737	754	788	794	206
175°	765	765	760	771	765	72
180°	765	765	765	765	765	



TEST NUMBER: P845132

CATALOG NUMBER: SQ4P-PP3-150U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	732.9	732.9	732.9	732.9	732.9
2.5°	737.5	731.6	732.9	731.9	728.8
5°	735.5	728.6	731.0	728.4	728.4
7.5°	730.5	723.0	725.3	722.8	722.7
10°	725.9	718.4	720.8	718.2	717.6
12.5°	719.2	711.7	714.5	711.5	711.4
15°	707.3	700.3	703.4	700.8	699.5
17.5°	693.8	686.3	689.9	686.4	685.8
20°	683.4	675.9	679.6	674.5	674.5
22.5°	671.2	663.7	667.9	661.1	661.1
25°	651.3	643.8	646.9	641.1	640.5
27.5°	627.8	620.4	623.6	617.0	616.9
30°	610.9	604.0	607.7	600.6	600.0
32.5°	592.4	586.0	588.7	581.6	580.9
35°	562.8	557.1	558.9	552.4	551.8
37.5°	531.5	525.8	527.7	522.2	522.0
40°	509.3	505.6	506.1	501.6	500.3
42.5°	488.9	484.6	485.1	480.6	480.4
45°	457.4	454.2	454.2	449.7	449.7
47.5°	424.0	421.6	420.9	417.1	417.0
50°	400.8	399.0	398.3	395.0	394.4
52.5°	376.7	375.8	373.6	370.9	370.8
55°	339.2	337.9	334.7	332.7	332.1
57.5°	298.5	295.9	292.3	289.6	289.9
60°	269.1	266.6	261.5	260.2	260.2
62.5°	240.9	237.9	232.7	230.9	231.9
65°	200.5	196.7	192.1	190.8	191.4
67.5°	163.7	160.3	155.3	155.3	154.8
70°	140.0	138.1	134.3	134.3	134.3
72.5°	119.0	118.0	115.3	115.2	114.8
75°	91.3	91.3	89.9	89.2	88.6
77.5°	68.3	68.6	68.0	67.3	66.2
80°	53.9	55.3	54.6	53.9	53.2
82.5°	40.6	41.9	41.8	40.6	40.4
85°	21.1	23.0	23.2	23.2	23.2
87.5°	5.7	7.6	8.2	8.2	8.7
90°	11.4	17.1	17.1	11.4	5.7
92.5°	28.6	85.6	79.9	34.2	28.6
95°	51.4	177.0	514.0	131.3	79.9
97.5°	79.9	199.9	1028.1	468.3	251.3
100°	108.5	211.3	1199.4	1125.2	725.3
102.5°	142.8	228.5	1193.7	1582.0	1302.2
105°	177.0	251.3	1113.7	1879.0	1747.7



TEST NUMBER: P845132

CATALOG NUMBER: SQ4P-PP3-150U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.1	337.0	868.1	1890.5	2153.1
115°	308.4	371.3	828.2	1747.7	2061.8
117.5°	342.7	411.2	805.3	1616.3	1930.4
120°	371.3	445.4	788.1	1490.6	1799.1
122.5°	394.1	479.8	776.8	1387.9	1667.7
125°	417.0	514.0	771.0	1302.2	1553.5
127.5°	439.8	536.8	771.0	1239.4	1450.7
130°	462.7	548.3	765.3	1176.5	1365.0
132.5°	485.5	554.0	765.3	1130.8	1290.7
135°	502.6	565.4	765.3	1085.1	1227.9
137.5°	525.5	576.9	765.3	1045.2	1176.5
140°	542.6	594.0	765.3	1005.2	1119.4
142.5°	565.4	611.1	765.3	965.3	1068.0
145°	588.3	628.2	759.6	936.7	1016.6
147.5°	611.1	645.4	753.9	908.1	970.9
150°	628.2	662.5	753.9	879.5	930.9
152.5°	651.1	679.6	748.2	851.0	896.7
155°	668.3	691.1	748.2	833.8	862.4
157.5°	685.4	708.2	748.2	816.7	839.6
160°	702.5	719.6	753.9	805.3	822.4
162.5°	719.6	731.1	753.9	793.9	805.3
165°	731.1	736.8	753.9	788.1	793.9
167.5°	742.4	748.2	753.9	782.5	782.5
170°	748.2	753.9	759.6	776.8	776.8
172.5°	759.6	759.6	759.6	771.0	771.0
175°	765.3	765.3	759.6	771.0	765.3
177.5°	765.3	765.3	759.6	771.0	765.3
180°	765.3	765.3	765.3	765.3	765.3



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	211.3	279.9	1011.0	2010.4	2033.3
110°	239.8	308.4	930.9	1993.2	2158.9



(END OF REPORT)