

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845018

Luminaire Tested: **SQ4P-PC3-0U-100D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845018
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P562810)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-0U-100D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3701.9 lumens
Efficiency: N/A
Efficacy: 106.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 34.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845018

CATALOG NUMBER: SQ4P-PC3-0U-100D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845018

CATALOG NUMBER: SQ4P-PC3-OU-100D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85																			
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																			
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60																			
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51																			
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44																			
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39																			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34																			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31																			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28																			
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12513	12513	12513
5°	12609	12528	12482
10°	12579	12520	12484
15°	12513	12513	12499
20°	12431	12466	12466
25°	12313	12401	12364
30°	12162	12309	12256
35°	11982	12164	12080
40°	11783	11950	11830
45°	11571	11652	11470
50°	11267	11267	11088
55°	10909	10768	10608
60°	10383	10175	10010
65°	9595	9407	9320
70°	8406	8468	8438
75°	6759	7479	7525
80°	4808	6339	6408
85°	2932	5314	5314



TEST NUMBER: P845018

CATALOG NUMBER: SQ4P-PC3-OU-100D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	128.4	3.5
10°-20°	368.4	10.0
20°-30°	557.9	15.1
30°-40°	668.8	18.1
40°-50°	682.0	18.4
50°-60°	595.3	16.1
60°-70°	426.2	11.5
70°-80°	219.5	5.9
80°-90°	55.5	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1054.6	28.5
0°-40°	1723.4	46.6
0°-60°	3000.7	81.1
0°-90°	3701.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3701.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1356	1356	1356	1356	1356	
5°	1362	1348	1353	1349	1348	129
15°	1310	1299	1310	1310	1309	369
25°	1210	1201	1218	1214	1214	557
35°	1064	1061	1080	1072	1072	665
45°	887	884	893	882	879	683
55°	678	670	669	660	660	605
65°	440	430	431	427	427	435
75°	190	198	210	211	211	205
85°	28	42	50	52	50	39
90°	0	0	0	0	0	



TEST NUMBER: P845018

CATALOG NUMBER: SQ4P-PC3-OU-100D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1356.3	1356.3	1356.3	1356.3	1356.3
2.5°	1364.5	1352.7	1356.3	1353.3	1348.3
5°	1361.5	1347.9	1352.7	1348.8	1347.7
7.5°	1351.6	1338.1	1344.5	1341.8	1340.5
10°	1342.7	1329.0	1336.4	1333.8	1332.5
12.5°	1330.6	1318.0	1326.3	1323.8	1323.4
15°	1310.0	1298.9	1310.0	1310.0	1308.6
17.5°	1284.0	1274.1	1285.7	1286.6	1285.7
20°	1266.1	1255.0	1269.7	1268.4	1269.7
22.5°	1244.0	1234.9	1250.7	1247.4	1248.7
25°	1209.5	1200.9	1218.2	1214.5	1214.5
27.5°	1168.8	1162.5	1181.6	1177.5	1177.5
30°	1141.6	1135.5	1155.4	1150.4	1150.4
32.5°	1111.5	1107.3	1126.4	1120.4	1120.4
35°	1063.8	1061.3	1080.0	1072.5	1072.5
37.5°	1014.5	1012.3	1029.5	1020.4	1017.3
40°	978.3	977.2	992.2	982.2	982.2
42.5°	942.2	940.9	954.1	942.0	942.0
45°	886.8	884.1	893.0	881.6	879.1
47.5°	826.1	823.8	829.1	816.8	815.5
50°	785.0	782.4	785.0	773.6	772.5
52.5°	742.7	738.2	738.6	727.4	727.2
55°	678.2	669.6	669.4	659.5	659.5
57.5°	609.8	598.6	599.7	591.1	589.7
60°	562.7	550.3	551.4	543.8	542.5
62.5°	516.3	502.3	505.0	496.6	496.4
65°	439.5	429.7	430.9	426.9	426.9
67.5°	365.7	356.6	363.2	360.2	360.0
70°	311.6	305.2	313.9	313.9	312.8
72.5°	261.3	261.1	271.6	271.6	272.5
75°	189.6	198.3	209.8	211.1	211.1
77.5°	126.6	141.8	154.6	155.0	154.8
80°	90.5	107.6	119.3	121.9	120.6
82.5°	61.3	79.5	89.1	91.6	90.5
85°	27.7	42.5	50.2	51.6	50.2
87.5°	8.0	16.9	20.2	20.2	18.2
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)