

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845135

Luminaire Tested: **SQ4P-PP3-150U-075D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845135
REPORT IS A COMBINATION OF REPORTS P700144 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-150U-075D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7759.5 lumens
Efficiency: N/A
Efficacy: 113.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 68.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845135

CATALOG NUMBER: SQ4P-PP3-150U-075D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845135

CATALOG NUMBER: SQ4P-PP3-150U-075D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36				36
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37	31				31
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26				26
3	79	70	63	57	71	63	57	52	51	47	44	40	37	35	30	28	27	22				22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19				19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16				16
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18	14				14
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	18	16	13				13
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	12				12
9	48	37	29	24	44	33	27	23	28	23	19	22	19	16	17	14	13	10				10
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	16	13	11	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10061	10061	10061
5°	10134	10072	10037
10°	10117	10046	10001
15°	10051	9996	9940
20°	9983	9927	9852
25°	9865	9797	9701
30°	9683	9632	9509
35°	9429	9365	9246
40°	9127	9069	8967
45°	8879	8816	8728
50°	8559	8504	8421
55°	8115	8011	7949
60°	7388	7180	7141
65°	6512	6237	6217
70°	5616	5387	5387
75°	4837	4770	4698
80°	4261	4314	4213
85°	3335	3642	3642



TEST NUMBER: P845135

CATALOG NUMBER: SQ4P-PP3-150U-075D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	1.3
10°-20°	294.4	3.8
20°-30°	441.0	5.7
30°-40°	517.3	6.7
40°-50°	518.9	6.7
50°-60°	442.7	5.7
60°-70°	288.7	3.7
70°-80°	144.8	1.9
80°-90°	41.9	0.5
90°-100°	304.6	3.9
100°-110°	1059.8	13.7
110°-120°	1026.6	13.2
120°-130°	805.3	10.4
130°-140°	637.4	8.2
140°-150°	491.9	6.3
150°-160°	352.6	4.5
160°-170°	215.7	2.8
170°-180°	73.0	0.9
0°-30°	838.5	10.8
0°-40°	1355.8	17.5
0°-60°	2317.3	29.9
0°-90°	2792.7	36.0
90°-120°	2391.0	30.8
90°-150°	4325.6	55.7
90°-180°	4967.0	64.0
0°-180°	7759.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1094	1084	1088	1084	1084	104
15°	1052	1042	1046	1043	1041	297
25°	969	958	962	954	953	446
35°	837	829	832	822	821	523
45°	680	676	676	669	669	524
55°	504	503	498	495	494	448
65°	298	293	286	284	285	298
75°	136	136	134	133	132	147
85°	32	34	34	34	34	37
90°	11	17	17	11	6	8
95°	51	177	514	131	80	54
105°	177	251	1114	1879	1748	186
115°	308	371	828	1748	2062	305
125°	417	514	771	1302	1554	373
135°	503	565	765	1085	1228	390
145°	588	628	760	937	1017	368
155°	668	691	748	834	862	308
165°	731	737	754	788	794	206
175°	765	765	760	771	765	72
180°	765	765	765	765	765	



TEST NUMBER: P845135

CATALOG NUMBER: SQ4P-PP3-150U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1090.5	1090.5	1090.5	1090.5	1090.5
2.5°	1097.3	1088.4	1090.5	1088.9	1084.3
5°	1094.2	1084.1	1087.5	1083.7	1083.7
7.5°	1086.8	1075.6	1079.1	1075.3	1075.2
10°	1079.9	1068.7	1072.3	1068.4	1067.5
12.5°	1070.1	1058.8	1063.1	1058.5	1058.3
15°	1052.3	1041.9	1046.5	1042.6	1040.7
17.5°	1032.1	1020.9	1026.4	1021.1	1020.3
20°	1016.8	1005.6	1011.1	1003.4	1003.4
22.5°	998.5	987.3	993.5	983.6	983.6
25°	969.1	957.8	962.4	953.7	952.9
27.5°	934.1	923.1	927.9	918.0	917.8
30°	908.9	898.5	904.1	893.5	892.6
32.5°	881.4	871.8	875.8	865.2	864.3
35°	837.2	828.8	831.5	821.9	820.9
37.5°	790.8	782.2	785.1	776.9	776.6
40°	757.8	752.2	753.0	746.3	744.5
42.5°	727.3	720.9	721.7	714.9	714.6
45°	680.5	675.7	675.7	668.9	668.9
47.5°	630.8	627.2	626.2	620.5	620.4
50°	596.3	593.5	592.5	587.7	586.7
52.5°	560.4	559.1	555.8	551.8	551.6
55°	504.5	502.7	498.0	495.0	494.2
57.5°	444.1	440.3	434.9	430.8	431.4
60°	400.4	396.6	389.1	387.0	387.0
62.5°	358.4	353.9	346.2	343.6	345.0
65°	298.3	292.6	285.7	283.9	284.8
67.5°	243.6	238.4	231.0	231.0	230.4
70°	208.2	205.5	199.7	199.7	199.7
72.5°	176.9	175.7	171.5	171.3	170.7
75°	135.7	135.7	133.8	132.8	131.8
77.5°	101.7	102.0	101.2	100.2	98.3
80°	80.2	82.2	81.2	80.2	79.3
82.5°	60.5	62.2	62.1	60.5	60.2
85°	31.5	34.2	34.4	34.4	34.4
87.5°	8.4	11.4	12.2	12.2	13.0
90°	11.4	17.1	17.1	11.4	5.7
92.5°	28.6	85.6	79.9	34.2	28.6
95°	51.4	177.0	514.0	131.3	79.9
97.5°	79.9	199.9	1028.1	468.3	251.3
100°	108.5	211.3	1199.4	1125.2	725.3
102.5°	142.8	228.5	1193.7	1582.0	1302.2
105°	177.0	251.3	1113.7	1879.0	1747.7



TEST NUMBER: P845135

CATALOG NUMBER: SQ4P-PP3-150U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.1	337.0	868.1	1890.5	2153.1
115°	308.4	371.3	828.2	1747.7	2061.8
117.5°	342.7	411.2	805.3	1616.3	1930.4
120°	371.3	445.4	788.1	1490.6	1799.1
122.5°	394.1	479.8	776.8	1387.9	1667.7
125°	417.0	514.0	771.0	1302.2	1553.5
127.5°	439.8	536.8	771.0	1239.4	1450.7
130°	462.7	548.3	765.3	1176.5	1365.0
132.5°	485.5	554.0	765.3	1130.8	1290.7
135°	502.6	565.4	765.3	1085.1	1227.9
137.5°	525.5	576.9	765.3	1045.2	1176.5
140°	542.6	594.0	765.3	1005.2	1119.4
142.5°	565.4	611.1	765.3	965.3	1068.0
145°	588.3	628.2	759.6	936.7	1016.6
147.5°	611.1	645.4	753.9	908.1	970.9
150°	628.2	662.5	753.9	879.5	930.9
152.5°	651.1	679.6	748.2	851.0	896.7
155°	668.3	691.1	748.2	833.8	862.4
157.5°	685.4	708.2	748.2	816.7	839.6
160°	702.5	719.6	753.9	805.3	822.4
162.5°	719.6	731.1	753.9	793.9	805.3
165°	731.1	736.8	753.9	788.1	793.9
167.5°	742.4	748.2	753.9	782.5	782.5
170°	748.2	753.9	759.6	776.8	776.8
172.5°	759.6	759.6	759.6	771.0	771.0
175°	765.3	765.3	759.6	771.0	765.3
177.5°	765.3	765.3	759.6	771.0	765.3
180°	765.3	765.3	765.3	765.3	765.3



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	211.3	279.9	1011.0	2010.4	2033.3
110°	239.8	308.4	930.9	1993.2	2158.9



(END OF REPORT)