

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845048

Luminaire Tested: **SQ4P-PC3-150U-050D-B35-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845048  
REPORT IS A COMBINATION OF REPORTS P700139 AND P700248  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PC3-150U-050D-B35-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6862.2 lumens  
Efficiency: N/A  
Efficacy: 114.8 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 59.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845048

CATALOG NUMBER: SQ4P-PC3-150U-050D-B35-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845048

CATALOG NUMBER: SQ4P-PC3-150U-050D-B35-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	36	36	36	28								
1	93	89	85	82	83	79	76	73	62	60	58	46	45	44	31	31	30	23								
2	84	77	71	67	75	69	64	60	54	51	48	40	38	36	28	26	25	20								
3	77	68	61	55	69	61	55	50	48	44	40	36	33	31	24	23	21	17								
4	70	60	52	47	63	54	47	42	42	38	34	32	29	26	22	20	18	14								
5	64	53	45	40	57	48	41	36	38	33	29	28	25	23	20	18	16	12								
6	59	48	40	34	53	43	36	31	34	29	25	26	22	20	18	16	14	11								
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12	10								
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11	8								
9	47	35	28	23	42	32	25	21	25	21	17	19	16	14	14	11	10	8								
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	11	9	7								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6400	6400	6400
5°	6450	6407	6384
10°	6434	6403	6386
15°	6400	6400	6394
20°	6358	6377	6377
25°	6297	6344	6324
30°	6221	6296	6269
35°	6129	6223	6179
40°	6027	6112	6051
45°	5918	5960	5868
50°	5763	5763	5671
55°	5580	5508	5426
60°	5311	5204	5121
65°	4908	4812	4768
70°	4297	4332	4316
75°	3458	3825	3846
80°	2460	3246	3273
85°	1503	2721	2721



TEST NUMBER: P845048

CATALOG NUMBER: SQ4P-PC3-150U-050D-B35-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.7	1.0
10°-20°	188.4	2.7
20°-30°	285.4	4.2
30°-40°	342.1	5.0
40°-50°	348.8	5.1
50°-60°	304.5	4.4
60°-70°	218.0	3.2
70°-80°	112.3	1.6
80°-90°	30.3	0.4
90°-100°	304.6	4.4
100°-110°	1059.8	15.4
110°-120°	1026.6	15.0
120°-130°	805.3	11.7
130°-140°	637.4	9.3
140°-150°	491.9	7.2
150°-160°	352.6	5.1
160°-170°	215.7	3.1
170°-180°	73.0	1.1
0°-30°	539.4	7.9
0°-40°	881.5	12.8
0°-60°	1534.9	22.4
0°-90°	1895.4	27.6
90°-120°	2391.0	34.8
90°-150°	4325.6	63.0
90°-180°	4967.0	72.4
0°-180°	6862.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	694	694	694	694	694	
5°	696	689	692	690	689	66
15°	670	664	670	670	669	189
25°	619	614	623	621	621	285
35°	544	543	552	549	549	340
45°	454	452	457	451	450	349
55°	347	342	342	337	337	309
65°	225	220	220	218	218	222
75°	97	102	107	108	108	105
85°	14	22	26	26	26	19
90°	11	17	17	11	6	8
95°	51	177	514	131	80	54
105°	177	251	1114	1879	1748	186
115°	308	371	828	1748	2062	305
125°	417	514	771	1302	1554	373
135°	503	565	765	1085	1228	390
145°	588	628	760	937	1017	368
155°	668	691	748	834	862	308
165°	731	737	754	788	794	206
175°	765	765	760	771	765	72
180°	765	765	765	765	765	



TEST NUMBER: P845048

CATALOG NUMBER: SQ4P-PC3-150U-050D-B35-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	693.7	693.7	693.7	693.7	693.7
2.5°	697.9	691.8	693.7	692.2	689.7
5°	696.4	689.4	691.8	689.9	689.3
7.5°	691.4	684.4	687.6	686.4	685.7
10°	686.8	679.8	683.5	682.3	681.6
12.5°	680.6	674.1	678.3	677.2	676.9
15°	670.0	664.4	670.0	670.0	669.4
17.5°	656.8	651.6	657.7	658.1	657.7
20°	647.6	641.9	649.5	648.8	649.5
22.5°	636.3	631.7	639.7	638.0	638.7
25°	618.6	614.2	623.2	621.2	621.2
27.5°	597.9	594.7	604.4	602.3	602.3
30°	583.9	580.8	591.0	588.4	588.4
32.5°	568.5	566.4	576.2	573.0	573.0
35°	544.2	542.8	552.5	548.6	548.6
37.5°	518.9	517.8	526.6	521.9	520.3
40°	500.4	499.9	507.5	502.4	502.4
42.5°	481.9	481.3	488.0	481.8	481.8
45°	453.6	452.2	456.8	450.9	449.7
47.5°	422.5	421.4	424.1	417.8	417.2
50°	401.5	400.2	401.5	395.6	395.1
52.5°	380.0	377.6	377.8	372.1	372.0
55°	346.9	342.5	342.4	337.3	337.3
57.5°	312.0	306.2	306.8	302.3	301.6
60°	287.8	281.5	282.0	278.2	277.5
62.5°	264.1	256.9	258.3	254.0	253.9
65°	224.8	219.8	220.4	218.4	218.4
67.5°	187.0	182.4	185.8	184.3	184.2
70°	159.3	156.2	160.6	160.6	160.0
72.5°	133.7	133.6	139.0	139.0	139.4
75°	97.0	101.5	107.3	107.9	107.9
77.5°	64.8	72.5	79.1	79.3	79.2
80°	46.3	55.0	61.1	62.3	61.6
82.5°	31.3	40.6	45.6	46.9	46.3
85°	14.2	21.7	25.7	26.3	25.7
87.5°	4.1	8.6	10.3	10.3	9.3
90°	11.4	17.1	17.1	11.4	5.7
92.5°	28.6	85.6	79.9	34.2	28.6
95°	51.4	177.0	514.0	131.3	79.9
97.5°	79.9	199.9	1028.1	468.3	251.3
100°	108.5	211.3	1199.4	1125.2	725.3
102.5°	142.8	228.5	1193.7	1582.0	1302.2
105°	177.0	251.3	1113.7	1879.0	1747.7



TEST NUMBER: P845048

CATALOG NUMBER: SQ4P-PC3-150U-050D-B35-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	274.1	337.0	868.1	1890.5	2153.1
115°	308.4	371.3	828.2	1747.7	2061.8
117.5°	342.7	411.2	805.3	1616.3	1930.4
120°	371.3	445.4	788.1	1490.6	1799.1
122.5°	394.1	479.8	776.8	1387.9	1667.7
125°	417.0	514.0	771.0	1302.2	1553.5
127.5°	439.8	536.8	771.0	1239.4	1450.7
130°	462.7	548.3	765.3	1176.5	1365.0
132.5°	485.5	554.0	765.3	1130.8	1290.7
135°	502.6	565.4	765.3	1085.1	1227.9
137.5°	525.5	576.9	765.3	1045.2	1176.5
140°	542.6	594.0	765.3	1005.2	1119.4
142.5°	565.4	611.1	765.3	965.3	1068.0
145°	588.3	628.2	759.6	936.7	1016.6
147.5°	611.1	645.4	753.9	908.1	970.9
150°	628.2	662.5	753.9	879.5	930.9
152.5°	651.1	679.6	748.2	851.0	896.7
155°	668.3	691.1	748.2	833.8	862.4
157.5°	685.4	708.2	748.2	816.7	839.6
160°	702.5	719.6	753.9	805.3	822.4
162.5°	719.6	731.1	753.9	793.9	805.3
165°	731.1	736.8	753.9	788.1	793.9
167.5°	742.4	748.2	753.9	782.5	782.5
170°	748.2	753.9	759.6	776.8	776.8
172.5°	759.6	759.6	759.6	771.0	771.0
175°	765.3	765.3	759.6	771.0	765.3
177.5°	765.3	765.3	759.6	771.0	765.3
180°	765.3	765.3	765.3	765.3	765.3



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	211.3	279.9	1011.0	2010.4	2033.3
110°	239.8	308.4	930.9	1993.2	2158.9



(END OF REPORT)