

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845141

Luminaire Tested: **SQ4P-PP3-150U-125D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845141
REPORT IS A COMBINATION OF REPORTS P700146 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-150U-125D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9556.2 lumens
Efficiency: N/A
Efficacy: 107.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 88.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845141

CATALOG NUMBER: SQ4P-PP3-150U-125D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845141

CATALOG NUMBER: SQ4P-PP3-150U-125D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48																
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41																
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35																
3	81	72	65	59	74	66	60	55	56	52	48	47	43	40	38	36	34	29	29	29	29																
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25	25																
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22	22	22	22																
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19	19	19	19																
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17	17	17	17																
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15	15	15	15																
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	22	18	16	14	14	14	14																
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13	13	13	13																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16537	16537	16537
5°	16659	16555	16498
10°	16630	16514	16441
15°	16521	16430	16339
20°	16410	16317	16195
25°	16215	16105	15945
30°	15916	15832	15631
35°	15500	15393	15197
40°	15002	14908	14738
45°	14595	14494	14347
50°	14069	13980	13844
55°	13340	13166	13066
60°	12145	11800	11741
65°	10704	10252	10217
70°	9234	8856	8856
75°	7956	7839	7725
80°	7008	7098	6918
85°	5483	5992	5992



TEST NUMBER: P845141

CATALOG NUMBER: SQ4P-PP3-150U-125D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.5	1.8
10°-20°	483.9	5.1
20°-30°	724.9	7.6
30°-40°	850.2	8.9
40°-50°	852.9	8.9
50°-60°	727.6	7.6
60°-70°	474.5	5.0
70°-80°	238.1	2.5
80°-90°	67.7	0.7
90°-100°	304.6	3.2
100°-110°	1059.8	11.1
110°-120°	1026.6	10.7
120°-130°	805.3	8.4
130°-140°	637.4	6.7
140°-150°	491.9	5.1
150°-160°	352.6	3.7
160°-170°	215.7	2.3
170°-180°	73.0	0.8
0°-30°	1378.3	14.4
0°-40°	2228.6	23.3
0°-60°	3809.1	39.9
0°-90°	4589.4	48.0
90°-120°	2391.0	25.0
90°-150°	4325.6	45.3
90°-180°	4967.0	52.0
0°-180°	9556.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1792	1792	1792	1792	1792	
5°	1799	1782	1788	1781	1781	171
15°	1730	1713	1720	1714	1711	488
25°	1593	1574	1582	1568	1566	732
35°	1376	1362	1367	1351	1349	860
45°	1119	1111	1111	1100	1100	861
55°	829	826	818	814	812	737
65°	490	481	470	467	468	489
75°	223	223	220	218	217	242
85°	52	56	57	57	57	61
90°	11	17	17	11	6	9
95°	51	177	514	131	80	54
105°	177	251	1114	1879	1748	186
115°	308	371	828	1748	2062	305
125°	417	514	771	1302	1554	373
135°	503	565	765	1085	1228	390
145°	588	628	760	937	1017	368
155°	668	691	748	834	862	308
165°	731	737	754	788	794	206
175°	765	765	760	771	765	72
180°	765	765	765	765	765	



TEST NUMBER: P845141

CATALOG NUMBER: SQ4P-PP3-150U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1792.4	1792.4	1792.4	1792.4	1792.4
2.5°	1803.6	1788.9	1792.4	1789.8	1782.5
5°	1798.7	1781.9	1787.5	1781.4	1781.4
7.5°	1786.5	1768.1	1773.7	1767.6	1767.3
10°	1775.1	1756.7	1762.7	1756.1	1754.9
12.5°	1758.9	1740.5	1747.5	1739.9	1739.7
15°	1729.6	1712.6	1720.1	1713.7	1710.6
17.5°	1696.5	1678.1	1687.1	1678.4	1677.1
20°	1671.4	1653.0	1661.9	1649.5	1649.5
22.5°	1641.3	1623.0	1633.2	1616.7	1616.7
25°	1592.8	1574.4	1582.0	1567.7	1566.3
27.5°	1535.5	1517.3	1525.1	1508.9	1508.7
30°	1494.0	1476.9	1486.1	1468.8	1467.2
32.5°	1448.8	1433.0	1439.6	1422.2	1420.6
35°	1376.2	1362.4	1366.7	1351.0	1349.3
37.5°	1299.8	1285.7	1290.6	1277.0	1276.5
40°	1245.6	1236.4	1237.8	1226.6	1223.7
42.5°	1195.5	1184.9	1186.3	1175.2	1174.7
45°	1118.6	1110.8	1110.8	1099.6	1099.6
47.5°	1036.8	1030.8	1029.3	1020.1	1019.8
50°	980.2	975.6	974.0	966.1	964.5
52.5°	921.1	919.0	913.6	907.0	906.8
55°	829.3	826.4	818.5	813.6	812.3
57.5°	729.9	723.7	714.7	708.0	709.1
60°	658.2	651.9	639.5	636.3	636.3
62.5°	589.1	581.8	569.0	564.7	567.2
65°	490.3	481.1	469.6	466.7	468.0
67.5°	400.3	391.9	379.7	379.7	378.6
70°	342.3	337.7	328.3	328.3	328.3
72.5°	290.9	288.7	281.9	281.7	280.6
75°	223.2	223.2	219.9	218.3	216.7
77.5°	167.1	167.6	166.3	164.7	161.7
80°	131.9	135.1	133.6	131.9	130.2
82.5°	99.4	102.4	102.1	99.4	98.8
85°	51.8	56.4	56.6	56.6	56.6
87.5°	13.8	18.7	20.1	20.1	21.4
90°	11.4	17.1	17.1	11.4	5.7
92.5°	28.6	85.6	79.9	34.2	28.6
95°	51.4	177.0	514.0	131.3	79.9
97.5°	79.9	199.9	1028.1	468.3	251.3
100°	108.5	211.3	1199.4	1125.2	725.3
102.5°	142.8	228.5	1193.7	1582.0	1302.2
105°	177.0	251.3	1113.7	1879.0	1747.7



TEST NUMBER: P845141

CATALOG NUMBER: SQ4P-PP3-150U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	274.1	337.0	868.1	1890.5	2153.1
115°	308.4	371.3	828.2	1747.7	2061.8
117.5°	342.7	411.2	805.3	1616.3	1930.4
120°	371.3	445.4	788.1	1490.6	1799.1
122.5°	394.1	479.8	776.8	1387.9	1667.7
125°	417.0	514.0	771.0	1302.2	1553.5
127.5°	439.8	536.8	771.0	1239.4	1450.7
130°	462.7	548.3	765.3	1176.5	1365.0
132.5°	485.5	554.0	765.3	1130.8	1290.7
135°	502.6	565.4	765.3	1085.1	1227.9
137.5°	525.5	576.9	765.3	1045.2	1176.5
140°	542.6	594.0	765.3	1005.2	1119.4
142.5°	565.4	611.1	765.3	965.3	1068.0
145°	588.3	628.2	759.6	936.7	1016.6
147.5°	611.1	645.4	753.9	908.1	970.9
150°	628.2	662.5	753.9	879.5	930.9
152.5°	651.1	679.6	748.2	851.0	896.7
155°	668.3	691.1	748.2	833.8	862.4
157.5°	685.4	708.2	748.2	816.7	839.6
160°	702.5	719.6	753.9	805.3	822.4
162.5°	719.6	731.1	753.9	793.9	805.3
165°	731.1	736.8	753.9	788.1	793.9
167.5°	742.4	748.2	753.9	782.5	782.5
170°	748.2	753.9	759.6	776.8	776.8
172.5°	759.6	759.6	759.6	771.0	771.0
175°	765.3	765.3	759.6	771.0	765.3
177.5°	765.3	765.3	759.6	771.0	765.3
180°	765.3	765.3	765.3	765.3	765.3



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	211.3	279.9	1011.0	2010.4	2033.3
110°	239.8	308.4	930.9	1993.2	2158.9



(END OF REPORT)