

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845108

Luminaire Tested: **SQ4P-PP3-100U-050D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845108
REPORT IS A COMBINATION OF REPORTS P700087 AND P700246
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-100U-050D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1000 LUMENS PER FOOT
UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5178.0 lumens
Efficiency: N/A
Efficacy: 121.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 42.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845108

CATALOG NUMBER: SQ4P-PP3-100U-050D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845108

CATALOG NUMBER: SQ4P-PP3-100U-050D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36				36
1	95	91	87	84	86	82	79	76	66	64	62	52	51	49	39	38	37	31				31
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	33	31	26				26
3	79	70	63	57	71	63	57	52	52	47	44	41	38	35	30	28	27	22				22
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19				19
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	17				17
6	61	49	41	36	55	45	38	33	37	32	28	29	26	23	22	20	18	15				15
7	56	44	37	31	51	41	34	29	33	28	24	27	23	20	20	18	16	13				13
8	52	40	33	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12				12
9	48	37	29	24	44	34	27	23	28	23	19	22	19	16	17	15	13	10				10
10	45	33	26	22	41	31	24	20	25	21	17	21	17	14	16	13	12	9				9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6762	6762	6762
5°	6812	6770	6746
10°	6801	6753	6723
15°	6756	6719	6681
20°	6710	6673	6622
25°	6630	6585	6520
30°	6508	6474	6392
35°	6339	6295	6215
40°	6134	6095	6026
45°	5968	5926	5868
50°	5753	5717	5661
55°	5456	5384	5342
60°	4966	4825	4801
65°	4377	4194	4178
70°	3777	3623	3623
75°	3255	3205	3158
80°	2864	2901	2827
85°	2234	2456	2456



TEST NUMBER: P845108

CATALOG NUMBER: SQ4P-PP3-100U-050D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.3	1.3
10°-20°	197.9	3.8
20°-30°	296.4	5.7
30°-40°	347.7	6.7
40°-50°	348.8	6.7
50°-60°	297.5	5.7
60°-70°	194.1	3.7
70°-80°	97.4	1.9
80°-90°	28.2	0.5
90°-100°	202.4	3.9
100°-110°	704.3	13.6
110°-120°	682.2	13.2
120°-130°	535.2	10.3
130°-140°	423.6	8.2
140°-150°	326.9	6.3
150°-160°	234.3	4.5
160°-170°	143.3	2.8
170°-180°	48.5	0.9
0°-30°	563.6	10.9
0°-40°	911.3	17.6
0°-60°	1557.6	30.1
0°-90°	1877.2	36.3
90°-120°	1588.9	30.7
90°-150°	2874.6	55.5
90°-180°	3301.0	63.8
0°-180°	5178.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	733	733	733	733	733	
5°	736	729	731	728	728	70
15°	707	700	703	701	700	200
25°	651	644	647	641	640	300
35°	563	557	559	552	552	352
45°	457	454	454	450	450	352
55°	339	338	335	333	332	301
65°	200	197	192	191	191	200
75°	91	91	90	89	89	99
85°	21	23	23	23	23	25
90°	8	11	11	8	4	5
95°	34	118	342	87	53	36
105°	118	167	740	1249	1162	124
115°	205	247	550	1162	1370	202
125°	277	342	512	865	1032	248
135°	334	376	509	721	816	259
145°	391	418	505	622	676	245
155°	444	459	497	554	573	205
165°	486	490	501	524	528	137
175°	509	509	505	512	509	48
180°	509	509	509	509	509	



TEST NUMBER: P845108

CATALOG NUMBER: SQ4P-PP3-100U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	732.9	732.9	732.9	732.9	732.9
2.5°	737.5	731.6	732.9	731.9	728.8
5°	735.5	728.6	731.0	728.4	728.4
7.5°	730.5	723.0	725.3	722.8	722.7
10°	725.9	718.4	720.8	718.2	717.6
12.5°	719.2	711.7	714.5	711.5	711.4
15°	707.3	700.3	703.4	700.8	699.5
17.5°	693.8	686.3	689.9	686.4	685.8
20°	683.4	675.9	679.6	674.5	674.5
22.5°	671.2	663.7	667.9	661.1	661.1
25°	651.3	643.8	646.9	641.1	640.5
27.5°	627.8	620.4	623.6	617.0	616.9
30°	610.9	604.0	607.7	600.6	600.0
32.5°	592.4	586.0	588.7	581.6	580.9
35°	562.8	557.1	558.9	552.4	551.8
37.5°	531.5	525.8	527.7	522.2	522.0
40°	509.3	505.6	506.1	501.6	500.3
42.5°	488.9	484.6	485.1	480.6	480.4
45°	457.4	454.2	454.2	449.7	449.7
47.5°	424.0	421.6	420.9	417.1	417.0
50°	400.8	399.0	398.3	395.0	394.4
52.5°	376.7	375.8	373.6	370.9	370.8
55°	339.2	337.9	334.7	332.7	332.1
57.5°	298.5	295.9	292.3	289.6	289.9
60°	269.1	266.6	261.5	260.2	260.2
62.5°	240.9	237.9	232.7	230.9	231.9
65°	200.5	196.7	192.1	190.8	191.4
67.5°	163.7	160.3	155.3	155.3	154.8
70°	140.0	138.1	134.3	134.3	134.3
72.5°	119.0	118.0	115.3	115.2	114.8
75°	91.3	91.3	89.9	89.2	88.6
77.5°	68.3	68.6	68.0	67.3	66.2
80°	53.9	55.3	54.6	53.9	53.2
82.5°	40.6	41.9	41.8	40.6	40.4
85°	21.1	23.0	23.2	23.2	23.2
87.5°	5.7	7.6	8.2	8.2	8.7
90°	7.6	11.4	11.4	7.6	3.8
92.5°	19.0	57.0	53.1	22.8	19.0
95°	34.2	117.6	341.6	87.3	53.1
97.5°	53.1	132.9	683.2	311.3	167.0
100°	72.1	140.4	797.0	747.7	482.0
102.5°	94.9	151.8	793.2	1051.4	865.3
105°	117.6	167.0	740.1	1248.7	1161.5



TEST NUMBER: P845108

CATALOG NUMBER: SQ4P-PP3-100U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.2	223.9	577.0	1256.3	1431.0
115°	204.9	246.7	550.3	1161.5	1370.2
117.5°	227.7	273.3	535.2	1074.2	1282.9
120°	246.7	296.0	523.8	990.6	1195.6
122.5°	261.9	318.8	516.2	922.3	1108.3
125°	277.0	341.6	512.4	865.3	1032.4
127.5°	292.3	356.8	512.4	823.7	964.1
130°	307.5	364.4	508.6	781.9	907.1
132.5°	322.6	368.1	508.6	751.5	857.8
135°	334.0	375.8	508.6	721.2	816.0
137.5°	349.2	383.3	508.6	694.6	781.9
140°	360.6	394.8	508.6	668.0	743.9
142.5°	375.8	406.1	508.6	641.5	709.8
145°	390.9	417.6	504.8	622.5	675.6
147.5°	406.1	428.9	501.0	603.5	645.3
150°	417.6	440.3	501.0	584.5	618.6
152.5°	432.7	451.7	497.2	565.5	595.9
155°	444.1	459.2	497.2	554.2	573.1
157.5°	455.4	470.7	497.2	542.8	558.0
160°	466.9	478.2	501.0	535.2	546.5
162.5°	478.2	485.9	501.0	527.5	535.2
165°	485.9	489.7	501.0	523.8	527.5
167.5°	493.4	497.2	501.0	520.0	520.0
170°	497.2	501.0	504.8	516.2	516.2
172.5°	504.8	504.8	504.8	512.4	512.4
175°	508.6	508.6	504.8	512.4	508.6
177.5°	508.6	508.6	504.8	512.4	508.6
180°	508.6	508.6	508.6	508.6	508.6



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	140.4	186.0	671.8	1336.0	1351.2
110°	159.4	204.9	618.6	1324.7	1434.7



(END OF REPORT)