

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845204

Luminaire Tested: **SQ4P-PR1-125U-050D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845204
REPORT IS A COMBINATION OF REPORTS P700119 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PR1-125U-050D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5986.4 lumens
Efficiency: N/A
Efficacy: 117.8 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845204

CATALOG NUMBER: SQ4P-PR1-125U-050D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845204

CATALOG NUMBER: SQ4P-PR1-125U-050D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31				31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	26				26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22				22
3	78	69	62	56	70	62	56	52	50	45	42	38	35	33	27	25	24	19				19
4	71	61	53	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17				17
5	65	54	47	41	59	49	42	37	39	35	31	30	27	24	22	20	18	15				15
6	60	49	41	35	54	44	37	32	35	31	27	27	24	21	20	18	16	13				13
7	56	44	36	31	50	40	33	28	32	27	24	25	21	19	18	16	14	11				11
8	51	40	32	27	46	36	30	25	29	24	21	23	19	17	17	14	13	10				10
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9				9
10	45	33	26	21	40	30	24	20	24	20	17	19	16	14	14	12	10	8				8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6844	6844	6844
5°	6906	6853	6817
10°	6883	6835	6800
15°	6854	6810	6774
20°	6819	6775	6725
25°	6771	6726	6648
30°	6697	6650	6555
35°	6600	6542	6448
40°	6448	6378	6264
45°	6186	6078	5952
50°	5723	5585	5474
55°	4995	4884	4781
60°	4209	4174	4091
65°	3639	3655	3626
70°	3342	3361	3361
75°	3212	3212	3233
80°	3023	3055	3023
85°	2435	2699	2699



TEST NUMBER: P845204

CATALOG NUMBER: SQ4P-PR1-125U-050D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.1	1.2
10°-20°	200.7	3.4
20°-30°	302.7	5.1
30°-40°	360.7	6.0
40°-50°	355.6	5.9
50°-60°	271.8	4.5
60°-70°	168.2	2.8
70°-80°	95.5	1.6
80°-90°	30.6	0.5
90°-100°	253.3	4.2
100°-110°	881.3	14.7
110°-120°	853.7	14.3
120°-130°	669.7	11.2
130°-140°	530.1	8.9
140°-150°	409.1	6.8
150°-160°	293.2	4.9
160°-170°	179.4	3.0
170°-180°	60.7	1.0
0°-30°	573.6	9.6
0°-40°	934.3	15.6
0°-60°	1561.6	26.1
0°-90°	1856.0	31.0
90°-120°	1988.3	33.2
90°-150°	3597.1	60.1
90°-180°	4130.0	69.0
0°-180°	5986.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	742	742	742	742	742	
5°	746	737	740	737	736	71
15°	718	710	713	710	709	202
25°	665	657	661	654	653	306
35°	586	579	581	573	572	366
45°	474	468	466	457	456	363
55°	310	306	304	298	297	278
65°	167	166	167	166	166	169
75°	90	90	90	91	91	95
85°	23	24	26	26	26	27
90°	10	14	14	10	5	7
95°	43	147	427	109	66	45
105°	147	209	926	1563	1453	155
115°	256	309	689	1453	1714	253
125°	347	427	641	1083	1292	310
135°	418	470	636	902	1021	324
145°	489	522	632	779	845	306
155°	556	575	622	693	717	256
165°	608	613	627	655	660	171
175°	636	636	632	641	636	60
180°	636	636	636	636	636	



TEST NUMBER: P845204

CATALOG NUMBER: SQ4P-PR1-125U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	741.8	741.8	741.8	741.8	741.8
2.5°	746.4	739.9	741.8	740.2	736.7
5°	745.7	737.4	739.9	737.3	736.1
7.5°	739.9	731.9	734.3	731.7	731.0
10°	734.7	727.3	729.6	727.1	725.8
12.5°	729.1	721.2	724.0	720.9	719.7
15°	717.6	710.0	713.0	710.4	709.2
17.5°	704.8	696.7	699.8	696.8	695.2
20°	694.5	687.1	690.0	685.6	684.9
22.5°	683.2	675.8	678.7	672.9	672.7
25°	665.1	656.9	660.7	653.7	653.0
27.5°	643.5	636.1	639.0	631.9	631.2
30°	628.6	621.2	624.2	616.5	615.3
32.5°	611.8	604.9	607.4	599.7	598.9
35°	586.0	579.0	580.8	573.1	572.5
37.5°	556.4	550.1	551.1	542.6	542.1
40°	535.4	529.2	529.6	520.7	520.1
42.5°	512.5	506.2	505.6	496.7	496.0
45°	474.1	467.9	465.8	457.4	456.2
47.5°	430.4	424.1	420.3	413.4	412.6
50°	398.7	392.4	389.1	383.3	381.4
52.5°	364.4	358.2	355.4	350.1	348.3
55°	310.5	305.5	303.6	298.4	297.2
57.5°	259.2	256.0	255.3	250.3	249.8
60°	228.1	226.2	226.2	221.7	221.7
62.5°	201.6	200.1	201.1	198.2	197.7
65°	166.7	165.6	167.4	166.1	166.1
67.5°	139.3	139.3	140.4	139.8	139.8
70°	123.9	123.9	124.6	124.6	124.6
72.5°	110.1	109.7	111.4	111.3	110.8
75°	90.1	90.1	90.1	90.7	90.7
77.5°	70.2	70.3	70.8	70.8	70.2
80°	56.9	57.5	57.5	56.9	56.9
82.5°	43.6	44.1	44.1	44.0	43.6
85°	23.0	24.3	25.5	25.5	25.5
87.5°	6.7	8.6	10.3	10.3	9.7
90°	9.5	14.3	14.3	9.5	4.8
92.5°	23.8	71.2	66.4	28.5	23.8
95°	42.8	147.3	427.4	109.2	66.4
97.5°	66.4	166.3	854.9	389.5	209.0
100°	90.2	175.8	997.4	935.6	603.2
102.5°	118.7	189.9	992.7	1315.6	1082.9
105°	147.3	209.0	926.1	1562.6	1453.4



TEST NUMBER: P845204

CATALOG NUMBER: SQ4P-PR1-125U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	228.0	280.3	721.9	1572.1	1790.6
115°	256.5	308.7	688.7	1453.4	1714.5
117.5°	285.0	342.0	669.6	1344.2	1605.3
120°	308.7	370.5	655.4	1239.6	1496.1
122.5°	327.7	399.0	646.0	1154.1	1386.8
125°	346.7	427.4	641.2	1082.9	1291.9
127.5°	365.7	446.4	641.2	1030.6	1206.4
130°	384.7	455.9	636.5	978.4	1135.1
132.5°	403.8	460.7	636.5	940.4	1073.4
135°	417.9	470.2	636.5	902.4	1021.1
137.5°	436.9	479.7	636.5	869.2	978.4
140°	451.2	494.0	636.5	835.9	930.9
142.5°	470.2	508.2	636.5	802.6	888.1
145°	489.2	522.5	631.7	778.9	845.4
147.5°	508.2	536.6	627.0	755.2	807.4
150°	522.5	550.9	627.0	731.4	774.1
152.5°	541.4	565.2	622.2	707.7	745.7
155°	555.7	574.7	622.2	693.4	717.2
157.5°	569.9	588.9	622.2	679.2	698.2
160°	584.2	598.4	627.0	669.6	683.9
162.5°	598.4	608.0	627.0	660.1	669.6
165°	608.0	612.7	627.0	655.4	660.1
167.5°	617.5	622.2	627.0	650.6	650.6
170°	622.2	627.0	631.7	646.0	646.0
172.5°	631.7	631.7	631.7	641.2	641.2
175°	636.5	636.5	631.7	641.2	636.5
177.5°	636.5	636.5	631.7	641.2	636.5
180°	636.5	636.5	636.5	636.5	636.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	175.8	232.7	840.7	1671.8	1690.9
110°	199.4	256.5	774.1	1657.6	1795.3



(END OF REPORT)