

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845126

Luminaire Tested: **SQ4P-PP3-125U-100D-B35-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P845126  
REPORT IS A COMBINATION OF REPORTS P700117 AND P700247  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-125U-100D-B35-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT  
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7799.6 lumens  
Efficiency: N/A  
Efficacy: 113.2 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 68.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845126

CATALOG NUMBER: SQ4P-PP3-125U-100D-B35-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845126

CATALOG NUMBER: SQ4P-PP3-125U-100D-B35-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47			47
1	97	93	89	86	89	86	82	80	72	70	67	59	58	56	48	46	45	40			40
2	89	81	75	70	81	75	70	66	63	59	56	52	49	47	42	40	39	34			34
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	29			29
4	74	64	56	50	68	59	52	47	50	44	40	41	37	34	33	31	28	25			25
5	68	57	49	43	62	52	45	40	44	39	35	37	33	30	30	27	25	22			22
6	63	51	43	37	57	47	40	35	40	35	30	33	29	26	27	24	22	19			19
7	58	46	38	32	53	43	35	31	36	31	27	30	26	23	25	22	19	17			17
8	54	42	34	29	49	39	32	27	33	28	24	28	24	21	23	20	17	15			15
9	50	38	30	25	46	35	29	24	30	25	21	26	21	18	21	18	16	14			14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14	12			12

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13221	13221	13221
5°	13318	13236	13190
10°	13296	13202	13144
15°	13208	13136	13063
20°	13119	13046	12947
25°	12964	12876	12748
30°	12725	12658	12497
35°	12392	12307	12151
40°	11995	11919	11784
45°	11669	11586	11470
50°	11247	11176	11068
55°	10666	10526	10446
60°	9710	9433	9387
65°	8556	8198	8169
70°	7383	7081	7081
75°	6359	6267	6174
80°	5605	5674	5531
85°	4383	4785	4785



TEST NUMBER: P845126

CATALOG NUMBER: SQ4P-PP3-125U-100D-B35-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.5	1.7
10°-20°	386.9	5.0
20°-30°	579.5	7.4
30°-40°	679.8	8.7
40°-50°	681.8	8.7
50°-60°	581.7	7.5
60°-70°	379.4	4.9
70°-80°	190.3	2.4
80°-90°	54.2	0.7
90°-100°	253.3	3.2
100°-110°	881.3	11.3
110°-120°	853.7	10.9
120°-130°	669.7	8.6
130°-140°	530.1	6.8
140°-150°	409.1	5.2
150°-160°	293.2	3.8
160°-170°	179.4	2.3
170°-180°	60.7	0.8
0°-30°	1102.0	14.1
0°-40°	1781.7	22.8
0°-60°	3045.3	39.0
0°-90°	3669.2	47.0
90°-120°	1988.3	25.5
90°-150°	3597.1	46.1
90°-180°	4130.0	53.0
0°-180°	7799.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1433	1433	1433	1433	1433	
5°	1438	1425	1429	1424	1424	137
15°	1383	1369	1375	1370	1368	390
25°	1274	1259	1265	1253	1252	586
35°	1100	1089	1093	1080	1079	687
45°	894	888	888	879	879	689
55°	663	661	654	650	649	589
65°	392	385	376	373	374	391
75°	178	178	176	175	173	193
85°	41	45	45	45	45	49
90°	10	14	14	10	5	7
95°	43	147	427	109	66	45
105°	147	209	926	1563	1453	155
115°	256	309	689	1453	1714	253
125°	347	427	641	1083	1292	310
135°	418	470	636	902	1021	324
145°	489	522	632	779	845	306
155°	556	575	622	693	717	256
165°	608	613	627	655	660	171
175°	636	636	632	641	636	60
180°	636	636	636	636	636	



TEST NUMBER: P845126

CATALOG NUMBER: SQ4P-PP3-125U-100D-B35-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1433.0	1433.0	1433.0	1433.0	1433.0
2.5°	1441.9	1430.3	1433.0	1430.9	1425.1
5°	1438.0	1424.6	1429.2	1424.2	1424.2
7.5°	1428.3	1413.5	1418.1	1413.1	1413.0
10°	1419.2	1404.4	1409.2	1404.0	1403.0
12.5°	1406.2	1391.5	1397.1	1391.0	1390.8
15°	1382.8	1369.2	1375.3	1370.1	1367.6
17.5°	1356.4	1341.7	1348.9	1341.9	1340.8
20°	1336.2	1321.6	1328.7	1318.7	1318.7
22.5°	1312.3	1297.5	1305.7	1292.5	1292.5
25°	1273.5	1258.7	1264.8	1253.3	1252.3
27.5°	1227.5	1213.0	1219.3	1206.4	1206.1
30°	1194.4	1180.8	1188.2	1174.3	1173.0
32.5°	1158.2	1145.7	1150.9	1137.1	1135.7
35°	1100.2	1089.1	1092.7	1080.1	1078.8
37.5°	1039.1	1027.9	1031.8	1020.9	1020.5
40°	995.9	988.5	989.6	980.7	978.4
42.5°	955.8	947.3	948.4	939.5	939.1
45°	894.3	888.0	888.0	879.1	879.1
47.5°	828.9	824.1	822.9	815.4	815.2
50°	783.6	780.0	778.6	772.4	771.1
52.5°	736.5	734.7	730.4	725.2	725.0
55°	663.1	660.6	654.4	650.5	649.4
57.5°	583.6	578.6	571.5	566.0	566.9
60°	526.2	521.2	511.2	508.7	508.7
62.5°	471.0	465.1	454.9	451.5	453.5
65°	391.9	384.6	375.5	373.1	374.2
67.5°	320.1	313.3	303.6	303.6	302.8
70°	273.7	270.0	262.5	262.5	262.5
72.5°	232.6	230.8	225.5	225.2	224.3
75°	178.4	178.4	175.8	174.6	173.2
77.5°	133.6	134.1	133.0	131.6	129.3
80°	105.5	108.0	106.8	105.5	104.1
82.5°	79.5	81.8	81.6	79.5	79.1
85°	41.4	45.0	45.2	45.2	45.2
87.5°	11.1	15.0	16.0	16.0	17.1
90°	9.5	14.3	14.3	9.5	4.8
92.5°	23.8	71.2	66.4	28.5	23.8
95°	42.8	147.3	427.4	109.2	66.4
97.5°	66.4	166.3	854.9	389.5	209.0
100°	90.2	175.8	997.4	935.6	603.2
102.5°	118.7	189.9	992.7	1315.6	1082.9
105°	147.3	209.0	926.1	1562.6	1453.4



TEST NUMBER: P845126

CATALOG NUMBER: SQ4P-PP3-125U-100D-B35-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	228.0	280.3	721.9	1572.1	1790.6
115°	256.5	308.7	688.7	1453.4	1714.5
117.5°	285.0	342.0	669.6	1344.2	1605.3
120°	308.7	370.5	655.4	1239.6	1496.1
122.5°	327.7	399.0	646.0	1154.1	1386.8
125°	346.7	427.4	641.2	1082.9	1291.9
127.5°	365.7	446.4	641.2	1030.6	1206.4
130°	384.7	455.9	636.5	978.4	1135.1
132.5°	403.8	460.7	636.5	940.4	1073.4
135°	417.9	470.2	636.5	902.4	1021.1
137.5°	436.9	479.7	636.5	869.2	978.4
140°	451.2	494.0	636.5	835.9	930.9
142.5°	470.2	508.2	636.5	802.6	888.1
145°	489.2	522.5	631.7	778.9	845.4
147.5°	508.2	536.6	627.0	755.2	807.4
150°	522.5	550.9	627.0	731.4	774.1
152.5°	541.4	565.2	622.2	707.7	745.7
155°	555.7	574.7	622.2	693.4	717.2
157.5°	569.9	588.9	622.2	679.2	698.2
160°	584.2	598.4	627.0	669.6	683.9
162.5°	598.4	608.0	627.0	660.1	669.6
165°	608.0	612.7	627.0	655.4	660.1
167.5°	617.5	622.2	627.0	650.6	650.6
170°	622.2	627.0	631.7	646.0	646.0
172.5°	631.7	631.7	631.7	641.2	641.2
175°	636.5	636.5	631.7	641.2	636.5
177.5°	636.5	636.5	631.7	641.2	636.5
180°	636.5	636.5	636.5	636.5	636.5



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	175.8	232.7	840.7	1671.8	1690.9
110°	199.4	256.5	774.1	1657.6	1795.3



(END OF REPORT)