

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845264

Luminaire Tested: **SQ4P-PW1-0U-050D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P564826)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PW1-0U-050D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1864.1 lumens
Efficiency: N/A
Efficacy: 111.0 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 16.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845264

CATALOG NUMBER: SQ4P-PW1-0U-050D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845264

CATALOG NUMBER: SQ4P-PW1-0U-050D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85			
2	100	92	85	80	97	90	84	79	86	81	77	83	79	75	80	76	73	71			
3	91	81	73	67	89	79	72	66	76	70	65	74	68	64	71	66	63	60			
4	84	72	63	57	81	71	63	56	68	61	56	66	60	55	64	58	54	52			
5	77	64	56	49	75	63	55	49	61	54	48	59	53	48	57	52	47	45			
6	71	58	49	43	69	57	49	43	55	48	42	54	47	42	52	46	42	40			
7	66	53	44	38	64	52	44	38	50	43	38	49	42	37	48	42	37	35			
8	62	48	40	34	60	48	40	34	46	39	34	45	38	34	44	38	33	31			
9	58	44	36	31	56	44	36	31	43	35	31	42	35	30	41	35	30	28			
10	54	41	33	28	53	40	33	28	39	33	28	39	32	28	38	32	28	26			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6760	6760	6760
5°	6803	6750	6720
10°	6749	6695	6658
15°	6679	6604	6579
20°	6598	6496	6484
25°	6506	6388	6368
30°	6369	6273	6231
35°	6188	6099	6063
40°	5994	5902	5877
45°	5761	5686	5660
50°	5523	5476	5439
55°	5263	5263	5181
60°	4943	5039	4860
65°	4523	4748	4412
70°	3987	4373	3882
75°	3408	3911	3315
80°	2641	3289	2678
85°	1704	2530	2244



TEST NUMBER: P845264

CATALOG NUMBER: SQ4P-PW1-0U-050D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.0	3.7
10°-20°	194.8	10.4
20°-30°	288.9	15.5
30°-40°	338.1	18.1
40°-50°	336.6	18.1
50°-60°	290.7	15.6
60°-70°	209.2	11.2
70°-80°	109.7	5.9
80°-90°	27.2	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.7	29.7
0°-40°	890.8	47.8
0°-60°	1518.0	81.4
0°-90°	1864.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1864.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	733	733	733	733	733	
5°	735	726	729	727	726	70
15°	699	690	691	690	689	197
25°	639	628	628	624	626	294
35°	549	542	542	536	538	343
45°	442	438	436	434	434	341
55°	327	327	327	323	322	292
65°	207	214	218	209	202	205
75°	96	104	110	102	93	102
85°	16	21	24	23	21	22
90°	0	0	0	0	0	



TEST NUMBER: P845264

CATALOG NUMBER: SQ4P-PW1-0U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	732.7	732.7	732.7	732.7	732.7
2.5°	736.9	730.8	732.7	731.1	727.6
5°	734.6	726.4	728.8	726.9	725.6
7.5°	727.2	719.6	721.3	719.2	718.6
10°	720.4	712.9	714.6	712.1	710.7
12.5°	712.7	704.6	706.4	703.7	703.0
15°	699.2	690.3	691.4	690.0	688.8
17.5°	683.3	674.4	674.5	672.6	672.2
20°	672.0	662.6	661.6	659.1	660.4
22.5°	659.7	649.7	648.8	645.2	646.9
25°	639.1	628.3	627.5	623.6	625.5
27.5°	615.3	604.8	604.8	599.4	601.3
30°	597.8	587.6	588.8	582.3	584.9
32.5°	579.2	570.1	570.6	564.2	566.9
35°	549.4	541.8	541.5	536.4	538.3
37.5°	518.8	512.2	511.1	508.2	508.7
40°	497.7	492.0	490.0	488.0	488.0
42.5°	475.5	470.4	468.2	466.8	466.4
45°	441.5	437.8	435.8	434.4	433.8
47.5°	408.0	404.4	402.7	401.8	401.1
50°	384.8	382.2	381.5	379.6	378.9
52.5°	361.6	360.0	359.3	356.9	356.2
55°	327.2	326.7	327.2	322.8	322.1
57.5°	291.6	292.7	294.7	288.7	287.1
60°	267.9	270.4	273.1	266.0	263.4
62.5°	243.6	247.7	251.4	243.2	239.6
65°	207.2	213.5	217.5	209.0	202.1
67.5°	172.1	180.0	184.8	175.6	167.7
70°	147.8	156.7	162.1	152.8	143.9
72.5°	126.6	136.5	140.9	132.1	123.3
75°	95.6	104.4	109.7	102.4	93.0
77.5°	67.8	76.1	80.5	74.2	66.3
80°	49.7	58.5	61.9	56.7	50.4
82.5°	35.2	42.7	44.9	41.7	37.4
85°	16.1	21.1	23.9	22.6	21.2
87.5°	4.1	7.6	9.8	9.8	10.4
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)