

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845330

Luminaire Tested: **SQ4P-WB-050U-100D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845330
REPORT IS A COMBINATION OF REPORTS P700213 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-050U-100D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4886.2 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 47.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845330

CATALOG NUMBER: SQ4P-WB-050U-100D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845330

CATALOG NUMBER: SQ4P-WB-050U-100D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70	65																			
1	103	99	95	92	96	93	90	87	83	80	78	73	71	70	64	63	62	58																			
2	95	88	83	78	89	83	78	74	74	71	67	66	63	61	58	56	55	51																			
3	87	79	72	67	82	75	69	64	67	62	59	60	56	53	53	51	48	45																			
4	81	71	64	58	76	67	61	56	61	56	52	54	50	47	49	46	43	40																			
5	75	64	57	51	71	61	54	49	55	50	46	50	45	42	45	41	39	36																			
6	70	58	51	45	66	56	49	44	51	45	41	46	41	38	41	38	35	32																			
7	65	53	46	41	61	51	44	39	46	41	37	42	38	34	38	35	32	29																			
8	61	49	42	37	57	47	40	36	43	37	33	39	35	31	35	32	29	27																			
9	57	45	38	33	54	43	37	32	40	34	30	36	32	29	33	29	27	25																			
10	53	42	35	30	51	40	34	30	37	32	28	34	29	26	31	27	25	23																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20106	20106	20106
5°	19855	19783	19899
10°	18758	18928	19367
15°	17316	17719	18513
20°	15725	16316	17396
25°	14105	14874	16208
30°	12613	13435	14973
35°	11028	11824	13517
40°	9281	10019	11701
45°	7659	8321	9769
50°	6393	6973	8137
55°	5429	5982	6719
60°	4641	5187	5364
65°	3696	4362	3462
70°	3275	3404	2115
75°	3030	2763	1298
80°	2795	2545	1116
85°	2519	2339	910



TEST NUMBER: P845330

CATALOG NUMBER: SQ4P-WB-050U-100D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	199.9	4.1
10°-20°	519.9	10.6
20°-30°	673.4	13.8
30°-40°	659.4	13.5
40°-50°	504.8	10.3
50°-60°	336.3	6.9
60°-70°	183.5	3.8
70°-80°	76.5	1.6
80°-90°	22.3	0.5
90°-100°	104.9	2.1
100°-110°	364.9	7.5
110°-120°	353.5	7.2
120°-130°	277.3	5.7
130°-140°	219.5	4.5
140°-150°	169.4	3.5
150°-160°	121.4	2.5
160°-170°	74.3	1.5
170°-180°	25.1	0.5
0°-30°	1393.2	28.5
0°-40°	2052.6	42.0
0°-60°	2893.7	59.2
0°-90°	3176.1	65.0
90°-120°	823.3	16.8
90°-150°	1489.4	30.5
90°-180°	1710.0	35.0
0°-180°	4886.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2179	2179	2179	2179	2179	
5°	2144	2122	2136	2141	2149	199
15°	1813	1806	1855	1906	1938	506
25°	1386	1389	1461	1525	1592	637
35°	979	984	1050	1121	1200	609
45°	587	598	638	686	749	458
55°	338	352	372	386	418	306
65°	169	183	200	175	159	176
75°	85	85	78	53	36	91
85°	24	24	22	14	9	26
90°	4	6	6	4	2	4
95°	18	61	177	45	28	19
105°	61	86	384	647	602	64
115°	106	128	285	602	710	105
125°	144	177	266	448	535	129
135°	173	195	264	374	423	134
145°	203	216	262	322	350	127
155°	230	238	258	287	297	106
165°	252	254	260	271	273	71
175°	264	264	262	266	264	25
180°	264	264	264	264	264	



TEST NUMBER: P845330

CATALOG NUMBER: SQ4P-WB-050U-100D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2179.2	2179.2	2179.2	2179.2	2179.2
2.5°	2184.6	2165.1	2170.1	2169.9	2163.8
5°	2143.8	2122.2	2136.1	2141.0	2148.6
7.5°	2064.2	2047.9	2073.3	2091.9	2107.0
10°	2002.2	1988.3	2020.4	2047.7	2067.2
12.5°	1930.4	1918.5	1958.6	1994.9	2020.7
15°	1812.9	1806.4	1855.1	1905.6	1938.2
17.5°	1687.3	1684.1	1739.9	1798.8	1840.6
20°	1601.6	1600.7	1661.8	1723.3	1771.8
22.5°	1515.2	1517.2	1581.5	1645.4	1700.7
25°	1385.6	1389.3	1461.1	1524.8	1592.1
27.5°	1265.7	1267.4	1341.4	1408.7	1480.6
30°	1183.9	1188.4	1261.1	1330.8	1405.5
32.5°	1102.1	1107.4	1178.7	1250.5	1326.7
35°	979.1	983.9	1049.8	1120.7	1200.1
37.5°	852.4	858.9	917.6	984.2	1062.6
40°	770.6	780.1	831.9	894.9	971.5
42.5°	691.8	703.5	751.5	811.3	880.3
45°	587.0	598.3	637.7	686.0	748.7
47.5°	496.8	509.7	540.1	581.7	635.1
50°	445.4	457.8	485.8	516.5	566.9
52.5°	400.4	412.6	437.5	461.3	504.4
55°	337.5	351.5	371.9	386.1	417.7
57.5°	285.9	299.3	315.6	321.9	341.1
60°	251.5	266.5	281.1	280.4	290.7
62.5°	220.2	232.9	247.4	237.2	237.9
65°	169.3	183.4	199.8	174.7	158.6
67.5°	136.8	139.6	156.8	121.8	102.8
70°	121.4	121.4	126.2	94.3	78.4
72.5°	107.0	107.0	102.7	76.6	60.0
75°	85.0	85.0	77.5	53.2	36.4
77.5°	65.6	65.0	59.3	39.6	26.4
80°	52.6	52.6	47.9	31.4	21.0
82.5°	41.1	41.1	37.0	24.5	15.6
85°	23.8	23.8	22.1	14.3	8.6
87.5°	8.4	8.4	7.5	4.5	3.9
90°	3.9	5.9	5.9	3.9	2.0
92.5°	9.8	29.5	27.5	11.8	9.8
95°	17.7	61.0	177.0	45.2	27.5
97.5°	27.5	68.8	353.9	161.3	86.5
100°	37.4	72.8	413.0	387.4	249.7
102.5°	49.1	78.7	411.0	544.7	448.4
105°	61.0	86.5	383.5	646.9	601.7



TEST NUMBER: P845330

CATALOG NUMBER: SQ4P-WB-050U-100D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	94.4	116.1	299.0	650.9	741.4
115°	106.2	127.8	285.2	601.7	709.9
117.5°	118.0	141.6	277.2	556.5	664.6
120°	127.8	153.3	271.4	513.3	619.4
122.5°	135.7	165.2	267.4	477.8	574.2
125°	143.6	177.0	265.5	448.4	534.9
127.5°	151.4	184.9	265.5	426.8	499.5
130°	159.3	188.8	263.5	405.1	470.0
132.5°	167.1	190.7	263.5	389.4	444.5
135°	173.0	194.6	263.5	373.6	422.8
137.5°	180.9	198.6	263.5	359.8	405.1
140°	186.8	204.5	263.5	346.1	385.5
142.5°	194.6	210.4	263.5	332.3	367.7
145°	202.6	216.4	261.6	322.5	350.0
147.5°	210.4	222.2	259.6	312.7	334.3
150°	216.4	228.1	259.6	302.9	320.6
152.5°	224.2	234.0	257.7	293.0	308.7
155°	230.1	238.0	257.7	287.1	296.9
157.5°	235.9	243.9	257.7	281.2	289.1
160°	241.9	247.8	259.6	277.2	283.2
162.5°	247.8	251.7	259.6	273.3	277.2
165°	251.7	253.6	259.6	271.4	273.3
167.5°	255.6	257.7	259.6	269.4	269.4
170°	257.7	259.6	261.6	267.4	267.4
172.5°	261.6	261.6	261.6	265.5	265.5
175°	263.5	263.5	261.6	265.5	263.5
177.5°	263.5	263.5	261.6	265.5	263.5
180°	263.5	263.5	263.5	263.5	263.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	72.8	96.4	348.1	692.2	700.1
110°	82.6	106.2	320.6	686.3	743.3



(END OF REPORT)