

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845255

Luminaire Tested: **SQ4P-PW1-075U-075D-B35-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P845255  
REPORT IS A COMBINATION OF REPORTS P700236 AND P700245  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PW1-075U-075D-B35-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT  
UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5235.6 lumens  
Efficiency: N/A  
Efficacy: 117.4 lumens/watt  
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 44.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845255

CATALOG NUMBER: SQ4P-PW1-075U-075D-B35-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845255

CATALOG NUMBER: SQ4P-PW1-075U-075D-B35-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53			
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	45			
2	90	82	76	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38			
3	82	73	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	32			
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	34	31	28			
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27	24			
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24	21			
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	19			
8	54	42	34	29	50	39	32	28	34	29	25	30	25	22	25	22	19	17			
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15			
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	16	14			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	10059	10059	10059
5°	10126	10045	10001
10°	10044	9963	9909
15°	9939	9828	9790
20°	9819	9667	9650
25°	9682	9506	9476
30°	9477	9335	9273
35°	9209	9077	9024
40°	8922	8781	8748
45°	8574	8462	8422
50°	8220	8151	8092
55°	7834	7834	7711
60°	7359	7499	7233
65°	6731	7067	6565
70°	5932	6504	5781
75°	5073	5821	4930
80°	3932	4904	3990
85°	2541	3769	3345



TEST NUMBER: P845255

CATALOG NUMBER: SQ4P-PW1-075U-075D-B35-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.7	2.0
10°-20°	289.9	5.5
20°-30°	430.0	8.2
30°-40°	503.1	9.6
40°-50°	500.9	9.6
50°-60°	432.6	8.3
60°-70°	311.3	5.9
70°-80°	163.3	3.1
80°-90°	41.4	0.8
90°-100°	150.9	2.9
100°-110°	525.0	10.0
110°-120°	508.6	9.7
120°-130°	398.9	7.6
130°-140°	315.7	6.0
140°-150°	243.7	4.7
150°-160°	174.7	3.3
160°-170°	106.8	2.0
170°-180°	36.1	0.7
0°-30°	822.6	15.7
0°-40°	1325.7	25.3
0°-60°	2259.1	43.1
0°-90°	2775.2	53.0
90°-120°	1184.4	22.6
90°-150°	2142.8	40.9
90°-180°	2460.0	47.0
0°-180°	5235.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1090	1090	1090	1090	1090	
5°	1093	1081	1085	1082	1080	104
15°	1040	1027	1029	1027	1025	293
25°	951	935	934	928	931	437
35°	818	806	806	798	801	511
45°	657	651	648	646	646	507
55°	487	486	487	480	479	435
65°	308	318	324	311	301	306
75°	142	155	163	152	138	152
85°	24	32	36	34	32	32
90°	6	8	8	6	3	4
95°	25	88	255	65	40	27
105°	88	124	552	931	866	92
115°	153	184	410	866	1021	151
125°	207	255	382	645	770	185
135°	249	280	379	538	608	193
145°	291	311	376	464	504	182
155°	331	342	371	413	427	153
165°	362	365	373	390	393	102
175°	379	379	376	382	379	36
180°	379	379	379	379	379	



TEST NUMBER: P845255

CATALOG NUMBER: SQ4P-PW1-075U-075D-B35-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1090.3	1090.3	1090.3	1090.3	1090.3
2.5°	1096.6	1087.5	1090.3	1088.0	1082.7
5°	1093.3	1081.0	1084.6	1081.7	1079.8
7.5°	1082.2	1070.9	1073.4	1070.5	1069.3
10°	1072.1	1060.9	1063.5	1059.7	1057.7
12.5°	1060.7	1048.5	1051.3	1047.3	1046.3
15°	1040.5	1027.2	1028.9	1026.9	1025.0
17.5°	1016.9	1003.7	1003.9	1000.9	1000.4
20°	1000.1	986.0	984.6	980.8	982.9
22.5°	981.7	966.8	965.5	960.2	962.8
25°	951.1	935.1	933.8	928.1	930.8
27.5°	915.7	900.1	900.1	892.0	894.9
30°	889.6	874.5	876.2	866.6	870.4
32.5°	861.9	848.4	849.2	839.8	843.5
35°	817.6	806.3	805.9	798.3	801.2
37.5°	772.2	762.3	760.6	756.3	756.9
40°	740.8	732.3	729.1	726.3	726.3
42.5°	707.6	700.0	696.8	694.7	694.0
45°	657.1	651.4	648.5	646.5	645.5
47.5°	607.1	601.9	599.3	598.0	597.0
50°	572.7	568.8	567.9	564.8	563.8
52.5°	538.0	535.8	534.7	531.1	530.1
55°	487.0	486.2	487.0	480.4	479.4
57.5°	434.0	435.6	438.7	429.6	427.2
60°	398.8	402.4	406.4	395.8	392.0
62.5°	362.5	368.6	374.1	361.9	356.5
65°	308.3	317.7	323.7	311.0	300.7
67.5°	256.2	267.7	274.9	261.3	249.5
70°	219.9	233.2	241.1	227.3	214.3
72.5°	188.5	203.2	209.6	196.6	183.5
75°	142.3	155.3	163.3	152.4	138.3
77.5°	100.9	113.3	119.9	110.5	98.7
80°	74.0	87.1	92.3	84.3	75.1
82.5°	52.5	63.4	66.9	62.1	55.7
85°	24.0	31.5	35.6	33.7	31.6
87.5°	6.2	11.4	14.6	14.6	15.4
90°	5.7	8.5	8.5	5.7	2.8
92.5°	14.2	42.5	39.6	16.9	14.2
95°	25.4	87.7	254.6	65.1	39.6
97.5°	39.6	99.0	509.2	232.0	124.5
100°	53.7	104.7	594.1	557.4	359.3
102.5°	70.8	113.1	591.3	783.7	645.1
105°	87.7	124.5	551.7	930.8	865.7



TEST NUMBER: P845255

CATALOG NUMBER: SQ4P-PW1-075U-075D-B35-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	135.8	166.9	430.1	936.5	1066.6
115°	152.8	183.9	410.2	865.7	1021.3
117.5°	169.8	203.7	399.0	800.7	956.3
120°	183.9	220.7	390.4	738.4	891.2
122.5°	195.2	237.7	384.8	687.5	826.1
125°	206.6	254.6	381.9	645.1	769.5
127.5°	217.8	266.0	381.9	614.0	718.7
130°	229.2	271.6	379.1	582.8	676.2
132.5°	240.4	274.4	379.1	560.2	639.4
135°	248.9	280.1	379.1	537.5	608.3
137.5°	260.3	285.7	379.1	517.8	582.8
140°	268.8	294.3	379.1	497.9	554.6
142.5°	280.1	302.8	379.1	478.1	529.0
145°	291.4	311.2	376.3	464.0	503.6
147.5°	302.8	319.7	373.4	449.8	481.0
150°	311.2	328.2	373.4	435.7	461.2
152.5°	322.5	336.6	370.6	421.6	444.2
155°	331.0	342.3	370.6	413.1	427.2
157.5°	339.5	350.8	370.6	404.5	415.9
160°	348.0	356.5	373.4	399.0	407.4
162.5°	356.5	362.2	373.4	393.3	399.0
165°	362.2	365.0	373.4	390.4	393.3
167.5°	367.8	370.6	373.4	387.6	387.6
170°	370.6	373.4	376.3	384.8	384.8
172.5°	376.3	376.3	376.3	381.9	381.9
175°	379.1	379.1	376.3	381.9	379.1
177.5°	379.1	379.1	376.3	381.9	379.1
180°	379.1	379.1	379.1	379.1	379.1



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	104.7	138.7	500.7	995.9	1007.2
110°	118.8	152.8	461.2	987.4	1069.5



(END OF REPORT)