

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845312

Luminaire Tested: **SQ4P-WB-025U-050D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845312
REPORT IS A COMBINATION OF REPORTS P700183 AND P700243
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-025U-050D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2475.7 lumens
Efficiency: N/A
Efficacy: 104.0 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 23.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845312

CATALOG NUMBER: SQ4P-WB-025U-050D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845312

CATALOG NUMBER: SQ4P-WB-025U-050D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	70	70	70	66			
1	103	99	95	92	97	93	90	88	83	81	79	73	72	70	65	63	62	58			
2	95	88	83	78	89	83	79	75	75	71	68	66	64	61	59	57	55	51			
3	88	79	72	67	82	75	69	64	67	63	59	60	57	54	54	51	49	45			
4	81	71	64	58	76	68	61	56	61	56	52	55	51	48	49	46	43	40			
5	75	64	57	51	71	61	55	49	55	50	46	50	46	42	45	42	39	36			
6	70	59	51	46	66	56	49	44	51	45	41	46	42	38	42	38	35	33			
7	65	54	46	41	61	51	44	40	47	41	37	42	38	34	38	35	32	30			
8	61	49	42	37	58	47	40	36	43	38	34	39	35	31	36	32	29	27			
9	57	45	38	33	54	44	37	33	40	34	31	37	32	29	33	30	27	25			
10	54	42	35	31	51	40	34	30	37	32	28	34	30	26	31	28	25	23			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10285	10285	10285
5°	10157	10121	10179
10°	9596	9683	9907
15°	8858	9065	9470
20°	8045	8347	8898
25°	7216	7609	8292
30°	6452	6874	7660
35°	5641	6048	6916
40°	4748	5126	5986
45°	3918	4258	4997
50°	3271	3567	4162
55°	2776	3059	3437
60°	2375	2653	2744
65°	1891	2231	1770
70°	1675	1743	1082
75°	1551	1412	663
80°	1429	1302	574
85°	1281	1196	466



TEST NUMBER: P845312

CATALOG NUMBER: SQ4P-WB-025U-050D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.3	4.1
10°-20°	266.0	10.7
20°-30°	344.5	13.9
30°-40°	337.3	13.6
40°-50°	258.2	10.4
50°-60°	172.1	6.9
60°-70°	93.9	3.8
70°-80°	39.1	1.6
80°-90°	11.4	0.5
90°-100°	52.2	2.1
100°-110°	181.6	7.3
110°-120°	175.9	7.1
120°-130°	138.0	5.6
130°-140°	109.2	4.4
140°-150°	84.3	3.4
150°-160°	60.4	2.4
160°-170°	37.0	1.5
170°-180°	12.5	0.5
0°-30°	712.7	28.8
0°-40°	1050.0	42.4
0°-60°	1480.3	59.8
0°-90°	1624.7	65.6
90°-120°	409.7	16.5
90°-150°	741.2	29.9
90°-180°	851.0	34.4
0°-180°	2475.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1115	1115	1115	1115	1115	
5°	1097	1086	1093	1095	1099	102
15°	927	924	949	975	992	259
25°	709	711	747	780	814	326
35°	501	503	537	573	614	311
45°	300	306	326	351	383	234
55°	173	180	190	198	214	157
65°	87	94	102	89	81	90
75°	44	44	40	27	19	46
85°	12	12	11	7	4	13
90°	2	3	3	2	1	2
95°	9	30	88	22	14	9
105°	30	43	191	322	300	32
115°	53	64	142	300	353	52
125°	71	88	132	223	266	64
135°	86	97	131	186	210	67
145°	101	108	130	160	174	63
155°	114	118	128	143	148	53
165°	125	126	129	135	136	35
175°	131	131	130	132	131	12
180°	131	131	131	131	131	



TEST NUMBER: P845312

CATALOG NUMBER: SQ4P-WB-025U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1114.8	1114.8	1114.8	1114.8	1114.8
2.5°	1117.5	1107.5	1110.1	1110.0	1106.9
5°	1096.7	1085.6	1092.8	1095.3	1099.1
7.5°	1056.0	1047.7	1060.6	1070.2	1077.9
10°	1024.3	1017.1	1033.6	1047.6	1057.5
12.5°	987.6	981.4	1002.0	1020.5	1033.7
15°	927.4	924.1	949.0	974.7	991.5
17.5°	863.2	861.5	890.1	920.2	941.6
20°	819.4	818.9	850.1	881.6	906.3
22.5°	775.1	776.1	809.0	841.7	870.0
25°	708.8	710.7	747.4	780.0	814.5
27.5°	647.4	648.3	686.2	720.6	757.4
30°	605.6	607.9	645.2	680.8	719.0
32.5°	563.8	566.5	603.0	639.7	678.7
35°	500.8	503.3	537.0	573.2	614.0
37.5°	436.0	439.4	469.4	503.5	543.6
40°	394.2	399.1	425.6	457.8	497.0
42.5°	353.9	359.9	384.5	415.0	450.3
45°	300.3	306.1	326.3	350.9	383.0
47.5°	254.1	260.8	276.2	297.6	324.9
50°	227.9	234.2	248.5	264.2	290.0
52.5°	204.8	211.1	223.8	235.9	258.0
55°	172.6	179.9	190.2	197.6	213.7
57.5°	146.3	153.1	161.5	164.7	174.5
60°	128.7	136.3	143.8	143.4	148.7
62.5°	112.6	119.2	126.5	121.3	121.7
65°	86.6	93.7	102.2	89.3	81.1
67.5°	70.0	71.4	80.1	62.3	52.6
70°	62.1	62.1	64.6	48.2	40.1
72.5°	54.7	54.7	52.5	39.2	30.6
75°	43.5	43.5	39.6	27.2	18.6
77.5°	33.6	33.2	30.3	20.3	13.5
80°	26.9	26.9	24.5	16.0	10.8
82.5°	21.0	21.0	19.0	12.5	7.9
85°	12.1	12.1	11.3	7.3	4.4
87.5°	4.3	4.3	3.9	2.3	2.0
90°	2.0	2.9	2.9	2.0	1.0
92.5°	4.9	14.7	13.7	5.9	4.9
95°	8.8	30.3	88.1	22.5	13.7
97.5°	13.7	34.2	176.1	80.2	43.1
100°	18.6	36.2	205.5	192.8	124.3
102.5°	24.5	39.1	204.5	271.1	223.1
105°	30.3	43.1	190.8	322.0	299.5



TEST NUMBER: P845312

CATALOG NUMBER: SQ4P-WB-025U-050D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	47.0	57.7	148.7	324.0	369.0
115°	52.8	63.6	141.9	299.5	353.4
117.5°	58.7	70.5	138.0	276.9	330.9
120°	63.6	76.3	135.0	255.4	308.3
122.5°	67.5	82.2	133.1	237.8	285.8
125°	71.4	88.1	132.1	223.1	266.2
127.5°	75.3	92.0	132.1	212.3	248.6
130°	79.3	93.9	131.1	201.6	233.9
132.5°	83.2	94.9	131.1	193.8	221.2
135°	86.1	96.9	131.1	185.9	210.4
137.5°	90.0	98.8	131.1	179.1	201.6
140°	93.0	101.8	131.1	172.2	191.8
142.5°	96.9	104.7	131.1	165.4	183.0
145°	100.8	107.6	130.1	160.5	174.2
147.5°	104.7	110.6	129.2	155.6	166.4
150°	107.6	113.5	129.2	150.7	159.5
152.5°	111.6	116.4	128.2	145.8	153.6
155°	114.5	118.4	128.2	142.9	147.8
157.5°	117.4	121.3	128.2	139.9	143.8
160°	120.4	123.3	129.2	138.0	140.9
162.5°	123.3	125.3	129.2	136.0	138.0
165°	125.3	126.2	129.2	135.0	136.0
167.5°	127.2	128.2	129.2	134.1	134.1
170°	128.2	129.2	130.1	133.1	133.1
172.5°	130.1	130.1	130.1	132.1	132.1
175°	131.1	131.1	130.1	132.1	131.1
177.5°	131.1	131.1	130.1	132.1	131.1
180°	131.1	131.1	131.1	131.1	131.1



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	36.2	47.9	173.2	344.6	348.5
110°	41.1	52.8	159.5	341.6	370.0



(END OF REPORT)