

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845345

Luminaire Tested: **SQ4P-WB-075U-125D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845345
REPORT IS A COMBINATION OF REPORTS P700242 AND P700245
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-075U-125D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6433.4 lumens
Efficiency: N/A
Efficacy: 99.3 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 64.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845345

CATALOG NUMBER: SQ4P-WB-075U-125D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845345

CATALOG NUMBER: SQ4P-WB-075U-125D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	62																			
1	102	98	95	91	95	92	89	86	81	79	77	71	69	68	61	60	59	55																			
2	94	87	82	77	88	82	77	73	73	69	66	64	61	59	56	54	52	48																			
3	87	78	71	66	81	74	68	63	65	61	57	58	54	52	51	48	46	43																			
4	80	70	63	57	75	66	60	55	59	54	50	53	49	46	46	44	41	38																			
5	74	63	56	50	70	60	53	48	54	49	45	48	44	41	43	39	37	34																			
6	69	58	50	45	65	55	48	43	49	44	40	44	40	37	39	36	33	31																			
7	64	53	45	40	60	50	43	39	45	40	36	41	36	33	36	33	30	28																			
8	60	48	41	36	56	46	39	35	42	36	32	38	33	30	34	30	28	26																			
9	56	45	38	33	53	43	36	32	39	33	30	35	31	28	32	28	25	24																			
10	53	41	34	30	50	39	33	29	36	31	27	33	28	25	30	26	24	22																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25149	25149	25149
5°	24836	24746	24891
10°	23463	23677	24225
15°	21659	22165	23157
20°	19670	20409	21759
25°	17643	18606	20273
30°	15776	16805	18730
35°	13794	14791	16907
40°	11609	12532	14636
45°	9581	10407	12221
50°	7998	8721	10179
55°	6791	7483	8406
60°	5805	6490	6709
65°	4624	5456	4333
70°	4098	4257	2646
75°	3793	3458	1622
80°	3496	3177	1392
85°	3144	2922	1154



TEST NUMBER: P845345

CATALOG NUMBER: SQ4P-WB-075U-125D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.0	3.9
10°-20°	650.3	10.1
20°-30°	842.3	13.1
30°-40°	824.9	12.8
40°-50°	631.4	9.8
50°-60°	420.7	6.5
60°-70°	229.6	3.6
70°-80°	95.7	1.5
80°-90°	28.0	0.4
90°-100°	150.9	2.3
100°-110°	525.0	8.2
110°-120°	508.6	7.9
120°-130°	398.9	6.2
130°-140°	315.7	4.9
140°-150°	243.7	3.8
150°-160°	174.7	2.7
160°-170°	106.8	1.7
170°-180°	36.1	0.6
0°-30°	1742.7	27.1
0°-40°	2567.5	39.9
0°-60°	3619.6	56.3
0°-90°	3972.9	61.8
90°-120°	1184.4	18.4
90°-150°	2142.8	33.3
90°-180°	2460.0	38.2
0°-180°	6433.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2726	2726	2726	2726	2726	
5°	2682	2655	2672	2678	2688	249
15°	2268	2260	2320	2384	2424	633
25°	1733	1738	1828	1907	1992	797
35°	1225	1231	1313	1402	1501	761
45°	734	748	798	858	937	573
55°	422	440	465	483	523	383
65°	212	229	250	218	198	220
75°	106	106	97	67	46	114
85°	30	30	28	18	11	32
90°	6	8	8	6	3	5
95°	25	88	255	65	40	27
105°	88	124	552	931	866	92
115°	153	184	410	866	1021	151
125°	207	255	382	645	770	185
135°	249	280	379	538	608	193
145°	291	311	376	464	504	182
155°	331	342	371	413	427	153
165°	362	365	373	390	393	102
175°	379	379	376	382	379	36
180°	379	379	379	379	379	



TEST NUMBER: P845345

CATALOG NUMBER: SQ4P-WB-075U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2725.8	2725.8	2725.8	2725.8	2725.8
2.5°	2732.5	2708.2	2714.4	2714.2	2706.5
5°	2681.7	2654.6	2671.9	2678.1	2687.6
7.5°	2582.0	2561.7	2593.4	2616.7	2635.6
10°	2504.5	2486.9	2527.3	2561.4	2585.8
12.5°	2414.7	2399.7	2449.8	2495.3	2527.5
15°	2267.6	2259.5	2320.5	2383.5	2424.4
17.5°	2110.6	2106.6	2176.4	2250.0	2302.3
20°	2003.4	2002.3	2078.7	2155.6	2216.2
22.5°	1895.4	1897.7	1978.2	2058.1	2127.4
25°	1733.1	1737.7	1827.7	1907.2	1991.5
27.5°	1583.1	1585.3	1677.9	1762.1	1852.0
30°	1480.8	1486.5	1577.4	1664.6	1758.1
32.5°	1378.4	1385.3	1474.3	1564.2	1659.6
35°	1224.7	1230.6	1313.2	1401.7	1501.1
37.5°	1066.2	1074.4	1147.8	1231.1	1329.2
40°	963.9	975.8	1040.5	1119.4	1215.2
42.5°	865.3	880.0	940.1	1014.8	1101.2
45°	734.3	748.4	797.6	858.0	936.6
47.5°	621.4	637.6	675.6	727.6	794.4
50°	557.2	572.7	607.6	646.0	709.2
52.5°	500.9	516.1	547.2	577.0	630.9
55°	422.2	439.8	465.2	483.0	522.6
57.5°	357.7	374.5	394.8	402.6	426.8
60°	314.6	333.3	351.7	350.6	363.6
62.5°	275.4	291.3	309.5	296.8	297.6
65°	211.8	229.4	249.9	218.5	198.5
67.5°	171.2	174.7	196.0	152.5	128.6
70°	151.9	151.9	157.8	118.0	98.1
72.5°	133.8	133.8	128.4	95.8	75.0
75°	106.4	106.4	97.0	66.6	45.5
77.5°	82.0	81.2	74.2	49.5	33.1
80°	65.8	65.8	59.8	39.2	26.2
82.5°	51.5	51.5	46.3	30.6	19.5
85°	29.7	29.7	27.6	17.9	10.9
87.5°	10.6	10.6	9.5	5.7	4.9
90°	5.7	8.5	8.5	5.7	2.8
92.5°	14.2	42.5	39.6	16.9	14.2
95°	25.4	87.7	254.6	65.1	39.6
97.5°	39.6	99.0	509.2	232.0	124.5
100°	53.7	104.7	594.1	557.4	359.3
102.5°	70.8	113.1	591.3	783.7	645.1
105°	87.7	124.5	551.7	930.8	865.7



TEST NUMBER: P845345

CATALOG NUMBER: SQ4P-WB-075U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	135.8	166.9	430.1	936.5	1066.6
115°	152.8	183.9	410.2	865.7	1021.3
117.5°	169.8	203.7	399.0	800.7	956.3
120°	183.9	220.7	390.4	738.4	891.2
122.5°	195.2	237.7	384.8	687.5	826.1
125°	206.6	254.6	381.9	645.1	769.5
127.5°	217.8	266.0	381.9	614.0	718.7
130°	229.2	271.6	379.1	582.8	676.2
132.5°	240.4	274.4	379.1	560.2	639.4
135°	248.9	280.1	379.1	537.5	608.3
137.5°	260.3	285.7	379.1	517.8	582.8
140°	268.8	294.3	379.1	497.9	554.6
142.5°	280.1	302.8	379.1	478.1	529.0
145°	291.4	311.2	376.3	464.0	503.6
147.5°	302.8	319.7	373.4	449.8	481.0
150°	311.2	328.2	373.4	435.7	461.2
152.5°	322.5	336.6	370.6	421.6	444.2
155°	331.0	342.3	370.6	413.1	427.2
157.5°	339.5	350.8	370.6	404.5	415.9
160°	348.0	356.5	373.4	399.0	407.4
162.5°	356.5	362.2	373.4	393.3	399.0
165°	362.2	365.0	373.4	390.4	393.3
167.5°	367.8	370.6	373.4	387.6	387.6
170°	370.6	373.4	376.3	384.8	384.8
172.5°	376.3	376.3	376.3	381.9	381.9
175°	379.1	379.1	376.3	381.9	379.1
177.5°	379.1	379.1	376.3	381.9	379.1
180°	379.1	379.1	379.1	379.1	379.1



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	104.7	138.7	500.7	995.9	1007.2
110°	118.8	152.8	461.2	987.4	1069.5



(END OF REPORT)