

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845321

Luminaire Tested: **SQ4P-WB-025U-125D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845321
REPORT IS A COMBINATION OF REPORTS P700186 AND P700243
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-025U-125D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4823.4 lumens
Efficiency: N/A
Efficacy: 91.4 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845321

CATALOG NUMBER: SQ4P-WB-025U-125D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845321

CATALOG NUMBER: SQ4P-WB-025U-125D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	115	115	115	115	110	110	110	110	101	101	101	93	93	93	86	86	86	86	86	86	82
1	107	103	100	97	102	99	96	93	92	89	87	85	83	82	79	77	76	76	76	76	73
2	99	92	87	82	95	89	84	80	83	79	76	77	74	71	72	69	67	67	67	67	64
3	92	83	76	71	88	80	74	69	75	70	66	70	66	63	65	62	60	60	60	60	57
4	85	75	68	62	82	73	66	61	68	63	58	64	59	56	60	56	53	53	53	53	51
5	79	68	61	55	76	66	59	54	62	56	52	59	54	50	55	51	48	48	48	48	46
6	74	62	55	49	71	61	53	48	57	51	47	54	49	45	51	47	43	43	43	43	41
7	69	57	50	44	66	56	49	44	53	47	42	50	45	41	47	43	39	39	39	39	37
8	65	53	45	40	62	51	44	40	49	43	38	46	41	37	44	39	36	36	36	36	34
9	61	49	42	37	58	48	41	36	45	39	35	43	38	34	41	36	33	33	33	33	31
10	57	45	38	34	55	44	38	33	42	36	32	40	35	32	38	34	31	31	31	31	29

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25149	25149	25149
5°	24836	24746	24891
10°	23463	23677	24225
15°	21659	22165	23157
20°	19670	20409	21759
25°	17643	18606	20273
30°	15776	16805	18730
35°	13794	14791	16907
40°	11609	12532	14636
45°	9581	10407	12221
50°	7998	8721	10179
55°	6791	7483	8406
60°	5805	6490	6709
65°	4624	5456	4333
70°	4098	4257	2646
75°	3793	3458	1622
80°	3496	3177	1392
85°	3144	2922	1154



TEST NUMBER: P845321

CATALOG NUMBER: SQ4P-WB-025U-125D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.0	5.2
10°-20°	650.3	13.5
20°-30°	842.3	17.5
30°-40°	824.9	17.1
40°-50°	631.4	13.1
50°-60°	420.7	8.7
60°-70°	229.6	4.8
70°-80°	95.7	2.0
80°-90°	27.4	0.6
90°-100°	52.2	1.1
100°-110°	181.6	3.8
110°-120°	175.9	3.6
120°-130°	138.0	2.9
130°-140°	109.2	2.3
140°-150°	84.3	1.7
150°-160°	60.4	1.3
160°-170°	37.0	0.8
170°-180°	12.5	0.3
0°-30°	1742.7	36.1
0°-40°	2567.5	53.2
0°-60°	3619.6	75.0
0°-90°	3972.3	82.4
90°-120°	409.7	8.5
90°-150°	741.2	15.4
90°-180°	851.0	17.6
0°-180°	4823.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2726	2726	2726	2726	2726	
5°	2682	2655	2672	2678	2688	249
15°	2268	2260	2320	2384	2424	633
25°	1733	1738	1828	1907	1992	797
35°	1225	1231	1313	1402	1501	761
45°	734	748	798	858	937	573
55°	422	440	465	483	523	383
65°	212	229	250	218	198	220
75°	106	106	97	67	46	114
85°	30	30	28	18	11	32
90°	2	3	3	2	1	3
95°	9	30	88	22	14	9
105°	30	43	191	322	300	32
115°	53	64	142	300	353	52
125°	71	88	132	223	266	64
135°	86	97	131	186	210	67
145°	101	108	130	160	174	63
155°	114	118	128	143	148	53
165°	125	126	129	135	136	35
175°	131	131	130	132	131	12
180°	131	131	131	131	131	



TEST NUMBER: P845321

CATALOG NUMBER: SQ4P-WB-025U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2725.8	2725.8	2725.8	2725.8	2725.8
2.5°	2732.5	2708.2	2714.4	2714.2	2706.5
5°	2681.7	2654.6	2671.9	2678.1	2687.6
7.5°	2582.0	2561.7	2593.4	2616.7	2635.6
10°	2504.5	2486.9	2527.3	2561.4	2585.8
12.5°	2414.7	2399.7	2449.8	2495.3	2527.5
15°	2267.6	2259.5	2320.5	2383.5	2424.4
17.5°	2110.6	2106.6	2176.4	2250.0	2302.3
20°	2003.4	2002.3	2078.7	2155.6	2216.2
22.5°	1895.4	1897.7	1978.2	2058.1	2127.4
25°	1733.1	1737.7	1827.7	1907.2	1991.5
27.5°	1583.1	1585.3	1677.9	1762.1	1852.0
30°	1480.8	1486.5	1577.4	1664.6	1758.1
32.5°	1378.4	1385.3	1474.3	1564.2	1659.6
35°	1224.7	1230.6	1313.2	1401.7	1501.1
37.5°	1066.2	1074.4	1147.8	1231.1	1329.2
40°	963.9	975.8	1040.5	1119.4	1215.2
42.5°	865.3	880.0	940.1	1014.8	1101.2
45°	734.3	748.4	797.6	858.0	936.6
47.5°	621.4	637.6	675.6	727.6	794.4
50°	557.2	572.7	607.6	646.0	709.2
52.5°	500.9	516.1	547.2	577.0	630.9
55°	422.2	439.8	465.2	483.0	522.6
57.5°	357.7	374.5	394.8	402.6	426.8
60°	314.6	333.3	351.7	350.6	363.6
62.5°	275.4	291.3	309.5	296.8	297.6
65°	211.8	229.4	249.9	218.5	198.5
67.5°	171.2	174.7	196.0	152.5	128.6
70°	151.9	151.9	157.8	118.0	98.1
72.5°	133.8	133.8	128.4	95.8	75.0
75°	106.4	106.4	97.0	66.6	45.5
77.5°	82.0	81.2	74.2	49.5	33.1
80°	65.8	65.8	59.8	39.2	26.2
82.5°	51.5	51.5	46.3	30.6	19.5
85°	29.7	29.7	27.6	17.9	10.9
87.5°	10.6	10.6	9.5	5.7	4.9
90°	2.0	2.9	2.9	2.0	1.0
92.5°	4.9	14.7	13.7	5.9	4.9
95°	8.8	30.3	88.1	22.5	13.7
97.5°	13.7	34.2	176.1	80.2	43.1
100°	18.6	36.2	205.5	192.8	124.3
102.5°	24.5	39.1	204.5	271.1	223.1
105°	30.3	43.1	190.8	322.0	299.5



TEST NUMBER: P845321

CATALOG NUMBER: SQ4P-WB-025U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	47.0	57.7	148.7	324.0	369.0
115°	52.8	63.6	141.9	299.5	353.4
117.5°	58.7	70.5	138.0	276.9	330.9
120°	63.6	76.3	135.0	255.4	308.3
122.5°	67.5	82.2	133.1	237.8	285.8
125°	71.4	88.1	132.1	223.1	266.2
127.5°	75.3	92.0	132.1	212.3	248.6
130°	79.3	93.9	131.1	201.6	233.9
132.5°	83.2	94.9	131.1	193.8	221.2
135°	86.1	96.9	131.1	185.9	210.4
137.5°	90.0	98.8	131.1	179.1	201.6
140°	93.0	101.8	131.1	172.2	191.8
142.5°	96.9	104.7	131.1	165.4	183.0
145°	100.8	107.6	130.1	160.5	174.2
147.5°	104.7	110.6	129.2	155.6	166.4
150°	107.6	113.5	129.2	150.7	159.5
152.5°	111.6	116.4	128.2	145.8	153.6
155°	114.5	118.4	128.2	142.9	147.8
157.5°	117.4	121.3	128.2	139.9	143.8
160°	120.4	123.3	129.2	138.0	140.9
162.5°	123.3	125.3	129.2	136.0	138.0
165°	125.3	126.2	129.2	135.0	136.0
167.5°	127.2	128.2	129.2	134.1	134.1
170°	128.2	129.2	130.1	133.1	133.1
172.5°	130.1	130.1	130.1	132.1	132.1
175°	131.1	131.1	130.1	132.1	131.1
177.5°	131.1	131.1	130.1	132.1	131.1
180°	131.1	131.1	131.1	131.1	131.1



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	36.2	47.9	173.2	344.6	348.5
110°	41.1	52.8	159.5	341.6	370.0



(END OF REPORT)