

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845357

Luminaire Tested: **SQ4P-WB-0U-125D-B35-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845357
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P519276)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-0U-125D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3972.0 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 45.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845357

CATALOG NUMBER: SQ4P-WB-0U-125D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845357

CATALOG NUMBER: SQ4P-WB-0U-125D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78																			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62																			
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55																			
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45																			
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41																			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	25149	25149	25149
5°	24836	24746	24891
10°	23463	23677	24225
15°	21659	22165	23157
20°	19670	20409	21759
25°	17643	18606	20273
30°	15776	16805	18730
35°	13794	14791	16907
40°	11609	12532	14636
45°	9581	10407	12221
50°	7998	8721	10179
55°	6791	7483	8406
60°	5805	6490	6709
65°	4624	5456	4333
70°	4098	4257	2646
75°	3793	3458	1622
80°	3496	3177	1392
85°	3144	2922	1154



TEST NUMBER: P845357

CATALOG NUMBER: SQ4P-WB-0U-125D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	250.0	6.3
10°-20°	650.3	16.4
20°-30°	842.3	21.2
30°-40°	824.9	20.8
40°-50°	631.4	15.9
50°-60°	420.7	10.6
60°-70°	229.6	5.8
70°-80°	95.7	2.4
80°-90°	27.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1742.7	43.9
0°-40°	2567.5	64.6
0°-60°	3619.6	91.1
0°-90°	3972.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3972.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2726	2726	2726	2726	2726	
5°	2682	2655	2672	2678	2688	249
15°	2268	2260	2320	2384	2424	633
25°	1733	1738	1828	1907	1992	797
35°	1225	1231	1313	1402	1501	761
45°	734	748	798	858	937	573
55°	422	440	465	483	523	383
65°	212	229	250	218	198	220
75°	106	106	97	67	46	114
85°	30	30	28	18	11	34
90°	0	0	0	0	0	



TEST NUMBER: P845357

CATALOG NUMBER: SQ4P-WB-0U-125D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2725.8	2725.8	2725.8	2725.8	2725.8
2.5°	2732.5	2708.2	2714.4	2714.2	2706.5
5°	2681.7	2654.6	2671.9	2678.1	2687.6
7.5°	2582.0	2561.7	2593.4	2616.7	2635.6
10°	2504.5	2486.9	2527.3	2561.4	2585.8
12.5°	2414.7	2399.7	2449.8	2495.3	2527.5
15°	2267.6	2259.5	2320.5	2383.5	2424.4
17.5°	2110.6	2106.6	2176.4	2250.0	2302.3
20°	2003.4	2002.3	2078.7	2155.6	2216.2
22.5°	1895.4	1897.7	1978.2	2058.1	2127.4
25°	1733.1	1737.7	1827.7	1907.2	1991.5
27.5°	1583.1	1585.3	1677.9	1762.1	1852.0
30°	1480.8	1486.5	1577.4	1664.6	1758.1
32.5°	1378.4	1385.3	1474.3	1564.2	1659.6
35°	1224.7	1230.6	1313.2	1401.7	1501.1
37.5°	1066.2	1074.4	1147.8	1231.1	1329.2
40°	963.9	975.8	1040.5	1119.4	1215.2
42.5°	865.3	880.0	940.1	1014.8	1101.2
45°	734.3	748.4	797.6	858.0	936.6
47.5°	621.4	637.6	675.6	727.6	794.4
50°	557.2	572.7	607.6	646.0	709.2
52.5°	500.9	516.1	547.2	577.0	630.9
55°	422.2	439.8	465.2	483.0	522.6
57.5°	357.7	374.5	394.8	402.6	426.8
60°	314.6	333.3	351.7	350.6	363.6
62.5°	275.4	291.3	309.5	296.8	297.6
65°	211.8	229.4	249.9	218.5	198.5
67.5°	171.2	174.7	196.0	152.5	128.6
70°	151.9	151.9	157.8	118.0	98.1
72.5°	133.8	133.8	128.4	95.8	75.0
75°	106.4	106.4	97.0	66.6	45.5
77.5°	82.0	81.2	74.2	49.5	33.1
80°	65.8	65.8	59.8	39.2	26.2
82.5°	51.5	51.5	46.3	30.6	19.5
85°	29.7	29.7	27.6	17.9	10.9
87.5°	10.6	10.6	9.5	5.7	4.9
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)