

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845375

Luminaire Tested: **SQ4P-WB-125U-075D-B35-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845375
REPORT IS A COMBINATION OF REPORTS P700128 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-125U-075D-B35-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT
UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6549.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 59.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845375
CATALOG NUMBER: SQ4P-WB-125U-075D-B35-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845375

CATALOG NUMBER: SQ4P-WB-125U-075D-B35-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	37																			
1	96	92	88	85	87	83	81	78	68	66	64	53	52	51	40	40	39	33																			
2	88	81	76	71	80	74	69	65	60	57	54	48	46	44	36	35	34	29																			
3	81	72	65	60	73	66	60	56	54	50	47	43	41	38	33	31	30	26																			
4	74	64	57	52	67	59	53	48	49	44	41	39	36	34	30	28	27	23																			
5	68	58	50	45	62	53	47	42	44	39	36	36	32	30	28	26	24	20																			
6	63	52	45	39	57	48	41	37	40	35	31	32	29	26	25	23	21	18																			
7	59	47	40	35	53	44	37	32	36	32	28	30	26	24	24	21	19	17																			
8	55	43	36	31	50	40	33	29	33	29	25	27	24	21	22	19	18	15																			
9	51	40	33	28	46	37	30	26	31	26	23	25	22	19	20	18	16	14																			
10	48	36	30	25	43	34	28	24	28	24	21	24	20	18	19	17	15	13																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15304	15304	15304
5°	15114	15058	15147
10°	14279	14408	14741
15°	13180	13488	14092
20°	11970	12419	13241
25°	10737	11321	12337
30°	9600	10227	11398
35°	8394	9000	10289
40°	7065	7626	8907
45°	5830	6333	7436
50°	4867	5306	6194
55°	4132	4554	5115
60°	3534	3949	4084
65°	2814	3321	2637
70°	2495	2592	1610
75°	2310	2103	987
80°	2125	1934	850
85°	1916	1778	699



TEST NUMBER: P845375

CATALOG NUMBER: SQ4P-WB-125U-075D-B35-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	152.1	2.3
10°-20°	395.7	6.0
20°-30°	512.6	7.8
30°-40°	502.0	7.7
40°-50°	384.2	5.9
50°-60°	256.0	3.9
60°-70°	139.7	2.1
70°-80°	58.2	0.9
80°-90°	18.0	0.3
90°-100°	253.3	3.9
100°-110°	881.3	13.5
110°-120°	853.7	13.0
120°-130°	669.7	10.2
130°-140°	530.1	8.1
140°-150°	409.1	6.2
150°-160°	293.2	4.5
160°-170°	179.4	2.7
170°-180°	60.7	0.9
0°-30°	1060.5	16.2
0°-40°	1562.4	23.9
0°-60°	2202.6	33.6
0°-90°	2418.6	36.9
90°-120°	1988.3	30.4
90°-150°	3597.1	54.9
90°-180°	4130.0	63.1
0°-180°	6549.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1659	1659	1659	1659	1659	
5°	1632	1615	1626	1630	1636	152
15°	1380	1375	1412	1450	1475	385
25°	1055	1057	1112	1161	1212	485
35°	745	749	799	853	914	463
45°	447	455	485	522	570	348
55°	257	268	283	294	318	233
65°	129	140	152	133	121	134
75°	65	65	59	40	28	69
85°	18	18	17	11	7	20
90°	10	14	14	10	5	7
95°	43	147	427	109	66	45
105°	147	209	926	1563	1453	155
115°	256	309	689	1453	1714	253
125°	347	427	641	1083	1292	310
135°	418	470	636	902	1021	324
145°	489	522	632	779	845	306
155°	556	575	622	693	717	256
165°	608	613	627	655	660	171
175°	636	636	632	641	636	60
180°	636	636	636	636	636	



TEST NUMBER: P845375

CATALOG NUMBER: SQ4P-WB-125U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1658.7	1658.7	1658.7	1658.7	1658.7
2.5°	1662.8	1648.0	1651.8	1651.6	1647.0
5°	1631.9	1615.3	1625.9	1629.7	1635.5
7.5°	1571.2	1558.9	1578.1	1592.3	1603.9
10°	1524.1	1513.4	1537.9	1558.7	1573.5
12.5°	1469.4	1460.3	1490.8	1518.4	1538.1
15°	1379.9	1375.0	1412.1	1450.4	1475.3
17.5°	1284.4	1281.9	1324.4	1369.2	1401.0
20°	1219.1	1218.4	1264.9	1311.7	1348.6
22.5°	1153.3	1154.8	1203.7	1252.4	1294.5
25°	1054.7	1057.4	1112.1	1160.6	1211.9
27.5°	963.4	964.7	1021.0	1072.3	1127.0
30°	901.1	904.6	960.0	1013.0	1069.9
32.5°	838.8	842.9	897.1	951.9	1009.9
35°	745.3	748.9	799.1	853.0	913.5
37.5°	648.9	653.8	698.4	749.2	808.9
40°	586.6	593.8	633.2	681.2	739.5
42.5°	526.6	535.5	572.1	617.6	670.1
45°	446.8	455.4	485.4	522.2	569.9
47.5°	378.1	388.0	411.1	442.7	483.4
50°	339.1	348.5	369.7	393.1	431.5
52.5°	304.8	314.0	333.0	351.1	383.9
55°	256.9	267.5	283.1	294.0	318.0
57.5°	217.6	227.9	240.2	245.0	259.7
60°	191.5	202.9	214.0	213.3	221.3
62.5°	167.5	177.3	188.4	180.5	181.0
65°	128.9	139.5	152.1	133.0	120.8
67.5°	104.1	106.3	119.3	92.8	78.3
70°	92.5	92.5	96.1	71.8	59.7
72.5°	81.4	81.4	78.1	58.3	45.6
75°	64.8	64.8	59.0	40.5	27.7
77.5°	49.9	49.4	45.1	30.1	20.1
80°	40.0	40.0	36.4	23.9	16.0
82.5°	31.3	31.3	28.2	18.6	11.8
85°	18.1	18.1	16.8	10.9	6.6
87.5°	6.5	6.5	5.8	3.4	2.9
90°	9.5	14.3	14.3	9.5	4.8
92.5°	23.8	71.2	66.4	28.5	23.8
95°	42.8	147.3	427.4	109.2	66.4
97.5°	66.4	166.3	854.9	389.5	209.0
100°	90.2	175.8	997.4	935.6	603.2
102.5°	118.7	189.9	992.7	1315.6	1082.9
105°	147.3	209.0	926.1	1562.6	1453.4



TEST NUMBER: P845375

CATALOG NUMBER: SQ4P-WB-125U-075D-B35-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	228.0	280.3	721.9	1572.1	1790.6
115°	256.5	308.7	688.7	1453.4	1714.5
117.5°	285.0	342.0	669.6	1344.2	1605.3
120°	308.7	370.5	655.4	1239.6	1496.1
122.5°	327.7	399.0	646.0	1154.1	1386.8
125°	346.7	427.4	641.2	1082.9	1291.9
127.5°	365.7	446.4	641.2	1030.6	1206.4
130°	384.7	455.9	636.5	978.4	1135.1
132.5°	403.8	460.7	636.5	940.4	1073.4
135°	417.9	470.2	636.5	902.4	1021.1
137.5°	436.9	479.7	636.5	869.2	978.4
140°	451.2	494.0	636.5	835.9	930.9
142.5°	470.2	508.2	636.5	802.6	888.1
145°	489.2	522.5	631.7	778.9	845.4
147.5°	508.2	536.6	627.0	755.2	807.4
150°	522.5	550.9	627.0	731.4	774.1
152.5°	541.4	565.2	622.2	707.7	745.7
155°	555.7	574.7	622.2	693.4	717.2
157.5°	569.9	588.9	622.2	679.2	698.2
160°	584.2	598.4	627.0	669.6	683.9
162.5°	598.4	608.0	627.0	660.1	669.6
165°	608.0	612.7	627.0	655.4	660.1
167.5°	617.5	622.2	627.0	650.6	650.6
170°	622.2	627.0	631.7	646.0	646.0
172.5°	631.7	631.7	631.7	641.2	641.2
175°	636.5	636.5	631.7	641.2	636.5
177.5°	636.5	636.5	631.7	641.2	636.5
180°	636.5	636.5	636.5	636.5	636.5



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	175.8	232.7	840.7	1671.8	1690.9
110°	199.4	256.5	774.1	1657.6	1795.3



(END OF REPORT)