

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936803

Luminaire Tested: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936803
REPORT IS A COMBINATION OF REPORTS P933478 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6300.1 lumens
Efficiency: N/A
Efficacy: 115.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936803
CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	60	60	60	55
1	98	94	89	86	91	87	83	80	75	72	69	63	61	59	53	51	50	50	50	50	45
2	89	81	74	69	82	75	70	65	65	60	56	55	51	49	45	43	41	41	41	41	37
3	81	71	63	57	74	66	59	53	56	51	47	48	44	40	40	37	34	34	34	34	30
4	73	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29	29	29	29	25
5	67	55	46	40	62	51	44	38	44	38	33	37	33	29	31	28	25	25	25	25	21
6	62	49	40	34	57	46	38	32	39	33	29	33	29	25	28	24	21	21	21	21	18
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	25	22	19	19	19	19	16
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16	16	16	16	14
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	15	15	15	12
10	46	33	25	20	42	31	24	19	27	21	17	23	18	15	19	16	13	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2756	2756	2756
5°	2691	3185	3704
10°	2440	4641	6141
15°	2073	6062	7416
20°	1687	7024	7558
25°	1407	7348	7405
30°	1186	7392	7390
35°	1048	7268	7582
40°	913	7105	7780
45°	826	6987	7810
50°	757	6880	7680
55°	725	6723	7339
60°	741	6425	6802
65°	769	5973	6063
70°	818	5205	5122
75°	902	4241	3998
80°	980	2938	2694
85°	853	1557	1379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7810 cd/sqm



TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.6	0.9
10°-20°	255.4	4.1
20°-30°	446.8	7.1
30°-40°	575.1	9.1
40°-50°	642.4	10.2
50°-60°	615.2	9.8
60°-70°	487.6	7.7
70°-80°	286.7	4.6
80°-90°	81.3	1.3
90°-100°	214.4	3.4
100°-110°	563.8	8.9
110°-120°	584.6	9.3
120°-130°	468.9	7.4
130°-140°	367.9	5.8
140°-150°	282.4	4.5
150°-160°	203.4	3.2
160°-170°	124.4	2.0
170°-180°	42.0	0.7
0°-30°	759.8	12.1
0°-40°	1335.0	21.2
0°-60°	2592.6	41.2
0°-90°	3448.2	54.7
90°-120°	1362.8	21.6
90°-150°	2482.0	39.4
90°-180°	2852.0	45.3
0°-180°	6300.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	446	446	446	446	446	
5°	434	466	524	593	614	40
15°	325	600	1011	1226	1265	90
25°	208	680	1205	1258	1259	96
35°	140	650	1135	1199	1246	88
45°	96	519	1003	1149	1200	74
55°	69	330	851	988	1016	63
65°	54	175	632	710	720	54
75°	40	107	347	381	382	42
85°	14	33	86	94	96	15
90°	3	8	22	11	11	3
95°	28	111	369	190	130	31
105°	102	154	623	946	883	108
115°	180	219	499	996	1137	178
125°	251	281	454	767	905	223
135°	299	329	440	619	702	231
145°	347	369	434	528	570	217
155°	392	403	434	477	491	180
165°	423	429	434	451	457	119
175°	440	440	437	443	443	42
180°	440	440	440	440	440	



TEST NUMBER: P936803
 CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5	445.5
2.5°	445.5	445.5	448.4	449.8	452.7	454.1	457.0	459.8	468.4	469.9	472.7
5°	434.0	439.8	458.4	465.6	485.6	512.8	524.3	542.9	581.6	593.1	600.2
7.5°	416.9	429.8	475.6	487.0	537.2	608.8	638.9	679.0	740.6	770.7	795.0
10°	389.6	416.9	498.5	525.7	607.4	716.2	772.1	828.0	921.1	962.6	978.4
12.5°	359.6	404.0	522.9	560.1	677.6	836.6	903.9	965.5	1071.5	1127.5	1136.1
15°	325.2	385.3	545.8	600.2	752.1	936.9	1011.3	1087.4	1186.2	1226.3	1236.3
17.5°	295.1	371.0	567.3	624.6	809.4	1027.1	1103.1	1166.2	1246.4	1273.6	1280.8
20°	257.8	348.1	581.6	656.1	869.5	1093.1	1166.2	1214.9	1269.3	1286.5	1289.3
22.5°	230.6	323.7	590.2	667.5	909.6	1133.2	1194.8	1233.5	1270.7	1276.5	1277.9
25°	207.7	296.5	588.8	680.4	944.0	1157.6	1204.8	1233.5	1255.0	1257.8	1257.8
27.5°	186.2	266.4	583.0	683.3	969.8	1163.3	1200.5	1220.6	1230.6	1236.3	1236.3
30°	167.6	237.8	568.7	677.6	981.3	1157.6	1187.6	1197.7	1207.7	1216.3	1220.6
32.5°	153.3	210.6	547.2	666.1	982.7	1143.2	1164.7	1170.4	1184.8	1204.8	1212.0
35°	140.4	183.4	522.9	650.4	974.1	1120.3	1134.6	1140.4	1169.0	1199.1	1209.1
37.5°	127.5	163.3	491.3	623.1	961.2	1093.1	1103.1	1113.1	1157.6	1193.4	1204.8
40°	114.6	146.1	454.1	593.1	941.2	1060.0	1068.6	1084.4	1143.2	1184.8	1196.2
42.5°	104.6	131.8	414.0	561.5	915.4	1022.8	1035.7	1058.6	1126.0	1170.4	1183.3
45°	96.0	117.5	371.0	518.6	882.4	984.1	1002.8	1034.3	1106.0	1149.0	1160.4
47.5°	87.4	107.4	326.6	474.2	846.6	945.4	969.8	1005.6	1078.7	1120.3	1130.3
50°	80.2	97.4	282.2	426.9	807.9	903.9	932.6	969.8	1044.3	1083.0	1096.0
52.5°	74.5	88.8	240.7	379.6	763.5	860.9	893.9	932.6	1002.8	1040.0	1048.6
55°	68.8	81.7	204.8	329.5	717.7	815.1	850.9	888.2	956.9	988.4	994.2
57.5°	65.9	75.9	174.8	282.2	669.0	763.5	803.6	838.0	902.5	926.8	932.6
60°	61.6	71.6	151.8	242.1	616.0	714.8	749.2	783.6	838.0	858.1	862.4
62.5°	57.3	68.8	134.7	203.4	561.5	657.5	691.9	723.4	769.3	783.6	789.3
65°	54.4	65.9	121.8	174.8	505.7	597.4	631.7	658.9	696.2	710.5	713.4
67.5°	51.6	63.0	111.7	150.4	449.8	537.2	563.0	588.8	617.4	631.7	633.2
70°	47.3	60.2	103.1	133.2	392.5	468.4	489.9	517.1	540.1	547.2	551.5
72.5°	44.4	55.9	97.4	120.3	333.8	402.5	422.6	438.3	458.4	465.6	465.6
75°	40.1	50.1	91.7	107.4	273.6	329.5	346.7	362.4	378.2	381.0	376.7
77.5°	35.8	44.4	78.8	90.2	213.4	260.7	275.0	283.6	296.5	299.4	300.8
80°	30.1	38.7	61.6	70.2	154.7	192.0	202.0	209.1	220.6	220.6	223.5
82.5°	22.9	30.1	44.4	50.1	104.6	131.8	140.4	144.7	151.8	151.8	151.8
85°	14.3	18.6	28.6	32.9	63.0	80.2	86.0	87.4	93.1	94.5	94.5
87.5°	7.2	10.0	18.6	20.1	32.9	41.5	41.5	44.4	44.4	43.0	41.5
90°	3.0	5.3	7.7	8.3	13.0	19.3	22.4	20.0	14.9	11.2	11.2
92.5°	11.8	31.9	52.0	57.0	80.1	111.0	126.3	110.7	79.5	56.1	53.9
95°	28.4	65.0	101.8	111.0	197.1	312.0	369.4	329.7	250.1	190.4	183.6
97.5°	49.0	81.5	113.8	122.0	265.6	457.1	552.8	527.6	477.3	439.6	426.7
100°	64.9	94.4	123.8	131.1	290.4	502.9	609.1	610.9	614.6	617.4	602.1
102.5°	78.5	106.0	133.4	140.3	301.9	517.3	625.0	657.0	721.1	769.2	756.1
105°	101.6	124.8	148.0	153.9	310.3	518.9	623.2	695.0	838.6	946.3	939.2
107.5°	125.2	146.9	168.5	173.9	311.9	495.8	587.8	687.9	888.2	1038.4	1040.1
110°	141.1	160.6	180.2	185.1	309.5	475.4	558.3	670.2	894.2	1062.1	1069.4



TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	156.8	175.4	194.1	198.7	309.6	457.5	531.5	646.1	875.2	1047.0	1058.2
115°	180.4	197.6	214.8	219.1	312.5	437.0	499.3	609.7	830.4	995.9	1011.5
117.5°	203.7	219.4	234.9	238.8	318.3	424.2	477.1	576.7	775.9	925.3	942.7
120°	217.3	232.0	246.7	250.4	323.0	419.8	468.2	559.2	741.3	877.7	894.6
122.5°	230.6	245.4	260.2	264.0	329.8	417.5	461.5	543.4	707.4	830.3	846.9
125°	251.0	264.4	278.0	281.3	338.9	415.7	454.1	523.7	663.0	767.3	782.6
127.5°	267.5	281.2	294.8	298.2	348.1	414.7	447.9	507.7	627.1	716.8	729.7
130°	276.4	291.1	305.8	309.4	354.8	415.2	445.5	498.7	605.2	685.0	697.0
132.5°	285.5	300.3	315.0	318.6	360.2	415.7	443.5	491.2	586.4	657.8	668.5
135°	299.1	312.5	325.8	329.2	366.1	415.3	440.0	479.9	559.6	619.4	628.7
137.5°	313.0	326.2	339.4	342.7	374.9	417.8	439.3	473.0	540.4	591.0	598.6
140°	324.5	336.7	348.9	351.9	380.4	418.3	437.3	466.4	524.7	568.3	575.4
142.5°	333.3	344.6	355.8	358.7	384.9	419.8	437.3	462.9	514.0	552.4	558.5
145°	347.0	356.8	366.6	369.1	390.9	419.8	434.3	455.2	497.1	528.5	533.1
147.5°	360.5	370.1	379.7	382.1	399.5	422.7	434.3	450.8	483.7	508.4	512.3
150°	369.4	378.1	386.7	388.9	404.1	424.2	434.3	448.3	476.1	496.9	499.9
152.5°	378.5	385.1	391.6	393.3	406.9	425.2	434.3	446.2	470.0	487.7	490.0
155°	392.1	397.0	401.8	403.0	413.4	427.4	434.3	443.8	462.7	476.8	478.4
157.5°	402.2	406.8	411.6	412.8	419.9	429.6	434.3	441.7	456.4	467.4	468.4
160°	408.9	412.6	416.2	417.1	422.9	430.5	434.3	440.6	453.2	462.7	463.3
162.5°	415.7	418.5	421.3	421.9	426.0	431.6	434.3	439.7	450.3	458.2	458.8
165°	423.1	425.5	428.0	428.7	430.6	433.1	434.3	438.2	445.7	451.4	452.1
167.5°	429.8	431.0	432.2	432.5	434.1	436.2	437.3	439.8	444.7	448.5	448.8
170°	434.3	435.5	436.7	437.0	437.1	437.2	437.3	439.8	444.7	448.5	448.5
172.5°	436.7	437.0	437.2	437.3	437.3	437.3	437.3	439.2	443.1	446.1	445.9
175°	440.0	440.0	440.0	440.0	439.1	437.9	437.3	438.5	441.0	442.8	442.8
177.5°	440.0	440.0	440.0	440.0	439.3	438.3	437.9	438.8	440.8	442.3	442.0
180°	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0	440.0



TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	445.5	445.5
2.5°	475.6	472.7
5°	611.7	614.5
7.5°	823.7	822.3
10°	1024.2	1037.1
12.5°	1170.4	1173.3
15°	1259.3	1265.0
17.5°	1293.6	1295.1
20°	1295.1	1292.2
22.5°	1279.3	1276.5
25°	1260.7	1259.3
27.5°	1243.5	1244.9
30°	1236.3	1240.6
32.5°	1236.3	1243.5
35°	1239.2	1246.4
37.5°	1237.8	1246.4
40°	1232.0	1242.1
42.5°	1216.3	1223.5
45°	1191.9	1200.5
47.5°	1160.4	1166.2
50°	1120.3	1126.0
52.5°	1070.1	1071.5
55°	1009.9	1015.6
57.5°	945.4	946.9
60°	873.8	878.1
62.5°	797.9	797.9
65°	717.7	720.5
67.5°	634.6	641.8
70°	550.1	551.5
72.5°	467.0	467.0
75°	381.0	382.5
77.5°	299.4	299.4
80°	222.0	223.5
82.5°	153.3	156.1
85°	96.0	96.0
87.5°	44.4	40.1
90°	11.2	11.2
92.5°	44.9	36.0
95°	156.6	129.6
97.5°	375.3	323.9
100°	540.8	479.5
102.5°	703.5	651.0
105°	911.1	882.8
107.5°	1046.9	1053.7
110°	1098.7	1128.1



TEST NUMBER: P936803

CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1103.4	1148.5
115°	1074.1	1136.7
117.5°	1012.1	1081.5
120°	962.1	1029.6
122.5°	913.5	979.9
125°	843.9	905.2
127.5°	781.5	833.2
130°	744.7	792.5
132.5°	711.3	754.1
135°	665.5	702.4
137.5°	628.9	659.0
140°	603.6	631.8
142.5°	582.7	607.0
145°	551.5	569.8
147.5°	527.4	542.6
150°	512.4	524.7
152.5°	499.4	508.7
155°	484.6	490.7
157.5°	472.8	477.1
160°	465.8	468.2
162.5°	461.2	463.6
165°	454.6	457.1
167.5°	449.8	450.9
170°	448.5	448.5
172.5°	444.9	444.1
175°	442.8	442.8
177.5°	441.0	440.0
180°	440.0	440.0



TEST NUMBER: P936803
 CATALOG NUMBER: SQ4-FB-050U-075D-B40-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.94	5.89	5.85	6.83	8.02	18.11	19.06	19.02	19.99	21.19
	3H	5.66	6.51	6.57	7.45	8.67	19.95	20.80	20.87	21.74	22.97
	4H	5.96	6.77	6.89	7.71	8.94	20.60	21.40	21.53	22.35	23.58
	6H	6.21	6.96	7.16	7.91	9.16	21.03	21.77	21.97	22.72	23.97
	8H	6.28	7.00	7.24	7.97	9.21	21.15	21.86	22.10	22.83	24.07
	12H	6.30	6.98	7.26	7.95	9.22	21.22	21.89	22.17	22.86	24.13
4H	2H	12.16	12.97	13.10	13.92	15.15	18.39	19.20	19.33	20.15	21.38
	3H	13.74	14.41	14.69	15.39	16.64	20.44	21.12	21.39	22.10	23.34
	4H	13.84	14.46	14.80	15.43	16.70	21.21	21.83	22.17	22.80	24.07
	6H	13.85	14.39	14.82	15.38	16.65	21.75	22.29	22.72	23.28	24.55
	8H	13.83	14.33	14.81	15.32	16.60	21.91	22.41	22.89	23.40	24.69
	12H	13.79	14.25	14.79	15.25	16.54	22.01	22.46	23.00	23.46	24.75
8H	4H	15.29	15.79	16.26	16.77	18.06	21.28	21.78	22.25	22.77	24.05
	6H	15.53	15.95	16.53	16.98	18.26	21.91	22.32	22.91	23.35	24.63
	8H	15.55	15.92	16.56	16.93	18.24	22.13	22.49	23.14	23.51	24.81
	12H	15.52	15.85	16.54	16.86	18.20	22.27	22.59	23.29	23.61	24.95
12H	4H	15.43	15.88	16.43	16.89	18.18	21.24	21.69	22.23	22.69	23.98
	6H	15.79	16.16	16.80	17.17	18.48	21.89	22.26	22.90	23.28	24.58
	8H	15.86	16.19	16.88	17.20	18.54	22.12	22.45	23.14	23.46	24.80