

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936904

Luminaire Tested: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936904
REPORT IS A COMBINATION OF REPORTS P933487 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9876.6 lumens
Efficiency: N/A
Efficacy: 109.3 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 90.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936904
CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

Luminous Intensity Polar Plot





TEST NUMBER: P936904

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62
1	100	95	91	87	93	89	85	82	78	75	72	67	65	63	58	56	55	55	55	55	50
2	90	82	75	70	84	77	71	66	67	63	59	58	55	52	50	48	45	45	45	45	41
3	82	72	64	57	76	67	60	54	59	53	49	51	47	43	44	40	38	38	38	38	34
4	74	63	54	48	69	59	51	45	52	46	41	45	40	36	39	35	32	32	32	32	28
5	68	56	47	41	63	52	44	39	46	40	35	40	35	31	34	30	27	27	27	27	24
6	63	50	41	35	58	47	39	33	41	35	30	36	31	27	31	27	23	23	23	23	21
7	58	45	36	30	54	42	34	29	37	31	26	32	27	23	28	24	21	21	21	21	18
8	53	40	32	26	50	38	30	25	34	27	23	29	24	20	25	21	18	18	18	18	16
9	50	37	29	23	46	35	27	22	31	24	20	27	22	18	23	19	16	16	16	16	14
10	46	33	26	21	43	32	25	20	28	22	18	25	20	16	21	17	14	14	14	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3642	3642	3642
5°	3558	4209	4895
10°	3227	6135	8115
15°	2743	8015	9799
20°	2233	9289	9986
25°	1863	9720	9783
30°	1571	9782	9765
35°	1389	9619	10017
40°	1210	9408	10278
45°	1096	9254	10319
50°	1005	9115	10147
55°	962	8911	9698
60°	985	8519	8988
65°	1025	7925	8012
70°	1092	6911	6768
75°	1211	5634	5282
80°	1322	3907	3559
85°	1174	2074	1822

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 10319 cd/sqm



TEST NUMBER: P936904

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	1.0
10°-20°	450.0	4.6
20°-30°	787.1	8.0
30°-40°	1013.2	10.3
40°-50°	1131.7	11.5
50°-60°	1083.9	11.0
60°-70°	859.0	8.7
70°-80°	505.1	5.1
80°-90°	142.6	1.4
90°-100°	285.9	2.9
100°-110°	751.7	7.6
110°-120°	779.4	7.9
120°-130°	625.2	6.3
130°-140°	490.6	5.0
140°-150°	376.5	3.8
150°-160°	271.2	2.7
160°-170°	165.9	1.7
170°-180°	56.1	0.6
0°-30°	1338.6	13.6
0°-40°	2351.8	23.8
0°-60°	4567.4	46.2
0°-90°	6074.1	61.5
90°-120°	1817.1	18.4
90°-150°	3309.4	33.5
90°-180°	3802.0	38.5
0°-180°	9876.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	785	785	785	785	785	
5°	765	820	924	1045	1083	71
15°	573	1058	1782	2160	2228	159
25°	366	1199	2122	2216	2218	169
35°	247	1146	1999	2112	2196	154
45°	169	914	1767	2024	2115	131
55°	121	580	1499	1741	1789	110
65°	96	308	1113	1252	1270	95
75°	71	189	611	671	674	74
85°	25	58	152	167	169	27
90°	4	11	30	15	15	5
95°	38	148	492	254	173	42
105°	135	205	831	1262	1177	144
115°	241	292	666	1328	1516	238
125°	335	375	606	1023	1207	297
135°	399	439	587	826	937	309
145°	463	492	579	705	760	290
155°	523	537	579	636	654	240
165°	564	572	579	602	609	159
175°	587	587	583	590	590	56
180°	587	587	587	587	587	



TEST NUMBER: P936904

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9	784.9
2.5°	784.9	784.9	790.0	792.5	797.5	800.0	805.1	810.1	825.3	827.8	832.9
5°	764.7	774.8	807.6	820.2	855.6	903.5	923.7	956.5	1024.6	1044.9	1057.5
7.5°	734.4	757.1	837.9	858.1	946.4	1072.6	1125.6	1196.2	1304.8	1357.8	1400.7
10°	686.5	734.4	878.3	926.3	1070.1	1261.8	1360.3	1458.8	1622.7	1696.0	1723.7
12.5°	633.5	711.7	921.2	986.8	1193.8	1473.9	1592.5	1701.0	1887.7	1986.2	2001.3
15°	572.9	678.9	961.6	1057.5	1325.0	1650.5	1781.7	1915.5	2089.6	2160.3	2178.0
17.5°	519.9	653.7	999.4	1100.4	1425.9	1809.5	1943.3	2054.3	2195.6	2243.6	2256.3
20°	454.3	613.3	1024.6	1155.8	1531.9	1925.7	2054.3	2140.2	2236.0	2266.3	2271.4
22.5°	406.4	570.3	1039.8	1176.1	1602.6	1996.3	2104.8	2172.9	2238.6	2248.6	2251.2
25°	366.0	522.4	1037.2	1198.8	1663.1	2039.2	2122.5	2172.9	2210.8	2215.9	2215.9
27.5°	328.0	469.4	1027.2	1203.9	1708.6	2049.3	2114.9	2150.3	2167.9	2178.0	2178.0
30°	295.3	419.0	1001.9	1193.8	1728.7	2039.2	2092.2	2109.9	2127.5	2142.6	2150.3
32.5°	270.1	371.0	964.1	1173.5	1731.3	2014.0	2051.8	2061.9	2087.2	2122.5	2135.1
35°	247.3	323.1	921.2	1145.8	1716.1	1973.6	1998.8	2008.9	2059.4	2112.4	2130.0
37.5°	224.6	287.7	865.6	1097.9	1693.4	1925.7	1943.3	1961.0	2039.2	2102.2	2122.5
40°	201.9	257.5	800.0	1044.9	1658.1	1867.6	1882.7	1910.5	2014.0	2087.2	2107.3
42.5°	184.2	232.2	729.3	989.3	1612.7	1802.0	1824.7	1865.0	1983.6	2061.9	2084.7
45°	169.1	206.9	653.7	913.6	1554.6	1733.8	1766.7	1822.1	1948.3	2024.0	2044.3
47.5°	153.9	189.3	575.4	835.3	1491.5	1665.7	1708.6	1771.7	1900.4	1973.6	1991.3
50°	141.3	171.6	497.2	752.1	1423.4	1592.5	1643.0	1708.6	1839.8	1908.0	1930.6
52.5°	131.2	156.4	424.0	668.8	1345.1	1516.7	1574.8	1643.0	1766.7	1832.3	1847.4
55°	121.1	143.8	360.9	580.4	1264.4	1436.0	1499.1	1564.8	1685.9	1741.3	1751.5
57.5°	116.1	133.8	307.9	497.2	1178.6	1345.1	1415.8	1476.4	1590.0	1632.9	1643.0
60°	108.5	126.2	267.5	426.5	1085.3	1259.4	1319.9	1380.5	1476.4	1511.8	1519.3
62.5°	100.9	121.1	237.2	358.4	989.3	1158.4	1219.0	1274.5	1355.2	1380.5	1390.6
65°	95.9	116.1	214.5	307.9	890.9	1052.4	1113.0	1160.9	1226.5	1251.8	1256.9
67.5°	90.8	111.1	196.8	265.0	792.5	946.4	991.9	1037.2	1087.7	1113.0	1115.5
70°	83.3	106.0	181.7	234.7	691.5	825.3	863.1	911.1	951.5	964.1	971.6
72.5°	78.2	98.5	171.6	212.0	588.0	709.2	744.5	772.3	807.6	820.2	820.2
75°	70.7	88.3	161.5	189.3	482.1	580.4	610.7	638.5	666.3	671.4	663.7
77.5°	63.1	78.2	138.8	159.0	376.1	459.4	484.6	499.7	522.4	527.4	530.0
80°	53.0	68.2	108.5	123.7	272.6	338.2	355.8	368.4	388.7	388.7	393.7
82.5°	40.4	53.0	78.2	88.3	184.2	232.2	247.3	254.9	267.5	267.5	267.5
85°	25.2	32.9	50.5	58.1	111.1	141.3	151.5	153.9	164.1	166.6	166.6
87.5°	12.6	17.7	32.9	35.3	58.1	73.2	73.2	78.2	78.2	75.7	73.2
90°	3.9	7.1	10.2	11.0	17.3	25.7	29.9	26.5	20.0	15.0	15.0
92.5°	15.8	42.5	69.3	76.0	106.9	147.9	168.5	147.6	106.0	74.8	71.8
95°	37.8	86.8	135.8	148.0	262.8	415.9	492.5	439.5	333.5	253.9	245.0
97.5°	65.3	108.5	151.7	162.5	354.0	609.3	737.0	703.5	636.4	586.2	569.0
100°	86.6	125.8	164.9	174.8	387.3	670.5	812.1	814.6	819.5	823.1	802.7
102.5°	104.8	141.3	177.8	187.0	402.4	689.8	833.4	876.1	961.5	1025.5	1008.0
105°	135.4	166.4	197.4	205.1	413.8	692.0	831.0	926.7	1118.2	1261.7	1252.3
107.5°	166.9	195.8	224.6	231.9	415.8	661.1	783.8	917.3	1184.3	1384.6	1386.9
110°	188.1	214.2	240.4	246.9	412.8	633.8	744.4	893.7	1192.1	1416.0	1425.8



TEST NUMBER: P936904

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	209.0	233.9	258.7	264.9	412.8	610.1	708.6	861.3	1166.8	1395.9	1411.0
115°	240.6	263.5	286.4	292.1	416.7	582.7	665.7	812.9	1107.1	1327.8	1348.7
117.5°	271.6	292.4	313.2	318.5	424.4	565.6	636.1	769.0	1034.6	1233.8	1256.9
120°	289.7	309.3	329.0	333.9	430.7	559.8	624.4	745.7	988.3	1170.4	1192.8
122.5°	307.4	327.2	347.0	351.9	439.7	556.8	615.3	724.6	943.2	1107.0	1129.2
125°	334.6	352.6	370.6	375.1	451.9	554.3	605.5	698.3	883.9	1023.2	1043.6
127.5°	356.7	374.8	393.0	397.6	464.1	552.8	597.2	676.9	836.3	955.9	973.0
130°	368.4	388.0	407.7	412.6	473.0	553.7	594.0	665.0	806.9	913.3	929.2
132.5°	380.7	400.2	419.9	424.8	480.3	554.3	591.3	654.8	781.9	877.1	891.3
135°	398.8	416.7	434.4	438.9	488.1	553.7	586.6	639.8	746.1	825.9	838.2
137.5°	417.3	435.0	452.7	457.1	499.9	557.1	585.8	630.8	720.7	788.2	798.2
140°	432.6	448.9	465.2	469.3	507.2	557.7	583.0	621.9	699.5	757.8	767.2
142.5°	444.5	459.5	474.5	478.3	513.2	559.7	583.0	617.1	685.4	736.6	744.7
145°	462.6	475.7	488.9	492.1	521.1	559.8	579.1	607.0	662.9	704.7	710.8
147.5°	480.7	493.4	506.2	509.4	532.6	563.6	579.1	601.1	644.9	677.9	682.9
150°	492.5	504.0	515.6	518.5	538.7	565.6	579.1	597.6	634.8	662.6	666.7
152.5°	504.7	513.5	522.2	524.4	542.6	567.0	579.1	595.0	626.6	650.4	653.5
155°	522.8	529.3	535.8	537.4	551.3	569.8	579.1	591.7	616.8	635.7	637.8
157.5°	536.1	542.4	548.7	550.4	559.9	572.7	579.1	588.9	608.4	623.1	624.6
160°	545.2	550.2	555.0	556.3	563.9	574.1	579.1	587.5	604.2	616.8	617.7
162.5°	554.3	558.0	561.6	562.6	568.1	575.5	579.1	586.2	600.4	611.0	611.8
165°	564.1	567.5	570.7	571.6	574.1	577.4	579.1	584.2	594.3	601.9	602.8
167.5°	573.2	574.7	576.3	576.7	578.8	581.6	583.0	586.4	593.1	598.0	598.4
170°	579.1	580.6	582.3	582.6	582.7	582.9	583.0	586.4	593.1	598.0	598.0
172.5°	582.3	582.6	582.9	583.0	583.0	583.0	583.0	585.7	591.0	594.9	594.6
175°	586.6	586.6	586.6	586.6	585.4	583.8	583.0	584.7	588.0	590.5	590.5
177.5°	586.6	586.6	586.6	586.6	585.6	584.4	583.8	585.1	587.7	589.7	589.3
180°	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6	586.6



TEST NUMBER: P936904

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	784.9	784.9
2.5°	837.9	832.9
5°	1077.6	1082.7
7.5°	1451.1	1448.6
10°	1804.5	1827.2
12.5°	2061.9	2067.0
15°	2218.4	2228.5
17.5°	2278.9	2281.5
20°	2281.5	2276.4
22.5°	2253.7	2248.6
25°	2220.9	2218.4
27.5°	2190.6	2193.2
30°	2178.0	2185.6
32.5°	2178.0	2190.6
35°	2183.0	2195.6
37.5°	2180.6	2195.6
40°	2170.4	2188.1
42.5°	2142.6	2155.2
45°	2099.8	2114.9
47.5°	2044.3	2054.3
50°	1973.6	1983.6
52.5°	1885.3	1887.7
55°	1779.3	1789.4
57.5°	1665.7	1668.2
60°	1539.5	1547.1
62.5°	1405.8	1405.8
65°	1264.4	1269.5
67.5°	1118.0	1130.6
70°	969.1	971.6
72.5°	822.7	822.7
75°	671.4	673.8
77.5°	527.4	527.4
80°	391.2	393.7
82.5°	270.1	275.1
85°	169.1	169.1
87.5°	78.2	70.7
90°	15.0	15.0
92.5°	59.9	48.0
95°	208.9	172.9
97.5°	500.4	431.9
100°	721.0	639.3
102.5°	938.0	868.0
105°	1214.7	1177.0
107.5°	1395.9	1405.0
110°	1465.0	1504.2



TEST NUMBER: P936904

CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1471.2	1531.3
115°	1432.1	1515.6
117.5°	1349.5	1442.0
120°	1282.8	1372.7
122.5°	1217.9	1306.6
125°	1125.3	1207.0
127.5°	1042.0	1111.0
130°	992.9	1056.6
132.5°	948.4	1005.4
135°	887.4	936.6
137.5°	838.5	878.7
140°	804.8	842.4
142.5°	777.0	809.4
145°	735.4	759.8
147.5°	703.3	723.6
150°	683.1	699.5
152.5°	665.9	678.3
155°	646.1	654.3
157.5°	630.4	636.1
160°	621.0	624.4
162.5°	614.9	618.1
165°	606.0	609.4
167.5°	599.7	601.2
170°	598.0	598.0
172.5°	593.3	592.1
175°	590.5	590.5
177.5°	588.0	586.6
180°	586.6	586.6



TEST NUMBER: P936904
 CATALOG NUMBER: SQ4-FB-050U-100D-B40-1D-UNV-STD-W-8

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.48	7.50	7.32	8.38	9.47	19.66	20.68	20.50	21.55	22.65
	3H	7.20	8.12	8.05	9.00	10.12	21.51	22.43	22.36	23.31	24.43
	4H	7.50	8.38	8.37	9.26	10.39	22.16	23.04	23.03	23.92	25.05
	6H	7.76	8.57	8.65	9.46	10.61	22.60	23.41	23.48	24.30	25.45
	8H	7.83	8.60	8.73	9.52	10.66	22.73	23.50	23.62	24.41	25.55
	12H	7.86	8.59	8.76	9.50	10.67	22.80	23.53	23.70	24.44	25.61
4H	2H	13.71	14.59	14.59	15.48	16.61	19.95	20.83	20.83	21.71	22.84
	3H	15.30	16.03	16.18	16.95	18.09	22.01	22.74	22.90	23.66	24.81
	4H	15.40	16.07	16.30	16.98	18.15	22.79	23.46	23.69	24.37	25.54
	6H	15.42	16.00	16.33	16.94	18.11	23.34	23.92	24.25	24.85	26.03
	8H	15.40	15.94	16.32	16.88	18.06	23.50	24.04	24.42	24.98	26.16
	12H	15.37	15.86	16.30	16.81	18.00	23.60	24.09	24.54	25.05	26.24
8H	4H	16.86	17.40	17.78	18.33	19.52	22.86	23.40	23.78	24.34	25.52
	6H	17.11	17.56	18.05	18.53	19.72	23.50	23.95	24.44	24.92	26.11
	8H	17.13	17.53	18.08	18.49	19.70	23.72	24.12	24.67	25.08	26.29
	12H	17.10	17.46	18.06	18.41	19.67	23.87	24.22	24.83	25.18	26.44
12H	4H	17.01	17.50	17.95	18.45	19.64	22.82	23.31	23.76	24.26	25.46
	6H	17.37	17.77	18.32	18.73	19.94	23.48	23.88	24.44	24.85	26.05
	8H	17.45	17.80	18.40	18.76	20.01	23.72	24.07	24.68	25.03	26.28