

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937201

Luminaire Tested: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P937201  
REPORT IS A COMBINATION OF REPORTS P933494 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15476.7 lumens  
Efficiency: N/A  
Efficacy: 121.7 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 127.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P937201  
CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

### Luminous Intensity Polar Plot





TEST NUMBER: P937201

CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45						45													
1	96	92	88	84	88	84	80	77	70	67	65	57	55	53	44	43	42	37						37													
2	87	79	73	68	79	73	67	63	60	56	53	49	46	44	38	36	35	30						30													
3	79	69	62	56	72	64	57	52	53	48	44	43	39	36	34	31	29	25						25													
4	72	61	53	47	65	56	49	43	46	41	37	38	34	31	30	27	24	21						21													
5	66	54	46	39	60	50	42	37	41	36	31	34	29	26	26	23	21	17						17													
6	60	48	40	34	55	44	37	31	37	31	27	30	26	22	24	21	18	15						15													
7	56	43	35	29	51	40	32	27	33	28	23	27	23	20	21	18	16	13						13													
8	51	39	31	26	47	36	29	24	30	24	21	25	20	17	20	16	14	11						11													
9	48	35	28	23	44	33	26	21	27	22	18	22	18	15	18	15	12	10						10													
10	44	32	25	20	41	30	23	19	25	20	16	21	17	14	16	13	11	9						9													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2756	2756	2756
5°	2693	3186	3705
10°	2444	4646	6142
15°	2078	6071	7416
20°	1692	7037	7558
25°	1412	7366	7404
30°	1191	7414	7390
35°	1054	7293	7581
40°	919	7135	7779
45°	833	7020	7810
50°	764	6917	7680
55°	733	6765	7340
60°	751	6471	6802
65°	783	6023	6064
70°	835	5255	5123
75°	930	4289	3998
80°	1024	2978	2693
85°	927	1583	1379

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 7810 cd/sqm



TEST NUMBER: P937201

CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	115.3	0.7
10°-20°	510.8	3.3
20°-30°	893.5	5.8
30°-40°	1150.3	7.4
40°-50°	1284.8	8.3
50°-60°	1230.5	8.0
60°-70°	975.2	6.3
70°-80°	573.4	3.7
80°-90°	164.4	1.1
90°-100°	645.1	4.2
100°-110°	1695.9	11.0
110°-120°	1758.4	11.4
120°-130°	1410.5	9.1
130°-140°	1106.7	7.2
140°-150°	849.4	5.5
150°-160°	611.7	4.0
160°-170°	374.3	2.4
170°-180°	126.5	0.8
0°-30°	1519.6	9.8
0°-40°	2669.9	17.3
0°-60°	5185.2	33.5
0°-90°	6898.2	44.6
90°-120°	4099.3	26.5
90°-150°	7466.0	48.2
90°-180°	8578.0	55.4
0°-180°	15476.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	891	891	891	891	891	
5°	868	931	1049	1186	1229	80
15°	650	1200	2023	2452	2530	181
25°	415	1361	2410	2516	2518	191
35°	281	1301	2269	2398	2493	175
45°	192	1037	2006	2298	2401	148
55°	138	659	1702	1977	2031	125
65°	109	350	1264	1421	1441	108
75°	80	215	693	762	765	84
85°	29	66	172	189	192	30
90°	9	25	68	34	34	9
95°	85	334	1111	573	390	95
105°	306	463	1875	2846	2656	324
115°	543	659	1502	2996	3419	536
125°	755	846	1366	2308	2723	670
135°	900	990	1323	1863	2113	696
145°	1044	1110	1306	1590	1714	654
155°	1179	1212	1306	1434	1476	542
165°	1273	1290	1306	1358	1375	359
175°	1323	1323	1315	1332	1332	126
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P937201

CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0	891.0
2.5°	891.0	891.0	896.7	899.6	905.3	908.2	913.9	919.7	936.9	939.7	945.4
5°	868.1	879.6	916.8	931.1	971.2	1025.7	1048.6	1085.9	1163.3	1186.2	1200.5
7.5°	833.7	859.5	951.2	974.1	1074.4	1217.7	1277.9	1358.1	1481.3	1541.5	1590.2
10°	779.3	833.7	997.0	1051.5	1214.9	1432.6	1544.3	1656.1	1842.3	1925.4	1956.9
12.5°	719.1	807.9	1045.7	1120.3	1355.2	1673.3	1807.9	1931.1	2143.1	2254.9	2272.0
15°	650.4	770.7	1091.7	1200.5	1504.2	1873.8	2022.8	2174.6	2372.3	2452.5	2472.6
17.5°	590.2	742.0	1134.6	1249.2	1618.8	2054.3	2206.1	2332.2	2492.6	2547.1	2561.4
20°	515.7	696.2	1163.3	1312.3	1739.2	2186.1	2332.2	2429.6	2538.5	2572.9	2578.6
22.5°	461.3	647.5	1180.5	1335.2	1819.4	2266.3	2389.5	2466.9	2541.4	2552.8	2555.7
25°	415.4	593.1	1177.6	1361.0	1888.1	2315.0	2409.6	2466.9	2509.8	2515.6	2515.6
27.5°	372.4	532.9	1166.2	1366.7	1939.7	2326.5	2401.0	2441.1	2461.1	2472.6	2472.6
30°	335.2	475.6	1137.5	1355.2	1962.6	2315.0	2375.2	2395.2	2415.3	2432.5	2441.1
32.5°	306.6	421.2	1094.5	1332.3	1965.5	2286.4	2329.3	2340.8	2369.5	2409.6	2423.9
35°	280.8	366.7	1045.7	1300.8	1948.3	2240.5	2269.2	2280.6	2337.9	2398.1	2418.2
37.5°	255.0	326.6	982.7	1246.4	1922.5	2186.1	2206.1	2226.2	2315.0	2386.6	2409.6
40°	229.2	292.2	908.2	1186.2	1882.4	2120.2	2137.4	2168.9	2286.4	2369.5	2392.4
42.5°	209.1	263.6	828.0	1123.2	1830.8	2045.7	2071.5	2117.3	2252.0	2340.8	2366.6
45°	192.0	234.9	742.0	1037.1	1764.9	1968.4	2005.6	2068.6	2211.9	2297.8	2320.7
47.5°	174.8	214.9	653.2	948.3	1693.3	1891.0	1939.7	2011.3	2157.4	2240.5	2260.6
50°	160.4	194.8	564.4	853.8	1616.0	1807.9	1865.2	1939.7	2088.7	2166.0	2191.8
52.5°	149.0	177.6	481.3	759.2	1527.1	1722.0	1787.9	1865.2	2005.6	2080.1	2097.3
55°	137.5	163.3	409.7	658.9	1435.5	1630.3	1701.9	1776.4	1913.9	1976.9	1988.4
57.5°	131.8	151.8	349.5	564.4	1338.1	1527.1	1607.4	1676.1	1805.0	1853.8	1865.2
60°	123.2	143.2	303.7	484.2	1232.0	1429.7	1498.5	1567.3	1676.1	1716.2	1724.8
62.5°	114.6	137.5	269.3	406.8	1123.2	1315.1	1383.9	1446.9	1538.6	1567.3	1578.7
65°	108.9	131.8	243.5	349.5	1011.3	1194.8	1263.6	1318.0	1392.5	1421.1	1426.9
67.5°	103.1	126.1	223.5	300.8	899.6	1074.4	1126.0	1177.6	1234.9	1263.6	1266.4
70°	94.5	120.3	206.3	266.4	785.0	936.9	979.8	1034.3	1080.1	1094.5	1103.1
72.5°	88.8	111.7	194.8	240.7	667.5	805.1	845.2	876.7	916.8	931.1	931.1
75°	80.2	100.3	183.4	214.9	547.2	658.9	693.3	724.8	756.4	762.1	753.5
77.5°	71.6	88.8	157.6	180.5	426.9	521.4	550.1	567.3	593.1	598.8	601.6
80°	60.2	77.4	123.2	140.4	309.4	383.9	404.0	418.3	441.2	441.2	446.9
82.5°	45.8	60.2	88.8	100.3	209.1	263.6	280.8	289.4	303.7	303.7	303.7
85°	28.6	37.2	57.3	65.9	126.1	160.4	171.9	174.8	186.2	189.1	189.1
87.5°	14.3	20.1	37.2	40.1	65.9	83.1	83.1	88.8	88.8	86.0	83.1
90°	8.9	15.9	23.0	24.8	39.1	58.1	67.5	60.0	45.0	33.7	33.7
92.5°	35.5	95.9	156.3	171.4	240.9	333.7	380.1	333.1	239.2	168.7	162.1
95°	85.3	195.8	306.4	334.0	593.0	938.4	1111.0	991.5	752.3	572.8	552.5
97.5°	147.5	245.0	342.5	366.8	798.8	1374.6	1662.6	1586.9	1435.7	1322.4	1283.7
100°	195.4	283.8	372.3	394.3	873.6	1512.6	1832.2	1837.7	1848.8	1857.1	1811.0
102.5°	236.3	318.8	401.2	421.8	907.9	1556.1	1880.2	1976.5	2169.1	2313.6	2274.1
105°	305.5	375.4	445.2	462.7	933.4	1561.0	1874.9	2090.8	2522.6	2846.5	2825.3
107.5°	376.6	441.7	506.8	523.1	938.2	1491.6	1768.3	2069.5	2671.8	3123.5	3128.7
110°	424.5	483.3	542.2	556.9	931.0	1430.0	1679.5	2016.2	2689.6	3194.6	3216.6



TEST NUMBER: P937201

CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	471.6	527.6	583.7	597.7	931.4	1376.3	1598.7	1943.2	2632.5	3149.3	3183.2
115°	542.6	594.3	646.1	658.9	939.9	1314.6	1501.8	1833.8	2497.7	2995.6	3042.7
117.5°	612.8	659.8	706.7	718.4	957.4	1275.9	1435.2	1734.8	2333.9	2783.3	2835.6
120°	653.7	697.9	742.0	753.1	971.6	1262.9	1408.5	1682.2	2229.7	2640.4	2691.1
122.5°	693.6	738.2	782.8	794.0	992.1	1256.1	1388.1	1634.6	2127.6	2497.4	2547.5
125°	754.9	795.6	836.3	846.4	1019.6	1250.5	1365.9	1575.4	1994.1	2308.2	2354.4
127.5°	804.7	845.7	886.8	897.0	1047.2	1247.2	1347.3	1527.1	1886.7	2156.4	2195.3
130°	831.3	875.5	919.7	930.7	1067.2	1249.1	1340.2	1500.2	1820.3	2060.4	2096.3
132.5°	858.8	903.0	947.2	958.2	1083.4	1250.5	1333.9	1477.2	1763.8	1978.8	2010.9
135°	899.7	939.9	980.2	990.2	1101.3	1249.3	1323.3	1443.3	1683.3	1863.3	1891.0
137.5°	941.4	981.3	1021.2	1031.1	1128.0	1257.0	1321.5	1423.0	1625.9	1778.0	1800.7
140°	976.0	1012.7	1049.4	1058.6	1144.2	1258.3	1315.3	1403.0	1578.2	1709.6	1730.8
142.5°	1002.7	1036.7	1070.6	1079.1	1157.8	1262.8	1315.3	1392.3	1546.2	1661.7	1679.9
145°	1043.5	1073.1	1102.7	1110.2	1175.6	1262.8	1306.4	1369.4	1495.3	1589.8	1603.6
147.5°	1084.4	1113.2	1142.1	1149.2	1201.7	1271.5	1306.4	1356.0	1455.0	1529.3	1540.8
150°	1111.0	1137.1	1163.2	1169.7	1215.2	1276.1	1306.4	1348.3	1431.9	1494.7	1503.9
152.5°	1138.6	1158.3	1178.0	1183.0	1224.1	1279.0	1306.4	1342.2	1413.6	1467.2	1474.1
155°	1179.4	1194.0	1208.6	1212.3	1243.7	1285.5	1306.4	1334.9	1391.7	1434.3	1439.0
157.5°	1209.6	1223.8	1238.1	1241.6	1263.2	1292.0	1306.4	1328.5	1372.7	1405.9	1409.1
160°	1230.0	1241.1	1252.2	1255.0	1272.2	1295.0	1306.4	1325.3	1363.3	1391.7	1393.6
162.5°	1250.5	1258.8	1267.0	1269.1	1281.5	1298.1	1306.4	1322.4	1354.4	1378.4	1380.2
165°	1272.7	1280.2	1287.6	1289.5	1295.2	1302.7	1306.4	1317.9	1340.7	1357.9	1359.8
167.5°	1293.1	1296.6	1300.2	1301.1	1305.9	1312.2	1315.3	1322.8	1337.8	1349.0	1349.8
170°	1306.4	1310.0	1313.6	1314.5	1314.7	1315.1	1315.3	1322.8	1337.8	1349.0	1349.0
172.5°	1313.5	1314.3	1315.1	1315.3	1315.3	1315.3	1315.3	1321.2	1333.1	1342.0	1341.3
175°	1323.3	1323.3	1323.3	1323.3	1320.7	1317.1	1315.3	1319.0	1326.6	1332.2	1332.2
177.5°	1323.3	1323.3	1323.3	1323.3	1321.2	1318.5	1317.1	1320.1	1326.0	1330.4	1329.6
180°	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3	1323.3



TEST NUMBER: P937201

CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	891.0	891.0
2.5°	951.2	945.4
5°	1223.5	1229.2
7.5°	1647.5	1644.6
10°	2048.6	2074.4
12.5°	2340.8	2346.5
15°	2518.4	2529.9
17.5°	2587.2	2590.1
20°	2590.1	2584.3
22.5°	2558.5	2552.8
25°	2521.3	2518.4
27.5°	2486.9	2489.8
30°	2472.6	2481.2
32.5°	2472.6	2486.9
35°	2478.3	2492.6
37.5°	2475.5	2492.6
40°	2464.0	2484.1
42.5°	2432.5	2446.8
45°	2383.8	2401.0
47.5°	2320.7	2332.2
50°	2240.5	2252.0
52.5°	2140.3	2143.1
55°	2019.9	2031.4
57.5°	1891.0	1893.9
60°	1747.7	1756.3
62.5°	1595.9	1595.9
65°	1435.5	1441.2
67.5°	1269.3	1283.6
70°	1100.3	1103.1
72.5°	934.0	934.0
75°	762.1	765.0
77.5°	598.8	598.8
80°	444.1	446.9
82.5°	306.6	312.3
85°	192.0	192.0
87.5°	88.8	80.2
90°	33.7	33.7
92.5°	135.2	108.4
95°	471.2	389.9
97.5°	1129.0	974.3
100°	1626.7	1442.3
102.5°	2116.2	1958.3
105°	2740.4	2655.5
107.5°	3149.2	3169.7
110°	3305.1	3393.5





TEST NUMBER: P937201

CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	3319.0	3454.8
115°	3231.0	3419.3
117.5°	3044.3	3253.2
120°	2894.0	3096.9
122.5°	2747.5	2947.7
125°	2538.7	2723.0
127.5°	2350.8	2506.3
130°	2240.0	2383.8
132.5°	2139.6	2268.3
135°	2002.0	2112.8
137.5°	1891.5	1982.3
140°	1815.7	1900.5
142.5°	1753.0	1826.0
145°	1658.8	1714.0
147.5°	1586.5	1632.4
150°	1541.1	1578.2
152.5°	1502.2	1530.2
155°	1457.5	1476.0
157.5°	1422.2	1435.2
160°	1401.1	1408.5
162.5°	1387.2	1394.4
165°	1367.3	1374.8
167.5°	1353.0	1356.2
170°	1349.0	1349.0
172.5°	1338.5	1335.8
175°	1332.2	1332.2
177.5°	1326.5	1323.3
180°	1323.3	1323.3



TEST NUMBER: P937201  
 CATALOG NUMBER: SQ4-FB-075U-075D-B40-1D-UNV-STD-W-12

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.02	4.86	5.01	5.87	7.22	17.21	18.06	18.20	19.07	20.41
	3H	4.72	5.48	5.72	6.50	7.87	19.05	19.81	20.06	20.83	22.20
	4H	5.02	5.74	6.03	6.76	8.13	19.70	20.42	20.72	21.45	22.82
	6H	5.27	5.93	6.30	6.96	8.34	20.13	20.80	21.16	21.83	23.21
	8H	5.33	5.97	6.37	7.01	8.39	20.26	20.89	21.29	21.94	23.32
	12H	5.35	5.95	6.39	6.99	8.40	20.33	20.93	21.37	21.97	23.37
4H	2H	11.24	11.96	12.26	12.98	14.36	17.48	18.20	18.50	19.23	20.60
	3H	12.80	13.41	13.84	14.46	15.84	19.53	20.13	20.56	21.19	22.57
	4H	12.90	13.45	13.94	14.49	15.90	20.30	20.85	21.34	21.90	23.30
	6H	12.91	13.38	13.96	14.45	15.85	20.84	21.32	21.89	22.39	23.79
	8H	12.88	13.33	13.94	14.39	15.81	21.01	21.45	22.06	22.51	23.93
	12H	12.84	13.24	13.91	14.32	15.74	21.10	21.51	22.17	22.58	24.00
8H	4H	14.34	14.79	15.40	15.85	17.27	20.36	20.80	21.41	21.86	23.28
	6H	14.59	14.96	15.66	16.06	17.47	20.99	21.36	22.07	22.46	23.88
	8H	14.60	14.93	15.69	16.01	17.45	21.21	21.54	22.30	22.62	24.06
	12H	14.57	14.86	15.66	15.94	17.41	21.36	21.65	22.45	22.73	24.20
12H	4H	14.49	14.89	15.56	15.97	17.39	20.31	20.71	21.38	21.79	23.21
	6H	14.85	15.17	15.93	16.26	17.69	20.97	21.30	22.06	22.38	23.82
	8H	14.91	15.20	16.00	16.28	17.76	21.21	21.49	22.29	22.57	24.05