

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P937001

Luminaire Tested: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P937001
REPORT IS A COMBINATION OF REPORTS P933464 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 17371.4 lumens
Efficiency: N/A
Efficacy: 103.4 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 12' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 168
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P937001
CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

Luminous Intensity Polar Plot





TEST NUMBER: P937001

CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67	67	67	67
1	101	96	92	88	95	91	87	83	80	78	75	71	69	67	62	61	59	55	55	55	55
2	91	83	76	71	86	78	72	67	70	65	61	61	58	55	54	51	49	45	45	45	45
3	83	72	64	58	77	68	61	55	61	55	50	54	49	45	47	44	41	37	37	37	37
4	75	64	55	48	70	60	52	46	53	47	42	47	42	38	42	38	34	31	31	31	31
5	69	56	47	41	64	53	45	39	47	41	36	42	37	32	37	33	29	26	26	26	26
6	63	50	41	35	59	47	39	34	42	36	31	38	32	28	33	29	25	23	23	23	23
7	58	45	36	30	55	43	35	29	38	32	27	34	29	24	30	26	22	20	20	20	20
8	54	41	32	27	51	39	31	26	35	28	24	31	26	22	27	23	20	17	17	17	17
9	50	37	29	24	47	35	28	23	32	25	21	28	23	19	25	21	17	15	15	15	15
10	47	34	26	21	44	32	25	20	29	23	19	26	21	17	23	19	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4664	4664	4664
5°	4558	5392	6269
10°	4136	7861	10393
15°	3516	10273	12549
20°	2864	11908	12789
25°	2390	12464	12529
30°	2016	12546	12506
35°	1784	12341	12829
40°	1555	12074	13163
45°	1409	11879	13215
50°	1294	11704	12996
55°	1240	11448	12420
60°	1271	10950	11511
65°	1324	10191	10261
70°	1415	8893	8668
75°	1573	7258	6765
80°	1731	5039	4559
85°	1572	2678	2333

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 13215 cd/sqm



TEST NUMBER: P937001

CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.0	1.1
10°-20°	864.4	5.0
20°-30°	1512.0	8.7
30°-40°	1946.4	11.2
40°-50°	2174.1	12.5
50°-60°	2082.3	12.0
60°-70°	1650.2	9.5
70°-80°	970.4	5.6
80°-90°	272.9	1.6
90°-100°	428.9	2.5
100°-110°	1127.5	6.5
110°-120°	1169.1	6.7
120°-130°	937.8	5.4
130°-140°	735.9	4.2
140°-150°	564.8	3.3
150°-160°	406.7	2.3
160°-170°	248.9	1.4
170°-180°	84.1	0.5
0°-30°	2571.5	14.8
0°-40°	4517.9	26.0
0°-60°	8774.2	50.5
0°-90°	11667.7	67.2
90°-120°	2725.5	15.7
90°-150°	4964.0	28.6
90°-180°	5704.0	32.8
0°-180°	17371.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1508	1508	1508	1508	1508	
5°	1469	1576	1774	2007	2080	136
15°	1100	2031	3423	4150	4281	306
25°	703	2303	4077	4257	4262	324
35°	475	2201	3840	4058	4218	297
45°	325	1755	3394	3888	4063	251
55°	233	1115	2880	3345	3437	212
65°	184	592	2138	2405	2439	183
75°	136	364	1173	1290	1294	142
85°	48	112	291	320	325	51
90°	6	16	45	22	22	8
95°	57	222	739	381	259	63
105°	203	308	1247	1892	1766	215
115°	361	438	998	1992	2274	356
125°	502	563	908	1535	1810	446
135°	598	658	880	1239	1405	463
145°	694	738	869	1057	1140	435
155°	784	806	869	954	982	360
165°	846	857	869	903	914	239
175°	880	880	874	886	886	84
180°	880	880	880	880	880	



TEST NUMBER: P937001

CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8	1507.8
2.5°	1507.8	1507.8	1517.5	1522.4	1532.0	1536.9	1546.6	1556.3	1585.4	1590.3	1599.9
5°	1469.0	1488.4	1551.4	1575.7	1643.6	1735.7	1774.5	1837.5	1968.4	2007.2	2031.4
7.5°	1410.8	1454.5	1609.7	1648.4	1818.1	2060.5	2162.3	2298.1	2506.6	2608.4	2690.8
10°	1318.8	1410.8	1687.2	1779.3	2055.6	2424.1	2613.2	2802.3	3117.4	3258.0	3311.4
12.5°	1217.0	1367.2	1769.6	1895.7	2293.2	2831.4	3059.2	3267.7	3626.5	3815.6	3844.6
15°	1100.5	1304.1	1847.2	2031.4	2545.4	3170.8	3422.8	3679.8	4014.3	4150.1	4184.0
17.5°	998.7	1255.7	1919.9	2113.8	2739.2	3476.2	3733.2	3946.4	4217.9	4310.1	4334.4
20°	872.7	1178.1	1968.4	2220.5	2942.9	3699.2	3946.4	4111.3	4295.6	4353.7	4363.4
22.5°	780.5	1095.7	1997.5	2259.2	3078.6	3835.0	4043.5	4174.3	4300.4	4319.8	4324.6
25°	703.0	1003.6	1992.6	2302.9	3195.0	3917.4	4077.4	4174.3	4247.1	4256.7	4256.7
27.5°	630.3	901.8	1973.2	2312.6	3282.2	3936.8	4062.9	4130.7	4164.7	4184.0	4184.0
30°	567.3	804.8	1924.7	2293.2	3321.0	3917.4	4019.2	4053.1	4087.1	4116.1	4130.7
32.5°	518.8	712.7	1852.0	2254.5	3325.9	3868.9	3941.7	3961.1	4009.5	4077.4	4101.6
35°	475.1	620.6	1769.6	2201.1	3296.9	3791.4	3839.8	3859.3	3956.2	4058.0	4091.9
37.5°	431.5	552.7	1662.9	2109.0	3253.2	3699.2	3733.2	3767.1	3917.4	4038.6	4077.4
40°	387.8	494.5	1536.9	2007.2	3185.3	3587.7	3616.8	3670.2	3868.9	4009.5	4048.2
42.5°	353.9	446.1	1401.2	1900.5	3098.0	3461.7	3505.3	3582.9	3810.7	3961.1	4004.7
45°	324.8	397.6	1255.7	1755.1	2986.5	3330.8	3393.8	3500.5	3742.8	3888.3	3927.1
47.5°	295.8	363.7	1105.4	1604.8	2865.3	3199.8	3282.2	3403.4	3650.8	3791.4	3825.3
50°	271.5	329.7	955.1	1444.8	2734.5	3059.2	3156.2	3282.2	3534.4	3665.3	3708.9
52.5°	252.1	300.6	814.5	1284.8	2584.1	2913.8	3025.3	3156.2	3393.8	3519.8	3548.9
55°	232.7	276.4	693.3	1115.1	2428.9	2758.6	2879.9	3006.0	3238.6	3345.3	3364.7
57.5°	223.0	257.0	591.5	955.1	2264.1	2584.1	2719.8	2836.3	3054.4	3136.8	3156.2
60°	208.5	242.4	513.9	819.4	2084.8	2419.3	2535.6	2652.0	2836.3	2904.1	2918.7
62.5°	194.0	232.7	455.7	688.5	1900.5	2225.3	2341.7	2448.3	2603.5	2652.0	2671.4
65°	184.2	223.0	412.1	591.5	1711.5	2021.7	2138.1	2230.2	2356.3	2404.7	2414.4
67.5°	174.6	213.3	378.2	509.1	1522.4	1818.1	1905.3	1992.6	2089.6	2138.1	2142.9
70°	160.0	203.6	349.1	450.9	1328.4	1585.4	1658.1	1750.2	1827.8	1852.0	1866.5
72.5°	150.3	189.1	329.7	407.2	1129.7	1362.4	1430.2	1483.6	1551.4	1575.7	1575.7
75°	135.7	169.7	310.3	363.7	926.0	1115.1	1173.3	1226.6	1279.9	1289.6	1275.1
77.5°	121.2	150.3	266.6	305.4	722.4	882.4	930.8	960.0	1003.6	1013.3	1018.1
80°	101.8	130.9	208.5	237.6	523.6	649.7	683.6	707.8	746.6	746.6	756.4
82.5°	77.5	101.8	150.3	169.7	353.9	446.1	475.1	489.6	513.9	513.9	513.9
85°	48.5	63.0	96.9	111.5	213.3	271.5	290.9	295.8	315.2	320.0	320.0
87.5°	24.3	33.9	63.0	67.9	111.5	140.6	140.6	150.3	150.3	145.4	140.6
90°	5.9	10.6	15.4	16.5	26.0	38.6	44.9	39.9	29.9	22.4	22.4
92.5°	23.6	63.7	103.9	113.9	160.2	221.8	252.7	221.5	159.0	112.2	107.7
95°	56.7	130.2	203.7	222.0	394.2	623.9	738.7	659.1	500.1	380.9	367.3
97.5°	98.0	162.8	227.7	243.9	531.1	913.9	1105.4	1055.2	954.6	879.3	853.6
100°	129.9	188.7	247.4	262.1	580.8	1005.7	1218.2	1221.8	1229.2	1234.7	1204.1
102.5°	157.1	211.9	266.7	280.5	603.7	1034.6	1250.1	1314.1	1442.1	1538.2	1512.0
105°	203.1	249.5	296.0	307.6	620.6	1037.9	1246.6	1390.1	1677.2	1892.5	1878.4
107.5°	250.4	293.7	337.0	347.8	623.8	991.8	1175.7	1376.0	1776.5	2076.8	2080.3
110°	282.3	321.4	360.5	370.3	619.0	950.8	1116.7	1340.5	1788.2	2124.0	2138.7



TEST NUMBER: P937001

CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	313.5	350.8	388.0	397.4	619.2	915.0	1062.9	1292.0	1750.2	2093.9	2116.5
115°	360.8	395.2	429.6	438.2	625.0	874.0	998.5	1219.2	1660.6	1991.7	2023.1
117.5°	407.4	438.6	469.9	477.7	636.5	848.3	954.2	1153.4	1551.8	1850.6	1885.3
120°	434.6	464.0	493.4	500.7	646.0	839.7	936.6	1118.6	1482.5	1755.6	1789.3
122.5°	461.2	490.9	520.5	527.9	659.6	835.1	922.9	1086.8	1414.6	1660.5	1693.7
125°	501.9	529.0	556.0	562.8	678.0	831.4	908.2	1047.4	1325.8	1534.7	1565.3
127.5°	535.0	562.3	589.6	596.4	696.2	829.2	895.8	1015.4	1254.4	1433.7	1459.6
130°	552.8	582.2	611.5	618.8	709.6	830.6	891.1	997.5	1210.4	1369.9	1393.8
132.5°	571.0	600.4	629.8	637.2	720.5	831.4	886.9	982.2	1172.7	1315.6	1337.0
135°	598.2	625.0	651.7	658.4	732.2	830.7	879.8	959.7	1119.3	1238.9	1257.4
137.5°	625.9	652.5	679.0	685.6	750.0	835.8	878.7	946.1	1081.1	1182.2	1197.3
140°	648.9	673.4	697.7	703.8	760.8	836.6	874.5	932.7	1049.4	1136.7	1150.9
142.5°	666.7	689.2	711.9	717.5	769.8	839.6	874.5	925.7	1028.1	1104.8	1117.0
145°	693.8	713.5	733.2	738.1	781.7	839.6	868.7	910.5	994.3	1057.0	1066.2
147.5°	721.0	740.1	759.3	764.1	799.0	845.5	868.7	901.6	967.5	1016.9	1024.5
150°	738.7	756.0	773.4	777.7	808.0	848.4	868.7	896.5	952.0	993.8	1000.0
152.5°	757.0	770.1	783.3	786.5	813.9	850.4	868.7	892.4	939.9	975.5	980.2
155°	784.2	793.9	803.6	806.0	826.9	854.7	868.7	887.6	925.3	953.7	956.7
157.5°	804.3	813.8	823.1	825.5	839.9	859.1	868.7	883.4	912.7	934.8	937.0
160°	817.9	825.2	832.6	834.4	845.8	861.0	868.7	881.3	906.4	925.3	926.5
162.5°	831.4	837.0	842.5	843.8	852.1	863.1	868.7	879.3	900.5	916.4	917.6
165°	846.2	851.2	856.2	857.4	861.1	866.2	868.7	876.3	891.5	902.9	904.1
167.5°	859.8	862.1	864.5	865.0	868.2	872.4	874.5	879.5	889.5	896.9	897.5
170°	868.7	871.0	873.3	873.9	874.1	874.4	874.5	879.5	889.5	896.9	896.9
172.5°	873.3	873.8	874.4	874.5	874.5	874.5	874.5	878.4	886.3	892.3	891.8
175°	879.8	879.8	879.8	879.8	878.0	875.6	874.5	877.0	882.0	885.8	885.8
177.5°	879.8	879.8	879.8	879.8	878.5	876.7	875.7	877.7	881.7	884.6	884.0
180°	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8	879.8



TEST NUMBER: P937001

CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	1507.8	1507.8
2.5°	1609.7	1599.9
5°	2070.2	2079.9
7.5°	2787.7	2782.9
10°	3466.5	3510.1
12.5°	3961.1	3970.7
15°	4261.6	4281.0
17.5°	4378.0	4382.8
20°	4382.8	4373.1
22.5°	4329.5	4319.8
25°	4266.5	4261.6
27.5°	4208.3	4213.2
30°	4184.0	4198.6
32.5°	4184.0	4208.3
35°	4193.7	4217.9
37.5°	4188.9	4217.9
40°	4169.5	4203.4
42.5°	4116.1	4140.4
45°	4033.7	4062.9
47.5°	3927.1	3946.4
50°	3791.4	3810.7
52.5°	3621.6	3626.5
55°	3418.0	3437.4
57.5°	3199.8	3204.7
60°	2957.4	2972.0
62.5°	2700.5	2700.5
65°	2428.9	2438.7
67.5°	2147.8	2172.1
70°	1861.8	1866.5
72.5°	1580.5	1580.5
75°	1289.6	1294.5
77.5°	1013.3	1013.3
80°	751.5	756.4
82.5°	518.8	528.5
85°	324.8	324.8
87.5°	150.3	135.7
90°	22.4	22.4
92.5°	89.9	72.0
95°	313.2	259.2
97.5°	750.6	647.8
100°	1081.5	959.0
102.5°	1407.0	1302.0
105°	1822.0	1765.6
107.5°	2093.8	2107.5
110°	2197.5	2256.3



TEST NUMBER: P937001

CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	2206.8	2297.1
115°	2148.3	2273.5
117.5°	2024.1	2163.0
120°	1924.2	2059.1
122.5°	1826.8	1959.9
125°	1687.9	1810.5
127.5°	1563.0	1666.4
130°	1489.4	1584.9
132.5°	1422.6	1508.1
135°	1331.1	1404.8
137.5°	1257.6	1318.0
140°	1207.2	1263.7
142.5°	1165.6	1214.1
145°	1102.9	1139.7
147.5°	1054.9	1085.4
150°	1024.6	1049.4
152.5°	998.8	1017.5
155°	969.1	981.5
157.5°	945.5	954.2
160°	931.6	936.6
162.5°	922.3	927.1
165°	909.2	914.1
167.5°	899.6	901.7
170°	896.9	896.9
172.5°	890.0	888.2
175°	885.8	885.8
177.5°	881.9	879.8
180°	879.8	879.8



TEST NUMBER: P937001
 CATALOG NUMBER: SQ4-FB-050U-125D-B40-1D-UNV-STD-W-12

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.79	8.88	8.57	9.70	10.70	20.98	22.08	21.76	22.89	23.89
	3H	8.51	9.50	9.31	10.32	11.35	22.84	23.83	23.64	24.65	25.68
	4H	8.82	9.75	9.63	10.59	11.62	23.50	24.44	24.32	25.27	26.31
	6H	9.08	9.95	9.91	10.79	11.84	23.95	24.81	24.78	25.65	26.71
	8H	9.16	9.98	9.99	10.84	11.89	24.08	24.90	24.92	25.76	26.82
	12H	9.18	9.97	10.03	10.82	11.90	24.16	24.94	25.00	25.80	26.88
4H	2H	15.04	15.97	15.86	16.81	17.85	21.28	22.22	22.10	23.05	24.09
	3H	16.63	17.41	17.46	18.28	19.33	23.35	24.14	24.19	25.00	26.06
	4H	16.73	17.45	17.58	18.31	19.39	24.13	24.85	24.98	25.71	26.79
	6H	16.76	17.38	17.62	18.27	19.35	24.69	25.31	25.55	26.20	27.29
	8H	16.74	17.32	17.60	18.20	19.30	24.86	25.44	25.73	26.33	27.43
	12H	16.71	17.23	17.59	18.13	19.24	24.97	25.50	25.86	26.40	27.50
8H	4H	18.20	18.78	19.07	19.66	20.76	24.21	24.80	25.08	25.68	26.78
	6H	18.45	18.94	19.35	19.86	20.96	24.86	25.34	25.75	26.27	27.37
	8H	18.47	18.90	19.38	19.82	20.94	25.08	25.51	25.99	26.43	27.55
	12H	18.45	18.83	19.36	19.74	20.91	25.24	25.62	26.15	26.53	27.70
12H	4H	18.36	18.88	19.24	19.78	20.89	24.18	24.70	25.06	25.61	26.71
	6H	18.72	19.15	19.62	20.06	21.18	24.84	25.27	25.75	26.19	27.31
	8H	18.80	19.18	19.71	20.09	21.25	25.09	25.47	26.00	26.38	27.55