

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844833

Luminaire Tested: **SQ4P-BB-075U-050D-B40-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P844833  
REPORT IS A COMBINATION OF REPORTS P700215 AND P700245  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-BB-075U-050D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT  
UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 3631.4 lumens  
Efficiency: N/A  
Efficacy: 101.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.97 / 0.97  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Indirect

Input Watts (W): 35.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P844833

CATALOG NUMBER: SQ4P-BB-075U-050D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P844833

CATALOG NUMBER: SQ4P-BB-075U-050D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40	33																			
1	95	91	88	85	86	83	80	77	66	64	63	51	50	49	37	37	36	30																			
2	88	81	76	71	79	74	69	65	60	57	54	47	45	43	34	33	32	27																			
3	81	72	66	61	73	66	60	56	54	50	47	42	40	38	32	30	29	24																			
4	74	65	58	53	67	59	53	49	48	44	41	38	36	33	29	28	26	22																			
5	69	58	51	46	62	53	47	43	44	39	36	35	32	30	27	25	24	20																			
6	64	53	46	40	58	48	42	38	40	35	32	32	29	27	25	23	21	18																			
7	59	48	41	36	54	44	38	33	37	32	29	30	26	24	23	21	20	17																			
8	55	44	37	32	50	40	34	30	34	29	26	27	24	22	21	19	18	16																			
9	51	40	33	29	47	37	31	27	31	27	23	25	22	20	20	18	17	14																			
10	48	37	30	26	44	34	28	24	29	24	21	24	21	18	19	17	15	13																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9234	9234	9234
5°	9085	9063	9130
10°	8500	8614	8854
15°	7728	7974	8418
20°	6860	7216	7849
25°	5974	6447	7212
30°	5118	5679	6607
35°	4243	4821	5878
40°	3260	3855	5009
45°	2356	2920	4030
50°	1605	2175	3198
55°	1044	1573	2485
60°	600	1109	1797
65°	159	677	910
70°	81	210	262
75°	36	18	0
80°	27	0	0
85°	0	0	0



TEST NUMBER: P844833

CATALOG NUMBER: SQ4P-BB-075U-050D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	91.3	2.5
10°-20°	233.6	6.4
20°-30°	292.4	8.1
30°-40°	270.1	7.4
40°-50°	181.5	5.0
50°-60°	93.8	2.6
60°-70°	29.4	0.8
70°-80°	1.9	0.1
80°-90°	0.9	0.0
90°-100°	149.4	4.1
100°-110°	519.9	14.3
110°-120°	503.6	13.9
120°-130°	395.1	10.9
130°-140°	312.7	8.6
140°-150°	241.3	6.6
150°-160°	173.0	4.8
160°-170°	105.8	2.9
170°-180°	35.8	1.0
0°-30°	617.3	17.0
0°-40°	887.4	24.4
0°-60°	1162.7	32.0
0°-90°	1194.8	32.9
90°-120°	1172.9	32.3
90°-150°	2122.0	58.4
90°-180°	2437.0	67.1
0°-180°	3631.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1001	1001	1001	1001	1001	
5°	981	971	979	982	986	91
15°	809	806	835	863	881	225
25°	587	592	633	677	708	269
35°	377	386	428	478	522	233
45°	181	192	224	267	309	142
55°	65	76	98	126	154	61
65°	7	14	31	37	42	12
75°	1	1	0	0	0	1
85°	0	0	0	0	0	0
90°	6	8	8	6	3	3
95°	25	87	252	64	39	27
105°	87	123	546	922	857	91
115°	151	182	406	857	1011	149
125°	205	252	378	639	762	183
135°	246	277	375	532	602	191
145°	289	308	373	460	499	181
155°	328	339	367	409	423	151
165°	359	362	370	387	390	101
175°	375	375	373	378	375	36
180°	375	375	375	375	375	



TEST NUMBER: P844833

CATALOG NUMBER: SQ4P-BB-075U-050D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1000.8	1000.8	1000.8	1000.8	1000.8
2.5°	1003.2	993.7	996.1	996.1	993.5
5°	981.0	971.0	978.6	982.0	985.8
7.5°	939.6	931.8	946.3	956.9	964.9
10°	907.3	900.7	919.5	934.2	945.1
12.5°	870.1	865.0	887.7	908.0	921.9
15°	809.1	806.3	834.8	862.8	881.3
17.5°	743.7	743.6	776.0	810.9	833.1
20°	698.7	700.1	735.0	773.4	799.4
22.5°	653.7	657.0	694.3	734.4	764.2
25°	586.8	591.5	633.3	676.7	708.4
27.5°	522.5	529.5	573.4	618.4	657.0
30°	480.4	488.4	533.1	580.5	620.2
32.5°	438.8	448.5	492.0	542.2	582.6
35°	376.7	386.2	428.0	478.4	521.9
37.5°	312.5	321.7	362.6	412.2	459.3
40°	270.7	281.0	320.1	368.1	415.9
42.5°	232.8	243.1	279.8	327.0	372.1
45°	180.6	191.5	223.8	267.3	308.9
47.5°	137.5	149.2	177.4	217.0	254.9
50°	111.8	123.7	151.5	186.3	222.8
52.5°	91.3	102.8	127.9	160.6	194.0
55°	64.9	75.8	97.8	125.6	154.5
57.5°	44.9	54.3	74.0	97.1	119.8
60°	32.5	41.5	60.1	78.8	97.4
62.5°	21.6	29.8	48.0	62.5	74.9
65°	7.3	14.0	31.0	37.4	41.7
67.5°	3.7	4.4	16.2	17.2	18.6
70°	3.0	3.0	7.8	8.2	9.7
72.5°	2.0	2.0	3.1	4.0	4.3
75°	1.0	1.0	0.5	0.0	0.0
77.5°	0.5	0.5	0.5	0.0	0.0
80°	0.5	0.5	0.0	0.0	0.0
82.5°	0.1	0.1	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	5.6	8.4	8.4	5.6	2.8
92.5°	14.1	42.1	39.2	16.8	14.1
95°	25.2	86.8	252.2	64.4	39.2
97.5°	39.2	98.1	504.3	229.8	123.3
100°	53.2	103.7	588.3	552.0	355.8
102.5°	70.1	112.0	585.6	776.1	638.8
105°	86.8	123.3	546.4	921.8	857.3



TEST NUMBER: P844833

CATALOG NUMBER: SQ4P-BB-075U-050D-B40-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	134.5	165.3	425.9	927.4	1056.3
115°	151.3	182.1	406.2	857.3	1011.4
117.5°	168.1	201.8	395.1	792.9	947.0
120°	182.1	218.5	386.7	731.3	882.5
122.5°	193.3	235.4	381.0	680.9	818.1
125°	204.6	252.2	378.2	638.8	762.1
127.5°	215.7	263.4	378.2	608.0	711.7
130°	227.0	269.0	375.4	577.2	669.6
132.5°	238.1	271.7	375.4	554.8	633.2
135°	246.5	277.3	375.4	532.3	602.4
137.5°	257.8	283.0	375.4	512.7	577.2
140°	266.2	291.4	375.4	493.1	549.2
142.5°	277.3	299.8	375.4	473.5	523.9
145°	288.6	308.2	372.6	459.5	498.7
147.5°	299.8	316.6	369.8	445.5	476.3
150°	308.2	325.0	369.8	431.4	456.7
152.5°	319.4	333.4	367.0	417.5	439.9
155°	327.8	339.0	367.0	409.0	423.1
157.5°	336.2	347.4	367.0	400.6	411.9
160°	344.6	353.0	369.8	395.1	403.4
162.5°	353.0	358.7	369.8	389.5	395.1
165°	358.7	361.5	369.8	386.7	389.5
167.5°	364.3	367.0	369.8	383.8	383.8
170°	367.0	369.8	372.6	381.0	381.0
172.5°	372.6	372.6	372.6	378.2	378.2
175°	375.4	375.4	372.6	378.2	375.4
177.5°	375.4	375.4	372.6	378.2	375.4
180°	375.4	375.4	375.4	375.4	375.4



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	103.7	137.3	495.9	986.2	997.5
110°	117.6	151.3	456.7	977.8	1059.1



(END OF REPORT)