

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P844911

Luminaire Tested: **SQ4P-F-050U-100D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P844911
REPORT IS A COMBINATION OF REPORTS P700193 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-F-050U-100D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5438.6 lumens
Efficiency: N/A
Efficacy: 113.5 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.35
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 47.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P844911

CATALOG NUMBER: SQ4P-F-050U-100D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P844911

CATALOG NUMBER: SQ4P-F-050U-100D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69																			
1	102	98	94	90	96	92	89	86	82	80	77	73	71	69	65	63	62	58																			
2	93	85	79	73	87	81	75	70	72	68	64	64	61	58	57	54	52	48																			
3	85	75	67	61	80	71	64	58	63	58	54	57	52	49	50	47	44	41																			
4	77	66	58	52	73	63	55	50	56	50	46	50	46	42	45	41	38	35																			
5	71	59	50	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30																			
6	66	53	44	38	62	50	43	37	45	39	34	41	36	32	37	32	29	26																			
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23																			
8	56	44	35	30	53	42	34	29	38	31	27	34	29	25	31	26	23	21																			
9	53	40	32	27	50	38	31	26	35	28	24	31	26	22	28	24	21	19																			
10	49	37	29	24	46	35	28	23	32	26	22	29	24	20	26	22	19	17																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	12657	12657	12657
5°	12690	12537	12638
10°	12646	12491	12577
15°	12559	12402	12508
20°	12440	12297	12388
25°	12300	12153	12266
30°	12130	12032	12111
35°	12000	11854	11914
40°	11771	11656	11679
45°	11526	11431	11431
50°	11283	11177	11127
55°	11020	10872	10813
60°	10608	10439	10372
65°	10103	9903	9780
70°	9414	9212	9015
75°	8441	8185	7985
80°	6833	6742	6540
85°	4065	4679	4848



TEST NUMBER: P844911

CATALOG NUMBER: SQ4P-F-050U-100D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.4	2.4
10°-20°	368.6	6.8
20°-30°	553.7	10.2
30°-40°	660.9	12.2
40°-50°	677.3	12.5
50°-60°	604.0	11.1
60°-70°	449.8	8.3
70°-80°	244.2	4.5
80°-90°	57.2	1.1
90°-100°	103.8	1.9
100°-110°	361.4	6.6
110°-120°	350.0	6.4
120°-130°	274.6	5.0
130°-140°	217.3	4.0
140°-150°	167.7	3.1
150°-160°	120.2	2.2
160°-170°	73.5	1.4
170°-180°	24.9	0.5
0°-30°	1051.7	19.3
0°-40°	1712.6	31.5
0°-60°	2993.9	55.0
0°-90°	3745.0	68.9
90°-120°	815.2	15.0
90°-150°	1474.9	27.1
90°-180°	1694.0	31.1
0°-180°	5438.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1372	1372	1372	1372	1372	
5°	1370	1368	1354	1366	1365	130
15°	1315	1311	1298	1310	1310	370
25°	1208	1205	1194	1201	1205	556
35°	1065	1062	1052	1052	1058	665
45°	883	885	876	874	876	682
55°	685	685	676	670	672	610
65°	463	461	454	448	448	458
75°	237	235	230	226	224	250
85°	38	42	44	46	46	54
90°	4	6	6	4	2	3
95°	18	60	175	45	27	19
105°	60	86	380	641	596	63
115°	105	127	282	596	703	104
125°	142	175	263	444	530	127
135°	171	193	261	370	419	133
145°	201	214	259	319	347	125
155°	228	236	255	284	294	105
165°	249	251	257	269	271	70
175°	261	261	259	263	261	25
180°	261	261	261	261	261	



TEST NUMBER: P844911

CATALOG NUMBER: SQ4P-F-050U-100D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1371.9	1371.9	1371.9	1371.9	1371.9
2.5°	1376.2	1373.5	1361.6	1371.9	1370.6
5°	1370.2	1368.3	1353.7	1366.4	1364.6
7.5°	1360.1	1356.7	1342.2	1354.8	1352.8
10°	1349.8	1346.2	1333.3	1344.3	1342.5
12.5°	1336.7	1334.6	1320.3	1331.2	1330.7
15°	1314.9	1311.2	1298.4	1309.5	1309.5
17.5°	1286.4	1284.2	1271.6	1282.1	1281.0
20°	1267.0	1263.7	1252.5	1261.7	1261.7
22.5°	1243.7	1241.6	1230.6	1238.2	1239.6
25°	1208.3	1204.9	1193.8	1201.3	1204.9
27.5°	1169.6	1166.8	1157.5	1162.3	1164.8
30°	1138.6	1138.6	1129.4	1131.4	1136.8
32.5°	1110.8	1110.8	1100.1	1102.0	1104.6
35°	1065.4	1061.7	1052.5	1052.5	1057.8
37.5°	1012.2	1010.5	1004.7	1003.7	1005.1
40°	977.3	975.4	967.8	969.7	969.7
42.5°	941.9	940.0	932.4	930.1	932.9
45°	883.4	885.3	876.1	874.2	876.1
47.5°	825.9	825.9	818.5	813.3	816.0
50°	786.1	786.1	778.7	775.2	775.2
52.5°	744.9	746.4	737.4	732.5	734.0
55°	685.1	685.1	675.9	670.5	672.2
57.5°	618.8	618.8	609.8	604.3	607.5
60°	574.9	574.9	565.7	560.1	562.1
62.5°	530.8	530.8	521.7	516.2	516.4
65°	462.8	461.1	453.6	448.0	448.0
67.5°	397.4	392.7	387.1	379.9	379.9
70°	349.0	347.0	341.5	334.2	334.2
72.5°	304.9	301.6	296.0	290.2	290.2
75°	236.8	234.9	229.6	226.0	224.0
77.5°	169.8	168.2	167.8	162.7	164.2
80°	128.6	128.6	126.9	123.1	123.1
82.5°	91.8	93.2	90.0	89.2	87.7
85°	38.4	42.1	44.2	45.8	45.8
87.5°	7.5	11.5	10.3	11.8	11.8
90°	3.9	5.8	5.8	3.9	1.9
92.5°	9.7	29.2	27.2	11.7	9.7
95°	17.5	60.4	175.3	44.8	27.2
97.5°	27.2	68.1	350.5	159.7	85.7
100°	37.0	72.1	408.9	383.7	247.3
102.5°	48.6	77.9	407.0	539.4	444.0
105°	60.4	85.7	379.8	640.6	595.9



TEST NUMBER: P844911

CATALOG NUMBER: SQ4P-F-050U-100D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	93.5	114.9	296.0	644.6	734.2
115°	105.1	126.6	282.4	595.9	703.0
117.5°	116.9	140.2	274.5	551.1	658.2
120°	126.6	151.9	268.7	508.3	613.4
122.5°	134.4	163.6	264.8	473.2	568.6
125°	142.2	175.3	262.9	444.0	529.7
127.5°	149.9	183.1	262.9	422.6	494.6
130°	157.8	186.9	261.0	401.2	465.4
132.5°	165.5	188.9	261.0	385.6	440.1
135°	171.3	192.7	261.0	370.0	418.7
137.5°	179.2	196.7	261.0	356.3	401.2
140°	185.0	202.5	261.0	342.8	381.7
142.5°	192.7	208.3	261.0	329.1	364.2
145°	200.6	214.3	259.0	319.4	346.6
147.5°	208.3	220.1	257.1	309.6	331.0
150°	214.3	225.9	257.1	299.9	317.5
152.5°	222.0	231.7	255.2	290.1	305.7
155°	227.8	235.7	255.2	284.3	294.0
157.5°	233.6	241.5	255.2	278.5	286.3
160°	239.6	245.4	257.1	274.5	280.4
162.5°	245.4	249.2	257.1	270.7	274.5
165°	249.2	251.2	257.1	268.7	270.7
167.5°	253.1	255.2	257.1	266.8	266.8
170°	255.2	257.1	259.0	264.8	264.8
172.5°	259.0	259.0	259.0	262.9	262.9
175°	261.0	261.0	259.0	262.9	261.0
177.5°	261.0	261.0	259.0	262.9	261.0
180°	261.0	261.0	261.0	261.0	261.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	72.1	95.5	344.7	685.5	693.3
110°	81.8	105.1	317.5	679.6	736.1



(END OF REPORT)