

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845013

Luminaire Tested: **SQ4P-PC3-0U-050D-B40-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845013  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P562810)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PC3-0U-050D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 500 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1875.2 lumens  
Efficiency: N/A  
Efficacy: 111.6 lumens/watt  
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845013

CATALOG NUMBER: SQ4P-PC3-0U-050D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845013

CATALOG NUMBER: SQ4P-PC3-OU-050D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85																			
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																			
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60																			
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51																			
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44																			
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39																			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34																			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31																			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28																			
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6338	6338	6338
5°	6388	6345	6322
10°	6372	6342	6324
15°	6338	6338	6332
20°	6296	6315	6315
25°	6236	6282	6263
30°	6160	6234	6208
35°	6070	6162	6119
40°	5969	6053	5992
45°	5861	5903	5810
50°	5707	5707	5616
55°	5525	5455	5373
60°	5259	5154	5071
65°	4860	4764	4722
70°	4257	4289	4273
75°	3422	3789	3811
80°	2433	3214	3246
85°	1493	2699	2699



TEST NUMBER: P845013

CATALOG NUMBER: SQ4P-PC3-OU-050D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	65.0	3.5
10°-20°	186.6	10.0
20°-30°	282.6	15.1
30°-40°	338.8	18.1
40°-50°	345.4	18.4
50°-60°	301.5	16.1
60°-70°	215.9	11.5
70°-80°	111.2	5.9
80°-90°	28.1	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	534.2	28.5
0°-40°	873.0	46.6
0°-60°	1520.0	81.1
0°-90°	1875.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1875.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	687	687	687	687	687	
5°	690	683	685	683	683	65
15°	664	658	664	664	663	187
25°	613	608	617	615	615	282
35°	539	538	547	543	543	337
45°	449	448	452	446	445	346
55°	344	339	339	334	334	306
65°	223	218	218	216	216	220
75°	96	100	106	107	107	104
85°	14	22	26	26	26	20
90°	0	0	0	0	0	



TEST NUMBER: P845013

CATALOG NUMBER: SQ4P-PC3-OU-050D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	687.0	687.0	687.0	687.0	687.0
2.5°	691.1	685.1	687.0	685.5	683.0
5°	689.7	682.7	685.1	683.2	682.6
7.5°	684.6	677.8	681.0	679.7	679.0
10°	680.1	673.2	676.9	675.6	675.0
12.5°	674.0	667.6	671.8	670.6	670.3
15°	663.5	658.0	663.5	663.5	662.9
17.5°	650.4	645.3	651.3	651.7	651.3
20°	641.3	635.7	643.2	642.5	643.2
22.5°	630.1	625.5	633.5	631.8	632.5
25°	612.6	608.3	617.1	615.2	615.2
27.5°	592.1	588.9	598.5	596.5	596.5
30°	578.2	575.1	585.2	582.7	582.7
32.5°	563.0	560.9	570.6	567.5	567.5
35°	538.9	537.5	547.1	543.3	543.3
37.5°	513.9	512.7	521.5	516.8	515.3
40°	495.6	495.0	502.6	497.5	497.5
42.5°	477.3	476.6	483.3	477.2	477.2
45°	449.2	447.8	452.4	446.5	445.3
47.5°	418.4	417.3	420.0	413.8	413.1
50°	397.6	396.3	397.6	391.8	391.3
52.5°	376.3	374.0	374.2	368.4	368.3
55°	343.5	339.2	339.1	334.0	334.0
57.5°	308.9	303.2	303.8	299.3	298.7
60°	285.0	278.8	279.3	275.5	274.8
62.5°	261.6	254.4	255.8	251.6	251.5
65°	222.6	217.7	218.2	216.3	216.3
67.5°	185.2	180.6	184.0	182.5	182.4
70°	157.8	154.7	159.0	159.0	158.4
72.5°	132.4	132.3	137.6	137.6	138.1
75°	96.0	100.5	106.3	106.9	106.9
77.5°	64.2	71.8	78.3	78.5	78.4
80°	45.8	54.5	60.5	61.7	61.1
82.5°	31.0	40.2	45.2	46.4	45.8
85°	14.1	21.5	25.5	26.1	25.5
87.5°	4.1	8.5	10.2	10.2	9.2
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)