

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845067

Luminaire Tested: **SQ4P-PP3-025U-100D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845067
REPORT IS A COMBINATION OF REPORTS P700173 AND P700243
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-025U-100D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4475.1 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 41.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845067

CATALOG NUMBER: SQ4P-PP3-025U-100D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845067

CATALOG NUMBER: SQ4P-PP3-025U-100D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	115	115	115	115	110	110	110	110	101	101	101	92	92	92	85	85	85	81			
1	105	101	97	93	101	97	93	90	89	86	84	82	80	78	76	74	72	69			
2	96	88	82	77	92	85	79	74	78	74	70	72	69	66	67	64	61	58			
3	88	78	70	64	84	75	68	63	69	64	59	64	60	56	59	56	53	50			
4	80	69	61	55	77	67	59	53	62	56	51	57	52	48	53	49	45	43			
5	74	62	53	47	71	60	52	46	56	49	44	52	46	42	48	43	40	37			
6	68	56	47	41	65	54	46	40	50	44	39	47	41	37	44	39	35	33			
7	63	51	42	36	61	49	41	36	46	39	34	43	37	33	40	35	31	29			
8	59	46	38	32	56	45	37	32	42	35	31	39	33	29	37	32	28	26			
9	55	42	34	29	53	41	34	29	38	32	27	36	30	26	34	29	25	23			
10	52	39	31	26	49	38	31	26	36	29	25	33	28	24	31	27	23	21			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13093	13093	13093
5°	13188	13108	13062
10°	13167	13074	13016
15°	13080	13008	12937
20°	12993	12919	12822
25°	12838	12750	12624
30°	12601	12535	12375
35°	12271	12188	12032
40°	11878	11803	11669
45°	11555	11474	11359
50°	11138	11068	10960
55°	10562	10423	10345
60°	9616	9341	9294
65°	8473	8117	8091
70°	7310	7011	7011
75°	6299	6206	6114
80°	5552	5616	5478
85°	4340	4742	4742



TEST NUMBER: P845067

CATALOG NUMBER: SQ4P-PP3-025U-100D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.2	3.0
10°-20°	383.2	8.6
20°-30°	573.9	12.8
30°-40°	673.2	15.0
40°-50°	675.2	15.1
50°-60°	576.1	12.9
60°-70°	375.7	8.4
70°-80°	188.5	4.2
80°-90°	52.5	1.2
90°-100°	51.7	1.2
100°-110°	179.8	4.0
110°-120°	174.2	3.9
120°-130°	136.6	3.1
130°-140°	108.2	2.4
140°-150°	83.5	1.9
150°-160°	59.8	1.3
160°-170°	36.6	0.8
170°-180°	12.4	0.3
0°-30°	1091.3	24.4
0°-40°	1764.4	39.4
0°-60°	3015.7	67.4
0°-90°	3632.4	81.2
90°-120°	405.7	9.1
90°-150°	734.0	16.4
90°-180°	843.0	18.8
0°-180°	4475.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1419	1419	1419	1419	1419	
5°	1424	1411	1415	1410	1410	135
15°	1369	1356	1362	1357	1354	386
25°	1261	1246	1252	1241	1240	580
35°	1090	1079	1082	1070	1068	681
45°	886	879	879	871	871	682
55°	657	654	648	644	643	584
65°	388	381	372	370	371	387
75°	177	177	174	173	172	192
85°	41	45	45	45	45	48
90°	2	3	3	2	1	3
95°	9	30	87	22	14	9
105°	30	43	189	319	297	32
115°	52	63	140	297	350	52
125°	71	87	131	221	264	63
135°	85	96	130	184	208	66
145°	100	107	129	159	172	62
155°	113	117	127	142	146	52
165°	124	125	128	134	135	35
175°	130	130	129	131	130	12
180°	130	130	130	130	130	



TEST NUMBER: P845067

CATALOG NUMBER: SQ4P-PP3-025U-100D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1419.1	1419.1	1419.1	1419.1	1419.1
2.5°	1427.9	1416.4	1419.1	1417.0	1411.2
5°	1424.0	1410.8	1415.3	1410.4	1410.4
7.5°	1414.4	1399.8	1404.4	1399.4	1399.2
10°	1405.4	1390.8	1395.5	1390.4	1389.3
12.5°	1392.5	1378.0	1383.5	1377.5	1377.3
15°	1369.4	1355.9	1361.9	1356.8	1354.4
17.5°	1343.2	1328.7	1335.8	1328.9	1327.8
20°	1323.3	1308.7	1315.8	1305.9	1305.9
22.5°	1299.5	1284.9	1293.0	1279.9	1279.9
25°	1261.1	1246.5	1252.5	1241.2	1240.1
27.5°	1215.6	1201.3	1207.5	1194.7	1194.4
30°	1182.8	1169.4	1176.6	1162.9	1161.6
32.5°	1147.0	1134.6	1139.7	1126.1	1124.7
35°	1089.5	1078.6	1082.1	1069.7	1068.3
37.5°	1029.0	1017.9	1021.8	1011.0	1010.6
40°	986.2	978.9	980.0	971.2	968.9
42.5°	946.5	938.1	939.2	930.4	930.0
45°	885.6	879.4	879.4	870.6	870.6
47.5°	820.9	816.1	814.9	807.5	807.3
50°	776.0	772.4	771.1	764.9	763.6
52.5°	729.3	727.6	723.3	718.2	718.0
55°	656.6	654.2	648.0	644.1	643.1
57.5°	577.9	573.0	565.9	560.5	561.4
60°	521.1	516.1	506.2	503.7	503.7
62.5°	466.4	460.6	450.5	447.1	449.1
65°	388.1	380.8	371.8	369.5	370.6
67.5°	317.0	310.3	300.6	300.6	299.8
70°	271.0	267.4	259.9	259.9	259.9
72.5°	230.3	228.6	223.3	223.0	222.1
75°	176.7	176.7	174.1	172.9	171.5
77.5°	132.3	132.8	131.7	130.3	128.0
80°	104.5	107.0	105.7	104.5	103.1
82.5°	78.7	81.0	80.8	78.7	78.3
85°	41.0	44.6	44.8	44.8	44.8
87.5°	11.0	14.8	15.9	15.9	17.0
90°	1.9	2.9	2.9	1.9	1.0
92.5°	4.8	14.5	13.6	5.8	4.8
95°	8.7	30.0	87.2	22.3	13.6
97.5°	13.6	33.9	174.4	79.5	42.6
100°	18.4	35.9	203.5	190.9	123.1
102.5°	24.2	38.8	202.5	268.4	220.9
105°	30.0	42.6	189.0	318.9	296.6



TEST NUMBER: P845067

CATALOG NUMBER: SQ4P-PP3-025U-100D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	46.5	57.2	147.3	320.9	365.4
115°	52.3	63.0	140.5	296.6	349.9
117.5°	58.1	69.8	136.6	274.2	327.6
120°	63.0	75.6	133.7	252.9	305.4
122.5°	66.9	81.4	131.8	235.5	283.1
125°	70.7	87.2	130.8	220.9	263.6
127.5°	74.6	91.1	130.8	210.3	246.1
130°	78.5	93.0	129.9	199.6	231.6
132.5°	82.4	94.0	129.9	191.9	219.0
135°	85.3	95.9	129.9	184.1	208.3
137.5°	89.2	97.9	129.9	177.3	199.6
140°	92.1	100.8	129.9	170.6	189.9
142.5°	95.9	103.7	129.9	163.8	181.2
145°	99.8	106.6	128.9	158.9	172.5
147.5°	103.7	109.5	127.9	154.1	164.7
150°	106.6	112.4	127.9	149.2	158.0
152.5°	110.5	115.3	126.9	144.4	152.1
155°	113.4	117.3	126.9	141.5	146.3
157.5°	116.3	120.2	126.9	138.6	142.5
160°	119.2	122.1	127.9	136.6	139.5
162.5°	122.1	124.0	127.9	134.7	136.6
165°	124.0	125.0	127.9	133.7	134.7
167.5°	126.0	126.9	127.9	132.8	132.8
170°	126.9	127.9	128.9	131.8	131.8
172.5°	128.9	128.9	128.9	130.8	130.8
175°	129.9	129.9	128.9	130.8	129.9
177.5°	129.9	129.9	128.9	130.8	129.9
180°	129.9	129.9	129.9	129.9	129.9



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	35.9	47.5	171.5	341.2	345.1
110°	40.7	52.3	158.0	338.3	366.4



(END OF REPORT)