

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845001

Luminaire Tested: **SQ4P-PC3-075U-050D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845001
REPORT IS A COMBINATION OF REPORTS P700223 AND P700245
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-075U-050D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT
UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4312.6 lumens
Efficiency: N/A
Efficacy: 120.5 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 35.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845001

CATALOG NUMBER: SQ4P-PC3-075U-050D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845001

CATALOG NUMBER: SQ4P-PC3-075U-050D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44								
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	44	43	42	37								
2	88	80	74	69	80	74	69	64	61	57	54	50	47	45	39	37	36	31								
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	32	30	26								
4	73	62	55	49	67	57	51	45	48	43	39	39	35	32	31	28	26	22								
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	28	25	23	19								
6	62	50	42	36	56	46	39	34	38	33	29	32	28	24	25	22	20	17								
7	57	45	37	31	52	41	34	29	35	29	25	29	25	22	23	20	18	15								
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13								
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12								
10	46	34	27	22	42	31	25	21	27	22	18	22	18	15	18	15	13	11								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6338	6338	6338
5°	6388	6345	6322
10°	6372	6342	6324
15°	6338	6338	6332
20°	6296	6315	6315
25°	6236	6282	6263
30°	6160	6234	6208
35°	6070	6162	6119
40°	5969	6053	5992
45°	5861	5903	5810
50°	5707	5707	5616
55°	5525	5455	5373
60°	5259	5154	5071
65°	4860	4764	4722
70°	4257	4289	4273
75°	3422	3789	3811
80°	2433	3214	3246
85°	1493	2699	2699



TEST NUMBER: P845001

CATALOG NUMBER: SQ4P-PC3-075U-050D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.0	1.5
10°-20°	186.6	4.3
20°-30°	282.6	6.6
30°-40°	338.8	7.9
40°-50°	345.4	8.0
50°-60°	301.5	7.0
60°-70°	215.9	5.0
70°-80°	111.2	2.6
80°-90°	29.0	0.7
90°-100°	149.4	3.5
100°-110°	519.9	12.1
110°-120°	503.6	11.7
120°-130°	395.1	9.2
130°-140°	312.7	7.3
140°-150°	241.3	5.6
150°-160°	173.0	4.0
160°-170°	105.8	2.5
170°-180°	35.8	0.8
0°-30°	534.2	12.4
0°-40°	873.0	20.2
0°-60°	1520.0	35.2
0°-90°	1876.1	43.5
90°-120°	1172.9	27.2
90°-150°	2122.0	49.2
90°-180°	2437.0	56.5
0°-180°	4312.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	687	687	687	687	687	
5°	690	683	685	683	683	65
15°	664	658	664	664	663	187
25°	613	608	617	615	615	282
35°	539	538	547	543	543	337
45°	449	448	452	446	445	346
55°	344	339	339	334	334	306
65°	223	218	218	216	216	220
75°	96	100	106	107	107	104
85°	14	22	26	26	26	19
90°	6	8	8	6	3	4
95°	25	87	252	64	39	27
105°	87	123	546	922	857	91
115°	151	182	406	857	1011	149
125°	205	252	378	639	762	183
135°	246	277	375	532	602	191
145°	289	308	373	460	499	181
155°	328	339	367	409	423	151
165°	359	362	370	387	390	101
175°	375	375	373	378	375	36
180°	375	375	375	375	375	



TEST NUMBER: P845001

CATALOG NUMBER: SQ4P-PC3-075U-050D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	687.0	687.0	687.0	687.0	687.0
2.5°	691.1	685.1	687.0	685.5	683.0
5°	689.7	682.7	685.1	683.2	682.6
7.5°	684.6	677.8	681.0	679.7	679.0
10°	680.1	673.2	676.9	675.6	675.0
12.5°	674.0	667.6	671.8	670.6	670.3
15°	663.5	658.0	663.5	663.5	662.9
17.5°	650.4	645.3	651.3	651.7	651.3
20°	641.3	635.7	643.2	642.5	643.2
22.5°	630.1	625.5	633.5	631.8	632.5
25°	612.6	608.3	617.1	615.2	615.2
27.5°	592.1	588.9	598.5	596.5	596.5
30°	578.2	575.1	585.2	582.7	582.7
32.5°	563.0	560.9	570.6	567.5	567.5
35°	538.9	537.5	547.1	543.3	543.3
37.5°	513.9	512.7	521.5	516.8	515.3
40°	495.6	495.0	502.6	497.5	497.5
42.5°	477.3	476.6	483.3	477.2	477.2
45°	449.2	447.8	452.4	446.5	445.3
47.5°	418.4	417.3	420.0	413.8	413.1
50°	397.6	396.3	397.6	391.8	391.3
52.5°	376.3	374.0	374.2	368.4	368.3
55°	343.5	339.2	339.1	334.0	334.0
57.5°	308.9	303.2	303.8	299.3	298.7
60°	285.0	278.8	279.3	275.5	274.8
62.5°	261.6	254.4	255.8	251.6	251.5
65°	222.6	217.7	218.2	216.3	216.3
67.5°	185.2	180.6	184.0	182.5	182.4
70°	157.8	154.7	159.0	159.0	158.4
72.5°	132.4	132.3	137.6	137.6	138.1
75°	96.0	100.5	106.3	106.9	106.9
77.5°	64.2	71.8	78.3	78.5	78.4
80°	45.8	54.5	60.5	61.7	61.1
82.5°	31.0	40.2	45.2	46.4	45.8
85°	14.1	21.5	25.5	26.1	25.5
87.5°	4.1	8.5	10.2	10.2	9.2
90°	5.6	8.4	8.4	5.6	2.8
92.5°	14.1	42.1	39.2	16.8	14.1
95°	25.2	86.8	252.2	64.4	39.2
97.5°	39.2	98.1	504.3	229.8	123.3
100°	53.2	103.7	588.3	552.0	355.8
102.5°	70.1	112.0	585.6	776.1	638.8
105°	86.8	123.3	546.4	921.8	857.3



TEST NUMBER: P845001

CATALOG NUMBER: SQ4P-PC3-075U-050D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	134.5	165.3	425.9	927.4	1056.3
115°	151.3	182.1	406.2	857.3	1011.4
117.5°	168.1	201.8	395.1	792.9	947.0
120°	182.1	218.5	386.7	731.3	882.5
122.5°	193.3	235.4	381.0	680.9	818.1
125°	204.6	252.2	378.2	638.8	762.1
127.5°	215.7	263.4	378.2	608.0	711.7
130°	227.0	269.0	375.4	577.2	669.6
132.5°	238.1	271.7	375.4	554.8	633.2
135°	246.5	277.3	375.4	532.3	602.4
137.5°	257.8	283.0	375.4	512.7	577.2
140°	266.2	291.4	375.4	493.1	549.2
142.5°	277.3	299.8	375.4	473.5	523.9
145°	288.6	308.2	372.6	459.5	498.7
147.5°	299.8	316.6	369.8	445.5	476.3
150°	308.2	325.0	369.8	431.4	456.7
152.5°	319.4	333.4	367.0	417.5	439.9
155°	327.8	339.0	367.0	409.0	423.1
157.5°	336.2	347.4	367.0	400.6	411.9
160°	344.6	353.0	369.8	395.1	403.4
162.5°	353.0	358.7	369.8	389.5	395.1
165°	358.7	361.5	369.8	386.7	389.5
167.5°	364.3	367.0	369.8	383.8	383.8
170°	367.0	369.8	372.6	381.0	381.0
172.5°	372.6	372.6	372.6	378.2	378.2
175°	375.4	375.4	372.6	378.2	375.4
177.5°	375.4	375.4	372.6	378.2	375.4
180°	375.4	375.4	375.4	375.4	375.4



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	103.7	137.3	495.9	986.2	997.5
110°	117.6	151.3	456.7	977.8	1059.1



(END OF REPORT)