

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845088

Luminaire Tested: **SQ4P-PP3-075U-075D-B40-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845088  
REPORT IS A COMBINATION OF REPORTS P700228 AND P700245  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-075U-075D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 750 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5201.2 lumens  
Efficiency: N/A  
Efficacy: 116.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 44.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845088

CATALOG NUMBER: SQ4P-PP3-075U-075D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845088

CATALOG NUMBER: SQ4P-PP3-075U-075D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53								
1	99	94	91	87	91	88	84	81	75	73	70	63	62	60	53	51	50	45								
2	90	83	77	72	83	77	72	67	66	62	59	56	53	50	46	44	43	38								
3	82	73	66	60	76	68	61	56	58	53	49	49	46	43	41	39	36	33								
4	75	65	57	51	69	60	53	48	52	46	42	44	40	37	37	34	32	28								
5	69	58	49	43	64	54	47	41	46	41	36	40	35	32	33	30	28	24								
6	64	52	44	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21								
7	59	47	39	33	54	44	37	31	38	32	28	33	28	25	28	24	22	19								
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17								
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	15								
10	48	36	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	9963	9963	9963
5°	10036	9974	9938
10°	10020	9948	9904
15°	9953	9898	9844
20°	9887	9830	9756
25°	9770	9703	9607
30°	9589	9538	9417
35°	9337	9274	9156
40°	9038	8981	8880
45°	8793	8730	8644
50°	8476	8423	8341
55°	8036	7933	7872
60°	7316	7110	7073
65°	6449	6178	6156
70°	5562	5336	5336
75°	4791	4723	4652
80°	4224	4272	4171
85°	3303	3610	3610



TEST NUMBER: P845088

CATALOG NUMBER: SQ4P-PP3-075U-075D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.1	2.0
10°-20°	291.6	5.6
20°-30°	436.7	8.4
30°-40°	512.2	9.8
40°-50°	513.8	9.9
50°-60°	438.4	8.4
60°-70°	285.9	5.5
70°-80°	143.4	2.8
80°-90°	40.6	0.8
90°-100°	149.4	2.9
100°-110°	519.9	10.0
110°-120°	503.6	9.7
120°-130°	395.1	7.6
130°-140°	312.7	6.0
140°-150°	241.3	4.6
150°-160°	173.0	3.3
160°-170°	105.8	2.0
170°-180°	35.8	0.7
0°-30°	830.4	16.0
0°-40°	1342.6	25.8
0°-60°	2294.8	44.1
0°-90°	2764.7	53.2
90°-120°	1172.9	22.6
90°-150°	2122.0	40.8
90°-180°	2437.0	46.9
0°-180°	5201.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1080	1080	1080	1080	1080	
5°	1084	1074	1077	1073	1073	103
15°	1042	1032	1036	1032	1031	294
25°	960	948	953	944	944	441
35°	829	821	823	814	813	518
45°	674	669	669	662	662	519
55°	500	498	493	490	489	444
65°	295	290	283	281	282	295
75°	134	134	132	132	130	146
85°	31	34	34	34	34	37
90°	6	8	8	6	3	5
95°	25	87	252	64	39	27
105°	87	123	546	922	857	91
115°	151	182	406	857	1011	149
125°	205	252	378	639	762	183
135°	246	277	375	532	602	191
145°	289	308	373	460	499	181
155°	328	339	367	409	423	151
165°	359	362	370	387	390	101
175°	375	375	373	378	375	36
180°	375	375	375	375	375	



TEST NUMBER: P845088

CATALOG NUMBER: SQ4P-PP3-075U-075D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1079.9	1079.9	1079.9	1079.9	1079.9
2.5°	1086.6	1077.8	1079.9	1078.3	1073.8
5°	1083.6	1073.5	1076.9	1073.1	1073.1
7.5°	1076.2	1065.2	1068.6	1064.9	1064.7
10°	1069.5	1058.3	1061.9	1058.0	1057.2
12.5°	1059.7	1048.5	1052.8	1048.2	1048.0
15°	1042.0	1031.8	1036.3	1032.4	1030.6
17.5°	1022.1	1011.0	1016.5	1011.2	1010.3
20°	1007.0	995.8	1001.2	993.7	993.7
22.5°	988.8	977.7	983.9	974.0	974.0
25°	959.7	948.5	953.1	944.4	943.7
27.5°	925.1	914.1	918.9	909.1	908.9
30°	900.1	889.8	895.3	884.9	883.9
32.5°	872.8	863.3	867.3	856.8	855.9
35°	829.0	820.8	823.4	813.9	812.9
37.5°	783.1	774.6	777.5	769.3	769.0
40°	750.4	744.9	745.7	739.0	737.3
42.5°	720.2	713.9	714.7	708.0	707.7
45°	673.9	669.1	669.1	662.5	662.5
47.5°	624.7	621.1	620.1	614.5	614.4
50°	590.5	587.7	586.8	582.0	581.1
52.5°	555.0	553.6	550.4	546.5	546.3
55°	499.6	497.8	493.2	490.2	489.4
57.5°	439.8	436.0	430.7	426.6	427.2
60°	396.5	392.8	385.3	383.3	383.3
62.5°	354.9	350.5	342.9	340.2	341.7
65°	295.4	289.7	283.0	281.1	282.0
67.5°	241.2	236.1	228.8	228.8	228.1
70°	206.2	203.5	197.8	197.8	197.8
72.5°	175.2	173.9	169.9	169.7	169.0
75°	134.4	134.4	132.5	131.5	130.5
77.5°	100.7	101.0	100.2	99.2	97.4
80°	79.5	81.4	80.4	79.5	78.5
82.5°	59.9	61.6	61.5	59.9	59.6
85°	31.2	33.9	34.1	34.1	34.1
87.5°	8.3	11.2	12.1	12.1	12.9
90°	5.6	8.4	8.4	5.6	2.8
92.5°	14.1	42.1	39.2	16.8	14.1
95°	25.2	86.8	252.2	64.4	39.2
97.5°	39.2	98.1	504.3	229.8	123.3
100°	53.2	103.7	588.3	552.0	355.8
102.5°	70.1	112.0	585.6	776.1	638.8
105°	86.8	123.3	546.4	921.8	857.3



TEST NUMBER: P845088

CATALOG NUMBER: SQ4P-PP3-075U-075D-B40-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	134.5	165.3	425.9	927.4	1056.3
115°	151.3	182.1	406.2	857.3	1011.4
117.5°	168.1	201.8	395.1	792.9	947.0
120°	182.1	218.5	386.7	731.3	882.5
122.5°	193.3	235.4	381.0	680.9	818.1
125°	204.6	252.2	378.2	638.8	762.1
127.5°	215.7	263.4	378.2	608.0	711.7
130°	227.0	269.0	375.4	577.2	669.6
132.5°	238.1	271.7	375.4	554.8	633.2
135°	246.5	277.3	375.4	532.3	602.4
137.5°	257.8	283.0	375.4	512.7	577.2
140°	266.2	291.4	375.4	493.1	549.2
142.5°	277.3	299.8	375.4	473.5	523.9
145°	288.6	308.2	372.6	459.5	498.7
147.5°	299.8	316.6	369.8	445.5	476.3
150°	308.2	325.0	369.8	431.4	456.7
152.5°	319.4	333.4	367.0	417.5	439.9
155°	327.8	339.0	367.0	409.0	423.1
157.5°	336.2	347.4	367.0	400.6	411.9
160°	344.6	353.0	369.8	395.1	403.4
162.5°	353.0	358.7	369.8	389.5	395.1
165°	358.7	361.5	369.8	386.7	389.5
167.5°	364.3	367.0	369.8	383.8	383.8
170°	367.0	369.8	372.6	381.0	381.0
172.5°	372.6	372.6	372.6	378.2	378.2
175°	375.4	375.4	372.6	378.2	375.4
177.5°	375.4	375.4	372.6	378.2	375.4
180°	375.4	375.4	375.4	375.4	375.4



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	103.7	137.3	495.9	986.2	997.5
110°	117.6	151.3	456.7	977.8	1059.1



(END OF REPORT)