

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845016

Luminaire Tested: **SQ4P-PC3-0U-075D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845016
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P562810)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-0U-075D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2789.9 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 25.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845016

CATALOG NUMBER: SQ4P-PC3-0U-075D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845016

CATALOG NUMBER: SQ4P-PC3-OU-075D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	100	97	106	102	98	95	98	95	92	94	92	89	91	88	87	85																			
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71																			
3	91	80	72	66	88	79	71	65	76	70	64	73	68	63	71	66	62	60																			
4	83	71	63	56	81	70	62	56	68	61	55	65	59	54	63	58	53	51																			
5	77	64	55	48	74	63	54	48	61	53	48	59	52	47	57	51	47	44																			
6	71	58	49	42	69	57	48	42	55	47	42	53	46	41	52	46	41	39																			
7	66	52	43	37	64	51	43	37	50	42	37	48	42	37	47	41	36	34																			
8	61	48	39	33	60	47	39	33	46	38	33	44	38	33	43	37	33	31																			
9	57	44	36	30	56	43	35	30	42	35	30	41	34	30	40	34	29	28																			
10	54	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	27	25																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9431	9431	9431
5°	9503	9441	9407
10°	9480	9435	9408
15°	9430	9430	9421
20°	9368	9395	9395
25°	9280	9346	9318
30°	9165	9277	9237
35°	9030	9168	9104
40°	8880	9005	8916
45°	8720	8781	8644
50°	8491	8491	8355
55°	8223	8115	7993
60°	7826	7667	7543
65°	7230	7086	7023
70°	6334	6380	6361
75°	5094	5636	5671
80°	3624	4777	4830
85°	2212	4012	4012



TEST NUMBER: P845016

CATALOG NUMBER: SQ4P-PC3-OU-075D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.7	3.5
10°-20°	277.6	10.0
20°-30°	420.4	15.1
30°-40°	504.1	18.1
40°-50°	513.9	18.4
50°-60°	448.6	16.1
60°-70°	321.2	11.5
70°-80°	165.5	5.9
80°-90°	41.9	1.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	794.8	28.5
0°-40°	1298.9	46.6
0°-60°	2261.4	81.1
0°-90°	2789.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2789.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1022	1022	1022	1022	1022	
5°	1026	1016	1019	1016	1016	97
15°	987	979	987	987	986	278
25°	912	905	918	915	915	420
35°	802	800	814	808	808	501
45°	668	666	673	664	662	514
55°	511	505	504	497	497	456
65°	331	324	325	322	322	328
75°	143	149	158	159	159	154
85°	21	32	38	39	38	29
90°	0	0	0	0	0	



TEST NUMBER: P845016

CATALOG NUMBER: SQ4P-PC3-OU-075D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1022.2	1022.2	1022.2	1022.2	1022.2
2.5°	1028.4	1019.4	1022.2	1019.9	1016.2
5°	1026.1	1015.8	1019.4	1016.5	1015.7
7.5°	1018.6	1008.5	1013.3	1011.2	1010.2
10°	1011.9	1001.6	1007.1	1005.2	1004.2
12.5°	1002.8	993.3	999.5	997.7	997.4
15°	987.3	978.9	987.3	987.3	986.3
17.5°	967.7	960.1	969.0	969.6	969.0
20°	954.1	945.8	956.9	956.0	956.9
22.5°	937.5	930.7	942.5	940.1	941.1
25°	911.6	905.0	918.1	915.3	915.3
27.5°	880.9	876.1	890.5	887.4	887.4
30°	860.3	855.8	870.8	867.0	867.0
32.5°	837.7	834.6	848.9	844.3	844.3
35°	801.7	799.8	814.0	808.3	808.3
37.5°	764.6	762.9	775.8	769.0	766.7
40°	737.3	736.5	747.7	740.3	740.3
42.5°	710.0	709.1	719.0	709.9	709.9
45°	668.3	666.3	673.0	664.4	662.5
47.5°	622.6	620.8	624.9	615.5	614.6
50°	591.6	589.7	591.6	583.0	582.1
52.5°	559.8	556.3	556.7	548.2	548.0
55°	511.2	504.7	504.5	496.9	496.9
57.5°	459.6	451.1	452.0	445.4	444.4
60°	424.1	414.8	415.5	409.8	408.8
62.5°	389.2	378.5	380.6	374.3	374.2
65°	331.2	323.9	324.6	321.7	321.7
67.5°	275.6	268.7	273.8	271.5	271.3
70°	234.8	230.1	236.5	236.5	235.8
72.5°	196.9	196.7	204.8	204.8	205.4
75°	142.9	149.4	158.1	159.1	159.1
77.5°	95.5	106.9	116.5	116.8	116.7
80°	68.2	81.1	89.9	91.9	90.9
82.5°	46.1	59.9	67.3	69.0	68.2
85°	20.9	32.0	37.9	38.9	37.9
87.5°	6.0	12.7	15.2	15.2	13.7
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)