

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845115

Luminaire Tested: **SQ4P-PP3-100U-100D-B40-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P845115  
REPORT IS A COMBINATION OF REPORTS P700089 AND P700246  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-100U-100D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1000 LUMENS PER FOOT  
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6902.0 lumens  
Efficiency: N/A  
Efficacy: 113.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 60.9  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845115

CATALOG NUMBER: SQ4P-PP3-100U-100D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845115

CATALOG NUMBER: SQ4P-PP3-100U-100D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53								
1	99	94	91	87	91	88	84	81	75	72	70	63	61	60	52	51	50	45								
2	90	83	77	71	83	77	71	67	66	62	58	55	53	50	46	44	42	38								
3	82	73	65	60	76	68	61	56	58	53	49	49	46	43	41	38	36	32								
4	75	64	57	51	69	60	53	48	52	46	42	44	40	37	37	34	31	28								
5	69	57	49	43	64	54	46	41	46	41	36	39	35	32	33	30	27	24								
6	64	52	43	38	59	48	41	36	42	36	32	36	31	28	30	27	24	21								
7	59	47	39	33	54	44	36	31	38	32	28	32	28	25	27	24	21	19								
8	55	42	35	29	51	40	33	28	35	29	25	30	25	22	25	22	19	17								
9	51	39	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17	15								
10	48	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16	14								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	13093	13093	13093
5°	13188	13108	13062
10°	13167	13074	13016
15°	13080	13008	12937
20°	12993	12919	12822
25°	12838	12750	12624
30°	12601	12535	12375
35°	12271	12188	12032
40°	11878	11803	11669
45°	11555	11474	11359
50°	11138	11068	10960
55°	10562	10423	10345
60°	9616	9341	9294
65°	8473	8117	8091
70°	7310	7011	7011
75°	6299	6206	6114
80°	5552	5616	5478
85°	4340	4742	4742



TEST NUMBER: P845115

CATALOG NUMBER: SQ4P-PP3-100U-100D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.2	1.9
10°-20°	383.2	5.6
20°-30°	573.9	8.3
30°-40°	673.2	9.8
40°-50°	675.2	9.8
50°-60°	576.1	8.3
60°-70°	375.7	5.4
70°-80°	188.5	2.7
80°-90°	53.4	0.8
90°-100°	200.5	2.9
100°-110°	697.4	10.1
110°-120°	675.6	9.8
120°-130°	530.0	7.7
130°-140°	419.5	6.1
140°-150°	323.7	4.7
150°-160°	232.1	3.4
160°-170°	141.9	2.1
170°-180°	48.0	0.7
0°-30°	1091.3	15.8
0°-40°	1764.4	25.6
0°-60°	3015.7	43.7
0°-90°	3633.3	52.6
90°-120°	1573.5	22.8
90°-150°	2846.7	41.2
90°-180°	3269.0	47.4
0°-180°	6902.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1419	1419	1419	1419	1419	
5°	1424	1411	1415	1410	1410	135
15°	1369	1356	1362	1357	1354	386
25°	1261	1246	1252	1241	1240	580
35°	1090	1079	1082	1070	1068	681
45°	886	879	879	871	871	682
55°	657	654	648	644	643	584
65°	388	381	372	370	371	387
75°	177	177	174	173	172	192
85°	41	45	45	45	45	48
90°	8	11	11	8	4	6
95°	34	116	338	86	53	36
105°	116	165	733	1237	1150	122
115°	203	244	545	1150	1357	200
125°	274	338	507	857	1022	246
135°	331	372	504	714	808	256
145°	387	414	500	616	669	242
155°	440	455	492	549	568	203
165°	481	485	496	519	522	136
175°	504	504	500	507	504	48
180°	504	504	504	504	504	



TEST NUMBER: P845115

CATALOG NUMBER: SQ4P-PP3-100U-100D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1419.1	1419.1	1419.1	1419.1	1419.1
2.5°	1427.9	1416.4	1419.1	1417.0	1411.2
5°	1424.0	1410.8	1415.3	1410.4	1410.4
7.5°	1414.4	1399.8	1404.4	1399.4	1399.2
10°	1405.4	1390.8	1395.5	1390.4	1389.3
12.5°	1392.5	1378.0	1383.5	1377.5	1377.3
15°	1369.4	1355.9	1361.9	1356.8	1354.4
17.5°	1343.2	1328.7	1335.8	1328.9	1327.8
20°	1323.3	1308.7	1315.8	1305.9	1305.9
22.5°	1299.5	1284.9	1293.0	1279.9	1279.9
25°	1261.1	1246.5	1252.5	1241.2	1240.1
27.5°	1215.6	1201.3	1207.5	1194.7	1194.4
30°	1182.8	1169.4	1176.6	1162.9	1161.6
32.5°	1147.0	1134.6	1139.7	1126.1	1124.7
35°	1089.5	1078.6	1082.1	1069.7	1068.3
37.5°	1029.0	1017.9	1021.8	1011.0	1010.6
40°	986.2	978.9	980.0	971.2	968.9
42.5°	946.5	938.1	939.2	930.4	930.0
45°	885.6	879.4	879.4	870.6	870.6
47.5°	820.9	816.1	814.9	807.5	807.3
50°	776.0	772.4	771.1	764.9	763.6
52.5°	729.3	727.6	723.3	718.2	718.0
55°	656.6	654.2	648.0	644.1	643.1
57.5°	577.9	573.0	565.9	560.5	561.4
60°	521.1	516.1	506.2	503.7	503.7
62.5°	466.4	460.6	450.5	447.1	449.1
65°	388.1	380.8	371.8	369.5	370.6
67.5°	317.0	310.3	300.6	300.6	299.8
70°	271.0	267.4	259.9	259.9	259.9
72.5°	230.3	228.6	223.3	223.0	222.1
75°	176.7	176.7	174.1	172.9	171.5
77.5°	132.3	132.8	131.7	130.3	128.0
80°	104.5	107.0	105.7	104.5	103.1
82.5°	78.7	81.0	80.8	78.7	78.3
85°	41.0	44.6	44.8	44.8	44.8
87.5°	11.0	14.8	15.9	15.9	17.0
90°	7.6	11.2	11.2	7.6	3.8
92.5°	18.8	56.4	52.6	22.6	18.8
95°	33.8	116.5	338.3	86.4	52.6
97.5°	52.6	131.6	676.6	308.3	165.4
100°	71.4	139.1	789.3	740.5	477.4
102.5°	94.0	150.3	785.5	1041.2	856.9
105°	116.5	165.4	732.9	1236.6	1150.2



TEST NUMBER: P845115

CATALOG NUMBER: SQ4P-PP3-100U-100D-B40-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	180.4	221.7	571.4	1244.1	1417.1
115°	202.9	244.3	545.0	1150.2	1356.9
117.5°	225.5	270.7	530.0	1063.7	1270.4
120°	244.3	293.1	518.7	981.0	1184.0
122.5°	259.3	315.7	511.2	913.3	1097.6
125°	274.3	338.3	507.4	856.9	1022.4
127.5°	289.5	353.3	507.4	815.7	954.7
130°	304.5	360.9	503.6	774.3	898.3
132.5°	319.5	364.6	503.6	744.2	849.5
135°	330.7	372.1	503.6	714.2	808.1
137.5°	345.8	379.6	503.6	687.8	774.3
140°	357.1	390.9	503.6	661.5	736.7
142.5°	372.1	402.2	503.6	635.2	702.9
145°	387.1	413.5	499.9	616.4	669.0
147.5°	402.2	424.7	496.2	597.6	639.0
150°	413.5	436.0	496.2	578.8	612.6
152.5°	428.5	447.3	492.4	560.0	590.2
155°	439.8	454.8	492.4	548.8	567.6
157.5°	451.0	466.1	492.4	537.5	552.6
160°	462.3	473.6	496.2	530.0	541.2
162.5°	473.6	481.1	496.2	522.4	530.0
165°	481.1	484.9	496.2	518.7	522.4
167.5°	488.6	492.4	496.2	515.0	515.0
170°	492.4	496.2	499.9	511.2	511.2
172.5°	499.9	499.9	499.9	507.4	507.4
175°	503.6	503.6	499.9	507.4	503.6
177.5°	503.6	503.6	499.9	507.4	503.6
180°	503.6	503.6	503.6	503.6	503.6



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	139.1	184.2	665.3	1323.1	1338.1
110°	157.9	202.9	612.6	1311.8	1420.7



(END OF REPORT)