

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845058

Luminaire Tested: **SQ4P-PC3-150U-125D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845058
REPORT IS A COMBINATION OF REPORTS P700142 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PC3-150U-125D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9506.1 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.26 / 1.26 / 1.37
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 88.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845058

CATALOG NUMBER: SQ4P-PC3-150U-125D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845058

CATALOG NUMBER: SQ4P-PC3-150U-125D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	55	55	55	48				48															
1	97	93	89	86	90	86	83	80	72	70	68	60	58	57	48	47	46				41																
2	89	81	75	70	81	75	70	65	63	59	56	53	50	47	42	41	39				34																
3	81	71	64	58	74	66	60	55	56	51	47	46	43	40	38	35	33				29																
4	74	63	55	49	68	58	52	46	50	44	40	41	37	34	34	31	28				25																
5	68	56	48	42	62	52	45	40	44	39	35	37	33	30	30	27	25				21																
6	62	50	42	37	57	47	40	34	40	34	30	33	29	26	27	24	22				19																
7	58	45	38	32	53	42	35	30	36	30	26	30	26	23	25	22	19				17																
8	54	41	33	28	49	38	31	27	33	27	23	28	23	20	23	20	17				15																
9	50	38	30	25	46	35	28	24	30	25	21	25	21	18	21	18	16				13																
10	47	34	27	22	43	32	26	21	28	22	19	24	19	16	20	16	14				12																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15501	15501	15501
5°	15620	15518	15460
10°	15582	15510	15464
15°	15499	15499	15483
20°	15397	15442	15442
25°	15253	15362	15316
30°	15065	15247	15181
35°	14843	15069	14963
40°	14595	14803	14654
45°	14332	14433	14209
50°	13957	13957	13735
55°	13515	13338	13139
60°	12861	12603	12400
65°	11885	11651	11544
70°	10410	10491	10453
75°	8374	9265	9322
80°	5956	7853	7933
85°	3631	6584	6584



TEST NUMBER: P845058

CATALOG NUMBER: SQ4P-PC3-150U-125D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	159.0	1.7
10°-20°	456.3	4.8
20°-30°	691.0	7.3
30°-40°	828.5	8.7
40°-50°	844.7	8.9
50°-60°	737.4	7.8
60°-70°	527.9	5.6
70°-80°	272.0	2.9
80°-90°	70.6	0.7
90°-100°	301.6	3.2
100°-110°	1049.5	11.0
110°-120°	1016.6	10.7
120°-130°	797.5	8.4
130°-140°	631.2	6.6
140°-150°	487.1	5.1
150°-160°	349.2	3.7
160°-170°	213.6	2.2
170°-180°	72.2	0.8
0°-30°	1306.4	13.7
0°-40°	2134.8	22.5
0°-60°	3717.0	39.1
0°-90°	4587.5	48.3
90°-120°	2367.8	24.9
90°-150°	4283.6	45.1
90°-180°	4919.0	51.7
0°-180°	9506.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1680	1680	1680	1680	1680	
5°	1687	1670	1676	1671	1669	160
15°	1623	1609	1623	1623	1621	458
25°	1498	1488	1509	1504	1504	690
35°	1318	1314	1338	1328	1328	824
45°	1098	1095	1106	1092	1089	845
55°	840	829	829	817	817	749
65°	544	532	534	529	529	538
75°	235	246	260	262	262	254
85°	34	52	62	64	62	47
90°	11	17	17	11	6	8
95°	51	175	509	130	79	54
105°	175	249	1103	1861	1731	184
115°	305	368	820	1731	2042	302
125°	413	509	764	1290	1538	370
135°	498	560	758	1075	1216	386
145°	583	622	752	928	1007	364
155°	662	684	741	826	854	305
165°	724	730	747	780	786	204
175°	758	758	752	764	758	72
180°	758	758	758	758	758	



TEST NUMBER: P845058

CATALOG NUMBER: SQ4P-PC3-150U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1680.1	1680.1	1680.1	1680.1	1680.1
2.5°	1690.2	1675.5	1680.1	1676.3	1670.2
5°	1686.6	1669.6	1675.5	1670.7	1669.3
7.5°	1674.2	1657.6	1665.3	1662.1	1660.5
10°	1663.2	1646.2	1655.5	1652.2	1650.6
12.5°	1648.2	1632.6	1642.9	1639.8	1639.4
15°	1622.7	1609.0	1622.7	1622.7	1621.0
17.5°	1590.5	1578.2	1592.7	1593.7	1592.7
20°	1568.2	1554.6	1572.8	1571.2	1572.8
22.5°	1540.9	1529.7	1549.2	1545.2	1546.8
25°	1498.3	1487.5	1509.0	1504.5	1504.5
27.5°	1447.9	1440.0	1463.7	1458.5	1458.5
30°	1414.1	1406.6	1431.2	1425.0	1425.0
32.5°	1376.7	1371.7	1395.3	1387.8	1387.8
35°	1317.8	1314.5	1337.9	1328.5	1328.5
37.5°	1256.7	1254.0	1275.2	1263.9	1260.2
40°	1211.8	1210.6	1229.1	1216.7	1216.7
42.5°	1167.0	1165.5	1181.9	1166.8	1166.8
45°	1098.4	1095.2	1106.2	1091.9	1089.0
47.5°	1023.3	1020.4	1027.1	1011.8	1010.2
50°	972.4	969.2	972.4	958.2	956.9
52.5°	920.1	914.5	915.0	901.0	900.7
55°	840.2	829.4	829.2	816.8	816.8
57.5°	755.4	741.5	742.8	732.1	730.5
60°	697.0	681.6	683.0	673.6	672.0
62.5°	639.6	622.1	625.6	615.2	614.9
65°	544.4	532.3	533.7	528.8	528.8
67.5°	452.9	441.7	450.0	446.3	446.0
70°	385.9	378.1	388.9	388.9	387.5
72.5°	323.7	323.4	336.6	336.6	337.6
75°	234.9	245.7	259.9	261.5	261.5
77.5°	156.9	175.7	191.5	192.0	191.8
80°	112.1	133.2	147.8	151.0	149.3
82.5°	75.9	98.5	110.5	113.5	112.1
85°	34.3	52.5	62.2	63.9	62.2
87.5°	9.9	20.9	24.9	24.9	22.5
90°	11.3	17.0	17.0	11.3	5.6
92.5°	28.3	84.8	79.2	33.9	28.3
95°	50.9	175.3	509.0	130.0	79.2
97.5°	79.2	198.0	1018.1	463.8	248.9
100°	107.5	209.2	1187.8	1114.2	718.3
102.5°	141.4	226.3	1182.1	1566.7	1289.5
105°	175.3	248.9	1102.9	1860.8	1730.7



TEST NUMBER: P845058

CATALOG NUMBER: SQ4P-PC3-150U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.4	333.7	859.7	1872.1	2132.2
115°	305.4	367.7	820.1	1730.7	2041.8
117.5°	339.4	407.2	797.4	1600.6	1911.7
120°	367.7	441.1	780.5	1476.2	1781.6
122.5°	390.2	475.1	769.2	1374.4	1651.5
125°	412.9	509.0	763.5	1289.5	1538.4
127.5°	435.5	531.6	763.5	1227.3	1436.6
130°	458.2	543.0	757.9	1165.1	1351.7
132.5°	480.8	548.6	757.9	1119.8	1278.2
135°	497.7	559.9	757.9	1074.6	1216.0
137.5°	520.4	571.3	757.9	1035.1	1165.1
140°	537.3	588.2	757.9	995.4	1108.5
142.5°	559.9	605.2	757.9	955.9	1057.6
145°	582.6	622.1	752.2	927.6	1006.8
147.5°	605.2	639.1	746.6	899.3	961.5
150°	622.1	656.1	746.6	871.0	921.9
152.5°	644.8	673.0	740.9	842.7	888.0
155°	661.8	684.4	740.9	825.7	854.0
157.5°	678.7	701.3	740.9	808.8	831.5
160°	695.7	712.6	746.6	797.4	814.4
162.5°	712.6	724.0	746.6	786.2	797.4
165°	724.0	729.6	746.6	780.5	786.2
167.5°	735.2	740.9	746.6	774.9	774.9
170°	740.9	746.6	752.2	769.2	769.2
172.5°	752.2	752.2	752.2	763.5	763.5
175°	757.9	757.9	752.2	763.5	757.9
177.5°	757.9	757.9	752.2	763.5	757.9
180°	757.9	757.9	757.9	757.9	757.9



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	209.2	277.2	1001.1	1990.8	2013.5
110°	237.5	305.4	921.9	1973.9	2137.9



(END OF REPORT)