

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845121

Luminaire Tested: **SQ4P-PP3-125U-050D-B40-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845121
REPORT IS A COMBINATION OF REPORTS P700115 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-125U-050D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT
UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5949.5 lumens
Efficiency: N/A
Efficacy: 117.1 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 50.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845121

CATALOG NUMBER: SQ4P-PP3-125U-050D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845121

CATALOG NUMBER: SQ4P-PP3-125U-050D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	31				31															
1	94	90	86	82	84	81	78	75	64	62	60	49	47	46	35	34	33	27				27															
2	85	78	72	67	77	71	66	61	56	53	50	43	41	39	31	29	28	22				22															
3	78	69	62	56	70	62	56	51	50	45	42	38	35	33	27	25	24	19				19															
4	71	61	53	47	64	55	49	43	44	39	36	34	31	28	24	22	21	16				16															
5	65	54	46	41	58	49	42	37	39	34	31	30	27	24	22	20	18	14				14															
6	60	48	41	35	54	44	37	32	35	30	27	27	24	21	20	18	16	13				13															
7	55	44	36	31	50	40	33	28	32	27	23	25	21	19	18	16	14	11				11															
8	51	39	32	27	46	36	29	25	29	24	21	23	19	17	17	14	13	10				10															
9	48	36	29	24	43	33	26	22	27	22	18	21	17	15	15	13	11	9				9															
10	44	33	26	21	40	30	24	20	24	20	16	19	16	13	14	12	10	8				8															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6696	6696	6696
5°	6745	6704	6681
10°	6735	6687	6657
15°	6690	6654	6616
20°	6645	6608	6559
25°	6566	6521	6457
30°	6445	6411	6329
35°	6277	6233	6155
40°	6075	6036	5968
45°	5909	5868	5810
50°	5697	5661	5605
55°	5403	5331	5290
60°	4918	4777	4755
65°	4336	4152	4137
70°	3742	3588	3588
75°	3223	3176	3126
80°	2837	2874	2800
85°	2212	2435	2435



TEST NUMBER: P845121

CATALOG NUMBER: SQ4P-PP3-125U-050D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.6	1.2
10°-20°	196.0	3.3
20°-30°	293.5	4.9
30°-40°	344.3	5.8
40°-50°	345.4	5.8
50°-60°	294.6	5.0
60°-70°	192.2	3.2
70°-80°	96.4	1.6
80°-90°	28.2	0.5
90°-100°	250.8	4.2
100°-110°	872.7	14.7
110°-120°	845.4	14.2
120°-130°	663.2	11.1
130°-140°	524.9	8.8
140°-150°	405.1	6.8
150°-160°	290.4	4.9
160°-170°	177.6	3.0
170°-180°	60.1	1.0
0°-30°	558.1	9.4
0°-40°	902.4	15.2
0°-60°	1542.4	25.9
0°-90°	1859.3	31.3
90°-120°	1969.0	33.1
90°-150°	3562.1	59.9
90°-180°	4090.0	68.7
0°-180°	5949.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	728	722	724	721	721	69
15°	700	694	697	694	693	198
25°	645	638	641	635	634	297
35°	557	552	553	547	546	348
45°	453	450	450	445	445	349
55°	336	335	331	330	329	298
65°	199	195	190	189	190	198
75°	90	90	89	88	88	98
85°	21	23	23	23	23	25
90°	9	14	14	9	5	7
95°	42	146	423	108	66	45
105°	146	207	917	1547	1439	153
115°	254	306	682	1439	1698	251
125°	343	423	635	1072	1279	307
135°	414	466	630	894	1011	321
145°	484	517	626	771	837	303
155°	550	569	616	687	710	254
165°	602	607	621	649	654	170
175°	630	630	626	635	630	60
180°	630	630	630	630	630	



TEST NUMBER: P845121

CATALOG NUMBER: SQ4P-PP3-125U-050D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	725.8	725.8	725.8	725.8	725.8
2.5°	730.4	724.5	725.8	724.8	721.8
5°	728.3	721.6	723.9	721.4	721.4
7.5°	723.4	715.9	718.3	715.7	715.7
10°	718.9	711.4	713.8	711.2	710.6
12.5°	712.3	704.8	707.6	704.6	704.5
15°	700.4	693.5	696.6	693.9	692.7
17.5°	687.1	679.6	683.2	679.7	679.1
20°	676.8	669.3	673.0	668.0	668.0
22.5°	664.7	657.2	661.4	654.7	654.7
25°	645.0	637.5	640.6	634.8	634.3
27.5°	621.8	614.4	617.6	611.0	610.9
30°	605.0	598.1	601.8	594.8	594.1
32.5°	586.7	580.3	583.0	575.9	575.2
35°	557.3	551.7	553.4	547.0	546.5
37.5°	526.3	520.7	522.6	517.1	516.9
40°	504.4	500.7	501.2	496.7	495.5
42.5°	484.1	479.9	480.4	475.9	475.7
45°	452.9	449.7	449.7	445.3	445.3
47.5°	419.9	417.5	416.8	413.0	412.9
50°	396.9	395.1	394.4	391.2	390.5
52.5°	373.0	372.1	370.0	367.3	367.2
55°	335.9	334.6	331.4	329.5	328.9
57.5°	295.6	293.0	289.5	286.7	287.1
60°	266.5	264.0	258.9	257.7	257.7
62.5°	238.6	235.6	230.4	228.7	229.7
65°	198.6	194.8	190.2	189.0	189.5
67.5°	162.1	158.7	153.8	153.8	153.3
70°	138.7	136.7	133.0	133.0	133.0
72.5°	117.8	116.9	114.2	114.1	113.7
75°	90.4	90.4	89.1	88.4	87.7
77.5°	67.6	67.9	67.3	66.7	65.5
80°	53.4	54.8	54.1	53.4	52.7
82.5°	40.2	41.5	41.4	40.2	40.0
85°	20.9	22.8	23.0	23.0	23.0
87.5°	5.6	7.6	8.1	8.1	8.6
90°	9.4	14.1	14.1	9.4	4.7
92.5°	23.5	70.5	65.8	28.2	23.5
95°	42.3	145.8	423.3	108.1	65.8
97.5°	65.8	164.6	846.6	385.7	207.0
100°	89.3	174.0	987.7	926.5	597.3
102.5°	117.5	188.1	983.0	1302.8	1072.4
105°	145.8	207.0	917.1	1547.4	1439.3



TEST NUMBER: P845121

CATALOG NUMBER: SQ4P-PP3-125U-050D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.8	277.5	714.9	1556.8	1773.2
115°	254.0	305.7	682.0	1439.3	1697.9
117.5°	282.2	338.7	663.1	1331.1	1589.7
120°	305.7	366.9	649.1	1227.6	1481.6
122.5°	324.5	395.1	639.7	1142.9	1373.4
125°	343.3	423.3	634.9	1072.4	1279.4
127.5°	362.1	442.1	634.9	1020.6	1194.7
130°	380.9	451.5	630.3	968.9	1124.1
132.5°	399.8	456.2	630.3	931.3	1063.0
135°	413.9	465.6	630.3	893.7	1011.2
137.5°	432.7	475.0	630.3	860.7	968.9
140°	446.8	489.2	630.3	827.8	921.9
142.5°	465.6	503.2	630.3	794.8	879.5
145°	484.4	517.4	625.5	771.4	837.2
147.5°	503.2	531.4	620.9	747.8	799.6
150°	517.4	545.6	620.9	724.3	766.6
152.5°	536.2	559.7	616.1	700.8	738.4
155°	550.3	569.1	616.1	686.7	710.2
157.5°	564.4	583.2	616.1	672.6	691.4
160°	578.5	592.6	620.9	663.1	677.3
162.5°	592.6	602.1	620.9	653.7	663.1
165°	602.1	606.7	620.9	649.1	653.7
167.5°	611.5	616.1	620.9	644.3	644.3
170°	616.1	620.9	625.5	639.7	639.7
172.5°	625.5	625.5	625.5	634.9	634.9
175°	630.3	630.3	625.5	634.9	630.3
177.5°	630.3	630.3	625.5	634.9	630.3
180°	630.3	630.3	630.3	630.3	630.3



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	174.0	230.4	832.5	1655.5	1674.4
110°	197.5	254.0	766.6	1641.5	1777.8



(END OF REPORT)