

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845061

Luminaire Tested: **SQ4P-PP3-025U-050D-B40-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845061  
REPORT IS A COMBINATION OF REPORTS P700171 AND P700243  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-025U-050D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT UPLIGHT, 500 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 2700.8 lumens  
Efficiency: N/A  
Efficacy: 113.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 23.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845061

CATALOG NUMBER: SQ4P-PP3-025U-050D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845061

CATALOG NUMBER: SQ4P-PP3-025U-050D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	112	112	112	112	105	105	105	105	94	94	94	83	83	83	73	73	73	69								
1	102	98	94	91	96	93	89	86	83	80	78	74	72	70	65	64	63	59								
2	93	86	80	74	88	81	76	71	73	69	65	65	62	59	58	55	53	49								
3	85	76	68	62	80	72	65	60	64	59	55	58	54	50	51	48	45	42								
4	78	67	59	53	74	64	57	51	57	52	47	52	47	43	46	42	39	36								
5	72	60	52	46	68	57	50	44	52	45	41	46	41	37	42	38	34	32								
6	66	54	46	40	62	51	44	38	47	40	36	42	37	33	38	34	30	28								
7	61	49	41	35	58	47	39	34	42	36	31	38	33	29	34	30	27	25								
8	57	44	37	31	54	42	35	30	39	32	28	35	30	26	32	27	24	22								
9	53	41	33	28	50	39	32	27	36	29	25	32	27	24	29	25	22	20								
10	50	37	30	25	47	36	29	24	33	27	23	30	25	21	27	23	20	18								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6696	6696	6696
5°	6745	6704	6681
10°	6735	6687	6657
15°	6690	6654	6616
20°	6645	6608	6559
25°	6566	6521	6457
30°	6445	6411	6329
35°	6277	6233	6155
40°	6075	6036	5968
45°	5909	5868	5810
50°	5697	5661	5605
55°	5403	5331	5290
60°	4918	4777	4755
65°	4336	4152	4137
70°	3742	3588	3588
75°	3223	3176	3126
80°	2837	2874	2800
85°	2212	2435	2435



TEST NUMBER: P845061

CATALOG NUMBER: SQ4P-PP3-025U-050D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.6	2.5
10°-20°	196.0	7.3
20°-30°	293.5	10.9
30°-40°	344.3	12.7
40°-50°	345.4	12.8
50°-60°	294.6	10.9
60°-70°	192.2	7.1
70°-80°	96.4	3.6
80°-90°	27.0	1.0
90°-100°	51.7	1.9
100°-110°	179.8	6.7
110°-120°	174.2	6.5
120°-130°	136.6	5.1
130°-140°	108.2	4.0
140°-150°	83.5	3.1
150°-160°	59.8	2.2
160°-170°	36.6	1.4
170°-180°	12.4	0.5
0°-30°	558.1	20.7
0°-40°	902.4	33.4
0°-60°	1542.4	57.1
0°-90°	1858.0	68.8
90°-120°	405.7	15.0
90°-150°	734.0	27.2
90°-180°	843.0	31.2
0°-180°	2700.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	728	722	724	721	721	69
15°	700	694	697	694	693	198
25°	645	638	641	635	634	297
35°	557	552	553	547	546	348
45°	453	450	450	445	445	349
55°	336	335	331	330	329	298
65°	199	195	190	189	190	198
75°	90	90	89	88	88	98
85°	21	23	23	23	23	25
90°	2	3	3	2	1	2
95°	9	30	87	22	14	9
105°	30	43	189	319	297	32
115°	52	63	140	297	350	52
125°	71	87	131	221	264	63
135°	85	96	130	184	208	66
145°	100	107	129	159	172	62
155°	113	117	127	142	146	52
165°	124	125	128	134	135	35
175°	130	130	129	131	130	12
180°	130	130	130	130	130	



TEST NUMBER: P845061

CATALOG NUMBER: SQ4P-PP3-025U-050D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	725.8	725.8	725.8	725.8	725.8
2.5°	730.4	724.5	725.8	724.8	721.8
5°	728.3	721.6	723.9	721.4	721.4
7.5°	723.4	715.9	718.3	715.7	715.7
10°	718.9	711.4	713.8	711.2	710.6
12.5°	712.3	704.8	707.6	704.6	704.5
15°	700.4	693.5	696.6	693.9	692.7
17.5°	687.1	679.6	683.2	679.7	679.1
20°	676.8	669.3	673.0	668.0	668.0
22.5°	664.7	657.2	661.4	654.7	654.7
25°	645.0	637.5	640.6	634.8	634.3
27.5°	621.8	614.4	617.6	611.0	610.9
30°	605.0	598.1	601.8	594.8	594.1
32.5°	586.7	580.3	583.0	575.9	575.2
35°	557.3	551.7	553.4	547.0	546.5
37.5°	526.3	520.7	522.6	517.1	516.9
40°	504.4	500.7	501.2	496.7	495.5
42.5°	484.1	479.9	480.4	475.9	475.7
45°	452.9	449.7	449.7	445.3	445.3
47.5°	419.9	417.5	416.8	413.0	412.9
50°	396.9	395.1	394.4	391.2	390.5
52.5°	373.0	372.1	370.0	367.3	367.2
55°	335.9	334.6	331.4	329.5	328.9
57.5°	295.6	293.0	289.5	286.7	287.1
60°	266.5	264.0	258.9	257.7	257.7
62.5°	238.6	235.6	230.4	228.7	229.7
65°	198.6	194.8	190.2	189.0	189.5
67.5°	162.1	158.7	153.8	153.8	153.3
70°	138.7	136.7	133.0	133.0	133.0
72.5°	117.8	116.9	114.2	114.1	113.7
75°	90.4	90.4	89.1	88.4	87.7
77.5°	67.6	67.9	67.3	66.7	65.5
80°	53.4	54.8	54.1	53.4	52.7
82.5°	40.2	41.5	41.4	40.2	40.0
85°	20.9	22.8	23.0	23.0	23.0
87.5°	5.6	7.6	8.1	8.1	8.6
90°	1.9	2.9	2.9	1.9	1.0
92.5°	4.8	14.5	13.6	5.8	4.8
95°	8.7	30.0	87.2	22.3	13.6
97.5°	13.6	33.9	174.4	79.5	42.6
100°	18.4	35.9	203.5	190.9	123.1
102.5°	24.2	38.8	202.5	268.4	220.9
105°	30.0	42.6	189.0	318.9	296.6



TEST NUMBER: P845061

CATALOG NUMBER: SQ4P-PP3-025U-050D-B40-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	46.5	57.2	147.3	320.9	365.4
115°	52.3	63.0	140.5	296.6	349.9
117.5°	58.1	69.8	136.6	274.2	327.6
120°	63.0	75.6	133.7	252.9	305.4
122.5°	66.9	81.4	131.8	235.5	283.1
125°	70.7	87.2	130.8	220.9	263.6
127.5°	74.6	91.1	130.8	210.3	246.1
130°	78.5	93.0	129.9	199.6	231.6
132.5°	82.4	94.0	129.9	191.9	219.0
135°	85.3	95.9	129.9	184.1	208.3
137.5°	89.2	97.9	129.9	177.3	199.6
140°	92.1	100.8	129.9	170.6	189.9
142.5°	95.9	103.7	129.9	163.8	181.2
145°	99.8	106.6	128.9	158.9	172.5
147.5°	103.7	109.5	127.9	154.1	164.7
150°	106.6	112.4	127.9	149.2	158.0
152.5°	110.5	115.3	126.9	144.4	152.1
155°	113.4	117.3	126.9	141.5	146.3
157.5°	116.3	120.2	126.9	138.6	142.5
160°	119.2	122.1	127.9	136.6	139.5
162.5°	122.1	124.0	127.9	134.7	136.6
165°	124.0	125.0	127.9	133.7	134.7
167.5°	126.0	126.9	127.9	132.8	132.8
170°	126.9	127.9	128.9	131.8	131.8
172.5°	128.9	128.9	128.9	130.8	130.8
175°	129.9	129.9	128.9	130.8	129.9
177.5°	129.9	129.9	128.9	130.8	129.9
180°	129.9	129.9	129.9	129.9	129.9



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	35.9	47.5	171.5	341.2	345.1
110°	40.7	52.3	158.0	338.3	366.4



(END OF REPORT)