

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845064

Luminaire Tested: **SQ4P-PP3-025U-075D-B40-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845064
REPORT IS A COMBINATION OF REPORTS P700172 AND P700243
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-025U-075D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3606.9 lumens
Efficiency: N/A
Efficacy: 110.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 32.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845064

CATALOG NUMBER: SQ4P-PP3-025U-075D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845064

CATALOG NUMBER: SQ4P-PP3-025U-075D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	113	113	113	113	108	108	108	108	98	98	98	89	89	89	81	81	81	77			77
1	104	100	96	92	99	95	92	89	87	84	82	79	77	75	72	70	69	65			65
2	95	87	81	76	90	84	78	73	76	72	68	70	66	63	64	61	58	55			55
3	87	77	70	64	83	74	67	62	68	62	58	62	57	54	56	53	50	47			47
4	80	68	60	54	76	66	58	52	60	54	49	55	50	46	51	47	43	40			40
5	73	61	53	47	70	59	51	45	54	48	43	50	44	40	46	41	38	35			35
6	68	55	47	41	64	53	45	40	49	42	37	45	40	35	41	37	33	31			31
7	63	50	42	36	60	48	40	35	44	38	33	41	36	31	38	33	30	27			27
8	58	46	37	32	55	44	36	31	41	34	30	38	32	28	35	30	27	25			25
9	54	42	34	29	52	40	33	28	37	31	27	35	29	25	32	27	24	22			22
10	51	38	31	26	49	37	30	25	35	28	24	32	27	23	30	25	22	20			20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9963	9963	9963
5°	10036	9974	9938
10°	10020	9948	9904
15°	9953	9898	9844
20°	9887	9830	9756
25°	9770	9703	9607
30°	9589	9538	9417
35°	9337	9274	9156
40°	9038	8981	8880
45°	8793	8730	8644
50°	8476	8423	8341
55°	8036	7933	7872
60°	7316	7110	7073
65°	6449	6178	6156
70°	5562	5336	5336
75°	4791	4723	4652
80°	4224	4272	4171
85°	3303	3610	3610



TEST NUMBER: P845064

CATALOG NUMBER: SQ4P-PP3-025U-075D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	2.8
10°-20°	291.6	8.1
20°-30°	436.7	12.1
30°-40°	512.2	14.2
40°-50°	513.8	14.2
50°-60°	438.4	12.2
60°-70°	285.9	7.9
70°-80°	143.4	4.0
80°-90°	40.0	1.1
90°-100°	51.7	1.4
100°-110°	179.8	5.0
110°-120°	174.2	4.8
120°-130°	136.6	3.8
130°-140°	108.2	3.0
140°-150°	83.5	2.3
150°-160°	59.8	1.7
160°-170°	36.6	1.0
170°-180°	12.4	0.3
0°-30°	830.4	23.0
0°-40°	1342.6	37.2
0°-60°	2294.8	63.6
0°-90°	2764.1	76.6
90°-120°	405.7	11.2
90°-150°	734.0	20.3
90°-180°	843.0	23.4
0°-180°	3606.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1080	1080	1080	1080	1080	
5°	1084	1074	1077	1073	1073	103
15°	1042	1032	1036	1032	1031	294
25°	960	948	953	944	944	441
35°	829	821	823	814	813	518
45°	674	669	669	662	662	519
55°	500	498	493	490	489	444
65°	295	290	283	281	282	295
75°	134	134	132	132	130	146
85°	31	34	34	34	34	37
90°	2	3	3	2	1	2
95°	9	30	87	22	14	9
105°	30	43	189	319	297	32
115°	52	63	140	297	350	52
125°	71	87	131	221	264	63
135°	85	96	130	184	208	66
145°	100	107	129	159	172	62
155°	113	117	127	142	146	52
165°	124	125	128	134	135	35
175°	130	130	129	131	130	12
180°	130	130	130	130	130	



TEST NUMBER: P845064

CATALOG NUMBER: SQ4P-PP3-025U-075D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1079.9	1079.9	1079.9	1079.9	1079.9
2.5°	1086.6	1077.8	1079.9	1078.3	1073.8
5°	1083.6	1073.5	1076.9	1073.1	1073.1
7.5°	1076.2	1065.2	1068.6	1064.9	1064.7
10°	1069.5	1058.3	1061.9	1058.0	1057.2
12.5°	1059.7	1048.5	1052.8	1048.2	1048.0
15°	1042.0	1031.8	1036.3	1032.4	1030.6
17.5°	1022.1	1011.0	1016.5	1011.2	1010.3
20°	1007.0	995.8	1001.2	993.7	993.7
22.5°	988.8	977.7	983.9	974.0	974.0
25°	959.7	948.5	953.1	944.4	943.7
27.5°	925.1	914.1	918.9	909.1	908.9
30°	900.1	889.8	895.3	884.9	883.9
32.5°	872.8	863.3	867.3	856.8	855.9
35°	829.0	820.8	823.4	813.9	812.9
37.5°	783.1	774.6	777.5	769.3	769.0
40°	750.4	744.9	745.7	739.0	737.3
42.5°	720.2	713.9	714.7	708.0	707.7
45°	673.9	669.1	669.1	662.5	662.5
47.5°	624.7	621.1	620.1	614.5	614.4
50°	590.5	587.7	586.8	582.0	581.1
52.5°	555.0	553.6	550.4	546.5	546.3
55°	499.6	497.8	493.2	490.2	489.4
57.5°	439.8	436.0	430.7	426.6	427.2
60°	396.5	392.8	385.3	383.3	383.3
62.5°	354.9	350.5	342.9	340.2	341.7
65°	295.4	289.7	283.0	281.1	282.0
67.5°	241.2	236.1	228.8	228.8	228.1
70°	206.2	203.5	197.8	197.8	197.8
72.5°	175.2	173.9	169.9	169.7	169.0
75°	134.4	134.4	132.5	131.5	130.5
77.5°	100.7	101.0	100.2	99.2	97.4
80°	79.5	81.4	80.4	79.5	78.5
82.5°	59.9	61.6	61.5	59.9	59.6
85°	31.2	33.9	34.1	34.1	34.1
87.5°	8.3	11.2	12.1	12.1	12.9
90°	1.9	2.9	2.9	1.9	1.0
92.5°	4.8	14.5	13.6	5.8	4.8
95°	8.7	30.0	87.2	22.3	13.6
97.5°	13.6	33.9	174.4	79.5	42.6
100°	18.4	35.9	203.5	190.9	123.1
102.5°	24.2	38.8	202.5	268.4	220.9
105°	30.0	42.6	189.0	318.9	296.6



TEST NUMBER: P845064

CATALOG NUMBER: SQ4P-PP3-025U-075D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	46.5	57.2	147.3	320.9	365.4
115°	52.3	63.0	140.5	296.6	349.9
117.5°	58.1	69.8	136.6	274.2	327.6
120°	63.0	75.6	133.7	252.9	305.4
122.5°	66.9	81.4	131.8	235.5	283.1
125°	70.7	87.2	130.8	220.9	263.6
127.5°	74.6	91.1	130.8	210.3	246.1
130°	78.5	93.0	129.9	199.6	231.6
132.5°	82.4	94.0	129.9	191.9	219.0
135°	85.3	95.9	129.9	184.1	208.3
137.5°	89.2	97.9	129.9	177.3	199.6
140°	92.1	100.8	129.9	170.6	189.9
142.5°	95.9	103.7	129.9	163.8	181.2
145°	99.8	106.6	128.9	158.9	172.5
147.5°	103.7	109.5	127.9	154.1	164.7
150°	106.6	112.4	127.9	149.2	158.0
152.5°	110.5	115.3	126.9	144.4	152.1
155°	113.4	117.3	126.9	141.5	146.3
157.5°	116.3	120.2	126.9	138.6	142.5
160°	119.2	122.1	127.9	136.6	139.5
162.5°	122.1	124.0	127.9	134.7	136.6
165°	124.0	125.0	127.9	133.7	134.7
167.5°	126.0	126.9	127.9	132.8	132.8
170°	126.9	127.9	128.9	131.8	131.8
172.5°	128.9	128.9	128.9	130.8	130.8
175°	129.9	129.9	128.9	130.8	129.9
177.5°	129.9	129.9	128.9	130.8	129.9
180°	129.9	129.9	129.9	129.9	129.9



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	35.9	47.5	171.5	341.2	345.1
110°	40.7	52.3	158.0	338.3	366.4



(END OF REPORT)