

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845136

Luminaire Tested: **SQ4P-PP3-150U-075D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845136
REPORT IS A COMBINATION OF REPORTS P700144 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-150U-075D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT UPLIGHT, 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7684.2 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Indirect

Input Watts (W): 68.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845136

CATALOG NUMBER: SQ4P-PP3-150U-075D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845136

CATALOG NUMBER: SQ4P-PP3-150U-075D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	43	43	43	36																			
1	95	91	87	84	86	82	79	76	66	64	62	52	50	49	38	38	37	31																			
2	86	79	73	68	78	72	67	63	58	55	52	46	43	41	34	32	31	26																			
3	79	70	63	57	71	63	57	52	51	47	44	40	37	35	30	28	27	22																			
4	72	62	54	48	65	56	50	44	46	41	37	36	33	30	27	25	23	19																			
5	66	55	47	41	60	50	43	38	41	36	32	32	29	26	24	22	20	16																			
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	20	18	14																			
7	56	44	37	31	51	40	34	29	33	28	24	26	23	20	20	18	16	13																			
8	52	40	33	27	47	37	30	25	30	25	22	24	20	18	18	16	14	12																			
9	48	37	29	24	44	33	27	23	28	23	19	22	19	16	17	14	13	10																			
10	45	33	26	22	41	31	24	20	25	21	17	20	17	14	16	13	11	9																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9963	9963	9963
5°	10036	9974	9938
10°	10020	9948	9904
15°	9953	9898	9844
20°	9887	9830	9756
25°	9770	9703	9607
30°	9589	9538	9417
35°	9337	9274	9156
40°	9038	8981	8880
45°	8793	8730	8644
50°	8476	8423	8341
55°	8036	7933	7872
60°	7316	7110	7073
65°	6449	6178	6156
70°	5562	5336	5336
75°	4791	4723	4652
80°	4224	4272	4171
85°	3303	3610	3610



TEST NUMBER: P845136

CATALOG NUMBER: SQ4P-PP3-150U-075D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	102.1	1.3
10°-20°	291.6	3.8
20°-30°	436.7	5.7
30°-40°	512.2	6.7
40°-50°	513.8	6.7
50°-60°	438.4	5.7
60°-70°	285.9	3.7
70°-80°	143.4	1.9
80°-90°	41.5	0.5
90°-100°	301.6	3.9
100°-110°	1049.5	13.7
110°-120°	1016.6	13.2
120°-130°	797.5	10.4
130°-140°	631.2	8.2
140°-150°	487.1	6.3
150°-160°	349.2	4.5
160°-170°	213.6	2.8
170°-180°	72.2	0.9
0°-30°	830.4	10.8
0°-40°	1342.6	17.5
0°-60°	2294.8	29.9
0°-90°	2765.6	36.0
90°-120°	2367.8	30.8
90°-150°	4283.6	55.7
90°-180°	4919.0	64.0
0°-180°	7684.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1080	1080	1080	1080	1080	
5°	1084	1074	1077	1073	1073	103
15°	1042	1032	1036	1032	1031	294
25°	960	948	953	944	944	441
35°	829	821	823	814	813	518
45°	674	669	669	662	662	519
55°	500	498	493	490	489	444
65°	295	290	283	281	282	295
75°	134	134	132	132	130	146
85°	31	34	34	34	34	37
90°	11	17	17	11	6	8
95°	51	175	509	130	79	54
105°	175	249	1103	1861	1731	184
115°	305	368	820	1731	2042	302
125°	413	509	764	1290	1538	370
135°	498	560	758	1075	1216	386
145°	583	622	752	928	1007	364
155°	662	684	741	826	854	305
165°	724	730	747	780	786	204
175°	758	758	752	764	758	72
180°	758	758	758	758	758	



TEST NUMBER: P845136

CATALOG NUMBER: SQ4P-PP3-150U-075D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1079.9	1079.9	1079.9	1079.9	1079.9
2.5°	1086.6	1077.8	1079.9	1078.3	1073.8
5°	1083.6	1073.5	1076.9	1073.1	1073.1
7.5°	1076.2	1065.2	1068.6	1064.9	1064.7
10°	1069.5	1058.3	1061.9	1058.0	1057.2
12.5°	1059.7	1048.5	1052.8	1048.2	1048.0
15°	1042.0	1031.8	1036.3	1032.4	1030.6
17.5°	1022.1	1011.0	1016.5	1011.2	1010.3
20°	1007.0	995.8	1001.2	993.7	993.7
22.5°	988.8	977.7	983.9	974.0	974.0
25°	959.7	948.5	953.1	944.4	943.7
27.5°	925.1	914.1	918.9	909.1	908.9
30°	900.1	889.8	895.3	884.9	883.9
32.5°	872.8	863.3	867.3	856.8	855.9
35°	829.0	820.8	823.4	813.9	812.9
37.5°	783.1	774.6	777.5	769.3	769.0
40°	750.4	744.9	745.7	739.0	737.3
42.5°	720.2	713.9	714.7	708.0	707.7
45°	673.9	669.1	669.1	662.5	662.5
47.5°	624.7	621.1	620.1	614.5	614.4
50°	590.5	587.7	586.8	582.0	581.1
52.5°	555.0	553.6	550.4	546.5	546.3
55°	499.6	497.8	493.2	490.2	489.4
57.5°	439.8	436.0	430.7	426.6	427.2
60°	396.5	392.8	385.3	383.3	383.3
62.5°	354.9	350.5	342.9	340.2	341.7
65°	295.4	289.7	283.0	281.1	282.0
67.5°	241.2	236.1	228.8	228.8	228.1
70°	206.2	203.5	197.8	197.8	197.8
72.5°	175.2	173.9	169.9	169.7	169.0
75°	134.4	134.4	132.5	131.5	130.5
77.5°	100.7	101.0	100.2	99.2	97.4
80°	79.5	81.4	80.4	79.5	78.5
82.5°	59.9	61.6	61.5	59.9	59.6
85°	31.2	33.9	34.1	34.1	34.1
87.5°	8.3	11.2	12.1	12.1	12.9
90°	11.3	17.0	17.0	11.3	5.6
92.5°	28.3	84.8	79.2	33.9	28.3
95°	50.9	175.3	509.0	130.0	79.2
97.5°	79.2	198.0	1018.1	463.8	248.9
100°	107.5	209.2	1187.8	1114.2	718.3
102.5°	141.4	226.3	1182.1	1566.7	1289.5
105°	175.3	248.9	1102.9	1860.8	1730.7



TEST NUMBER: P845136

CATALOG NUMBER: SQ4P-PP3-150U-075D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.4	333.7	859.7	1872.1	2132.2
115°	305.4	367.7	820.1	1730.7	2041.8
117.5°	339.4	407.2	797.4	1600.6	1911.7
120°	367.7	441.1	780.5	1476.2	1781.6
122.5°	390.2	475.1	769.2	1374.4	1651.5
125°	412.9	509.0	763.5	1289.5	1538.4
127.5°	435.5	531.6	763.5	1227.3	1436.6
130°	458.2	543.0	757.9	1165.1	1351.7
132.5°	480.8	548.6	757.9	1119.8	1278.2
135°	497.7	559.9	757.9	1074.6	1216.0
137.5°	520.4	571.3	757.9	1035.1	1165.1
140°	537.3	588.2	757.9	995.4	1108.5
142.5°	559.9	605.2	757.9	955.9	1057.6
145°	582.6	622.1	752.2	927.6	1006.8
147.5°	605.2	639.1	746.6	899.3	961.5
150°	622.1	656.1	746.6	871.0	921.9
152.5°	644.8	673.0	740.9	842.7	888.0
155°	661.8	684.4	740.9	825.7	854.0
157.5°	678.7	701.3	740.9	808.8	831.5
160°	695.7	712.6	746.6	797.4	814.4
162.5°	712.6	724.0	746.6	786.2	797.4
165°	724.0	729.6	746.6	780.5	786.2
167.5°	735.2	740.9	746.6	774.9	774.9
170°	740.9	746.6	752.2	769.2	769.2
172.5°	752.2	752.2	752.2	763.5	763.5
175°	757.9	757.9	752.2	763.5	757.9
177.5°	757.9	757.9	752.2	763.5	757.9
180°	757.9	757.9	757.9	757.9	757.9



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	209.2	277.2	1001.1	1990.8	2013.5
110°	237.5	305.4	921.9	1973.9	2137.9



(END OF REPORT)