

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845082

Luminaire Tested: **SQ4P-PP3-050U-125D-B40-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P845082  
REPORT IS A COMBINATION OF REPORTS P700202 AND P700244  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-050U-125D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT  
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6237.2 lumens  
Efficiency: N/A  
Efficacy: 106.1 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Semi-Direct

Input Watts (W): 58.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845082

CATALOG NUMBER: SQ4P-PP3-050U-125D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845082

CATALOG NUMBER: SQ4P-PP3-050U-125D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	77	77	77	73																
1	103	99	95	91	98	94	91	87	85	82	80	76	74	73	69	67	66	66	66	66	62																
2	94	87	80	75	89	83	77	72	75	70	66	67	64	61	61	58	56	56	56	56	52																
3	86	76	69	63	81	73	66	61	66	61	56	60	56	52	54	51	48	48	48	48	45																
4	79	68	60	54	75	65	57	52	59	53	48	53	49	45	48	45	41	41	41	41	38																
5	73	61	52	46	69	58	50	45	53	47	42	48	43	39	44	39	36	36	36	36	33																
6	67	55	46	40	63	52	45	39	48	41	37	44	38	34	40	35	32	32	32	32	29																
7	62	49	41	35	59	47	40	34	43	37	32	40	34	30	36	32	28	28	28	28	26																
8	58	45	37	32	55	43	36	31	40	33	29	36	31	27	33	29	25	25	25	25	23																
9	54	41	33	28	51	40	32	27	36	30	26	34	28	24	31	26	23	23	23	23	21																
10	50	38	30	26	48	36	30	25	34	28	24	31	26	22	29	24	21	21	21	21	19																

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	16377	16377	16377
5°	16496	16395	16338
10°	16469	16354	16281
15°	16360	16270	16181
20°	16251	16159	16038
25°	16057	15949	15790
30°	15762	15679	15478
35°	15349	15243	15050
40°	14856	14763	14595
45°	14453	14353	14208
50°	13933	13844	13709
55°	13211	13037	12939
60°	12027	11686	11627
65°	10599	10154	10119
70°	9145	8770	8770
75°	7878	7760	7650
80°	6939	7029	6854
85°	5431	5928	5928



TEST NUMBER: P845082

CATALOG NUMBER: SQ4P-PP3-050U-125D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	167.8	2.7
10°-20°	479.2	7.7
20°-30°	717.8	11.5
30°-40°	842.0	13.5
40°-50°	844.6	13.5
50°-60°	720.5	11.6
60°-70°	469.9	7.5
70°-80°	235.7	3.8
80°-90°	65.9	1.1
90°-100°	103.8	1.7
100°-110°	361.4	5.8
110°-120°	350.0	5.6
120°-130°	274.6	4.4
130°-140°	217.3	3.5
140°-150°	167.7	2.7
150°-160°	120.2	1.9
160°-170°	73.5	1.2
170°-180°	24.9	0.4
0°-30°	1364.9	21.9
0°-40°	2206.9	35.4
0°-60°	3772.1	60.5
0°-90°	4543.6	72.8
90°-120°	815.2	13.1
90°-150°	1474.9	23.6
90°-180°	1694.0	27.2
0°-180°	6237.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1775	1775	1775	1775	1775	
5°	1781	1765	1770	1764	1764	169
15°	1713	1696	1703	1697	1694	483
25°	1577	1559	1567	1552	1551	725
35°	1363	1349	1353	1338	1336	851
45°	1108	1100	1100	1089	1089	853
55°	821	818	810	806	804	730
65°	486	476	465	462	464	484
75°	221	221	218	216	215	240
85°	51	56	56	56	56	60
90°	4	6	6	4	2	4
95°	18	60	175	45	27	19
105°	60	86	380	641	596	63
115°	105	127	282	596	703	104
125°	142	175	263	444	530	127
135°	171	193	261	370	419	133
145°	201	214	259	319	347	125
155°	228	236	255	284	294	105
165°	249	251	257	269	271	70
175°	261	261	259	263	261	25
180°	261	261	261	261	261	



TEST NUMBER: P845082

CATALOG NUMBER: SQ4P-PP3-050U-125D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1775.0	1775.0	1775.0	1775.0	1775.0
2.5°	1786.1	1771.5	1775.0	1772.4	1765.1
5°	1781.2	1764.6	1770.2	1764.1	1764.1
7.5°	1769.1	1750.9	1756.5	1750.4	1750.1
10°	1757.9	1739.7	1745.6	1739.1	1737.8
12.5°	1741.8	1723.6	1730.6	1723.0	1722.8
15°	1712.8	1696.0	1703.4	1697.0	1694.0
17.5°	1680.1	1661.8	1670.8	1662.1	1660.8
20°	1655.2	1636.9	1645.8	1633.5	1633.5
22.5°	1625.4	1607.2	1617.4	1601.0	1601.0
25°	1577.3	1559.1	1566.7	1552.4	1551.1
27.5°	1520.6	1502.5	1510.3	1494.2	1494.0
30°	1479.5	1462.6	1471.7	1454.6	1452.9
32.5°	1434.7	1419.1	1425.6	1408.4	1406.8
35°	1362.8	1349.1	1353.4	1337.9	1336.2
37.5°	1287.2	1273.3	1278.1	1264.6	1264.1
40°	1233.5	1224.4	1225.8	1214.7	1211.8
42.5°	1183.9	1173.4	1174.8	1163.7	1163.3
45°	1107.7	1100.0	1100.0	1088.9	1088.9
47.5°	1026.7	1020.8	1019.3	1010.2	1009.9
50°	970.7	966.2	964.5	956.8	955.1
52.5°	912.2	910.0	904.7	898.2	898.0
55°	821.3	818.4	810.5	805.7	804.4
57.5°	722.8	716.7	707.8	701.1	702.2
60°	651.8	645.6	633.3	630.1	630.1
62.5°	583.4	576.1	563.5	559.2	561.7
65°	485.5	476.4	465.1	462.1	463.5
67.5°	396.4	388.1	376.0	376.0	374.9
70°	339.0	334.4	325.1	325.1	325.1
72.5°	288.1	285.9	279.2	279.0	277.8
75°	221.0	221.0	217.7	216.2	214.6
77.5°	165.5	166.0	164.6	163.1	160.1
80°	130.6	133.8	132.3	130.6	129.0
82.5°	98.5	101.4	101.1	98.5	97.9
85°	51.3	55.8	56.0	56.0	56.0
87.5°	13.7	18.5	19.9	19.9	21.2
90°	3.9	5.8	5.8	3.9	1.9
92.5°	9.7	29.2	27.2	11.7	9.7
95°	17.5	60.4	175.3	44.8	27.2
97.5°	27.2	68.1	350.5	159.7	85.7
100°	37.0	72.1	408.9	383.7	247.3
102.5°	48.6	77.9	407.0	539.4	444.0
105°	60.4	85.7	379.8	640.6	595.9



TEST NUMBER: P845082

CATALOG NUMBER: SQ4P-PP3-050U-125D-B40-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	93.5	114.9	296.0	644.6	734.2
115°	105.1	126.6	282.4	595.9	703.0
117.5°	116.9	140.2	274.5	551.1	658.2
120°	126.6	151.9	268.7	508.3	613.4
122.5°	134.4	163.6	264.8	473.2	568.6
125°	142.2	175.3	262.9	444.0	529.7
127.5°	149.9	183.1	262.9	422.6	494.6
130°	157.8	186.9	261.0	401.2	465.4
132.5°	165.5	188.9	261.0	385.6	440.1
135°	171.3	192.7	261.0	370.0	418.7
137.5°	179.2	196.7	261.0	356.3	401.2
140°	185.0	202.5	261.0	342.8	381.7
142.5°	192.7	208.3	261.0	329.1	364.2
145°	200.6	214.3	259.0	319.4	346.6
147.5°	208.3	220.1	257.1	309.6	331.0
150°	214.3	225.9	257.1	299.9	317.5
152.5°	222.0	231.7	255.2	290.1	305.7
155°	227.8	235.7	255.2	284.3	294.0
157.5°	233.6	241.5	255.2	278.5	286.3
160°	239.6	245.4	257.1	274.5	280.4
162.5°	245.4	249.2	257.1	270.7	274.5
165°	249.2	251.2	257.1	268.7	270.7
167.5°	253.1	255.2	257.1	266.8	266.8
170°	255.2	257.1	259.0	264.8	264.8
172.5°	259.0	259.0	259.0	262.9	262.9
175°	261.0	261.0	259.0	262.9	261.0
177.5°	261.0	261.0	259.0	262.9	261.0
180°	261.0	261.0	261.0	261.0	261.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	72.1	95.5	344.7	685.5	693.3
110°	81.8	105.1	317.5	679.6	736.1



(END OF REPORT)