

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845097

Luminaire Tested: **SQ4P-PP3-0U-050D-B40-1D-UNV**

Issue Date: 8/14/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P845097  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P563482)  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-PP3-0U-050D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 500 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1857.7 lumens  
Efficiency: N/A  
Efficacy: 110.6 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: Direct

Input Watts (W): 16.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845097

CATALOG NUMBER: SQ4P-PP3-0U-050D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845097

CATALOG NUMBER: SQ4P-PP3-OU-050D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85																			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72																			
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61																			
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53																			
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46																			
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40																			
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36																			
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32																			
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29																			
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6696	6696	6696
5°	6745	6704	6681
10°	6735	6687	6657
15°	6690	6654	6616
20°	6645	6608	6559
25°	6566	6521	6457
30°	6445	6411	6329
35°	6277	6233	6155
40°	6075	6036	5968
45°	5909	5868	5810
50°	5697	5661	5605
55°	5403	5331	5290
60°	4918	4777	4755
65°	4336	4152	4137
70°	3742	3588	3588
75°	3223	3176	3126
80°	2837	2874	2800
85°	2212	2435	2435



TEST NUMBER: P845097

CATALOG NUMBER: SQ4P-PP3-OU-050D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.6	3.7
10°-20°	196.0	10.5
20°-30°	293.5	15.8
30°-40°	344.3	18.5
40°-50°	345.4	18.6
50°-60°	294.6	15.9
60°-70°	192.2	10.3
70°-80°	96.4	5.2
80°-90°	26.7	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	558.1	30.0
0°-40°	902.4	48.6
0°-60°	1542.4	83.0
0°-90°	1857.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1857.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	726	726	726	726	726	
5°	728	722	724	721	721	69
15°	700	694	697	694	693	198
25°	645	638	641	635	634	297
35°	557	552	553	547	546	348
45°	453	450	450	445	445	349
55°	336	335	331	330	329	298
65°	199	195	190	189	190	198
75°	90	90	89	88	88	98
85°	21	23	23	23	23	25
90°	0	0	0	0	0	



TEST NUMBER: P845097

CATALOG NUMBER: SQ4P-PP3-OU-050D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	725.8	725.8	725.8	725.8	725.8
2.5°	730.4	724.5	725.8	724.8	721.8
5°	728.3	721.6	723.9	721.4	721.4
7.5°	723.4	715.9	718.3	715.7	715.7
10°	718.9	711.4	713.8	711.2	710.6
12.5°	712.3	704.8	707.6	704.6	704.5
15°	700.4	693.5	696.6	693.9	692.7
17.5°	687.1	679.6	683.2	679.7	679.1
20°	676.8	669.3	673.0	668.0	668.0
22.5°	664.7	657.2	661.4	654.7	654.7
25°	645.0	637.5	640.6	634.8	634.3
27.5°	621.8	614.4	617.6	611.0	610.9
30°	605.0	598.1	601.8	594.8	594.1
32.5°	586.7	580.3	583.0	575.9	575.2
35°	557.3	551.7	553.4	547.0	546.5
37.5°	526.3	520.7	522.6	517.1	516.9
40°	504.4	500.7	501.2	496.7	495.5
42.5°	484.1	479.9	480.4	475.9	475.7
45°	452.9	449.7	449.7	445.3	445.3
47.5°	419.9	417.5	416.8	413.0	412.9
50°	396.9	395.1	394.4	391.2	390.5
52.5°	373.0	372.1	370.0	367.3	367.2
55°	335.9	334.6	331.4	329.5	328.9
57.5°	295.6	293.0	289.5	286.7	287.1
60°	266.5	264.0	258.9	257.7	257.7
62.5°	238.6	235.6	230.4	228.7	229.7
65°	198.6	194.8	190.2	189.0	189.5
67.5°	162.1	158.7	153.8	153.8	153.3
70°	138.7	136.7	133.0	133.0	133.0
72.5°	117.8	116.9	114.2	114.1	113.7
75°	90.4	90.4	89.1	88.4	87.7
77.5°	67.6	67.9	67.3	66.7	65.5
80°	53.4	54.8	54.1	53.4	52.7
82.5°	40.2	41.5	41.4	40.2	40.0
85°	20.9	22.8	23.0	23.0	23.0
87.5°	5.6	7.6	8.1	8.1	8.6
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







(END OF REPORT)