

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845142

Luminaire Tested: **SQ4P-PP3-150U-125D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845142
REPORT IS A COMBINATION OF REPORTS P700146 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-150U-125D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9463.4 lumens
Efficiency: N/A
Efficacy: 106.6 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 88.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845142

CATALOG NUMBER: SQ4P-PP3-150U-125D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845142

CATALOG NUMBER: SQ4P-PP3-150U-125D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	107	107	107	107	98	98	98	98	82	82	82	68	68	68	54	54	54	48	48	48	48																
1	98	93	90	86	90	86	83	80	72	70	68	60	58	57	48	47	46	41	41	41	41																
2	89	82	76	71	82	75	70	66	64	60	57	53	50	48	43	41	39	35	35	35	35																
3	81	72	65	59	74	66	60	55	56	52	48	47	43	40	38	36	34	29	29	29	29																
4	74	64	56	50	68	59	52	47	50	45	41	42	38	35	34	31	29	25	25	25	25																
5	68	57	49	43	63	53	46	40	45	39	35	37	33	30	31	28	25	22	22	22	22																
6	63	51	43	37	58	47	40	35	40	35	31	34	30	26	28	25	22	19	19	19	19																
7	58	46	38	33	53	43	36	31	37	31	27	31	27	23	25	22	20	17	17	17	17																
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15	15	15	15																
9	50	38	31	26	46	35	29	24	31	25	21	26	22	19	22	18	16	14	14	14	14																
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15	13	13	13	13																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16377	16377	16377
5°	16496	16395	16338
10°	16469	16354	16281
15°	16360	16270	16181
20°	16251	16159	16038
25°	16057	15949	15790
30°	15762	15679	15478
35°	15349	15243	15050
40°	14856	14763	14595
45°	14453	14353	14208
50°	13933	13844	13709
55°	13211	13037	12939
60°	12027	11686	11627
65°	10599	10154	10119
70°	9145	8770	8770
75°	7878	7760	7650
80°	6939	7029	6854
85°	5431	5928	5928



TEST NUMBER: P845142

CATALOG NUMBER: SQ4P-PP3-150U-125D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.8	1.8
10°-20°	479.2	5.1
20°-30°	717.8	7.6
30°-40°	842.0	8.9
40°-50°	844.6	8.9
50°-60°	720.5	7.6
60°-70°	469.9	5.0
70°-80°	235.7	2.5
80°-90°	67.1	0.7
90°-100°	301.6	3.2
100°-110°	1049.5	11.1
110°-120°	1016.6	10.7
120°-130°	797.5	8.4
130°-140°	631.2	6.7
140°-150°	487.1	5.1
150°-160°	349.2	3.7
160°-170°	213.6	2.3
170°-180°	72.2	0.8
0°-30°	1364.9	14.4
0°-40°	2206.9	23.3
0°-60°	3772.1	39.9
0°-90°	4544.8	48.0
90°-120°	2367.8	25.0
90°-150°	4283.6	45.3
90°-180°	4919.0	52.0
0°-180°	9463.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1775	1775	1775	1775	1775	
5°	1781	1765	1770	1764	1764	169
15°	1713	1696	1703	1697	1694	483
25°	1577	1559	1567	1552	1551	725
35°	1363	1349	1353	1338	1336	851
45°	1108	1100	1100	1089	1089	853
55°	821	818	810	806	804	730
65°	486	476	465	462	464	484
75°	221	221	218	216	215	240
85°	51	56	56	56	56	60
90°	11	17	17	11	6	9
95°	51	175	509	130	79	54
105°	175	249	1103	1861	1731	184
115°	305	368	820	1731	2042	302
125°	413	509	764	1290	1538	370
135°	498	560	758	1075	1216	386
145°	583	622	752	928	1007	364
155°	662	684	741	826	854	305
165°	724	730	747	780	786	204
175°	758	758	752	764	758	72
180°	758	758	758	758	758	



TEST NUMBER: P845142

CATALOG NUMBER: SQ4P-PP3-150U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1775.0	1775.0	1775.0	1775.0	1775.0
2.5°	1786.1	1771.5	1775.0	1772.4	1765.1
5°	1781.2	1764.6	1770.2	1764.1	1764.1
7.5°	1769.1	1750.9	1756.5	1750.4	1750.1
10°	1757.9	1739.7	1745.6	1739.1	1737.8
12.5°	1741.8	1723.6	1730.6	1723.0	1722.8
15°	1712.8	1696.0	1703.4	1697.0	1694.0
17.5°	1680.1	1661.8	1670.8	1662.1	1660.8
20°	1655.2	1636.9	1645.8	1633.5	1633.5
22.5°	1625.4	1607.2	1617.4	1601.0	1601.0
25°	1577.3	1559.1	1566.7	1552.4	1551.1
27.5°	1520.6	1502.5	1510.3	1494.2	1494.0
30°	1479.5	1462.6	1471.7	1454.6	1452.9
32.5°	1434.7	1419.1	1425.6	1408.4	1406.8
35°	1362.8	1349.1	1353.4	1337.9	1336.2
37.5°	1287.2	1273.3	1278.1	1264.6	1264.1
40°	1233.5	1224.4	1225.8	1214.7	1211.8
42.5°	1183.9	1173.4	1174.8	1163.7	1163.3
45°	1107.7	1100.0	1100.0	1088.9	1088.9
47.5°	1026.7	1020.8	1019.3	1010.2	1009.9
50°	970.7	966.2	964.5	956.8	955.1
52.5°	912.2	910.0	904.7	898.2	898.0
55°	821.3	818.4	810.5	805.7	804.4
57.5°	722.8	716.7	707.8	701.1	702.2
60°	651.8	645.6	633.3	630.1	630.1
62.5°	583.4	576.1	563.5	559.2	561.7
65°	485.5	476.4	465.1	462.1	463.5
67.5°	396.4	388.1	376.0	376.0	374.9
70°	339.0	334.4	325.1	325.1	325.1
72.5°	288.1	285.9	279.2	279.0	277.8
75°	221.0	221.0	217.7	216.2	214.6
77.5°	165.5	166.0	164.6	163.1	160.1
80°	130.6	133.8	132.3	130.6	129.0
82.5°	98.5	101.4	101.1	98.5	97.9
85°	51.3	55.8	56.0	56.0	56.0
87.5°	13.7	18.5	19.9	19.9	21.2
90°	11.3	17.0	17.0	11.3	5.6
92.5°	28.3	84.8	79.2	33.9	28.3
95°	50.9	175.3	509.0	130.0	79.2
97.5°	79.2	198.0	1018.1	463.8	248.9
100°	107.5	209.2	1187.8	1114.2	718.3
102.5°	141.4	226.3	1182.1	1566.7	1289.5
105°	175.3	248.9	1102.9	1860.8	1730.7



TEST NUMBER: P845142

CATALOG NUMBER: SQ4P-PP3-150U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.4	333.7	859.7	1872.1	2132.2
115°	305.4	367.7	820.1	1730.7	2041.8
117.5°	339.4	407.2	797.4	1600.6	1911.7
120°	367.7	441.1	780.5	1476.2	1781.6
122.5°	390.2	475.1	769.2	1374.4	1651.5
125°	412.9	509.0	763.5	1289.5	1538.4
127.5°	435.5	531.6	763.5	1227.3	1436.6
130°	458.2	543.0	757.9	1165.1	1351.7
132.5°	480.8	548.6	757.9	1119.8	1278.2
135°	497.7	559.9	757.9	1074.6	1216.0
137.5°	520.4	571.3	757.9	1035.1	1165.1
140°	537.3	588.2	757.9	995.4	1108.5
142.5°	559.9	605.2	757.9	955.9	1057.6
145°	582.6	622.1	752.2	927.6	1006.8
147.5°	605.2	639.1	746.6	899.3	961.5
150°	622.1	656.1	746.6	871.0	921.9
152.5°	644.8	673.0	740.9	842.7	888.0
155°	661.8	684.4	740.9	825.7	854.0
157.5°	678.7	701.3	740.9	808.8	831.5
160°	695.7	712.6	746.6	797.4	814.4
162.5°	712.6	724.0	746.6	786.2	797.4
165°	724.0	729.6	746.6	780.5	786.2
167.5°	735.2	740.9	746.6	774.9	774.9
170°	740.9	746.6	752.2	769.2	769.2
172.5°	752.2	752.2	752.2	763.5	763.5
175°	757.9	757.9	752.2	763.5	757.9
177.5°	757.9	757.9	752.2	763.5	757.9
180°	757.9	757.9	757.9	757.9	757.9



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	209.2	277.2	1001.1	1990.8	2013.5
110°	237.5	305.4	921.9	1973.9	2137.9



(END OF REPORT)