

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845106

Luminaire Tested: **SQ4P-PP3-0U-125D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845106
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P563482)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PP3-0U-125D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4543.0 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.22 / 1.33
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 45.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845106

CATALOG NUMBER: SQ4P-PP3-0U-125D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845106

CATALOG NUMBER: SQ4P-PP3-OU-125D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	109	105	101	97	107	103	99	96	98	95	93	95	92	90	91	89	87	85																			
2	100	92	86	80	97	90	84	79	87	82	77	84	79	76	81	77	74	72																			
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61																			
4	84	72	64	57	82	71	63	57	69	62	56	66	60	56	64	59	55	53																			
5	77	65	56	50	75	64	56	49	62	54	49	60	53	48	58	52	48	46																			
6	72	59	50	44	70	58	49	43	56	49	43	54	48	43	53	47	42	40																			
7	66	53	45	39	65	52	44	39	51	44	38	49	43	38	48	42	38	36																			
8	62	49	40	35	60	48	40	34	47	39	34	45	39	34	44	38	34	32																			
9	58	45	37	31	56	44	36	31	43	36	31	42	35	31	41	35	31	29																			
10	54	41	34	28	53	41	33	28	40	33	28	39	33	28	38	32	28	26																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16377	16377	16377
5°	16496	16395	16338
10°	16469	16354	16281
15°	16360	16270	16181
20°	16251	16159	16038
25°	16057	15949	15790
30°	15762	15679	15478
35°	15349	15243	15050
40°	14856	14763	14595
45°	14453	14353	14208
50°	13933	13844	13709
55°	13211	13037	12939
60°	12027	11686	11627
65°	10599	10154	10119
70°	9145	8770	8770
75°	7878	7760	7650
80°	6939	7029	6854
85°	5431	5928	5928



TEST NUMBER: P845106

CATALOG NUMBER: SQ4P-PP3-OU-125D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.8	3.7
10°-20°	479.2	10.5
20°-30°	717.8	15.8
30°-40°	842.0	18.5
40°-50°	844.6	18.6
50°-60°	720.5	15.9
60°-70°	469.9	10.3
70°-80°	235.7	5.2
80°-90°	65.3	1.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1364.9	30.0
0°-40°	2206.9	48.6
0°-60°	3772.1	83.0
0°-90°	4543.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4543.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1775	1775	1775	1775	1775	
5°	1781	1765	1770	1764	1764	169
15°	1713	1696	1703	1697	1694	483
25°	1577	1559	1567	1552	1551	725
35°	1363	1349	1353	1338	1336	851
45°	1108	1100	1100	1089	1089	853
55°	821	818	810	806	804	730
65°	486	476	465	462	464	484
75°	221	221	218	216	215	240
85°	51	56	56	56	56	62
90°	0	0	0	0	0	



TEST NUMBER: P845106

CATALOG NUMBER: SQ4P-PP3-OU-125D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1775.0	1775.0	1775.0	1775.0	1775.0
2.5°	1786.1	1771.5	1775.0	1772.4	1765.1
5°	1781.2	1764.6	1770.2	1764.1	1764.1
7.5°	1769.1	1750.9	1756.5	1750.4	1750.1
10°	1757.9	1739.7	1745.6	1739.1	1737.8
12.5°	1741.8	1723.6	1730.6	1723.0	1722.8
15°	1712.8	1696.0	1703.4	1697.0	1694.0
17.5°	1680.1	1661.8	1670.8	1662.1	1660.8
20°	1655.2	1636.9	1645.8	1633.5	1633.5
22.5°	1625.4	1607.2	1617.4	1601.0	1601.0
25°	1577.3	1559.1	1566.7	1552.4	1551.1
27.5°	1520.6	1502.5	1510.3	1494.2	1494.0
30°	1479.5	1462.6	1471.7	1454.6	1452.9
32.5°	1434.7	1419.1	1425.6	1408.4	1406.8
35°	1362.8	1349.1	1353.4	1337.9	1336.2
37.5°	1287.2	1273.3	1278.1	1264.6	1264.1
40°	1233.5	1224.4	1225.8	1214.7	1211.8
42.5°	1183.9	1173.4	1174.8	1163.7	1163.3
45°	1107.7	1100.0	1100.0	1088.9	1088.9
47.5°	1026.7	1020.8	1019.3	1010.2	1009.9
50°	970.7	966.2	964.5	956.8	955.1
52.5°	912.2	910.0	904.7	898.2	898.0
55°	821.3	818.4	810.5	805.7	804.4
57.5°	722.8	716.7	707.8	701.1	702.2
60°	651.8	645.6	633.3	630.1	630.1
62.5°	583.4	576.1	563.5	559.2	561.7
65°	485.5	476.4	465.1	462.1	463.5
67.5°	396.4	388.1	376.0	376.0	374.9
70°	339.0	334.4	325.1	325.1	325.1
72.5°	288.1	285.9	279.2	279.0	277.8
75°	221.0	221.0	217.7	216.2	214.6
77.5°	165.5	166.0	164.6	163.1	160.1
80°	130.6	133.8	132.3	130.6	129.0
82.5°	98.5	101.4	101.1	98.5	97.9
85°	51.3	55.8	56.0	56.0	56.0
87.5°	13.7	18.5	19.9	19.9	21.2
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)