

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845298

Luminaire Tested: **SQ4P-PW1-125U-125D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845298
REPORT IS A COMBINATION OF REPORTS P700126 AND P700247
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PW1-125U-125D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1250 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8606.7 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 79.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845298

CATALOG NUMBER: SQ4P-PW1-125U-125D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845298

CATALOG NUMBER: SQ4P-PW1-125U-125D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	58	58	58	52			
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	44			
2	90	82	76	71	83	76	71	67	65	61	58	55	52	50	46	44	42	37			
3	82	72	65	59	75	67	61	56	58	53	49	49	45	42	41	38	36	32			
4	75	64	56	50	69	60	53	47	51	46	42	44	39	36	36	33	31	27			
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	29	27	24			
6	63	51	43	37	58	48	41	35	41	36	31	35	31	27	30	26	24	21			
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	18			
8	54	42	34	29	50	39	32	28	34	29	25	29	25	22	25	21	19	17			
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	15			
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	21	18	15	14			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16372	16372	16372
5°	16479	16348	16276
10°	16346	16214	16126
15°	16173	15993	15934
20°	15979	15733	15704
25°	15757	15471	15421
30°	15424	15192	15091
35°	14986	14773	14686
40°	14519	14291	14237
45°	13953	13771	13708
50°	13376	13264	13172
55°	12749	12749	12550
60°	11976	12204	11771
65°	10955	11503	10684
70°	9655	10585	9409
75°	8252	9471	8021
80°	6402	7975	6487
85°	4139	6129	5452



TEST NUMBER: P845298

CATALOG NUMBER: SQ4P-PW1-125U-125D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	167.1	1.9
10°-20°	471.8	5.5
20°-30°	699.8	8.1
30°-40°	818.8	9.5
40°-50°	815.2	9.5
50°-60°	703.9	8.2
60°-70°	506.7	5.9
70°-80°	265.7	3.1
80°-90°	67.4	0.8
90°-100°	250.8	2.9
100°-110°	872.7	10.1
110°-120°	845.4	9.8
120°-130°	663.2	7.7
130°-140°	524.9	6.1
140°-150°	405.1	4.7
150°-160°	290.4	3.4
160°-170°	177.6	2.1
170°-180°	60.1	0.7
0°-30°	1338.6	15.6
0°-40°	2157.5	25.1
0°-60°	3676.6	42.7
0°-90°	4516.4	52.5
90°-120°	1969.0	22.9
90°-150°	3562.1	41.4
90°-180°	4090.0	47.5
0°-180°	8606.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1774	1774	1774	1774	1774	
5°	1779	1759	1765	1760	1757	169
15°	1693	1672	1674	1671	1668	477
25°	1548	1522	1520	1510	1515	712
35°	1330	1312	1312	1299	1304	832
45°	1069	1060	1055	1052	1051	825
55°	793	791	793	782	780	707
65°	502	517	527	506	489	497
75°	232	253	266	248	225	248
85°	39	51	58	55	52	52
90°	9	14	14	9	5	7
95°	42	146	423	108	66	45
105°	146	207	917	1547	1439	153
115°	254	306	682	1439	1698	251
125°	343	423	635	1072	1279	307
135°	414	466	630	894	1011	321
145°	484	517	626	771	837	303
155°	550	569	616	687	710	254
165°	602	607	621	649	654	170
175°	630	630	626	635	630	60
180°	630	630	630	630	630	



TEST NUMBER: P845298

CATALOG NUMBER: SQ4P-PW1-125U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1774.5	1774.5	1774.5	1774.5	1774.5
2.5°	1784.6	1769.8	1774.5	1770.7	1762.0
5°	1779.3	1759.3	1765.2	1760.4	1757.4
7.5°	1761.2	1742.9	1746.9	1742.1	1740.1
10°	1744.8	1726.4	1730.7	1724.5	1721.3
12.5°	1726.2	1706.5	1710.8	1704.3	1702.7
15°	1693.2	1671.7	1674.4	1671.1	1668.2
17.5°	1655.1	1633.5	1633.7	1628.9	1628.0
20°	1627.5	1604.6	1602.4	1596.2	1599.5
22.5°	1597.6	1573.4	1571.2	1562.6	1566.9
25°	1547.8	1521.9	1519.7	1510.3	1514.8
27.5°	1490.3	1464.7	1464.7	1451.6	1456.4
30°	1447.8	1423.3	1426.0	1410.3	1416.5
32.5°	1402.7	1380.6	1382.0	1366.7	1372.9
35°	1330.5	1312.2	1311.6	1299.3	1303.9
37.5°	1256.7	1240.5	1237.8	1230.8	1231.9
40°	1205.5	1191.8	1186.6	1182.1	1182.1
42.5°	1151.5	1139.2	1134.1	1130.6	1129.4
45°	1069.4	1060.3	1055.4	1052.1	1050.6
47.5°	988.0	979.6	975.4	973.1	971.6
50°	931.9	925.7	924.1	919.3	917.7
52.5°	875.6	871.9	870.2	864.3	862.7
55°	792.6	791.2	792.6	781.8	780.2
57.5°	706.4	708.8	713.9	699.1	695.3
60°	649.0	654.9	661.4	644.1	637.9
62.5°	590.0	599.9	608.8	588.9	580.3
65°	501.8	517.2	526.9	506.1	489.4
67.5°	416.9	435.8	447.4	425.3	406.1
70°	357.9	379.5	392.4	370.0	348.8
72.5°	306.7	330.6	341.2	319.9	298.6
75°	231.5	252.8	265.7	248.0	225.0
77.5°	164.2	184.3	195.1	179.8	160.7
80°	120.5	141.8	150.1	137.2	122.1
82.5°	85.5	103.2	108.9	101.1	90.5
85°	39.1	51.2	57.9	54.8	51.5
87.5°	10.0	18.6	23.7	23.7	25.1
90°	9.4	14.1	14.1	9.4	4.7
92.5°	23.5	70.5	65.8	28.2	23.5
95°	42.3	145.8	423.3	108.1	65.8
97.5°	65.8	164.6	846.6	385.7	207.0
100°	89.3	174.0	987.7	926.5	597.3
102.5°	117.5	188.1	983.0	1302.8	1072.4
105°	145.8	207.0	917.1	1547.4	1439.3



TEST NUMBER: P845298

CATALOG NUMBER: SQ4P-PW1-125U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	225.8	277.5	714.9	1556.8	1773.2
115°	254.0	305.7	682.0	1439.3	1697.9
117.5°	282.2	338.7	663.1	1331.1	1589.7
120°	305.7	366.9	649.1	1227.6	1481.6
122.5°	324.5	395.1	639.7	1142.9	1373.4
125°	343.3	423.3	634.9	1072.4	1279.4
127.5°	362.1	442.1	634.9	1020.6	1194.7
130°	380.9	451.5	630.3	968.9	1124.1
132.5°	399.8	456.2	630.3	931.3	1063.0
135°	413.9	465.6	630.3	893.7	1011.2
137.5°	432.7	475.0	630.3	860.7	968.9
140°	446.8	489.2	630.3	827.8	921.9
142.5°	465.6	503.2	630.3	794.8	879.5
145°	484.4	517.4	625.5	771.4	837.2
147.5°	503.2	531.4	620.9	747.8	799.6
150°	517.4	545.6	620.9	724.3	766.6
152.5°	536.2	559.7	616.1	700.8	738.4
155°	550.3	569.1	616.1	686.7	710.2
157.5°	564.4	583.2	616.1	672.6	691.4
160°	578.5	592.6	620.9	663.1	677.3
162.5°	592.6	602.1	620.9	653.7	663.1
165°	602.1	606.7	620.9	649.1	653.7
167.5°	611.5	616.1	620.9	644.3	644.3
170°	616.1	620.9	625.5	639.7	639.7
172.5°	625.5	625.5	625.5	634.9	634.9
175°	630.3	630.3	625.5	634.9	630.3
177.5°	630.3	630.3	625.5	634.9	630.3
180°	630.3	630.3	630.3	630.3	630.3



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	174.0	230.4	832.5	1655.5	1674.4
110°	197.5	254.0	766.6	1641.5	1777.8



(END OF REPORT)