

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845307

Luminaire Tested: **SQ4P-PW1-150U-100D-B40-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845307
REPORT IS A COMBINATION OF REPORTS P700153 AND P700248
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-PW1-150U-100D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT
UPLIGHT, 1000 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8530.2 lumens
Efficiency: N/A
Efficacy: 109.5 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.19 / 1.31
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: General Diffuse

Input Watts (W): 77.9
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845307

CATALOG NUMBER: SQ4P-PW1-150U-100D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845307

CATALOG NUMBER: SQ4P-PW1-150U-100D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49	42																			
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	44	43	42	36																			
2	88	80	74	69	80	74	68	64	61	57	54	49	47	44	38	37	35	30																			
3	80	71	63	58	73	65	59	54	54	49	45	44	40	38	34	32	30	26																			
4	73	62	55	49	66	57	51	45	48	43	39	39	35	32	30	28	26	22																			
5	67	56	48	42	61	51	44	39	43	37	33	35	31	28	27	25	23	19																			
6	62	50	42	36	56	46	39	34	38	33	29	31	27	24	25	22	20	17																			
7	57	45	37	32	52	41	34	30	35	29	26	29	25	22	23	20	18	15																			
8	53	41	33	28	48	38	31	26	32	26	23	26	22	19	21	18	16	13																			
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	19	16	14	12																			
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13	11																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13089	13089	13089
5°	13175	13071	13013
10°	13069	12964	12894
15°	12931	12788	12740
20°	12777	12579	12557
25°	12598	12370	12330
30°	12331	12146	12065
35°	11982	11812	11741
40°	11608	11426	11382
45°	11156	11010	10959
50°	10695	10606	10531
55°	10193	10193	10034
60°	9573	9758	9411
65°	8759	9197	8542
70°	7720	8462	7521
75°	6598	7571	6417
80°	5117	6381	5186
85°	3303	4901	4361



TEST NUMBER: P845307

CATALOG NUMBER: SQ4P-PW1-150U-100D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	133.6	1.6
10°-20°	377.2	4.4
20°-30°	559.5	6.6
30°-40°	654.7	7.7
40°-50°	651.8	7.6
50°-60°	562.8	6.6
60°-70°	405.1	4.7
70°-80°	212.4	2.5
80°-90°	54.5	0.6
90°-100°	301.6	3.5
100°-110°	1049.5	12.3
110°-120°	1016.6	11.9
120°-130°	797.5	9.3
130°-140°	631.2	7.4
140°-150°	487.1	5.7
150°-160°	349.2	4.1
160°-170°	213.6	2.5
170°-180°	72.2	0.8
0°-30°	1070.3	12.5
0°-40°	1724.9	20.2
0°-60°	2939.5	34.5
0°-90°	3611.6	42.3
90°-120°	2367.8	27.8
90°-150°	4283.6	50.2
90°-180°	4919.0	57.7
0°-180°	8530.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1419	1419	1419	1419	1419	
5°	1423	1407	1411	1408	1405	135
15°	1354	1337	1339	1336	1334	382
25°	1238	1217	1215	1208	1211	569
35°	1064	1049	1049	1039	1042	665
45°	855	848	844	841	840	660
55°	634	633	634	625	624	565
65°	401	414	421	405	391	398
75°	185	202	212	198	180	198
85°	31	41	46	44	41	41
90°	11	17	17	11	6	8
95°	51	175	509	130	79	54
105°	175	249	1103	1861	1731	184
115°	305	368	820	1731	2042	302
125°	413	509	764	1290	1538	370
135°	498	560	758	1075	1216	386
145°	583	622	752	928	1007	364
155°	662	684	741	826	854	305
165°	724	730	747	780	786	204
175°	758	758	752	764	758	72
180°	758	758	758	758	758	



TEST NUMBER: P845307

CATALOG NUMBER: SQ4P-PW1-150U-100D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1418.7	1418.7	1418.7	1418.7	1418.7
2.5°	1426.8	1415.0	1418.7	1415.7	1408.7
5°	1422.6	1406.6	1411.3	1407.5	1405.1
7.5°	1408.1	1393.5	1396.7	1392.8	1391.3
10°	1395.0	1380.3	1383.8	1378.8	1376.3
12.5°	1380.1	1364.3	1367.8	1362.7	1361.3
15°	1353.8	1336.6	1338.8	1336.1	1333.8
17.5°	1323.3	1306.0	1306.2	1302.3	1301.6
20°	1301.3	1282.9	1281.2	1276.3	1278.9
22.5°	1277.3	1257.9	1256.2	1249.3	1252.8
25°	1237.5	1216.8	1215.1	1207.5	1211.2
27.5°	1191.6	1171.1	1171.1	1160.5	1164.4
30°	1157.5	1138.0	1140.1	1127.6	1132.5
32.5°	1121.6	1103.9	1104.9	1092.7	1097.7
35°	1063.8	1049.1	1048.7	1038.8	1042.4
37.5°	1004.7	991.8	989.7	984.1	985.0
40°	963.8	952.8	948.7	945.0	945.0
42.5°	920.7	910.8	906.8	903.9	903.1
45°	855.0	847.6	843.8	841.2	839.9
47.5°	789.9	783.3	779.8	778.1	776.8
50°	745.1	740.2	738.9	734.9	733.7
52.5°	700.1	697.0	695.8	691.0	689.8
55°	633.7	632.6	633.7	625.0	623.8
57.5°	564.8	566.7	570.8	559.0	556.0
60°	518.8	523.6	528.8	515.0	510.0
62.5°	471.6	479.7	486.8	470.8	463.9
65°	401.2	413.5	421.3	404.7	391.3
67.5°	333.4	348.4	357.7	340.0	324.7
70°	286.2	303.4	313.7	295.9	278.8
72.5°	245.2	264.4	272.8	255.7	238.8
75°	185.1	202.1	212.4	198.3	180.0
77.5°	131.2	147.4	156.0	143.7	128.4
80°	96.3	113.4	120.1	109.7	97.6
82.5°	68.3	82.6	87.0	80.8	72.4
85°	31.2	40.9	46.3	43.7	41.2
87.5°	7.9	14.8	19.0	19.0	20.1
90°	11.3	17.0	17.0	11.3	5.6
92.5°	28.3	84.8	79.2	33.9	28.3
95°	50.9	175.3	509.0	130.0	79.2
97.5°	79.2	198.0	1018.1	463.8	248.9
100°	107.5	209.2	1187.8	1114.2	718.3
102.5°	141.4	226.3	1182.1	1566.7	1289.5
105°	175.3	248.9	1102.9	1860.8	1730.7



TEST NUMBER: P845307

CATALOG NUMBER: SQ4P-PW1-150U-100D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	271.4	333.7	859.7	1872.1	2132.2
115°	305.4	367.7	820.1	1730.7	2041.8
117.5°	339.4	407.2	797.4	1600.6	1911.7
120°	367.7	441.1	780.5	1476.2	1781.6
122.5°	390.2	475.1	769.2	1374.4	1651.5
125°	412.9	509.0	763.5	1289.5	1538.4
127.5°	435.5	531.6	763.5	1227.3	1436.6
130°	458.2	543.0	757.9	1165.1	1351.7
132.5°	480.8	548.6	757.9	1119.8	1278.2
135°	497.7	559.9	757.9	1074.6	1216.0
137.5°	520.4	571.3	757.9	1035.1	1165.1
140°	537.3	588.2	757.9	995.4	1108.5
142.5°	559.9	605.2	757.9	955.9	1057.6
145°	582.6	622.1	752.2	927.6	1006.8
147.5°	605.2	639.1	746.6	899.3	961.5
150°	622.1	656.1	746.6	871.0	921.9
152.5°	644.8	673.0	740.9	842.7	888.0
155°	661.8	684.4	740.9	825.7	854.0
157.5°	678.7	701.3	740.9	808.8	831.5
160°	695.7	712.6	746.6	797.4	814.4
162.5°	712.6	724.0	746.6	786.2	797.4
165°	724.0	729.6	746.6	780.5	786.2
167.5°	735.2	740.9	746.6	774.9	774.9
170°	740.9	746.6	752.2	769.2	769.2
172.5°	752.2	752.2	752.2	763.5	763.5
175°	757.9	757.9	752.2	763.5	757.9
177.5°	757.9	757.9	752.2	763.5	757.9
180°	757.9	757.9	757.9	757.9	757.9



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	209.2	277.2	1001.1	1990.8	2013.5
110°	237.5	305.4	921.9	1973.9	2137.9



(END OF REPORT)