

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845322

Luminaire Tested: **SQ4P-WB-025U-125D-B40-1D-UNV**

Issue Date: 8/14/2023

Test Information

Test Method: LM-79-08
Report Number: P845322
REPORT IS A COMBINATION OF REPORTS P700186 AND P700243
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-025U-125D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 250 LUMENS PER FOOT
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4776.5 lumens
Efficiency: N/A
Efficacy: 90.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 52.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845322

CATALOG NUMBER: SQ4P-WB-025U-125D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845322

CATALOG NUMBER: SQ4P-WB-025U-125D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	115	115	115	115	110	110	110	110	101	101	101	93	93	93	86	86	86	82								
1	107	103	100	97	102	99	96	93	92	89	87	85	83	82	79	77	76	73								
2	99	92	87	82	95	89	84	80	83	79	76	77	74	71	72	69	67	64								
3	92	83	76	71	88	80	74	69	75	70	66	70	66	63	65	62	60	57								
4	85	75	68	62	82	73	66	61	68	63	58	64	59	56	60	56	53	51								
5	79	68	61	55	76	66	59	54	62	56	52	59	54	50	55	51	48	46								
6	74	62	55	49	71	61	53	48	57	51	47	54	49	45	51	47	43	41								
7	69	57	50	44	66	56	49	44	53	47	42	50	45	41	47	43	39	37								
8	65	53	45	40	62	51	44	40	49	43	38	46	41	37	44	39	36	34								
9	61	49	42	37	58	48	41	36	45	39	35	43	38	34	41	36	33	31								
10	57	45	38	34	55	44	38	33	42	36	32	40	35	32	38	34	31	29								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24904	24904	24904
5°	24595	24505	24649
10°	23236	23448	23990
15°	21449	21949	22933
20°	19480	20211	21547
25°	17472	18425	20076
30°	15622	16642	18548
35°	13660	14648	16743
40°	11496	12410	14494
45°	9488	10306	12102
50°	7920	8636	10080
55°	6725	7411	8324
60°	5750	6427	6645
65°	4578	5403	4290
70°	4057	4216	2619
75°	3754	3422	1608
80°	3459	3145	1381
85°	3123	2890	1143



TEST NUMBER: P845322

CATALOG NUMBER: SQ4P-WB-025U-125D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.6	5.2
10°-20°	644.0	13.5
20°-30°	834.2	17.5
30°-40°	816.9	17.1
40°-50°	625.2	13.1
50°-60°	416.6	8.7
60°-70°	227.4	4.8
70°-80°	94.7	2.0
80°-90°	27.1	0.6
90°-100°	51.7	1.1
100°-110°	179.8	3.8
110°-120°	174.2	3.6
120°-130°	136.6	2.9
130°-140°	108.2	2.3
140°-150°	83.5	1.7
150°-160°	59.8	1.3
160°-170°	36.6	0.8
170°-180°	12.4	0.3
0°-30°	1725.8	36.1
0°-40°	2542.6	53.2
0°-60°	3584.5	75.0
0°-90°	3933.7	82.4
90°-120°	405.7	8.5
90°-150°	734.0	15.4
90°-180°	843.0	17.6
0°-180°	4776.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2699	2699	2699	2699	2699	
5°	2656	2629	2646	2652	2662	247
15°	2246	2238	2298	2360	2401	627
25°	1716	1721	1810	1889	1972	789
35°	1213	1219	1300	1388	1486	754
45°	727	741	790	850	928	567
55°	418	436	461	478	518	379
65°	210	227	248	216	196	218
75°	105	105	96	66	45	113
85°	30	30	27	18	11	32
90°	2	3	3	2	1	3
95°	9	30	87	22	14	9
105°	30	43	189	319	297	32
115°	52	63	140	297	350	52
125°	71	87	131	221	264	63
135°	85	96	130	184	208	66
145°	100	107	129	159	172	62
155°	113	117	127	142	146	52
165°	124	125	128	134	135	35
175°	130	130	129	131	130	12
180°	130	130	130	130	130	



TEST NUMBER: P845322

CATALOG NUMBER: SQ4P-WB-025U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2699.3	2699.3	2699.3	2699.3	2699.3
2.5°	2706.0	2681.9	2688.1	2687.8	2680.2
5°	2655.6	2628.8	2645.9	2652.1	2661.5
7.5°	2557.0	2536.8	2568.2	2591.3	2610.0
10°	2480.2	2462.8	2502.8	2536.5	2560.7
12.5°	2391.3	2376.4	2426.0	2471.1	2503.0
15°	2245.6	2237.6	2297.9	2360.3	2400.9
17.5°	2090.1	2086.1	2155.3	2228.2	2279.9
20°	1984.0	1982.9	2058.5	2134.7	2194.6
22.5°	1877.0	1879.3	1959.0	2038.1	2106.7
25°	1716.3	1720.9	1809.9	1888.7	1972.1
27.5°	1567.8	1569.9	1661.7	1745.0	1834.0
30°	1466.4	1472.1	1562.1	1648.5	1741.0
32.5°	1365.0	1371.8	1460.0	1549.0	1643.4
35°	1212.8	1218.7	1300.5	1388.1	1486.5
37.5°	1055.9	1063.9	1136.6	1219.2	1316.3
40°	954.5	966.3	1030.4	1108.5	1203.4
42.5°	856.9	871.5	931.0	1004.9	1090.5
45°	727.2	741.1	789.9	849.7	927.5
47.5°	615.4	631.4	669.0	720.5	786.7
50°	551.8	567.1	601.7	639.8	702.3
52.5°	496.1	511.1	541.9	571.4	624.8
55°	418.1	435.5	460.7	478.3	517.5
57.5°	354.2	370.9	390.9	398.7	422.6
60°	311.6	330.1	348.3	347.2	360.1
62.5°	272.7	288.5	306.5	293.9	294.7
65°	209.7	227.1	247.5	216.4	196.5
67.5°	169.5	173.0	194.1	151.0	127.3
70°	150.4	150.4	156.3	116.9	97.1
72.5°	132.5	132.5	127.1	94.9	74.2
75°	105.3	105.3	96.0	66.0	45.1
77.5°	81.2	80.4	73.5	49.0	32.8
80°	65.1	65.1	59.2	38.9	26.0
82.5°	51.0	51.0	45.8	30.3	19.3
85°	29.5	29.5	27.3	17.7	10.8
87.5°	10.5	10.5	9.4	5.6	4.8
90°	1.9	2.9	2.9	1.9	1.0
92.5°	4.8	14.5	13.6	5.8	4.8
95°	8.7	30.0	87.2	22.3	13.6
97.5°	13.6	33.9	174.4	79.5	42.6
100°	18.4	35.9	203.5	190.9	123.1
102.5°	24.2	38.8	202.5	268.4	220.9
105°	30.0	42.6	189.0	318.9	296.6



TEST NUMBER: P845322

CATALOG NUMBER: SQ4P-WB-025U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	46.5	57.2	147.3	320.9	365.4
115°	52.3	63.0	140.5	296.6	349.9
117.5°	58.1	69.8	136.6	274.2	327.6
120°	63.0	75.6	133.7	252.9	305.4
122.5°	66.9	81.4	131.8	235.5	283.1
125°	70.7	87.2	130.8	220.9	263.6
127.5°	74.6	91.1	130.8	210.3	246.1
130°	78.5	93.0	129.9	199.6	231.6
132.5°	82.4	94.0	129.9	191.9	219.0
135°	85.3	95.9	129.9	184.1	208.3
137.5°	89.2	97.9	129.9	177.3	199.6
140°	92.1	100.8	129.9	170.6	189.9
142.5°	95.9	103.7	129.9	163.8	181.2
145°	99.8	106.6	128.9	158.9	172.5
147.5°	103.7	109.5	127.9	154.1	164.7
150°	106.6	112.4	127.9	149.2	158.0
152.5°	110.5	115.3	126.9	144.4	152.1
155°	113.4	117.3	126.9	141.5	146.3
157.5°	116.3	120.2	126.9	138.6	142.5
160°	119.2	122.1	127.9	136.6	139.5
162.5°	122.1	124.0	127.9	134.7	136.6
165°	124.0	125.0	127.9	133.7	134.7
167.5°	126.0	126.9	127.9	132.8	132.8
170°	126.9	127.9	128.9	131.8	131.8
172.5°	128.9	128.9	128.9	130.8	130.8
175°	129.9	129.9	128.9	130.8	129.9
177.5°	129.9	129.9	128.9	130.8	129.9
180°	129.9	129.9	129.9	129.9	129.9



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	35.9	47.5	171.5	341.2	345.1
110°	40.7	52.3	158.0	338.3	366.4



(END OF REPORT)