

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845334

Luminaire Tested: **SQ4P-WB-050U-125D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845334
REPORT IS A COMBINATION OF REPORTS P700214 AND P700244
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-050U-125D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 500 LUMENS PER FOOT UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5627.6 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Semi-Direct

Input Watts (W): 58.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845334

CATALOG NUMBER: SQ4P-WB-050U-125D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845334

CATALOG NUMBER: SQ4P-WB-050U-125D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20									
RC	80					70					50					30					10					0				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0			
RCR																														
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	74	74	74	70			
1	104	100	97	93	98	95	92	89	85	83	81	76	75	73	68	67	66	66	66	66	66	66	66	66	66	66	62			
2	96	89	84	79	91	85	80	76	77	73	70	69	66	64	62	60	58	58	58	58	58	58	58	58	58	58	55			
3	89	80	73	68	84	76	70	66	69	65	61	63	59	56	57	54	51	51	51	51	51	51	51	51	51	51	48			
4	82	72	65	59	78	69	62	57	63	58	53	57	53	50	52	49	46	46	46	46	46	46	46	46	46	46	43			
5	76	65	58	52	72	63	56	51	57	52	47	52	48	44	48	44	41	41	41	41	41	41	41	41	41	41	39			
6	71	60	52	47	67	57	50	45	52	47	42	48	43	40	44	40	37	37	37	37	37	37	37	37	37	37	35			
7	66	55	47	42	63	52	45	41	48	42	38	44	40	36	41	37	34	34	34	34	34	34	34	34	34	34	32			
8	62	50	43	38	59	48	41	37	45	39	35	41	36	33	38	34	31	31	31	31	31	31	31	31	31	31	29			
9	58	46	39	34	55	45	38	33	41	36	32	38	34	30	35	31	29	29	29	29	29	29	29	29	29	29	27			
10	55	43	36	31	52	41	35	31	38	33	29	36	31	28	33	29	26	26	26	26	26	26	26	26	26	26	25			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	24904	24904	24904
5°	24595	24505	24649
10°	23236	23448	23990
15°	21449	21949	22933
20°	19480	20211	21547
25°	17472	18425	20076
30°	15622	16642	18548
35°	13660	14648	16743
40°	11496	12410	14494
45°	9488	10306	12102
50°	7920	8636	10080
55°	6725	7411	8324
60°	5750	6427	6645
65°	4578	5403	4290
70°	4057	4216	2619
75°	3754	3422	1608
80°	3459	3145	1381
85°	3123	2890	1143



TEST NUMBER: P845334

CATALOG NUMBER: SQ4P-WB-050U-125D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	247.6	4.4
10°-20°	644.0	11.4
20°-30°	834.2	14.8
30°-40°	816.9	14.5
40°-50°	625.2	11.1
50°-60°	416.6	7.4
60°-70°	227.4	4.0
70°-80°	94.7	1.7
80°-90°	27.5	0.5
90°-100°	103.8	1.8
100°-110°	361.4	6.4
110°-120°	350.0	6.2
120°-130°	274.6	4.9
130°-140°	217.3	3.9
140°-150°	167.7	3.0
150°-160°	120.2	2.1
160°-170°	73.5	1.3
170°-180°	24.9	0.4
0°-30°	1725.8	30.7
0°-40°	2542.6	45.2
0°-60°	3584.5	63.7
0°-90°	3934.1	69.9
90°-120°	815.2	14.5
90°-150°	1474.9	26.2
90°-180°	1694.0	30.1
0°-180°	5627.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2699	2699	2699	2699	2699	
5°	2656	2629	2646	2652	2662	247
15°	2246	2238	2298	2360	2401	627
25°	1716	1721	1810	1889	1972	789
35°	1213	1219	1300	1388	1486	754
45°	727	741	790	850	928	567
55°	418	436	461	478	518	379
65°	210	227	248	216	196	218
75°	105	105	96	66	45	113
85°	30	30	27	18	11	32
90°	4	6	6	4	2	4
95°	18	60	175	45	27	19
105°	60	86	380	641	596	63
115°	105	127	282	596	703	104
125°	142	175	263	444	530	127
135°	171	193	261	370	419	133
145°	201	214	259	319	347	125
155°	228	236	255	284	294	105
165°	249	251	257	269	271	70
175°	261	261	259	263	261	25
180°	261	261	261	261	261	



TEST NUMBER: P845334

CATALOG NUMBER: SQ4P-WB-050U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2699.3	2699.3	2699.3	2699.3	2699.3
2.5°	2706.0	2681.9	2688.1	2687.8	2680.2
5°	2655.6	2628.8	2645.9	2652.1	2661.5
7.5°	2557.0	2536.8	2568.2	2591.3	2610.0
10°	2480.2	2462.8	2502.8	2536.5	2560.7
12.5°	2391.3	2376.4	2426.0	2471.1	2503.0
15°	2245.6	2237.6	2297.9	2360.3	2400.9
17.5°	2090.1	2086.1	2155.3	2228.2	2279.9
20°	1984.0	1982.9	2058.5	2134.7	2194.6
22.5°	1877.0	1879.3	1959.0	2038.1	2106.7
25°	1716.3	1720.9	1809.9	1888.7	1972.1
27.5°	1567.8	1569.9	1661.7	1745.0	1834.0
30°	1466.4	1472.1	1562.1	1648.5	1741.0
32.5°	1365.0	1371.8	1460.0	1549.0	1643.4
35°	1212.8	1218.7	1300.5	1388.1	1486.5
37.5°	1055.9	1063.9	1136.6	1219.2	1316.3
40°	954.5	966.3	1030.4	1108.5	1203.4
42.5°	856.9	871.5	931.0	1004.9	1090.5
45°	727.2	741.1	789.9	849.7	927.5
47.5°	615.4	631.4	669.0	720.5	786.7
50°	551.8	567.1	601.7	639.8	702.3
52.5°	496.1	511.1	541.9	571.4	624.8
55°	418.1	435.5	460.7	478.3	517.5
57.5°	354.2	370.9	390.9	398.7	422.6
60°	311.6	330.1	348.3	347.2	360.1
62.5°	272.7	288.5	306.5	293.9	294.7
65°	209.7	227.1	247.5	216.4	196.5
67.5°	169.5	173.0	194.1	151.0	127.3
70°	150.4	150.4	156.3	116.9	97.1
72.5°	132.5	132.5	127.1	94.9	74.2
75°	105.3	105.3	96.0	66.0	45.1
77.5°	81.2	80.4	73.5	49.0	32.8
80°	65.1	65.1	59.2	38.9	26.0
82.5°	51.0	51.0	45.8	30.3	19.3
85°	29.5	29.5	27.3	17.7	10.8
87.5°	10.5	10.5	9.4	5.6	4.8
90°	3.9	5.8	5.8	3.9	1.9
92.5°	9.7	29.2	27.2	11.7	9.7
95°	17.5	60.4	175.3	44.8	27.2
97.5°	27.2	68.1	350.5	159.7	85.7
100°	37.0	72.1	408.9	383.7	247.3
102.5°	48.6	77.9	407.0	539.4	444.0
105°	60.4	85.7	379.8	640.6	595.9



TEST NUMBER: P845334

CATALOG NUMBER: SQ4P-WB-050U-125D-B40-1D-UNV

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	93.5	114.9	296.0	644.6	734.2
115°	105.1	126.6	282.4	595.9	703.0
117.5°	116.9	140.2	274.5	551.1	658.2
120°	126.6	151.9	268.7	508.3	613.4
122.5°	134.4	163.6	264.8	473.2	568.6
125°	142.2	175.3	262.9	444.0	529.7
127.5°	149.9	183.1	262.9	422.6	494.6
130°	157.8	186.9	261.0	401.2	465.4
132.5°	165.5	188.9	261.0	385.6	440.1
135°	171.3	192.7	261.0	370.0	418.7
137.5°	179.2	196.7	261.0	356.3	401.2
140°	185.0	202.5	261.0	342.8	381.7
142.5°	192.7	208.3	261.0	329.1	364.2
145°	200.6	214.3	259.0	319.4	346.6
147.5°	208.3	220.1	257.1	309.6	331.0
150°	214.3	225.9	257.1	299.9	317.5
152.5°	222.0	231.7	255.2	290.1	305.7
155°	227.8	235.7	255.2	284.3	294.0
157.5°	233.6	241.5	255.2	278.5	286.3
160°	239.6	245.4	257.1	274.5	280.4
162.5°	245.4	249.2	257.1	270.7	274.5
165°	249.2	251.2	257.1	268.7	270.7
167.5°	253.1	255.2	257.1	266.8	266.8
170°	255.2	257.1	259.0	264.8	264.8
172.5°	259.0	259.0	259.0	262.9	262.9
175°	261.0	261.0	259.0	262.9	261.0
177.5°	261.0	261.0	259.0	262.9	261.0
180°	261.0	261.0	261.0	261.0	261.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







107.5°	72.1	95.5	344.7	685.5	693.3
110°	81.8	105.1	317.5	679.6	736.1



(END OF REPORT)