

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845352

Luminaire Tested: **SQ4P-WB-0U-075D-B40-1D-UNV**

Issue Date: 8/14/2023



Test Information

Test Method: LM-79-08
Report Number: P845352
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P519276)
Test Lab: INNOVATION CENTER
Issue Date: 8/14/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: CORELITE
Catalog Number: SQ4P-WB-0U-075D-B40-1D-UNV
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, DIRECT ONLY 750 LUMENS PER FOOT DOWNLIGHT

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2393.6 lumens
Efficiency: N/A
Efficacy: 93.5 lumens/watt
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')
CIE Type: Direct

Input Watts (W): 25.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P845352

CATALOG NUMBER: SQ4P-WB-0U-075D-B40-1D-UNV

Luminous Intensity Polar Plot





TEST NUMBER: P845352

CATALOG NUMBER: SQ4P-WB-0U-075D-B40-1D-UNV

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	97	91	87	101	95	90	86	92	87	84	88	85	82	85	83	80	78																			
3	96	87	81	75	94	86	80	75	83	78	73	80	76	72	78	74	71	69																			
4	89	79	72	66	87	78	71	66	76	70	65	74	68	64	71	67	64	62																			
5	83	72	65	59	81	71	64	59	69	63	58	67	62	58	66	61	57	55																			
6	78	66	59	53	76	65	58	53	64	57	53	62	56	52	61	56	52	50																			
7	73	61	53	48	71	60	53	48	59	52	48	58	52	47	56	51	47	45																			
8	68	57	49	44	67	56	49	44	55	48	44	53	48	43	52	47	43	41																			
9	64	53	45	40	63	52	45	40	51	45	40	50	44	40	49	44	40	38																			
10	61	49	42	37	60	48	42	37	48	41	37	47	41	37	46	41	37	35																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	15155	15155	15155
5°	14966	14912	15000
10°	14140	14268	14599
15°	13052	13357	13955
20°	11854	12298	13112
25°	10633	11211	12217
30°	9506	10128	11287
35°	8312	8913	10189
40°	6996	7553	8820
45°	5774	6272	7364
50°	4820	5255	6135
55°	4092	4509	5065
60°	3499	3910	4043
65°	2786	3288	2611
70°	2471	2568	1594
75°	2289	2082	977
80°	2104	1913	839
85°	1895	1768	688



TEST NUMBER: P845352

CATALOG NUMBER: SQ4P-WB-0U-075D-B40-1D-UNV

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.7	6.3
10°-20°	391.9	16.4
20°-30°	507.6	21.2
30°-40°	497.1	20.8
40°-50°	380.5	15.9
50°-60°	253.5	10.6
60°-70°	138.4	5.8
70°-80°	57.7	2.4
80°-90°	16.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1050.2	43.9
0°-40°	1547.2	64.6
0°-60°	2181.3	91.1
0°-90°	2393.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2393.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1643	1643	1643	1643	1643	
5°	1616	1600	1610	1614	1620	150
15°	1366	1362	1398	1436	1461	382
25°	1044	1047	1101	1149	1200	480
35°	738	742	791	845	905	459
45°	442	451	481	517	564	345
55°	254	265	280	291	315	231
65°	128	138	151	132	120	133
75°	64	64	58	40	27	68
85°	18	18	17	11	6	20
90°	0	0	0	0	0	



TEST NUMBER: P845352

CATALOG NUMBER: SQ4P-WB-0U-075D-B40-1D-UNV

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1642.6	1642.6	1642.6	1642.6	1642.6
2.5°	1646.6	1632.0	1635.8	1635.6	1631.0
5°	1616.0	1599.6	1610.1	1613.9	1619.6
7.5°	1555.9	1543.7	1562.8	1576.9	1588.3
10°	1509.3	1498.7	1523.0	1543.5	1558.3
12.5°	1455.1	1446.1	1476.4	1503.7	1523.2
15°	1366.5	1361.6	1398.4	1436.3	1461.0
17.5°	1271.9	1269.5	1311.5	1355.9	1387.4
20°	1207.3	1206.6	1252.6	1298.9	1335.5
22.5°	1142.1	1143.6	1192.0	1240.2	1282.0
25°	1044.5	1047.2	1101.3	1149.3	1200.1
27.5°	954.0	955.3	1011.1	1061.9	1116.1
30°	892.3	895.8	950.7	1003.2	1059.5
32.5°	830.7	834.8	888.4	942.6	1000.1
35°	738.0	741.6	791.3	844.7	904.6
37.5°	642.6	647.4	691.6	741.9	801.0
40°	580.9	588.0	627.1	674.6	732.3
42.5°	521.5	530.3	566.5	611.6	663.6
45°	442.5	451.0	480.7	517.1	564.4
47.5°	374.4	384.2	407.1	438.4	478.7
50°	335.8	345.1	366.1	389.3	427.4
52.5°	301.9	311.0	329.8	347.7	380.2
55°	254.4	264.9	280.3	291.1	314.9
57.5°	215.5	225.7	237.9	242.7	257.2
60°	189.6	200.9	211.9	211.3	219.1
62.5°	165.9	175.6	186.5	178.8	179.3
65°	127.6	138.2	150.6	131.7	119.6
67.5°	103.1	105.2	118.1	91.9	77.5
70°	91.6	91.6	95.2	71.1	59.1
72.5°	80.6	80.6	77.3	57.8	45.2
75°	64.2	64.2	58.4	40.1	27.4
77.5°	49.4	48.9	44.7	29.8	19.9
80°	39.6	39.6	36.0	23.6	15.8
82.5°	31.0	31.0	27.9	18.4	11.7
85°	17.9	17.9	16.7	10.8	6.5
87.5°	6.4	6.4	5.7	3.4	2.9
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180° - - 45°-225° - - - - 90°-270°







(END OF REPORT)