

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: CORELITE

Report Number: P845394

Luminaire Tested: **SQ4P-WB-150U-125D-B40-1D-UNV**

Issue Date: 8/14/2023

**Test Information**

Test Method: LM-79-08  
Report Number: P845394  
REPORT IS A COMBINATION OF REPORTS P700158 AND P700248  
Test Lab: INNOVATION CENTER  
Issue Date: 8/14/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: CORELITE  
Catalog Number: SQ4P-WB-150U-125D-B40-1D-UNV  
Description: CORELITE SQ4 SUSPENDED LED LUMINAIRE WITH, 1500 LUMENS PER FOOT  
UPLIGHT, 1250 LUMENS PER FOOT DOWNLIGHT  
  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 8853.9 lumens  
Efficiency: N/A  
Efficacy: 99.7 lumens/watt  
Spacing Criteria (0/90/45): 0.89 / 1 / 1.02  
Luminous Opening: Rectangular (W 0.29' x L: 4' x H: 0')  
CIE Type: General Diffuse

Input Watts (W): 88.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P845394

CATALOG NUMBER: SQ4P-WB-150U-125D-B40-1D-UNV

### Luminous Intensity Polar Plot





TEST NUMBER: P845394

CATALOG NUMBER: SQ4P-WB-150U-125D-B40-1D-UNV

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0					
RCR																										
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	44								
1	98	94	90	87	89	86	83	80	72	70	68	59	57	56	47	46	45	39								
2	90	83	77	73	82	76	72	68	64	61	58	53	51	48	42	41	40	35								
3	82	74	67	62	76	68	62	58	58	53	50	48	45	42	38	37	35	31								
4	76	66	59	53	70	61	55	50	52	47	44	43	40	37	35	33	31	27								
5	70	59	52	46	64	55	49	44	47	42	38	39	36	33	32	30	28	25								
6	65	54	46	41	60	50	43	39	43	38	34	36	32	29	30	27	25	22								
7	60	49	42	36	55	46	39	34	39	34	30	33	29	27	27	25	23	20								
8	56	45	37	32	52	42	35	31	36	31	27	31	27	24	25	23	21	18								
9	53	41	34	29	48	38	32	28	33	28	25	28	25	22	24	21	19	17								
10	49	38	31	27	45	35	29	25	31	26	23	26	23	20	22	20	18	16								

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	24904	24904	24904
5°	24595	24505	24649
10°	23236	23448	23990
15°	21449	21949	22933
20°	19480	20211	21547
25°	17472	18425	20076
30°	15622	16642	18548
35°	13660	14648	16743
40°	11496	12410	14494
45°	9488	10306	12102
50°	7920	8636	10080
55°	6725	7411	8324
60°	5750	6427	6645
65°	4578	5403	4290
70°	4057	4216	2619
75°	3754	3422	1608
80°	3459	3145	1381
85°	3123	2890	1143



TEST NUMBER: P845394

CATALOG NUMBER: SQ4P-WB-150U-125D-B40-1D-UNV

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	247.6	2.8
10°-20°	644.0	7.3
20°-30°	834.2	9.4
30°-40°	816.9	9.2
40°-50°	625.2	7.1
50°-60°	416.6	4.7
60°-70°	227.4	2.6
70°-80°	94.7	1.1
80°-90°	28.7	0.3
90°-100°	301.6	3.4
100°-110°	1049.5	11.9
110°-120°	1016.6	11.5
120°-130°	797.5	9.0
130°-140°	631.2	7.1
140°-150°	487.1	5.5
150°-160°	349.2	3.9
160°-170°	213.6	2.4
170°-180°	72.2	0.8
0°-30°	1725.8	19.5
0°-40°	2542.6	28.7
0°-60°	3584.5	40.5
0°-90°	3935.3	44.4
90°-120°	2367.8	26.7
90°-150°	4283.6	48.4
90°-180°	4919.0	55.6
0°-180°	8853.9	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2699	2699	2699	2699	2699	
5°	2656	2629	2646	2652	2662	247
15°	2246	2238	2298	2360	2401	627
25°	1716	1721	1810	1889	1972	789
35°	1213	1219	1300	1388	1486	754
45°	727	741	790	850	928	567
55°	418	436	461	478	518	379
65°	210	227	248	216	196	218
75°	105	105	96	66	45	113
85°	30	30	27	18	11	32
90°	11	17	17	11	6	8
95°	51	175	509	130	79	54
105°	175	249	1103	1861	1731	184
115°	305	368	820	1731	2042	302
125°	413	509	764	1290	1538	370
135°	498	560	758	1075	1216	386
145°	583	622	752	928	1007	364
155°	662	684	741	826	854	305
165°	724	730	747	780	786	204
175°	758	758	752	764	758	72
180°	758	758	758	758	758	



TEST NUMBER: P845394

CATALOG NUMBER: SQ4P-WB-150U-125D-B40-1D-UNV

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2699.3	2699.3	2699.3	2699.3	2699.3
2.5°	2706.0	2681.9	2688.1	2687.8	2680.2
5°	2655.6	2628.8	2645.9	2652.1	2661.5
7.5°	2557.0	2536.8	2568.2	2591.3	2610.0
10°	2480.2	2462.8	2502.8	2536.5	2560.7
12.5°	2391.3	2376.4	2426.0	2471.1	2503.0
15°	2245.6	2237.6	2297.9	2360.3	2400.9
17.5°	2090.1	2086.1	2155.3	2228.2	2279.9
20°	1984.0	1982.9	2058.5	2134.7	2194.6
22.5°	1877.0	1879.3	1959.0	2038.1	2106.7
25°	1716.3	1720.9	1809.9	1888.7	1972.1
27.5°	1567.8	1569.9	1661.7	1745.0	1834.0
30°	1466.4	1472.1	1562.1	1648.5	1741.0
32.5°	1365.0	1371.8	1460.0	1549.0	1643.4
35°	1212.8	1218.7	1300.5	1388.1	1486.5
37.5°	1055.9	1063.9	1136.6	1219.2	1316.3
40°	954.5	966.3	1030.4	1108.5	1203.4
42.5°	856.9	871.5	931.0	1004.9	1090.5
45°	727.2	741.1	789.9	849.7	927.5
47.5°	615.4	631.4	669.0	720.5	786.7
50°	551.8	567.1	601.7	639.8	702.3
52.5°	496.1	511.1	541.9	571.4	624.8
55°	418.1	435.5	460.7	478.3	517.5
57.5°	354.2	370.9	390.9	398.7	422.6
60°	311.6	330.1	348.3	347.2	360.1
62.5°	272.7	288.5	306.5	293.9	294.7
65°	209.7	227.1	247.5	216.4	196.5
67.5°	169.5	173.0	194.1	151.0	127.3
70°	150.4	150.4	156.3	116.9	97.1
72.5°	132.5	132.5	127.1	94.9	74.2
75°	105.3	105.3	96.0	66.0	45.1
77.5°	81.2	80.4	73.5	49.0	32.8
80°	65.1	65.1	59.2	38.9	26.0
82.5°	51.0	51.0	45.8	30.3	19.3
85°	29.5	29.5	27.3	17.7	10.8
87.5°	10.5	10.5	9.4	5.6	4.8
90°	11.3	17.0	17.0	11.3	5.6
92.5°	28.3	84.8	79.2	33.9	28.3
95°	50.9	175.3	509.0	130.0	79.2
97.5°	79.2	198.0	1018.1	463.8	248.9
100°	107.5	209.2	1187.8	1114.2	718.3
102.5°	141.4	226.3	1182.1	1566.7	1289.5
105°	175.3	248.9	1102.9	1860.8	1730.7



TEST NUMBER: P845394

CATALOG NUMBER: SQ4P-WB-150U-125D-B40-1D-UNV

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	271.4	333.7	859.7	1872.1	2132.2
115°	305.4	367.7	820.1	1730.7	2041.8
117.5°	339.4	407.2	797.4	1600.6	1911.7
120°	367.7	441.1	780.5	1476.2	1781.6
122.5°	390.2	475.1	769.2	1374.4	1651.5
125°	412.9	509.0	763.5	1289.5	1538.4
127.5°	435.5	531.6	763.5	1227.3	1436.6
130°	458.2	543.0	757.9	1165.1	1351.7
132.5°	480.8	548.6	757.9	1119.8	1278.2
135°	497.7	559.9	757.9	1074.6	1216.0
137.5°	520.4	571.3	757.9	1035.1	1165.1
140°	537.3	588.2	757.9	995.4	1108.5
142.5°	559.9	605.2	757.9	955.9	1057.6
145°	582.6	622.1	752.2	927.6	1006.8
147.5°	605.2	639.1	746.6	899.3	961.5
150°	622.1	656.1	746.6	871.0	921.9
152.5°	644.8	673.0	740.9	842.7	888.0
155°	661.8	684.4	740.9	825.7	854.0
157.5°	678.7	701.3	740.9	808.8	831.5
160°	695.7	712.6	746.6	797.4	814.4
162.5°	712.6	724.0	746.6	786.2	797.4
165°	724.0	729.6	746.6	780.5	786.2
167.5°	735.2	740.9	746.6	774.9	774.9
170°	740.9	746.6	752.2	769.2	769.2
172.5°	752.2	752.2	752.2	763.5	763.5
175°	757.9	757.9	752.2	763.5	757.9
177.5°	757.9	757.9	752.2	763.5	757.9
180°	757.9	757.9	757.9	757.9	757.9



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°    - - 45°-225°    - - - - 90°-270°







107.5°	209.2	277.2	1001.1	1990.8	2013.5
110°	237.5	305.4	921.9	1973.9	2137.9



(END OF REPORT)