

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936406

Luminaire Tested: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936406
REPORT IS A COMBINATION OF REPORTS P933438 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3151.2 lumens
Efficiency: N/A
Efficacy: 105.0 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 30
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936406
CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

Luminous Intensity Polar Plot





TEST NUMBER: P936406

CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	76	76	76	71
1	102	97	93	89	96	92	88	85	82	79	77	74	71	69	66	64	62	66	64	62	58
2	92	84	77	71	87	79	73	68	71	66	62	64	60	57	57	54	51	57	54	51	48
3	83	73	65	58	79	69	62	56	62	56	51	56	51	47	50	46	43	50	46	43	39
4	76	64	55	49	71	61	53	47	55	48	43	49	44	39	44	40	36	44	40	36	33
5	69	57	48	41	65	54	46	40	49	42	37	44	38	34	39	34	31	39	34	31	28
6	64	51	42	35	60	48	40	34	43	37	32	39	33	29	35	30	27	35	30	27	24
7	59	45	37	31	55	43	35	30	39	32	27	35	30	25	32	27	23	32	27	23	21
8	54	41	33	27	51	39	31	26	36	29	24	32	26	22	29	24	21	29	24	21	18
9	51	37	29	24	48	36	28	23	32	26	21	29	24	20	26	22	18	26	22	18	16
10	47	34	26	21	45	33	25	21	30	23	19	27	22	18	24	20	16	24	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2696	2696	2696
5°	2630	3113	3623
10°	2383	4534	6006
15°	2023	5920	7252
20°	1645	6855	7392
25°	1370	7168	7241
30°	1154	7208	7227
35°	1019	7082	7415
40°	886	6922	7608
45°	801	6801	7638
50°	733	6692	7511
55°	700	6535	7178
60°	715	6240	6652
65°	740	5794	5930
70°	782	5043	5010
75°	859	4101	3910
80°	917	2834	2634
85°	770	1495	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7638 cd/sqm



TEST NUMBER: P936406

CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.6	1.2
10°-20°	166.5	5.3
20°-30°	291.3	9.2
30°-40°	375.0	11.9
40°-50°	418.8	13.3
50°-60°	401.1	12.7
60°-70°	317.9	10.1
70°-80°	186.9	5.9
80°-90°	52.5	1.7
90°-100°	67.9	2.2
100°-110°	178.6	5.7
110°-120°	185.2	5.9
120°-130°	148.6	4.7
130°-140°	116.6	3.7
140°-150°	89.5	2.8
150°-160°	64.4	2.0
160°-170°	39.4	1.3
170°-180°	13.3	0.4
0°-30°	495.4	15.7
0°-40°	870.4	27.6
0°-60°	1690.3	53.6
0°-90°	2247.6	71.3
90°-120°	431.8	13.7
90°-150°	786.4	25.0
90°-180°	904.0	28.7
0°-180°	3151.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	290	290	290	290	290	
5°	283	304	342	387	401	26
15°	212	391	659	800	825	59
25°	135	444	786	820	821	62
35°	92	424	740	782	813	57
45°	63	338	654	749	783	48
55°	45	215	555	644	662	41
65°	36	114	412	463	470	35
75°	26	70	226	248	249	27
85°	9	22	56	62	63	10
90°	1	3	7	4	4	1
95°	9	35	117	60	41	10
105°	32	49	197	300	280	34
115°	57	69	158	316	360	56
125°	80	89	144	243	287	71
135°	95	104	139	196	223	73
145°	110	117	138	168	180	69
155°	124	128	138	151	156	57
165°	134	136	138	143	145	38
175°	139	139	138	140	140	13
180°	139	139	139	139	139	



TEST NUMBER: P936406
 CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5	290.5
2.5°	290.5	290.5	292.3	293.3	295.1	296.1	297.9	299.8	305.4	306.4	308.2
5°	283.0	286.7	298.9	303.6	316.6	334.4	341.8	354.0	379.2	386.7	391.3
7.5°	271.8	280.2	310.1	317.6	350.2	397.0	416.6	442.7	482.9	502.5	518.4
10°	254.0	271.8	325.0	342.8	396.0	467.0	503.4	539.9	600.6	627.6	637.9
12.5°	234.4	263.4	340.9	365.2	441.8	545.5	589.4	629.5	698.6	735.1	740.7
15°	212.0	251.2	355.9	391.3	490.4	610.8	659.4	708.9	773.4	799.5	806.0
17.5°	192.4	241.9	369.9	407.2	527.7	669.7	719.2	760.3	812.6	830.3	835.0
20°	168.1	227.0	379.2	427.8	566.9	712.6	760.3	792.0	827.5	838.7	840.6
22.5°	150.4	211.1	384.8	435.2	593.1	738.8	779.0	804.2	828.5	832.2	833.1
25°	135.4	193.3	383.9	443.6	615.5	754.7	785.5	804.2	818.2	820.1	820.1
27.5°	121.4	173.7	380.1	445.5	632.3	758.4	782.7	795.8	802.3	806.0	806.0
30°	109.3	155.0	370.8	441.8	639.8	754.7	774.3	780.8	787.4	793.0	795.8
32.5°	99.9	137.3	356.8	434.3	640.7	745.3	759.3	763.1	772.4	785.5	790.2
35°	91.5	119.6	340.9	424.0	635.1	730.4	739.7	743.5	762.1	781.8	788.3
37.5°	83.1	106.5	320.4	406.3	626.7	712.6	719.2	725.7	754.7	778.0	785.5
40°	74.7	95.3	296.1	386.7	613.6	691.2	696.8	707.0	745.3	772.4	779.9
42.5°	68.2	85.9	269.9	366.1	596.8	666.9	675.3	690.2	734.1	763.1	771.5
45°	62.6	76.6	241.9	338.1	575.3	641.7	653.8	674.3	721.0	749.1	756.5
47.5°	57.0	70.0	213.0	309.2	552.0	616.4	632.3	655.7	703.3	730.4	736.9
50°	52.3	63.5	184.0	278.3	526.8	589.4	608.0	632.3	680.9	706.1	714.5
52.5°	48.6	57.9	156.9	247.5	497.8	561.3	582.8	608.0	653.8	678.1	683.7
55°	44.8	53.2	133.6	214.8	467.9	531.4	554.8	579.1	623.9	644.5	648.2
57.5°	43.0	49.5	113.9	184.0	436.2	497.8	524.0	546.4	588.4	604.3	608.0
60°	40.2	46.7	99.0	157.8	401.6	466.1	488.5	510.9	546.4	559.5	562.3
62.5°	37.4	44.8	87.8	132.6	366.1	428.7	451.1	471.7	501.6	510.9	514.6
65°	35.5	43.0	79.4	113.9	329.7	389.5	411.9	429.6	453.9	463.3	465.1
67.5°	33.6	41.1	72.9	98.1	293.3	350.2	367.1	383.9	402.6	411.9	412.8
70°	30.8	39.2	67.2	86.9	255.9	305.4	319.4	337.2	352.1	356.8	359.6
72.5°	29.0	36.4	63.5	78.5	217.6	262.5	275.5	285.8	298.9	303.6	303.6
75°	26.2	32.7	59.8	70.0	178.4	214.8	226.0	236.3	246.6	248.4	245.6
77.5°	23.4	29.0	51.4	58.8	139.2	170.0	179.3	184.9	193.3	195.2	196.1
80°	19.6	25.2	40.2	45.8	100.9	125.2	131.7	136.4	143.8	143.8	145.7
82.5°	14.9	19.6	29.0	32.7	68.2	85.9	91.5	94.3	99.0	99.0	99.0
85°	9.3	12.1	18.7	21.5	41.1	52.3	56.0	57.0	60.7	61.6	61.6
87.5°	4.7	6.5	12.1	13.1	21.5	27.1	27.1	29.0	29.0	28.0	27.1
90°	0.9	1.7	2.4	2.6	4.1	6.1	7.1	6.4	4.8	3.5	3.5
92.5°	3.7	10.1	16.4	18.0	25.4	35.2	40.1	35.1	25.2	17.7	17.0
95°	9.0	20.6	32.3	35.2	62.5	98.8	117.0	104.4	79.2	60.3	58.2
97.5°	15.5	25.8	36.1	38.7	84.2	144.8	175.1	167.2	151.2	139.3	135.1
100°	20.5	29.9	39.2	41.6	92.0	159.3	193.0	193.5	194.7	195.6	190.7
102.5°	24.8	33.5	42.3	44.5	95.6	163.9	198.0	208.2	228.5	243.7	239.5
105°	32.2	39.6	46.9	48.8	98.4	164.4	197.4	220.2	265.7	299.8	297.6
107.5°	39.7	46.5	53.4	55.1	98.8	157.1	186.2	218.0	281.4	329.0	329.6
110°	44.7	50.9	57.1	58.7	98.1	150.7	176.9	212.4	283.3	336.5	338.9



TEST NUMBER: P936406

CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	49.7	55.6	61.5	63.0	98.1	145.0	168.4	204.7	277.3	331.8	335.3
115°	57.2	62.6	68.0	69.4	99.0	138.5	158.2	193.2	263.1	315.5	320.5
117.5°	64.5	69.5	74.4	75.7	100.9	134.4	151.2	182.8	245.8	293.2	298.7
120°	68.8	73.5	78.2	79.3	102.3	133.0	148.3	177.2	234.9	278.1	283.5
122.5°	73.0	77.7	82.4	83.6	104.4	132.3	146.2	172.1	224.1	263.0	268.2
125°	79.5	83.8	88.1	89.2	107.4	131.7	143.8	165.9	210.1	243.1	248.0
127.5°	84.7	89.1	93.4	94.5	110.3	131.3	141.9	160.8	198.8	227.1	231.3
130°	87.5	92.2	96.9	98.1	112.5	131.6	141.1	158.0	191.8	217.1	220.8
132.5°	90.5	95.2	99.8	101.0	114.1	131.7	140.5	155.6	185.8	208.5	211.8
135°	94.8	99.0	103.3	104.3	116.0	131.6	139.4	152.0	177.3	196.2	199.1
137.5°	99.2	103.4	107.6	108.6	118.8	132.3	139.2	149.8	171.2	187.3	189.7
140°	102.8	106.7	110.6	111.5	120.5	132.5	138.5	147.8	166.3	180.1	182.3
142.5°	105.6	109.2	112.7	113.7	122.0	133.0	138.5	146.6	162.9	175.0	177.0
145°	109.9	113.0	116.2	116.9	123.8	133.0	137.6	144.2	157.5	167.5	169.0
147.5°	114.2	117.2	120.3	121.0	126.6	133.9	137.6	142.8	153.3	161.1	162.3
150°	117.0	119.7	122.5	123.2	128.0	134.4	137.6	142.0	150.8	157.5	158.4
152.5°	119.9	122.0	124.0	124.6	128.9	134.7	137.6	141.3	148.9	154.6	155.3
155°	124.2	125.7	127.3	127.7	130.9	135.3	137.6	140.6	146.6	151.1	151.6
157.5°	127.4	128.9	130.4	130.8	133.0	136.1	137.6	139.9	144.6	148.0	148.4
160°	129.5	130.7	131.9	132.2	133.9	136.4	137.6	139.5	143.6	146.5	146.7
162.5°	131.7	132.5	133.5	133.7	135.0	136.7	137.6	139.3	142.6	145.1	145.3
165°	134.0	134.8	135.6	135.8	136.4	137.2	137.6	138.8	141.2	143.0	143.2
167.5°	136.2	136.6	136.9	137.0	137.5	138.1	138.5	139.3	140.8	142.1	142.2
170°	137.6	138.0	138.3	138.4	138.4	138.5	138.5	139.3	140.8	142.1	142.1
172.5°	138.3	138.4	138.5	138.5	138.5	138.5	138.5	139.2	140.4	141.3	141.2
175°	139.4	139.4	139.4	139.4	139.1	138.7	138.5	138.9	139.7	140.3	140.3
177.5°	139.4	139.4	139.4	139.4	139.2	138.9	138.7	139.0	139.6	140.1	140.0
180°	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4	139.4



TEST NUMBER: P936406

CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	290.5	290.5
2.5°	310.1	308.2
5°	398.8	400.7
7.5°	537.1	536.1
10°	667.8	676.2
12.5°	763.1	764.9
15°	821.0	824.7
17.5°	843.4	844.3
20°	844.3	842.5
22.5°	834.1	832.2
25°	821.9	821.0
27.5°	810.7	811.6
30°	806.0	808.8
32.5°	806.0	810.7
35°	807.9	812.6
37.5°	807.0	812.6
40°	803.2	809.8
42.5°	793.0	797.6
45°	777.1	782.7
47.5°	756.5	760.3
50°	730.4	734.1
52.5°	697.7	698.6
55°	658.5	662.2
57.5°	616.4	617.4
60°	569.7	572.5
62.5°	520.2	520.2
65°	467.9	469.8
67.5°	413.8	418.4
70°	358.7	359.6
72.5°	304.5	304.5
75°	248.4	249.4
77.5°	195.2	195.2
80°	144.8	145.7
82.5°	99.9	101.8
85°	62.6	62.6
87.5°	29.0	26.2
90°	3.5	3.5
92.5°	14.2	11.4
95°	49.7	41.1
97.5°	118.9	102.6
100°	171.4	152.0
102.5°	222.9	206.2
105°	288.7	279.7
107.5°	331.8	333.9
110°	348.1	357.4



TEST NUMBER: P936406

CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	349.6	363.9
115°	340.3	360.2
117.5°	320.6	342.7
120°	304.9	326.2
122.5°	289.4	310.5
125°	267.4	286.8
127.5°	247.6	263.9
130°	235.9	251.1
132.5°	225.4	238.9
135°	210.9	222.6
137.5°	199.2	208.8
140°	191.2	200.2
142.5°	184.7	192.3
145°	174.8	180.5
147.5°	167.1	171.9
150°	162.3	166.3
152.5°	158.2	161.2
155°	153.5	155.5
157.5°	149.8	151.2
160°	147.6	148.3
162.5°	146.1	146.8
165°	144.0	144.8
167.5°	142.4	142.8
170°	142.1	142.1
172.5°	140.9	140.7
175°	140.3	140.3
177.5°	139.7	139.4
180°	139.4	139.4



TEST NUMBER: P936406
 CATALOG NUMBER: SQ4-FB-025U-075D-B50-1D-UNV-STD-W-4

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.17	7.33	6.91	8.10	9.02	19.31	20.47	20.06	21.24	22.16
	3H	6.90	7.94	7.66	8.72	9.68	21.16	22.20	21.91	22.98	23.94
	4H	7.21	8.20	7.99	8.99	9.95	21.81	22.79	22.58	23.58	24.55
	6H	7.48	8.39	8.27	9.19	10.17	22.24	23.15	23.03	23.95	24.93
	8H	7.56	8.43	8.35	9.24	10.23	22.36	23.23	23.16	24.05	25.03
	12H	7.58	8.41	8.39	9.22	10.24	22.44	23.27	23.24	24.08	25.09
4H	2H	13.40	14.39	14.18	15.17	16.14	19.63	20.61	20.40	21.40	22.37
	3H	15.00	15.82	15.79	16.65	17.63	21.68	22.51	22.47	23.33	24.32
	4H	15.11	15.86	15.91	16.68	17.69	22.45	23.21	23.26	24.03	25.04
	6H	15.13	15.79	15.95	16.64	17.65	23.00	23.65	23.82	24.50	25.51
	8H	15.12	15.73	15.94	16.57	17.61	23.16	23.77	23.98	24.61	25.65
	12H	15.09	15.64	15.94	16.51	17.54	23.26	23.81	24.10	24.67	25.71
8H	4H	16.57	17.18	17.39	18.02	19.05	22.54	23.15	23.36	23.99	25.02
	6H	16.82	17.33	17.68	18.21	19.25	23.17	23.68	24.02	24.56	25.59
	8H	16.84	17.30	17.71	18.18	19.23	23.39	23.84	24.25	24.72	25.77
	12H	16.83	17.23	17.70	18.10	19.20	23.54	23.93	24.40	24.81	25.91
12H	4H	16.72	17.27	17.57	18.14	19.17	22.51	23.06	23.35	23.92	24.96
	6H	17.08	17.53	17.94	18.41	19.46	23.16	23.61	24.02	24.49	25.54
	8H	17.16	17.56	18.03	18.43	19.54	23.39	23.79	24.26	24.66	25.77