

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936807

Luminaire Tested: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

Issue Date: 12/17/2024

Test Information

Test Method: LM-79-2019
Report Number: P936807
REPORT IS A COMBINATION OF REPORTS P933478 AND P933786
Test Lab: INNOVATION CENTER
Issue Date: 12/17/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: CORELITE
Catalog Number: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6161.6 lumens
Efficiency: N/A
Efficacy: 112.8 lumens/watt
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 6' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 54.6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P936807
CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

Luminous Intensity Polar Plot





TEST NUMBER: P936807

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	86	86	86	73	73	73	60	60	60	60	60	60	55
1	98	94	89	86	91	87	83	80	75	72	69	63	61	59	53	51	50	50	50	50	45
2	89	81	74	69	82	75	70	65	65	60	56	55	51	49	45	43	41	41	41	41	37
3	81	71	63	57	74	66	59	53	56	51	47	48	44	40	40	37	34	34	34	34	30
4	73	62	54	47	68	58	50	45	50	44	39	42	38	34	35	32	29	29	29	29	25
5	67	55	46	40	62	51	44	38	44	38	33	37	33	29	31	28	25	25	25	25	21
6	62	49	40	34	57	46	38	32	39	33	29	33	29	25	28	24	21	21	21	21	18
7	57	44	36	30	52	41	34	28	35	29	25	30	25	22	25	22	19	19	19	19	16
8	53	40	32	26	49	37	30	25	32	26	22	27	23	19	23	19	16	16	16	16	14
9	49	36	28	23	45	34	27	22	29	23	19	25	20	17	21	17	15	15	15	15	12
10	46	33	25	20	42	31	24	19	27	21	17	23	18	15	19	16	13	13	13	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2695	2695	2695
5°	2632	3115	3623
10°	2387	4539	6006
15°	2028	5929	7253
20°	1650	6869	7392
25°	1376	7186	7242
30°	1160	7230	7228
35°	1025	7108	7415
40°	893	6949	7609
45°	808	6833	7638
50°	741	6728	7512
55°	708	6575	7178
60°	724	6283	6652
65°	752	5841	5930
70°	799	5090	5010
75°	882	4147	3910
80°	957	2872	2635
85°	835	1522	1349

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 45°
 Luminance: 7638 cd/sqm



TEST NUMBER: P936807

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	0.9
10°-20°	249.8	4.1
20°-30°	437.0	7.1
30°-40°	562.5	9.1
40°-50°	628.3	10.2
50°-60°	601.7	9.8
60°-70°	476.9	7.7
70°-80°	280.4	4.6
80°-90°	79.5	1.3
90°-100°	209.7	3.4
100°-110°	551.4	8.9
110°-120°	571.7	9.3
120°-130°	458.6	7.4
130°-140°	359.8	5.8
140°-150°	276.2	4.5
150°-160°	198.9	3.2
160°-170°	121.7	2.0
170°-180°	41.1	0.7
0°-30°	743.1	12.1
0°-40°	1305.6	21.2
0°-60°	2535.6	41.2
0°-90°	3372.4	54.7
90°-120°	1332.8	21.6
90°-150°	2427.4	39.4
90°-180°	2789.0	45.3
0°-180°	6161.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	436	436	436	436	436	
5°	424	455	513	580	601	39
15°	318	587	989	1199	1237	89
25°	203	666	1178	1230	1232	94
35°	137	636	1110	1173	1219	86
45°	94	507	981	1124	1174	73
55°	67	322	832	967	993	61
65°	53	171	618	695	705	53
75°	39	105	339	373	374	41
85°	14	32	84	92	94	15
90°	3	8	22	11	11	3
95°	28	108	361	186	127	31
105°	99	150	610	926	863	105
115°	176	214	488	974	1112	174
125°	246	275	444	750	885	218
135°	292	322	430	606	687	226
145°	339	361	425	517	557	213
155°	384	394	425	466	480	176
165°	414	419	425	442	447	117
175°	430	430	428	433	433	41
180°	430	430	430	430	430	



TEST NUMBER: P936807

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (FULL):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7	435.7
2.5°	435.7	435.7	438.5	439.9	442.7	444.1	446.9	449.7	458.1	459.5	462.3
5°	424.5	430.1	448.3	455.3	474.9	501.6	512.8	531.0	568.8	580.0	587.0
7.5°	407.7	420.3	465.1	476.3	525.4	595.4	624.8	664.1	724.3	753.7	777.6
10°	381.1	407.7	487.5	514.2	594.0	700.5	755.1	809.8	900.8	941.5	956.9
12.5°	351.7	395.1	511.4	547.8	662.7	818.2	884.0	944.3	1047.9	1102.7	1111.1
15°	318.0	376.9	533.8	587.0	735.5	916.3	989.1	1063.5	1160.1	1199.3	1209.2
17.5°	288.6	362.9	554.8	610.8	791.6	1004.5	1078.9	1140.5	1219.0	1245.6	1252.6
20°	252.2	340.4	568.8	641.7	850.4	1069.1	1140.5	1188.1	1241.4	1258.2	1261.0
22.5°	225.6	316.6	577.2	652.9	889.6	1108.3	1168.5	1206.4	1242.8	1248.4	1249.8
25°	203.1	290.0	575.8	665.5	923.3	1132.1	1178.3	1206.4	1227.4	1230.2	1230.2
27.5°	182.1	260.6	570.2	668.3	948.5	1137.7	1174.1	1193.7	1203.6	1209.2	1209.2
30°	163.9	232.6	556.2	662.7	959.7	1132.1	1161.5	1171.3	1181.1	1189.5	1193.7
32.5°	149.9	205.9	535.2	651.5	961.1	1118.1	1139.1	1144.7	1158.7	1178.3	1185.3
35°	137.3	179.3	511.4	636.1	952.7	1095.7	1109.7	1115.3	1143.3	1172.7	1182.5
37.5°	124.7	159.7	480.5	609.4	940.1	1069.1	1078.9	1088.7	1132.1	1167.1	1178.3
40°	112.1	142.9	444.1	580.0	920.5	1036.7	1045.1	1060.6	1118.1	1158.7	1169.9
42.5°	102.3	128.9	404.9	549.2	895.2	1000.3	1012.9	1035.3	1101.3	1144.7	1157.3
45°	93.9	114.9	362.9	507.2	863.0	962.5	980.7	1011.5	1081.7	1123.7	1134.9
47.5°	85.5	105.1	319.4	463.7	828.0	924.7	948.5	983.5	1055.0	1095.7	1105.5
50°	78.5	95.3	276.0	417.5	790.2	884.0	912.1	948.5	1021.3	1059.2	1071.9
52.5°	72.9	86.9	235.4	371.3	746.7	842.0	874.2	912.1	980.7	1017.1	1025.5
55°	67.2	79.9	200.3	322.2	701.9	797.2	832.2	868.6	935.9	966.7	972.3
57.5°	64.4	74.3	170.9	276.0	654.3	746.7	786.0	819.6	882.6	906.4	912.1
60°	60.2	70.0	148.5	236.8	602.4	699.1	732.7	766.3	819.6	839.2	843.4
62.5°	56.0	67.2	131.7	198.9	549.2	643.1	676.7	707.5	752.3	766.3	772.0
65°	53.2	64.4	119.1	170.9	494.6	584.2	617.8	644.5	680.9	694.9	697.7
67.5°	50.4	61.6	109.3	147.1	439.9	525.4	550.6	575.8	603.8	617.8	619.2
70°	46.2	58.8	100.9	130.3	383.9	458.1	479.1	505.8	528.2	535.2	539.4
72.5°	43.4	54.6	95.3	117.7	326.4	393.7	413.3	428.7	448.3	455.3	455.3
75°	39.2	49.0	89.7	105.1	267.6	322.2	339.0	354.5	369.9	372.7	368.5
77.5°	35.0	43.4	77.1	88.3	208.7	255.0	269.0	277.4	290.0	292.8	294.2
80°	29.4	37.8	60.2	68.6	151.3	187.7	197.5	204.5	215.8	215.8	218.6
82.5°	22.4	29.4	43.4	49.0	102.3	128.9	137.3	141.5	148.5	148.5	148.5
85°	14.0	18.2	28.0	32.2	61.6	78.5	84.1	85.5	91.1	92.5	92.5
87.5°	7.0	9.8	18.2	19.6	32.2	40.6	40.6	43.4	43.4	42.0	40.6
90°	2.9	5.2	7.6	8.1	12.7	18.9	21.9	19.5	14.6	10.9	10.9
92.5°	11.6	31.2	50.8	55.8	78.4	108.5	123.6	108.3	77.7	54.8	52.7
95°	27.7	63.6	99.6	108.5	192.8	305.1	361.3	322.4	244.6	186.2	179.6
97.5°	47.9	79.7	111.3	119.3	259.7	447.0	540.6	516.0	466.8	429.9	417.3
100°	63.5	92.3	121.0	128.2	284.0	491.8	595.7	597.5	601.1	603.8	588.9
102.5°	76.8	103.7	130.5	137.2	295.2	505.9	611.3	642.6	705.3	752.2	739.4
105°	99.4	122.1	144.8	150.5	303.5	507.5	609.5	679.8	820.1	925.5	918.6
107.5°	122.4	143.6	164.8	170.1	305.0	484.9	574.9	672.8	868.6	1015.5	1017.2
110°	138.0	157.1	176.2	181.0	302.7	464.9	546.0	655.5	874.5	1038.7	1045.9



TEST NUMBER: P936807

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	153.4	171.6	189.8	194.4	302.8	447.5	519.8	631.9	855.9	1023.9	1035.0
115°	176.4	193.2	210.1	214.3	305.6	427.4	488.3	596.3	812.1	974.0	989.3
117.5°	199.2	214.5	229.8	233.6	311.3	414.9	466.6	564.0	758.9	905.0	922.0
120°	212.5	226.9	241.3	244.9	315.9	410.6	457.9	547.0	725.0	858.4	875.0
122.5°	225.6	240.0	254.5	258.2	322.5	408.3	451.3	531.4	691.8	812.0	828.3
125°	245.5	258.6	271.9	275.2	331.5	406.6	444.1	512.2	648.4	750.5	765.4
127.5°	261.6	275.0	288.3	291.7	340.4	405.5	438.0	496.5	613.4	701.1	713.7
130°	270.3	284.7	299.1	302.6	347.0	406.1	435.7	487.7	591.9	670.0	681.6
132.5°	279.3	293.6	308.0	311.6	352.3	406.6	433.7	480.4	573.5	643.3	653.8
135°	292.5	305.6	318.7	321.9	358.1	406.2	430.3	469.3	547.3	605.8	614.9
137.5°	306.1	319.1	331.9	335.2	366.7	408.6	429.6	462.6	528.6	578.1	585.4
140°	317.4	329.3	341.2	344.2	372.0	409.1	427.7	456.2	513.1	555.8	562.7
142.5°	326.0	337.0	348.0	350.8	376.4	410.6	427.7	452.7	502.7	540.2	546.2
145°	339.3	348.9	358.6	361.0	382.3	410.6	424.8	445.2	486.1	516.9	521.4
147.5°	352.6	361.9	371.4	373.7	390.7	413.4	424.8	440.8	473.1	497.3	501.0
150°	361.3	369.8	378.2	380.3	395.2	414.9	424.8	438.4	465.6	486.0	488.9
152.5°	370.1	376.6	383.0	384.6	398.0	415.8	424.8	436.4	459.6	477.0	479.2
155°	383.5	388.3	392.9	394.1	404.3	418.0	424.8	434.0	452.5	466.3	467.8
157.5°	393.3	397.9	402.6	403.7	410.7	420.1	424.8	432.0	446.4	457.1	458.1
160°	399.9	403.5	407.0	408.0	413.6	421.0	424.8	430.9	443.3	452.5	453.1
162.5°	406.6	409.3	412.0	412.6	416.7	422.1	424.8	430.0	440.4	448.1	448.7
165°	413.8	416.2	418.6	419.3	421.1	423.6	424.8	428.5	435.9	441.5	442.2
167.5°	420.4	421.5	422.7	423.0	424.6	426.7	427.7	430.1	435.0	438.6	438.9
170°	424.8	425.9	427.1	427.4	427.5	427.6	427.7	430.1	435.0	438.6	438.6
172.5°	427.1	427.4	427.6	427.7	427.7	427.7	427.7	429.5	433.4	436.3	436.1
175°	430.3	430.3	430.3	430.3	429.5	428.2	427.7	428.9	431.3	433.1	433.1
177.5°	430.3	430.3	430.3	430.3	429.6	428.7	428.2	429.2	431.1	432.5	432.3
180°	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3	430.3



TEST NUMBER: P936807

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
0°	435.7	435.7
2.5°	465.1	462.3
5°	598.2	601.0
7.5°	805.6	804.2
10°	1001.7	1014.3
12.5°	1144.7	1147.5
15°	1231.6	1237.2
17.5°	1265.2	1266.6
20°	1266.6	1263.8
22.5°	1251.2	1248.4
25°	1233.0	1231.6
27.5°	1216.2	1217.6
30°	1209.2	1213.4
32.5°	1209.2	1216.2
35°	1212.0	1219.0
37.5°	1210.6	1219.0
40°	1205.0	1214.8
42.5°	1189.5	1196.5
45°	1165.7	1174.1
47.5°	1134.9	1140.5
50°	1095.7	1101.3
52.5°	1046.5	1047.9
55°	987.7	993.3
57.5°	924.7	926.1
60°	854.6	858.8
62.5°	780.4	780.4
65°	701.9	704.7
67.5°	620.6	627.6
70°	538.0	539.4
72.5°	456.7	456.7
75°	372.7	374.1
77.5°	292.8	292.8
80°	217.2	218.6
82.5°	149.9	152.7
85°	93.9	93.9
87.5°	43.4	39.2
90°	10.9	10.9
92.5°	43.9	35.2
95°	153.2	126.7
97.5°	367.1	316.8
100°	528.9	469.0
102.5°	688.1	636.7
105°	891.0	863.4
107.5°	1023.9	1030.6
110°	1074.6	1103.3



TEST NUMBER: P936807

CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

CANDELA DISTRIBUTION (continued):

	80°	90°
112.5°	1079.1	1123.2
115°	1050.5	1111.7
117.5°	989.9	1057.8
120°	940.9	1006.9
122.5°	893.4	958.4
125°	825.4	885.3
127.5°	764.3	814.9
130°	728.3	775.0
132.5°	695.6	737.5
135°	650.9	687.0
137.5°	615.0	644.6
140°	590.3	617.9
142.5°	569.9	593.7
145°	539.4	557.3
147.5°	515.8	530.7
150°	501.1	513.1
152.5°	488.4	497.5
155°	473.9	479.9
157.5°	462.4	466.6
160°	455.5	457.9
162.5°	451.0	453.4
165°	444.6	447.0
167.5°	439.9	440.9
170°	438.6	438.6
172.5°	435.2	434.3
175°	433.1	433.1
177.5°	431.3	430.3
180°	430.3	430.3



TEST NUMBER: P936807
 CATALOG NUMBER: SQ4-FB-050U-075D-B50-1D-UNV-STD-W-6

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.87	5.81	5.77	6.75	7.95	18.03	18.98	18.94	19.91	21.11
	3H	5.58	6.43	6.50	7.37	8.59	19.87	20.73	20.79	21.67	22.89
	4H	5.88	6.69	6.81	7.63	8.87	20.52	21.33	21.45	22.27	23.50
	6H	6.13	6.88	7.08	7.83	9.08	20.95	21.70	21.89	22.65	23.89
	8H	6.20	6.92	7.16	7.89	9.13	21.07	21.78	22.02	22.75	23.99
	12H	6.23	6.90	7.18	7.87	9.14	21.14	21.82	22.10	22.78	24.05
4H	2H	12.08	12.89	13.02	13.84	15.07	18.32	19.13	19.26	20.07	21.30
	3H	13.66	14.34	14.61	15.31	16.56	20.37	21.04	21.32	22.02	23.27
	4H	13.76	14.38	14.72	15.35	16.62	21.13	21.75	22.09	22.72	23.99
	6H	13.77	14.31	14.75	15.30	16.57	21.67	22.21	22.65	23.20	24.47
	8H	13.75	14.25	14.73	15.24	16.53	21.84	22.34	22.81	23.32	24.61
	12H	13.71	14.17	14.71	15.17	16.46	21.93	22.38	22.92	23.39	24.68
8H	4H	15.21	15.71	16.18	16.70	17.98	21.20	21.70	22.18	22.69	23.97
	6H	15.45	15.87	16.45	16.90	18.18	21.83	22.25	22.83	23.28	24.56
	8H	15.47	15.84	16.48	16.86	18.16	22.05	22.42	23.06	23.43	24.73
	12H	15.45	15.77	16.46	16.78	18.13	22.19	22.52	23.21	23.53	24.87
12H	4H	15.35	15.81	16.35	16.81	18.10	21.16	21.61	22.15	22.62	23.91
	6H	15.71	16.08	16.72	17.10	18.40	21.81	22.18	22.82	23.20	24.50
	8H	15.79	16.11	16.80	17.12	18.47	22.05	22.37	23.06	23.38	24.73