

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: CORELITE

Report Number: P936608

Luminaire Tested: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

Issue Date: 12/17/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P936608  
REPORT IS A COMBINATION OF REPORTS P933456 AND P933786  
Test Lab: INNOVATION CENTER  
Issue Date: 12/17/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: CORELITE  
Catalog Number: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8  
Description: CORELITE SQ4 SUSPENDED INDIRECT LED LUMINAIRE WITH Batwing Frosted Continuous Roll L  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9413.8 lumens  
Efficiency: N/A  
Efficacy: 94.9 lumens/watt  
Spacing Criteria (0/90/45): 0.71 / 2.69 / 2.33  
Luminous Opening: Rectangular w/ Sides (W: 0.29' x L: 8' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 99.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P936608  
CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

### Luminous Intensity Polar Plot





TEST NUMBER: P936608

CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	114	114	114	114	110	110	110	110	100	100	100	92	92	92	84	84	84	84	84	84	81
1	104	99	94	90	99	95	91	87	87	84	81	80	77	75	73	71	70	70	70	70	66
2	94	85	78	72	89	82	75	70	75	70	66	69	65	61	63	60	57	57	57	57	54
3	85	74	66	59	81	71	64	58	65	59	54	60	55	51	55	51	48	48	48	48	45
4	77	65	56	49	74	63	54	48	58	51	45	53	47	43	49	44	40	40	40	40	37
5	71	58	49	42	67	55	47	41	51	44	39	47	41	36	43	38	34	34	34	34	32
6	65	51	42	36	62	49	41	35	46	39	33	42	36	31	39	34	30	30	30	30	27
7	60	46	37	31	57	45	36	30	41	34	29	38	32	27	35	30	26	26	26	26	24
8	55	42	33	27	53	40	32	27	37	30	25	35	29	24	32	27	23	23	23	23	21
9	52	38	30	24	49	37	29	24	34	27	23	32	26	22	29	24	20	20	20	20	18
10	48	35	27	22	46	34	26	21	31	25	20	29	23	19	27	22	18	18	18	18	16

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4561	4561	4561
5°	4456	5272	6131
10°	4042	7685	10165
15°	3435	10040	12274
20°	2797	11635	12509
25°	2333	12176	12254
30°	1967	12252	12231
35°	1739	12049	12548
40°	1516	11785	12875
45°	1373	11591	12925
50°	1259	11417	12711
55°	1206	11162	12147
60°	1234	10671	11258
65°	1284	9926	10035
70°	1368	8656	8478
75°	1516	7058	6617
80°	1657	4895	4458
85°	1472	2597	2282

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 90°  
 Vertical Angle: 45°  
 Luminance: 12925 cd/sqm



TEST NUMBER: P936608

CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.2	1.4
10°-20°	563.6	6.0
20°-30°	985.9	10.5
30°-40°	1269.1	13.5
40°-50°	1417.6	15.1
50°-60°	1357.7	14.4
60°-70°	1076.0	11.4
70°-80°	632.7	6.7
80°-90°	176.8	1.9
90°-100°	135.9	1.4
100°-110°	357.3	3.8
110°-120°	370.4	3.9
120°-130°	297.1	3.2
130°-140°	233.1	2.5
140°-150°	179.0	1.9
150°-160°	128.9	1.4
160°-170°	78.9	0.8
170°-180°	26.6	0.3
0°-30°	1676.7	17.8
0°-40°	2945.8	31.3
0°-60°	5721.1	60.8
0°-90°	7606.6	80.8
90°-120°	863.6	9.2
90°-150°	1572.8	16.7
90°-180°	1807.0	19.2
0°-180°	9413.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	983	983	983	983	983	
5°	958	1027	1157	1309	1356	88
15°	718	1324	2232	2706	2791	200
25°	458	1502	2659	2776	2779	211
35°	310	1435	2504	2646	2750	193
45°	212	1144	2213	2535	2649	164
55°	152	727	1878	2181	2241	138
65°	120	386	1394	1568	1590	119
75°	88	237	765	841	844	93
85°	32	73	190	209	212	34
90°	2	5	14	7	7	4
95°	18	70	234	121	82	20
105°	64	98	395	600	559	68
115°	114	139	316	631	720	113
125°	159	178	288	486	574	141
135°	190	209	279	393	445	147
145°	220	234	275	335	361	138
155°	248	255	275	302	311	114
165°	268	272	275	286	290	76
175°	279	279	277	281	281	26
180°	279	279	279	279	279	



TEST NUMBER: P936608

CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (FULL):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
0°	983.1	983.1	983.1	983.1	983.1	983.1	983.1	983.1	983.1	983.1	983.1
2.5°	983.1	983.1	989.5	992.7	998.9	1002.1	1008.4	1014.8	1033.8	1036.9	1043.2
5°	957.8	970.5	1011.6	1027.4	1071.7	1131.7	1157.0	1198.1	1283.4	1308.7	1324.5
7.5°	919.9	948.4	1049.5	1074.8	1185.4	1343.6	1409.9	1498.4	1634.3	1700.7	1754.5
10°	859.8	919.9	1100.1	1160.1	1340.4	1580.6	1703.9	1827.2	2032.7	2124.4	2159.1
12.5°	793.4	891.5	1153.9	1236.1	1495.2	1846.1	1994.7	2130.6	2364.6	2487.9	2506.9
15°	717.6	850.4	1204.4	1324.5	1659.6	2067.4	2231.8	2399.4	2617.5	2706.0	2728.1
17.5°	651.2	818.7	1251.8	1378.3	1786.1	2266.6	2434.1	2573.3	2750.3	2810.3	2826.1
20°	569.0	768.2	1283.4	1447.8	1918.9	2412.1	2573.3	2680.7	2800.9	2838.8	2845.1
22.5°	508.9	714.4	1302.5	1473.1	2007.4	2500.5	2636.5	2721.8	2804.0	2816.7	2819.8
25°	458.4	654.4	1299.3	1501.6	2083.3	2554.3	2658.6	2721.8	2769.2	2775.6	2775.6
27.5°	411.0	588.0	1286.6	1507.9	2140.2	2566.9	2649.1	2693.4	2715.5	2728.1	2728.1
30°	369.9	524.7	1255.0	1495.2	2165.5	2554.3	2620.6	2642.8	2664.9	2683.8	2693.4
32.5°	338.3	464.7	1207.6	1469.9	2168.6	2522.6	2570.1	2582.7	2614.4	2658.6	2674.4
35°	309.8	404.6	1153.9	1435.2	2149.6	2472.1	2503.7	2516.3	2579.5	2645.9	2668.1
37.5°	281.3	360.3	1084.3	1375.1	2121.2	2412.1	2434.1	2456.2	2554.3	2633.3	2658.6
40°	252.9	322.4	1002.1	1308.7	2076.9	2339.3	2358.3	2393.0	2522.6	2614.4	2639.6
42.5°	230.8	290.8	913.6	1239.2	2020.1	2257.1	2285.6	2336.1	2484.7	2582.7	2611.2
45°	211.8	259.2	818.7	1144.3	1947.3	2171.7	2212.8	2282.4	2440.4	2535.3	2560.6
47.5°	192.9	237.0	720.8	1046.4	1868.3	2086.4	2140.2	2219.2	2380.4	2472.1	2494.2
50°	177.0	215.0	622.8	942.0	1782.9	1994.7	2058.0	2140.2	2304.6	2389.9	2418.3
52.5°	164.4	196.0	531.1	837.7	1684.9	1899.8	1972.6	2058.0	2212.8	2295.0	2314.0
55°	151.8	180.2	452.1	727.1	1583.8	1798.7	1877.8	1960.0	2111.7	2181.3	2193.9
57.5°	145.4	167.6	385.6	622.8	1476.3	1684.9	1773.5	1849.3	1991.6	2045.3	2058.0
60°	135.9	158.0	335.1	534.2	1359.3	1577.4	1653.3	1729.2	1849.3	1893.6	1903.0
62.5°	126.5	151.8	297.2	448.9	1239.2	1451.0	1526.9	1596.4	1697.5	1729.2	1741.8
65°	120.1	145.4	268.7	385.6	1115.9	1318.2	1394.1	1454.1	1536.3	1568.0	1574.3
67.5°	113.8	139.1	246.6	331.9	992.7	1185.4	1242.3	1299.3	1362.5	1394.1	1397.3
70°	104.3	132.8	227.6	294.0	866.2	1033.8	1081.1	1141.2	1191.8	1207.6	1217.1
72.5°	98.0	123.3	215.0	265.5	736.6	888.3	932.6	967.3	1011.6	1027.4	1027.4
75°	88.5	110.7	202.3	237.0	603.8	727.1	765.0	799.8	834.5	840.9	831.4
77.5°	79.0	98.0	173.9	199.1	471.0	575.3	606.9	626.0	654.4	660.7	663.9
80°	66.4	85.4	135.9	154.9	341.4	423.6	445.7	461.6	486.8	486.8	493.2
82.5°	50.6	66.4	98.0	110.7	230.8	290.8	309.8	319.2	335.1	335.1	335.1
85°	31.6	41.1	63.2	72.7	139.1	177.0	189.7	192.9	205.5	208.7	208.7
87.5°	15.8	22.1	41.1	44.3	72.7	91.7	91.7	98.0	98.0	94.8	91.7
90°	1.9	3.4	4.9	5.2	8.2	12.2	14.2	12.6	9.4	7.1	7.1
92.5°	7.5	20.2	33.0	36.1	50.8	70.3	80.0	70.1	50.4	35.6	34.2
95°	17.9	41.2	64.5	70.3	124.9	197.6	234.1	208.8	158.5	120.7	116.4
97.5°	31.1	51.7	72.1	77.2	168.2	289.5	350.2	334.4	302.5	278.6	270.5
100°	41.2	59.8	78.4	83.0	184.0	318.6	385.9	387.1	389.5	391.3	381.5
102.5°	49.8	67.2	84.5	88.8	191.3	327.8	396.1	416.4	456.9	487.4	479.0
105°	64.4	79.1	93.9	97.5	196.7	328.9	395.0	440.5	531.4	599.6	595.1
107.5°	79.3	93.0	106.8	110.2	197.6	314.2	372.5	435.9	562.8	658.0	659.1
110°	89.5	101.8	114.2	117.3	196.1	301.2	353.8	424.7	566.6	672.9	677.6



TEST NUMBER: P936608

CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	0°	10°	20°	22.5°	30°	40°	45°	50°	60°	67.5°	70°
112.5°	99.4	111.1	122.9	125.9	196.2	289.9	336.8	409.4	554.5	663.4	670.6
115°	114.3	125.2	136.1	138.8	198.0	276.9	316.3	386.3	526.2	631.1	641.0
117.5°	129.1	139.0	148.9	151.4	201.7	268.8	302.3	365.5	491.7	586.4	597.4
120°	137.7	147.0	156.4	158.7	204.7	266.1	296.7	354.4	469.7	556.2	566.8
122.5°	146.1	155.5	164.9	167.3	209.0	264.6	292.4	344.4	448.2	526.1	536.7
125°	159.1	167.7	176.2	178.3	214.8	263.5	287.8	331.9	420.1	486.2	496.0
127.5°	169.5	178.1	186.8	188.9	220.6	262.7	283.8	321.8	397.5	454.3	462.5
130°	175.1	184.5	193.7	196.0	224.8	263.2	282.3	316.1	383.5	434.0	441.6
132.5°	180.9	190.3	199.5	201.8	228.3	263.5	281.0	311.2	371.5	416.8	423.7
135°	189.5	198.0	206.5	208.7	232.0	263.2	278.8	304.1	354.6	392.6	398.4
137.5°	198.3	206.7	215.1	217.2	237.6	264.8	278.4	299.8	342.5	374.5	379.3
140°	205.6	213.3	221.1	223.0	241.1	265.1	277.1	295.6	332.5	360.2	364.6
142.5°	211.3	218.4	225.6	227.3	244.0	266.1	277.1	293.4	325.8	350.1	353.9
145°	219.9	226.1	232.3	233.9	247.7	266.1	275.2	288.5	315.0	334.9	337.8
147.5°	228.5	234.5	240.6	242.1	253.1	267.9	275.2	285.7	306.5	322.1	324.6
150°	234.1	239.6	245.0	246.4	256.0	268.8	275.2	284.0	301.7	314.9	316.8
152.5°	239.9	244.0	248.2	249.2	257.9	269.5	275.2	282.7	297.8	309.1	310.6
155°	248.4	251.5	254.6	255.4	262.0	270.9	275.2	281.2	293.2	302.1	303.1
157.5°	254.8	257.8	260.8	261.5	266.1	272.2	275.2	279.9	289.2	296.2	296.8
160°	259.1	261.4	263.8	264.3	268.0	272.8	275.2	279.3	287.2	293.2	293.6
162.5°	263.4	265.2	266.8	267.3	269.9	273.5	275.2	278.6	285.3	290.4	290.8
165°	268.2	269.7	271.3	271.7	272.9	274.5	275.2	277.7	282.4	286.1	286.5
167.5°	272.4	273.2	273.9	274.1	275.2	276.5	277.1	278.7	281.9	284.2	284.4
170°	275.2	276.0	276.7	276.9	277.0	277.1	277.1	278.7	281.9	284.2	284.2
172.5°	276.7	276.9	277.1	277.1	277.1	277.1	277.1	278.3	280.9	282.7	282.5
175°	278.8	278.8	278.8	278.8	278.2	277.5	277.1	277.9	279.5	280.7	280.7
177.5°	278.8	278.8	278.8	278.8	278.3	277.8	277.5	278.1	279.4	280.3	280.1
180°	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8	278.8



TEST NUMBER: P936608

CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	80°	90°
0°	983.1	983.1
2.5°	1049.5	1043.2
5°	1349.8	1356.2
7.5°	1817.7	1814.6
10°	2260.3	2288.8
12.5°	2582.7	2589.0
15°	2778.7	2791.4
17.5°	2854.6	2857.8
20°	2857.8	2851.4
22.5°	2823.0	2816.7
25°	2781.9	2778.7
27.5°	2743.9	2747.1
30°	2728.1	2737.6
32.5°	2728.1	2743.9
35°	2734.5	2750.3
37.5°	2731.3	2750.3
40°	2718.7	2740.8
42.5°	2683.8	2699.7
45°	2630.1	2649.1
47.5°	2560.6	2573.3
50°	2472.1	2484.7
52.5°	2361.4	2364.6
55°	2228.6	2241.3
57.5°	2086.4	2089.5
60°	1928.3	1937.9
62.5°	1760.8	1760.8
65°	1583.8	1590.1
67.5°	1400.4	1416.2
70°	1213.9	1217.1
72.5°	1030.6	1030.6
75°	840.9	844.1
77.5°	660.7	660.7
80°	490.0	493.2
82.5°	338.3	344.6
85°	211.8	211.8
87.5°	98.0	88.5
90°	7.1	7.1
92.5°	28.5	22.8
95°	99.3	82.1
97.5°	237.8	205.2
100°	342.7	303.8
102.5°	445.8	412.5
105°	577.3	559.4
107.5°	663.4	667.7
110°	696.2	714.9





TEST NUMBER: P936608

CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

**CANDELA DISTRIBUTION (continued):**

	80°	90°
112.5°	699.2	727.8
115°	680.7	720.3
117.5°	641.4	685.4
120°	609.6	652.4
122.5°	578.8	620.9
125°	534.8	573.7
127.5°	495.2	528.0
130°	471.9	502.1
132.5°	450.7	477.8
135°	421.7	445.1
137.5°	398.4	417.6
140°	382.5	400.4
142.5°	369.3	384.6
145°	349.5	361.1
147.5°	334.2	343.9
150°	324.7	332.5
152.5°	316.4	322.3
155°	307.0	310.9
157.5°	299.6	302.3
160°	295.1	296.7
162.5°	292.2	293.7
165°	288.0	289.6
167.5°	285.1	285.7
170°	284.2	284.2
172.5°	282.0	281.4
175°	280.7	280.7
177.5°	279.5	278.8
180°	278.8	278.8



TEST NUMBER: P936608  
 CATALOG NUMBER: SQ4-FB-025U-125D-B50-1D-UNV-STD-W-8

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.70	10.00	9.33	10.65	11.40	21.88	23.18	22.51	23.83	24.58
	3H	9.44	10.62	10.08	11.28	12.06	23.75	24.93	24.40	25.59	26.37
	4H	9.76	10.87	10.42	11.54	12.34	24.42	25.53	25.08	26.20	27.00
	6H	10.03	11.06	10.71	11.74	12.55	24.87	25.90	25.55	26.58	27.39
	8H	10.11	11.10	10.80	11.80	12.61	25.00	25.99	25.69	26.69	27.51
	12H	10.14	11.08	10.84	11.78	12.62	25.09	26.03	25.78	26.73	27.57
4H	2H	15.97	17.08	16.63	17.75	18.55	22.21	23.32	22.87	23.99	24.79
	3H	17.58	18.51	18.26	19.22	20.04	24.29	25.23	24.97	25.94	26.75
	4H	17.69	18.54	18.39	19.25	20.10	25.08	25.93	25.77	26.64	27.49
	6H	17.73	18.47	18.44	19.21	20.06	25.64	26.38	26.36	27.12	27.98
	8H	17.71	18.41	18.44	19.14	20.01	25.82	26.51	26.54	27.25	28.11
	12H	17.69	18.32	18.44	19.08	19.95	25.93	26.56	26.67	27.32	28.19
8H	4H	19.17	19.87	19.89	20.60	21.47	25.18	25.87	25.90	26.61	27.47
	6H	19.43	20.01	20.19	20.79	21.66	25.82	26.40	26.58	27.18	28.05
	8H	19.46	19.97	20.22	20.75	21.64	26.05	26.57	26.82	27.35	28.23
	12H	19.45	19.90	20.22	20.67	21.62	26.22	26.67	26.98	27.44	28.39
12H	4H	19.34	19.96	20.08	20.72	21.60	25.15	25.78	25.89	26.54	27.41
	6H	19.70	20.22	20.46	20.99	21.88	25.81	26.33	26.58	27.11	27.99
	8H	19.79	20.25	20.56	21.02	21.96	26.07	26.52	26.83	27.29	28.23